

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905589

Luminaire Tested: DFN2DIP-PN2F0-020D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905589
REPORT IS A COMBINATION OF REPORTS P901011 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US835-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6930.0 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1685	1685	1685
5°	1685	1658	1671
10°	1669	1633	1646
15°	1642	1602	1608
20°	1606	1561	1569
25°	1570	1513	1525
30°	1526	1468	1469
35°	1484	1415	1411
40°	1433	1362	1355
45°	1381	1308	1297
50°	1325	1252	1231
55°	1266	1187	1169
60°	1199	1110	1099
65°	1125	1030	1016
70°	1032	932	926
75°	904	815	839
80°	749	666	681
85°	507	421	427

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1549 cd/sqm

TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	1.1
10°-20°	206.1	3.0
20°-30°	302.9	4.4
30°-40°	351.8	5.1
40°-50°	351.3	5.1
50°-60°	306.3	4.4
60°-70°	226.5	3.3
70°-80°	128.1	1.8
80°-90°	36.8	0.5
90°-100°	55.7	0.8
100°-110°	207.4	3.0
110°-120°	550.1	7.9
120°-130°	912.4	13.2
130°-140°	969.2	14.0
140°-150°	900.8	13.0
150°-160°	724.2	10.5
160°-170°	466.6	6.7
170°-180°	160.6	2.3
0°-30°	582.2	8.4
0°-40°	934.0	13.5
0°-60°	1591.6	23.0
0°-90°	1983.0	28.6
90°-120°	813.2	11.7
90°-150°	3595.6	51.9
90°-180°	4947.0	71.4
0°-180°	6930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	775	767	773	772	74
15°	741	736	727	730	726	209
25°	670	664	652	653	652	309
35°	578	571	559	554	551	361
45°	471	466	454	446	443	363
55°	356	352	343	334	330	318
65°	240	236	228	222	218	238
75°	126	124	120	116	118	134
85°	31	30	29	27	26	34
90°	1	15	24	31	33	6
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	778.2	778.2	778.2	778.2	778.2
2.5°	782.7	779.0	770.7	778.2	776.8
5°	778.2	775.3	767.0	773.0	771.5
7.5°	773.0	768.5	760.3	766.3	764.8
10°	764.8	759.6	750.6	756.5	754.3
12.5°	753.5	749.1	740.1	743.8	742.3
15°	740.8	736.4	726.6	729.6	725.9
17.5°	725.1	720.7	710.9	714.6	710.9
20°	707.9	703.4	692.9	695.2	692.2
22.5°	690.7	684.0	674.2	674.2	672.7
25°	670.5	664.5	651.8	653.2	651.8
27.5°	648.0	642.8	633.1	630.9	627.1
30°	625.6	619.6	608.4	606.2	603.1
32.5°	601.6	597.2	585.2	580.7	577.7
35°	578.5	571.0	559.0	554.5	550.7
37.5°	552.3	545.5	533.5	528.3	524.5
40°	525.3	519.3	507.3	500.7	497.6
42.5°	499.1	493.1	481.2	473.7	469.2
45°	470.7	465.5	454.2	446.0	443.0
47.5°	443.0	437.8	425.8	417.5	413.1
50°	413.8	410.1	399.6	389.1	385.4
52.5°	385.4	380.1	370.4	362.2	357.0
55°	356.2	351.7	342.7	333.8	330.0
57.5°	327.0	323.3	313.5	304.6	301.5
60°	297.8	294.9	284.4	276.1	273.9
62.5°	269.4	264.1	256.7	249.2	246.2
65°	240.2	235.7	228.3	221.5	217.8
67.5°	210.3	206.5	199.8	194.6	191.6
70°	182.6	179.6	172.8	167.6	164.7
72.5°	154.2	151.2	147.4	142.2	140.0
75°	125.7	124.3	120.4	116.0	117.5
77.5°	100.3	97.3	95.7	93.5	91.3
80°	74.9	74.1	72.6	70.3	68.8
82.5°	50.9	50.9	50.2	47.2	47.2
85°	30.6	29.9	29.2	26.9	26.2
87.5°	13.5	12.0	10.5	8.3	7.5
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P905589

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US835-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.56	7.26	7.68	8.37	9.92	6.13	6.82	7.25	7.94	9.48
	3H	8.19	8.81	9.32	9.94	11.50	7.71	8.33	8.84	9.46	11.02
	4H	8.76	9.35	9.90	10.47	12.04	8.27	8.87	9.41	9.99	11.56
	6H	9.13	9.68	10.28	10.80	12.38	8.65	9.19	9.79	10.32	11.90
	8H	9.22	9.74	10.37	10.89	12.46	8.74	9.26	9.89	10.40	11.97
	12H	9.26	9.75	10.41	10.89	12.48	8.77	9.26	9.92	10.39	11.99
4H	2H	6.99	7.59	8.14	8.71	10.28	6.64	7.24	7.79	8.36	9.93
	3H	8.82	9.32	9.97	10.47	12.05	8.42	8.92	9.57	10.07	11.65
	4H	9.51	9.97	10.67	11.11	12.71	9.10	9.55	10.25	10.69	12.29
	6H	10.00	10.39	11.16	11.55	13.14	9.58	9.97	10.74	11.13	12.72
	8H	10.13	10.50	11.29	11.65	13.26	9.71	10.07	10.87	11.23	12.83
	12H	10.19	10.52	11.37	11.68	13.30	9.76	10.09	10.93	11.25	12.86
8H	4H	9.68	10.05	10.84	11.20	12.81	9.32	9.68	10.48	10.83	12.44
	6H	10.28	10.58	11.46	11.78	13.38	9.91	10.21	11.09	11.41	13.01
	8H	10.49	10.75	11.68	11.93	13.55	10.11	10.37	11.29	11.54	13.17
	12H	10.60	10.83	11.79	12.00	13.66	10.20	10.43	11.39	11.60	13.26
12H	4H	9.66	9.99	10.84	11.15	12.77	9.30	9.63	10.47	10.79	12.41
	6H	10.31	10.57	11.49	11.74	13.37	9.94	10.21	11.13	11.38	13.00
	8H	10.53	10.76	11.72	11.93	13.58	10.16	10.39	11.35	11.56	13.21

END OF REPORT