

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912101

Luminaire Tested: DFN2DIP-SQ3F0-120D080US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912101
REPORT IS A COMBINATION OF REPORTS P901469 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D080US850-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21958.2 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 186.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912101
CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P912101

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55	51
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5933	5933	5933
5°	5939	5847	5888
10°	5887	5764	5806
15°	5797	5665	5680
20°	5676	5529	5550
25°	5556	5368	5401
30°	5406	5217	5212
35°	5264	5040	5012
40°	5089	4861	4821
45°	4915	4681	4626
50°	4724	4492	4400
55°	4524	4274	4192
60°	4298	4015	3953
65°	4051	3747	3672
70°	3736	3419	3369
75°	3300	3027	3085
80°	2774	2526	2550
85°	1952	1673	1669

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4915 cd/sqm



TEST NUMBER: P912101

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	487.4	2.2
10°-20°	1371.3	6.2
20°-30°	2015.2	9.2
30°-40°	2340.6	10.7
40°-50°	2337.7	10.6
50°-60°	2038.4	9.3
60°-70°	1506.8	6.9
70°-80°	852.5	3.9
80°-90°	230.3	1.0
90°-100°	98.7	0.4
100°-110°	368.1	1.7
110°-120°	976.2	4.4
120°-130°	1619.0	7.4
130°-140°	1719.8	7.8
140°-150°	1598.3	7.3
150°-160°	1285.0	5.9
160°-170°	828.0	3.8
170°-180°	285.0	1.3
0°-30°	3873.9	17.6
0°-40°	6214.5	28.3
0°-60°	10590.5	48.2
0°-90°	13180.2	60.0
90°-120°	1442.9	6.6
90°-150°	6380.0	29.1
90°-180°	8778.0	40.0
0°-180°	21958.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5178	5178	5178	5178	5178	
5°	5178	5159	5104	5143	5134	492
15°	4929	4900	4835	4855	4830	1388
25°	4461	4422	4337	4347	4337	2053
35°	3849	3799	3720	3690	3665	2404
45°	3132	3097	3022	2968	2948	2417
55°	2370	2340	2280	2221	2196	2119
65°	1599	1568	1519	1474	1449	1581
75°	836	827	801	772	782	893
85°	204	199	194	179	174	227
90°	2	26	43	54	58	20
95°	141	69	84	96	93	167
105°	659	724	132	156	165	704
115°	1246	1283	1337	334	178	1226
125°	1761	1790	1831	1846	1852	1571
135°	2180	2214	2234	2256	2251	1684
145°	2528	2526	2563	2578	2567	1581
155°	2784	2765	2791	2804	2786	1283
165°	2934	2921	2927	2942	2927	829
175°	3001	2985	2990	3005	2983	286
180°	2994	2994	2994	2994	2994	



TEST NUMBER: P912101

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5178.3	5178.3	5178.3	5178.3	5178.3
2.5°	5208.3	5183.5	5128.6	5178.3	5168.7
5°	5178.3	5158.6	5103.7	5143.3	5133.8
7.5°	5143.3	5113.7	5058.8	5099.0	5089.0
10°	5089.0	5054.0	4994.4	5034.0	5019.2
12.5°	5013.9	4984.3	4924.6	4949.5	4939.4
15°	4929.4	4899.8	4834.8	4854.9	4830.0
17.5°	4824.8	4795.2	4730.2	4755.1	4730.2
20°	4710.1	4680.5	4610.9	4625.6	4606.1
22.5°	4596.0	4551.1	4486.1	4486.1	4476.1
25°	4461.3	4421.7	4337.2	4346.7	4337.2
27.5°	4311.8	4277.0	4212.5	4197.7	4172.9
30°	4162.9	4122.7	4048.2	4033.4	4013.4
32.5°	4003.3	3973.8	3893.9	3863.9	3843.8
35°	3849.0	3799.4	3719.6	3689.5	3664.7
37.5°	3674.7	3629.9	3550.0	3515.2	3490.4
40°	3495.7	3455.5	3375.7	3331.3	3311.3
42.5°	3321.3	3281.2	3201.9	3151.8	3122.2
45°	3132.1	3097.3	3022.2	2967.9	2947.8
47.5°	2947.8	2912.9	2833.2	2778.3	2748.7
50°	2753.4	2728.6	2658.8	2589.1	2564.2
52.5°	2564.2	2529.4	2465.0	2410.0	2375.1
55°	2370.4	2340.3	2280.5	2220.9	2196.0
57.5°	2176.0	2151.1	2086.1	2026.5	2006.4
60°	1981.6	1962.0	1892.3	1837.4	1822.5
62.5°	1792.5	1757.5	1708.0	1658.3	1638.2
65°	1598.6	1568.5	1518.8	1473.9	1449.1
67.5°	1399.4	1374.1	1329.7	1294.9	1274.8
70°	1215.0	1194.9	1150.0	1115.2	1095.7
72.5°	1025.9	1005.9	981.0	946.2	931.3
75°	836.3	826.8	801.4	771.9	781.8
77.5°	667.2	647.1	637.1	622.3	607.5
80°	498.2	492.8	482.9	468.1	458.0
82.5°	338.6	338.6	333.9	313.8	313.8
85°	203.9	199.2	194.4	179.1	174.3
87.5°	89.8	79.7	69.8	54.9	49.7
90°	2.1	26.0	43.3	54.2	58.4
92.5°	54.2	45.6	52.0	56.3	58.4
95°	140.7	69.2	84.4	95.5	93.2
97.5°	253.4	75.9	110.3	117.1	119.1
100°	383.6	86.7	123.5	140.7	145.1
102.5°	526.4	522.2	127.9	151.5	158.3
105°	658.6	723.7	132.2	155.9	164.7
107.5°	812.5	866.5	136.6	160.3	169.0
110°	960.0	1005.2	379.3	162.6	171.1



TEST NUMBER: P912101

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1098.6	1137.4	1100.7	166.7	173.4
115°	1245.7	1282.6	1336.8	333.7	177.8
117.5°	1373.6	1416.9	1453.9	1143.8	576.3
120°	1516.7	1549.1	1588.2	1614.1	1321.6
122.5°	1637.8	1672.6	1716.1	1728.9	1731.3
125°	1761.3	1789.6	1830.7	1845.9	1852.4
127.5°	1874.0	1904.4	1937.1	1958.6	1960.7
130°	1980.2	2014.9	2038.7	2062.6	2060.5
132.5°	2088.6	2116.9	2140.6	2160.1	2158.0
135°	2179.6	2214.3	2233.6	2255.6	2251.2
137.5°	2274.9	2300.8	2322.7	2344.3	2337.9
140°	2367.9	2385.5	2409.2	2428.7	2417.8
142.5°	2446.2	2461.3	2489.4	2506.7	2495.8
145°	2528.5	2526.2	2563.0	2578.2	2567.3
147.5°	2599.8	2593.4	2630.1	2641.0	2632.4
150°	2669.3	2654.1	2688.8	2701.6	2690.9
152.5°	2727.7	2710.4	2742.8	2756.0	2740.8
155°	2784.0	2764.7	2790.7	2803.6	2786.4
157.5°	2829.5	2812.3	2831.8	2847.0	2829.5
160°	2868.7	2855.6	2868.7	2881.5	2866.3
162.5°	2903.1	2890.3	2901.0	2916.2	2896.7
165°	2933.5	2920.7	2927.1	2942.2	2927.1
167.5°	2957.4	2944.3	2950.9	2966.1	2946.6
170°	2977.0	2963.8	2968.2	2983.4	2963.8
172.5°	2989.9	2977.0	2981.3	2996.5	2977.0
175°	3000.6	2985.4	2989.9	3004.9	2983.4
177.5°	3004.9	2989.9	2992.1	3007.3	2987.8
180°	2994.2	2994.2	2994.2	2994.2	2994.2



TEST NUMBER: P912101
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.30	15.26	15.17	16.15	17.27	13.86	14.82	14.72	15.70	16.82
	3H	15.96	16.83	16.84	17.72	18.87	15.47	16.34	16.35	17.23	18.38
	4H	16.55	17.37	17.45	18.27	19.43	16.06	16.87	16.95	17.78	18.93
	6H	16.95	17.71	17.86	18.61	19.78	16.45	17.20	17.36	18.11	19.28
	8H	17.06	17.78	17.97	18.70	19.87	16.56	17.27	17.47	18.20	19.37
	12H	17.11	17.79	18.03	18.71	19.91	16.60	17.28	17.52	18.20	19.40
4H	2H	14.77	15.58	15.67	16.49	17.64	14.42	15.23	15.31	16.13	17.29
	3H	16.64	17.32	17.55	18.25	19.42	16.23	16.91	17.14	17.85	19.02
	4H	17.35	17.97	18.27	18.90	20.10	16.93	17.55	17.85	18.48	19.68
	6H	17.87	18.41	18.81	19.36	20.56	17.44	17.97	18.37	18.93	20.12
	8H	18.02	18.52	18.96	19.47	20.68	17.58	18.08	18.52	19.03	20.24
	12H	18.10	18.55	19.05	19.51	20.73	17.65	18.10	18.60	19.06	20.28
8H	4H	17.55	18.05	18.49	19.00	20.21	17.18	17.68	18.11	18.62	19.84
	6H	18.18	18.60	19.15	19.59	20.80	17.80	18.21	18.76	19.20	20.41
	8H	18.40	18.77	19.37	19.75	20.97	18.01	18.37	18.98	19.35	20.58
	12H	18.53	18.86	19.51	19.83	21.11	18.12	18.45	19.10	19.42	20.69
12H	4H	17.54	17.99	18.50	18.96	20.18	17.18	17.63	18.13	18.59	19.81
	6H	18.21	18.58	19.19	19.56	20.79	17.84	18.21	18.81	19.19	20.41
	8H	18.45	18.78	19.43	19.75	21.03	18.07	18.40	19.05	19.37	20.65