

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908361

Luminaire Tested: DFN2DIP-PN2F0-040D060US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908361
REPORT IS A COMBINATION OF REPORTS P901025 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D060US840-FLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9997.6 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 91.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908361
CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P908361

CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3404	3404	3404
5°	3404	3349	3374
10°	3371	3297	3324
15°	3316	3236	3247
20°	3244	3153	3170
25°	3171	3056	3080
30°	3082	2965	2968
35°	2997	2858	2849
40°	2894	2750	2736
45°	2790	2642	2620
50°	2677	2528	2486
55°	2557	2397	2362
60°	2422	2242	2220
65°	2273	2080	2052
70°	2085	1882	1869
75°	1826	1646	1695
80°	1511	1344	1376
85°	1025	850	862

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2790 cd/sqm



TEST NUMBER: P908361

CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	1.5
10°-20°	416.2	4.2
20°-30°	611.7	6.1
30°-40°	710.5	7.1
40°-50°	709.6	7.1
50°-60°	618.7	6.2
60°-70°	457.4	4.6
70°-80°	258.8	2.6
80°-90°	71.9	0.7
90°-100°	67.4	0.7
100°-110°	251.4	2.5
110°-120°	666.7	6.7
120°-130°	1105.7	11.1
130°-140°	1174.5	11.7
140°-150°	1091.6	10.9
150°-160°	877.6	8.8
160°-170°	565.5	5.7
170°-180°	194.6	1.9
0°-30°	1175.9	11.8
0°-40°	1886.3	18.9
0°-60°	3214.6	32.2
0°-90°	4002.6	40.0
90°-120°	985.5	9.9
90°-150°	4357.2	43.6
90°-180°	5995.0	60.0
0°-180°	9997.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	1	18	30	37	40	9
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	



TEST NUMBER: P908361

CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8



TEST NUMBER: P908361

CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9



TEST NUMBER: P908361
 CATALOG NUMBER: DFN2DIP-PN2F0-040D060US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.41	11.19	11.45	12.24	13.64	9.98	10.76	11.02	11.80	13.21
	3H	12.05	12.75	13.10	13.80	15.22	11.57	12.27	12.62	13.32	14.74
	4H	12.62	13.28	13.68	14.34	15.77	12.14	12.80	13.20	13.85	15.29
	6H	13.00	13.61	14.07	14.67	16.11	12.51	13.12	13.58	14.18	15.63
	8H	13.09	13.67	14.17	14.75	16.19	12.61	13.19	13.68	14.26	15.70
	12H	13.13	13.68	14.21	14.75	16.21	12.64	13.19	13.72	14.26	15.72
4H	2H	10.86	11.52	11.92	12.57	14.01	10.51	11.17	11.57	12.22	13.65
	3H	12.69	13.24	13.76	14.32	15.77	12.29	12.84	13.36	13.92	15.37
	4H	13.38	13.89	14.46	14.96	16.43	12.97	13.48	14.05	14.55	16.02
	6H	13.88	14.31	14.96	15.41	16.87	13.46	13.89	14.54	14.99	16.45
	8H	14.01	14.42	15.10	15.51	16.99	13.59	14.00	14.68	15.08	16.56
	12H	14.07	14.44	15.18	15.54	17.02	13.64	14.01	14.75	15.11	16.59
8H	4H	13.56	13.97	14.65	15.06	16.54	13.19	13.60	14.28	14.69	16.17
	6H	14.17	14.50	15.28	15.63	17.11	13.79	14.13	14.90	15.26	16.73
	8H	14.37	14.67	15.49	15.78	17.27	13.99	14.29	15.11	15.40	16.89
	12H	14.49	14.75	15.61	15.85	17.39	14.09	14.35	15.21	15.46	16.99
12H	4H	13.54	13.91	14.65	15.01	16.49	13.18	13.55	14.29	14.65	16.13
	6H	14.19	14.49	15.31	15.60	17.09	13.83	14.12	14.95	15.24	16.73
	8H	14.41	14.67	15.54	15.78	17.31	14.04	14.30	15.17	15.41	16.94