

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914665

Luminaire Tested: DFN2DIP-SQ3F0-070D120US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914665
REPORT IS A COMBINATION OF REPORTS P901531 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D120US927-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14900.9 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 159.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2472	2472	2472
5°	2475	2436	2453
10°	2453	2402	2419
15°	2415	2361	2367
20°	2365	2304	2313
25°	2315	2237	2251
30°	2253	2174	2172
35°	2193	2100	2088
40°	2121	2025	2009
45°	2048	1951	1927
50°	1969	1872	1833
55°	1885	1781	1746
60°	1791	1673	1647
65°	1688	1561	1530
70°	1557	1425	1404
75°	1375	1261	1286
80°	1156	1052	1062
85°	814	697	695

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2198 cd/sqm

TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	1.4
10°-20°	571.4	3.8
20°-30°	839.7	5.6
30°-40°	975.3	6.5
40°-50°	974.1	6.5
50°-60°	849.4	5.7
60°-70°	627.9	4.2
70°-80°	355.2	2.4
80°-90°	99.4	0.7
90°-100°	105.8	0.7
100°-110°	394.4	2.6
110°-120°	1045.9	7.0
120°-130°	1734.7	11.6
130°-140°	1842.7	12.4
140°-150°	1712.6	11.5
150°-160°	1376.9	9.2
160°-170°	887.2	6.0
170°-180°	305.4	2.0
0°-30°	1614.2	10.8
0°-40°	2589.5	17.4
0°-60°	4412.9	29.6
0°-90°	5495.5	36.9
90°-120°	1546.1	10.4
90°-150°	6836.0	45.9
90°-180°	9405.0	63.1
0°-180°	14900.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2127	2143	2139	205
15°	2054	2042	2015	2023	2013	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1002
45°	1305	1291	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	2	28	46	58	63	14
95°	151	74	90	102	100	179
105°	706	776	142	167	176	754
115°	1335	1374	1432	358	190	1314
125°	1887	1918	1962	1978	1985	1683
135°	2335	2373	2393	2417	2412	1804
145°	2709	2707	2746	2762	2751	1694
155°	2983	2962	2990	3004	2986	1375
165°	3143	3129	3136	3153	3136	888
175°	3215	3199	3204	3220	3197	306
180°	3208	3208	3208	3208	3208	

TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.7	2157.7	2157.7	2157.7	2157.7
2.5°	2170.3	2159.9	2137.0	2157.7	2153.7
5°	2157.7	2149.6	2126.7	2143.2	2139.2
7.5°	2143.2	2130.8	2107.9	2124.7	2120.5
10°	2120.5	2105.9	2081.1	2097.6	2091.4
12.5°	2089.2	2076.9	2052.1	2062.4	2058.2
15°	2054.0	2041.7	2014.6	2023.0	2012.6
17.5°	2010.4	1998.1	1971.0	1981.4	1971.0
20°	1962.6	1950.4	1921.3	1927.5	1919.3
22.5°	1915.1	1896.4	1869.3	1869.3	1865.1
25°	1859.0	1842.5	1807.3	1811.2	1807.3
27.5°	1796.7	1782.2	1755.3	1749.1	1738.8
30°	1734.6	1717.8	1686.9	1680.7	1672.3
32.5°	1668.1	1655.8	1622.5	1610.0	1601.6
35°	1603.8	1583.2	1549.9	1537.4	1527.0
37.5°	1531.2	1512.5	1479.2	1464.7	1454.4
40°	1456.6	1439.9	1406.6	1388.1	1379.7
42.5°	1383.9	1367.2	1334.2	1313.3	1300.9
45°	1305.1	1290.6	1259.3	1236.7	1228.3
47.5°	1228.3	1213.8	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.9	1068.5
52.5°	1068.5	1054.0	1027.1	1004.2	989.7
55°	987.7	975.2	950.3	925.4	915.0
57.5°	906.7	896.4	869.3	844.4	836.1
60°	825.7	817.5	788.5	765.6	759.5
62.5°	746.9	732.4	711.7	691.0	682.6
65°	666.1	653.5	632.9	614.2	603.8
67.5°	583.1	572.6	554.1	539.6	531.2
70°	506.3	498.0	479.2	464.7	456.5
72.5°	427.5	419.1	408.8	394.3	388.1
75°	348.5	344.5	333.9	321.6	325.8
77.5°	278.1	269.7	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	2.2	27.8	46.3	58.1	62.6
92.5°	58.1	48.8	55.7	60.4	62.6
95°	150.8	74.1	90.4	102.3	99.8
97.5°	271.6	81.4	118.3	125.4	127.6
100°	411.0	92.9	132.3	150.8	155.5
102.5°	564.0	559.6	137.0	162.4	169.5
105°	705.7	775.5	141.7	167.1	176.4
107.5°	870.5	928.4	146.4	171.7	181.1
110°	1028.5	1077.0	406.3	174.2	183.3

TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1177.1	1218.7	1179.3	178.6	185.8
115°	1334.7	1374.2	1432.3	357.5	190.5
117.5°	1471.8	1518.1	1557.8	1225.6	617.5
120°	1625.1	1659.8	1701.7	1729.6	1416.1
122.5°	1754.9	1792.2	1838.7	1852.5	1855.0
125°	1887.2	1917.6	1961.7	1977.9	1984.8
127.5°	2007.9	2040.5	2075.5	2098.6	2100.9
130°	2121.8	2159.0	2184.4	2210.0	2207.8
132.5°	2237.8	2268.2	2293.5	2314.5	2312.3
135°	2335.4	2372.7	2393.3	2416.8	2412.1
137.5°	2437.5	2465.3	2488.7	2511.8	2505.0
140°	2537.3	2556.0	2581.3	2602.3	2590.7
142.5°	2621.0	2637.3	2667.4	2685.8	2674.2
145°	2709.3	2706.8	2746.2	2762.5	2750.8
147.5°	2785.6	2778.7	2818.2	2829.8	2820.6
150°	2860.0	2843.8	2881.0	2894.8	2883.2
152.5°	2922.6	2904.1	2938.9	2952.9	2936.7
155°	2983.0	2962.3	2990.2	3004.0	2985.5
157.5°	3031.8	3013.3	3034.3	3050.5	3031.8
160°	3073.7	3059.6	3073.7	3087.4	3071.2
162.5°	3110.7	3096.9	3108.4	3124.7	3103.8
165°	3143.1	3129.4	3136.2	3152.6	3136.2
167.5°	3168.8	3154.7	3161.9	3178.2	3157.2
170°	3189.7	3175.7	3180.4	3196.6	3175.7
172.5°	3203.5	3189.7	3194.5	3210.7	3189.7
175°	3215.1	3198.8	3203.5	3219.8	3196.6
177.5°	3219.8	3203.5	3206.0	3222.3	3201.4
180°	3208.3	3208.3	3208.3	3208.3	3208.3

TEST NUMBER: P914665

CATALOG NUMBER: DFN2DIP-SQ3F0-070D120US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.03	9.79	10.09	10.85	12.30	8.59	9.34	9.65	10.41	11.85
	3H	10.68	11.36	11.75	12.43	13.89	10.19	10.87	11.26	11.94	13.40
	4H	11.26	11.90	12.34	12.98	14.45	10.77	11.41	11.85	12.48	13.95
	6H	11.65	12.24	12.74	13.32	14.80	11.15	11.74	12.24	12.82	14.30
	8H	11.75	12.31	12.85	13.41	14.88	11.25	11.81	12.34	12.90	14.38
	12H	11.79	12.33	12.89	13.42	14.92	11.28	11.82	12.38	12.91	14.41
4H	2H	9.48	10.12	10.57	11.19	12.66	9.12	9.76	10.21	10.84	12.31
	3H	11.33	11.86	12.42	12.96	14.45	10.92	11.45	12.02	12.56	14.04
	4H	12.03	12.52	13.13	13.62	15.12	11.61	12.10	12.71	13.19	14.70
	6H	12.54	12.96	13.65	14.07	15.57	12.10	12.53	13.21	13.64	15.14
	8H	12.68	13.08	13.79	14.18	15.70	12.24	12.64	13.35	13.75	15.26
	12H	12.75	13.10	13.87	14.22	15.74	12.30	12.66	13.43	13.78	15.30
8H	4H	12.22	12.61	13.33	13.72	15.23	11.84	12.23	12.95	13.34	14.86
	6H	12.84	13.16	13.97	14.31	15.82	12.45	12.78	13.58	13.93	15.44
	8H	13.05	13.34	14.19	14.47	16.00	12.66	12.95	13.80	14.08	15.61
	12H	13.18	13.43	14.32	14.55	16.12	12.77	13.02	13.91	14.14	15.71
12H	4H	12.20	12.55	13.32	13.67	15.19	11.83	12.18	12.95	13.30	14.82
	6H	12.86	13.15	14.00	14.28	15.81	12.49	12.78	13.63	13.91	15.44
	8H	13.10	13.35	14.24	14.47	16.04	12.72	12.97	13.86	14.09	15.66

END OF REPORT