

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908481

Luminaire Tested: DFN2DIP-PN3F0-050D080US840-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P908481  
REPORT IS A COMBINATION OF REPORTS P901105 AND P897955  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-050D080US840-FLONL  
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12997.0 lumens  
Efficiency: N/A  
Efficacy: 122.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 106.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9613  
Total Harmonic Distortion (THDi): 0.083  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908481  
CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P908481

CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38				38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2297	2297	2297
5°	2299	2263	2279
10°	2279	2231	2247
15°	2244	2193	2198
20°	2198	2140	2148
25°	2151	2077	2090
30°	2093	2019	2016
35°	2038	1950	1938
40°	1971	1881	1864
45°	1903	1811	1788
50°	1830	1738	1701
55°	1753	1653	1620
60°	1665	1553	1528
65°	1569	1449	1418
70°	1448	1322	1300
75°	1280	1170	1190
80°	1076	975	982
85°	759	645	640

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1903 cd/sqm



TEST NUMBER: P908481

CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.9	1.4
10°-20°	520.3	4.0
20°-30°	764.6	5.9
30°-40°	888.1	6.8
40°-50°	887.0	6.8
50°-60°	773.4	6.0
60°-70°	571.7	4.4
70°-80°	323.5	2.5
80°-90°	90.2	0.7
90°-100°	89.9	0.7
100°-110°	335.1	2.6
110°-120°	888.9	6.8
120°-130°	1474.3	11.3
130°-140°	1566.0	12.0
140°-150°	1455.4	11.2
150°-160°	1170.1	9.0
160°-170°	754.0	5.8
170°-180°	259.5	2.0
0°-30°	1469.8	11.3
0°-40°	2357.9	18.1
0°-60°	4018.3	30.9
0°-90°	5003.6	38.5
90°-120°	1314.0	10.1
90°-150°	5809.7	44.7
90°-180°	7993.0	61.5
0°-180°	12997.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	2	24	39	49	53	12
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	



TEST NUMBER: P908481

CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8



TEST NUMBER: P908481

CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5



TEST NUMBER: P908481  
 CATALOG NUMBER: DFN2DIP-PN3F0-050D080US840-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.96	9.72	10.01	10.78	12.20	8.52	9.28	9.57	10.34	11.76
	3H	10.60	11.29	11.66	12.35	13.80	10.12	10.81	11.18	11.87	13.31
	4H	11.18	11.83	12.25	12.90	14.35	10.70	11.35	11.77	12.41	13.87
	6H	11.57	12.17	12.65	13.24	14.70	11.08	11.68	12.16	12.75	14.22
	8H	11.67	12.24	12.76	13.33	14.79	11.18	11.75	12.27	12.84	14.30
	12H	11.71	12.26	12.80	13.34	14.82	11.22	11.76	12.31	12.84	14.32
4H	2H	9.40	10.05	10.48	11.12	12.57	9.05	9.70	10.13	10.77	12.22
	3H	11.25	11.79	12.34	12.89	14.35	10.85	11.39	11.93	12.49	13.95
	4H	11.96	12.46	13.05	13.54	15.02	11.54	12.04	12.63	13.12	14.61
	6H	12.46	12.89	13.56	14.00	15.47	12.04	12.47	13.14	13.57	15.05
	8H	12.61	13.01	13.70	14.10	15.60	12.18	12.58	13.28	13.68	15.17
	12H	12.67	13.03	13.79	14.14	15.64	12.23	12.60	13.35	13.71	15.21
8H	4H	12.14	12.54	13.24	13.64	15.14	11.77	12.17	12.87	13.27	14.77
	6H	12.76	13.09	13.88	14.23	15.72	12.39	12.72	13.51	13.86	15.35
	8H	12.98	13.27	14.10	14.39	15.90	12.59	12.88	13.72	14.01	15.52
	12H	13.10	13.35	14.23	14.47	16.02	12.70	12.96	13.83	14.07	15.62
12H	4H	12.12	12.48	13.24	13.60	15.10	11.76	12.12	12.88	13.23	14.73
	6H	12.79	13.08	13.92	14.20	15.71	12.43	12.71	13.55	13.84	15.35
	8H	13.02	13.28	14.15	14.39	15.94	12.65	12.91	13.78	14.02	15.57