

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920372

Luminaire Tested: DFN2DIP-SQ4F0-070D160US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920372
REPORT IS A COMBINATION OF REPORTS P900205 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D160US935-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18159.3 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 183.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	62	60	50	48	47	36	35	34
2	86	78	72	67	77	71	66	61	57	53	50	43	41	39	31	30	29
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	39	35	31	31	27	24	22	20	18
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1646	1646	1646
5°	1648	1623	1634
10°	1635	1601	1612
15°	1611	1575	1578
20°	1578	1539	1543
25°	1546	1496	1503
30°	1505	1455	1451
35°	1467	1407	1397
40°	1420	1359	1345
45°	1373	1311	1292
50°	1321	1260	1230
55°	1267	1202	1174
60°	1206	1132	1109
65°	1140	1060	1033
70°	1055	972	951
75°	938	867	876
80°	796	734	732
85°	576	502	492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3430 cd/sqm

TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	1.2
10°-20°	621.0	3.4
20°-30°	912.7	5.0
30°-40°	1060.0	5.8
40°-50°	1058.7	5.8
50°-60°	923.2	5.1
60°-70°	682.4	3.8
70°-80°	386.1	2.1
80°-90°	114.3	0.6
90°-100°	269.6	1.5
100°-110°	856.6	4.7
110°-120°	1466.0	8.1
120°-130°	1928.1	10.6
130°-140°	2164.2	11.9
140°-150°	2122.2	11.7
150°-160°	1780.2	9.8
160°-170°	1180.6	6.5
170°-180°	412.7	2.3
0°-30°	1754.4	9.7
0°-40°	2814.4	15.5
0°-60°	4796.3	26.4
0°-90°	5979.1	32.9
90°-120°	2592.3	14.3
90°-150°	8806.7	48.5
90°-180°	12180.0	67.1
0°-180°	18159.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	4	47	129	121	125	18
95°	192	229	235	235	229	213
105°	791	801	809	816	816	834
115°	1471	1492	1486	1482	1471	1455
125°	2140	2173	2162	2150	2146	1912
135°	2768	2808	2816	2812	2802	2139
145°	3360	3386	3407	3411	3397	2099
155°	3842	3853	3864	3883	3871	1768
165°	4180	4176	4176	4202	4184	1179
175°	4349	4339	4331	4357	4335	413
180°	4357	4357	4357	4357	4357	

TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	4.0	47.3	128.7	120.9	124.8
92.5°	81.5	110.4	114.3	118.2	118.2
95°	191.7	228.6	235.1	235.1	228.6
97.5°	319.2	353.4	367.8	367.8	367.8
100°	466.3	496.5	507.0	507.0	503.1
102.5°	621.3	643.7	658.1	662.0	658.1
105°	790.7	801.2	809.2	815.7	815.7
107.5°	958.9	974.6	974.6	977.3	958.9
110°	1121.8	1142.8	1142.8	1142.8	1132.3

TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1297.8	1320.2	1316.2	1305.7	1297.8
115°	1471.2	1492.2	1485.7	1481.7	1471.2
117.5°	1643.3	1672.1	1653.8	1643.3	1632.8
120°	1816.7	1845.5	1816.7	1816.7	1804.8
122.5°	1974.3	2011.1	1992.7	1982.2	1974.3
125°	2139.8	2172.6	2162.1	2150.3	2146.4
127.5°	2301.4	2342.1	2327.6	2311.9	2301.4
130°	2452.5	2499.7	2493.2	2485.3	2470.8
132.5°	2621.9	2658.7	2661.3	2642.9	2632.4
135°	2767.7	2808.4	2816.3	2812.4	2801.9
137.5°	2930.6	2963.4	2970.0	2967.3	2951.6
140°	3073.8	3106.6	3125.0	3125.0	3110.5
142.5°	3220.9	3253.7	3264.2	3268.2	3253.7
145°	3360.1	3386.4	3407.4	3411.4	3396.9
147.5°	3484.9	3517.8	3533.5	3540.1	3525.6
150°	3613.6	3636.0	3650.5	3662.3	3650.5
152.5°	3727.9	3750.2	3768.7	3783.1	3768.7
155°	3842.2	3852.7	3864.5	3882.9	3871.1
157.5°	3940.7	3948.6	3955.2	3981.4	3963.1
160°	4028.7	4036.6	4040.6	4062.9	4047.1
162.5°	4110.1	4110.1	4114.1	4139.1	4120.6
165°	4179.8	4175.8	4175.8	4202.1	4183.8
167.5°	4242.8	4231.0	4231.0	4257.3	4238.9
170°	4290.1	4279.6	4275.7	4302.0	4279.6
172.5°	4323.0	4312.5	4308.5	4334.8	4312.5
175°	4349.2	4338.7	4330.8	4357.2	4334.8
177.5°	4363.7	4353.2	4345.3	4367.7	4345.3
180°	4357.2	4357.2	4357.2	4357.2	4357.2

TEST NUMBER: P920372

CATALOG NUMBER: DFN2DIP-SQ4F0-070D160US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.18	7.91	8.27	9.00	10.49	6.74	7.46	7.83	8.55	10.05
	3H	8.84	9.49	9.94	10.59	12.10	8.35	9.00	9.45	10.10	11.61
	4H	9.42	10.04	10.53	11.14	12.66	8.93	9.54	10.04	10.64	12.16
	6H	9.82	10.39	10.94	11.49	13.02	9.32	9.89	10.44	10.99	12.52
	8H	9.92	10.46	11.04	11.58	13.10	9.42	9.96	10.54	11.08	12.60
	12H	9.97	10.48	11.09	11.59	13.14	9.46	9.97	10.58	11.08	12.63
4H	2H	7.63	8.25	8.74	9.34	10.86	7.27	7.89	8.39	8.99	10.51
	3H	9.49	10.00	10.61	11.13	12.66	9.08	9.59	10.20	10.72	12.25
	4H	10.20	10.67	11.33	11.79	13.34	9.77	10.25	10.90	11.36	12.91
	6H	10.71	11.12	11.84	12.25	13.80	10.28	10.68	11.41	11.82	13.36
	8H	10.86	11.24	11.99	12.37	13.93	10.42	10.80	11.55	11.93	13.49
	12H	10.93	11.27	12.08	12.41	13.98	10.48	10.82	11.63	11.96	13.53
8H	4H	10.38	10.76	11.52	11.89	13.45	10.01	10.39	11.14	11.52	13.08
	6H	11.01	11.33	12.17	12.50	14.06	10.63	10.94	11.79	12.12	13.67
	8H	11.24	11.51	12.40	12.66	14.24	10.84	11.12	12.00	12.27	13.85
	12H	11.36	11.61	12.53	12.75	14.36	10.95	11.19	12.12	12.34	13.95
12H	4H	10.36	10.71	11.51	11.85	13.41	9.99	10.34	11.15	11.48	13.05
	6H	11.04	11.32	12.20	12.47	14.05	10.67	10.95	11.83	12.10	13.67
	8H	11.28	11.52	12.45	12.67	14.28	10.90	11.14	12.07	12.29	13.90