

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911598

Luminaire Tested: DFN2DIP-PN4F0-110D080US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911598
REPORT IS A COMBINATION OF REPORTS P899696 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D080US850-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18220.9 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 172.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		63	63	63
1	100	96	92	89		93	89	86	83		77	75	73		66	65	63		56	55	54
2	91	84	78	73		85	79	74	69		68	65	61		59	56	54		50	48	46
3	84	75	67	62		78	70	64	58		61	56	52		53	49	46		45	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	52	46		66	56	49	43		49	43	39		43	38	35		37	33	31
6	65	54	46	40		61	50	43	38		44	39	34		39	34	31		34	30	27
7	61	49	41	35		57	46	39	34		40	35	31		35	31	28		31	27	25
8	56	44	37	31		53	42	35	30		37	31	27		33	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	22		26	23	20
10	49	37	30	26		46	35	29	24		32	26	22		28	24	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3680	3680	3680
5°	3686	3622	3646
10°	3650	3552	3528
15°	3599	3435	3345
20°	3533	3274	3121
25°	3465	3093	2904
30°	3373	2907	2628
35°	3284	2707	2387
40°	3193	2501	2109
45°	3087	2272	1858
50°	2977	2040	1612
55°	2863	1793	1376
60°	2731	1534	1133
65°	2579	1271	1021
70°	2394	1025	925
75°	2162	905	843
80°	1827	761	734
85°	1273	510	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3087 cd/sqm

TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.5	2.6
10°-20°	1297.2	7.1
20°-30°	1821.2	10.0
30°-40°	1985.2	10.9
40°-50°	1824.6	10.0
50°-60°	1433.0	7.9
60°-70°	932.7	5.1
70°-80°	480.1	2.6
80°-90°	130.6	0.7
90°-100°	173.6	1.0
100°-110°	551.7	3.0
110°-120°	944.1	5.2
120°-130°	1241.6	6.8
130°-140°	1393.7	7.6
140°-150°	1366.6	7.5
150°-160°	1146.4	6.3
160°-170°	760.3	4.2
170°-180°	265.7	1.5
0°-30°	3590.9	19.7
0°-40°	5576.1	30.6
0°-60°	8833.7	48.5
0°-90°	10377.1	57.0
90°-120°	1669.4	9.2
90°-150°	5671.3	31.1
90°-180°	7844.0	43.0
0°-180°	18220.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5042	5042	5042	5042	5042	
5°	5042	5019	4960	5001	4987	478
15°	4795	4745	4590	4504	4458	1351
25°	4353	4207	3906	3719	3650	2002
35°	3751	3518	3117	2829	2728	2348
45°	3066	2760	2282	1957	1848	2368
55°	2331	1976	1483	1209	1123	2083
65°	1574	1204	794	639	625	1561
75°	839	520	365	333	329	888
85°	196	100	87	87	87	225
90°	3	30	83	78	80	18
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	

TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5041.8	5041.8	5041.8	5041.8	5041.8
2.5°	5064.6	5041.8	4991.5	5037.5	5028.3
5°	5041.8	5019.1	4959.6	5000.7	4987.2
7.5°	5000.7	4973.5	4909.7	4927.6	4904.8
10°	4946.0	4914.0	4823.0	4809.0	4781.9
12.5°	4877.7	4836.6	4713.1	4686.0	4635.6
15°	4795.4	4745.1	4590.2	4503.5	4458.0
17.5°	4699.6	4626.5	4434.8	4334.5	4261.4
20°	4590.2	4498.7	4270.6	4156.9	4056.2
22.5°	4471.6	4366.5	4101.7	3946.8	3878.5
25°	4352.9	4206.8	3905.7	3718.8	3650.1
27.5°	4211.6	4056.2	3723.1	3508.7	3403.6
30°	4061.0	3887.3	3522.3	3289.8	3166.4
32.5°	3914.9	3704.7	3331.0	3057.1	2942.8
35°	3750.7	3517.9	3116.6	2829.1	2728.4
37.5°	3591.1	3339.8	2915.7	2600.5	2486.8
40°	3422.0	3148.6	2705.6	2381.7	2263.1
42.5°	3248.7	2956.8	2496.0	2158.1	2044.3
45°	3066.3	2760.3	2281.5	1957.2	1847.8
47.5°	2892.9	2569.1	2076.3	1751.9	1651.7
50°	2701.2	2377.4	1875.4	1560.3	1464.9
52.5°	2513.9	2171.6	1683.7	1382.6	1295.9
55°	2331.3	1975.6	1482.7	1209.3	1122.6
57.5°	2144.6	1779.5	1305.1	1049.6	976.4
60°	1952.8	1587.9	1117.8	885.4	812.3
62.5°	1766.0	1401.0	958.1	739.3	702.9
65°	1574.2	1204.4	793.9	639.0	624.9
67.5°	1391.8	1021.9	639.0	561.0	547.5
70°	1200.0	844.3	529.1	483.6	465.2
72.5°	1017.5	679.7	442.5	406.1	396.9
75°	839.4	519.9	365.0	333.0	328.7
77.5°	661.7	369.4	287.6	269.2	259.9
80°	497.2	264.8	218.8	201.0	201.0
82.5°	346.6	178.1	150.6	141.4	141.4
85°	196.1	100.3	86.6	86.6	86.6
87.5°	73.1	36.3	36.3	31.9	31.9
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2

TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9

TEST NUMBER: P911598

CATALOG NUMBER: DFN2DIP-PN4F0-110D080US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.31	13.20	13.21	14.11	15.28	8.27	9.16	9.17	10.08	11.25
	3H	13.99	14.79	14.91	15.71	16.91	9.46	10.26	10.38	11.19	12.38
	4H	14.60	15.36	15.53	16.29	17.49	9.92	10.67	10.85	11.60	12.81
	6H	15.03	15.72	15.97	16.66	17.88	10.24	10.94	11.18	11.87	13.09
	8H	15.16	15.82	16.11	16.77	17.99	10.34	10.99	11.28	11.95	13.17
	12H	15.23	15.85	16.18	16.80	18.04	10.38	11.01	11.33	11.96	13.20
4H	2H	12.33	13.08	13.27	14.01	15.22	8.88	9.63	9.81	10.56	11.76
	3H	14.17	14.79	15.11	15.76	16.98	10.23	10.86	11.18	11.82	13.04
	4H	14.87	15.44	15.82	16.39	17.64	10.78	11.35	11.74	12.31	13.55
	6H	15.39	15.88	16.35	16.86	18.10	11.21	11.70	12.17	12.68	13.92
	8H	15.57	16.02	16.53	17.00	18.25	11.34	11.79	12.31	12.77	14.03
	12H	15.66	16.08	16.65	17.07	18.33	11.41	11.82	12.39	12.81	14.07
8H	4H	14.84	15.30	15.81	16.27	17.53	11.07	11.53	12.04	12.50	13.76
	6H	15.41	15.79	16.40	16.80	18.06	11.59	11.97	12.59	12.98	14.24
	8H	15.63	15.96	16.63	16.97	18.24	11.78	12.12	12.79	13.12	14.40
	12H	15.77	16.07	16.78	17.06	18.38	11.91	12.20	12.91	13.20	14.52
12H	4H	14.79	15.21	15.78	16.20	17.46	11.08	11.49	12.06	12.48	13.74
	6H	15.39	15.72	16.39	16.72	18.00	11.64	11.97	12.64	12.98	14.25
	8H	15.61	15.90	16.62	16.90	18.22	11.86	12.15	12.86	13.15	14.47