

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920640

Luminaire Tested: DFN2DIP-TR2F0-020D050US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920640
REPORT IS A COMBINATION OF REPORTS P900251 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D050US935-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5514.7 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	61	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1494	1494	1494
5°	1495	1470	1481
10°	1480	1447	1458
15°	1456	1420	1425
20°	1425	1384	1390
25°	1393	1341	1350
30°	1354	1301	1301
35°	1317	1254	1248
40°	1272	1206	1198
45°	1226	1159	1147
50°	1177	1109	1088
55°	1125	1051	1033
60°	1066	983	970
65°	1001	911	896
70°	918	824	815
75°	805	720	737
80°	668	588	595
85°	453	370	371

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1778 cd/sqm

TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.1
10°-20°	177.4	3.2
20°-30°	260.8	4.7
30°-40°	302.9	5.5
40°-50°	302.5	5.5
50°-60°	263.8	4.8
60°-70°	195.0	3.5
70°-80°	110.3	2.0
80°-90°	33.0	0.6
90°-100°	84.2	1.5
100°-110°	267.7	4.9
110°-120°	458.1	8.3
120°-130°	602.5	10.9
130°-140°	676.3	12.3
140°-150°	663.1	12.0
150°-160°	556.3	10.1
160°-170°	368.9	6.7
170°-180°	128.9	2.3
0°-30°	501.3	9.1
0°-40°	804.1	14.6
0°-60°	1370.4	24.8
0°-90°	1708.6	31.0
90°-120°	810.0	14.7
90°-150°	2751.9	49.9
90°-180°	3806.0	69.0
0°-180°	5514.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	1	15	40	38	39	5
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8

TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5

TEST NUMBER: P920640

CATALOG NUMBER: DFN2DIP-TR2F0-020D050US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.46	7.17	7.56	8.27	9.79	6.03	6.75	7.14	7.85	9.37
	3H	8.08	8.72	9.19	9.83	11.36	7.62	8.26	8.73	9.37	10.90
	4H	8.65	9.25	9.77	10.36	11.90	8.19	8.79	9.31	9.90	11.44
	6H	9.02	9.58	10.15	10.69	12.24	8.56	9.12	9.69	10.23	11.78
	8H	9.11	9.64	10.25	10.77	12.32	8.65	9.18	9.79	10.31	11.86
	12H	9.15	9.65	10.29	10.77	12.34	8.68	9.19	9.82	10.31	11.88
4H	2H	6.89	7.50	8.02	8.61	10.15	6.55	7.16	7.68	8.27	9.81
	3H	8.71	9.22	9.85	10.36	11.91	8.33	8.84	9.47	9.97	11.53
	4H	9.40	9.87	10.54	10.99	12.57	9.01	9.48	10.15	10.60	12.17
	6H	9.89	10.29	11.03	11.44	13.00	9.49	9.89	10.64	11.04	12.60
	8H	10.02	10.40	11.17	11.54	13.12	9.62	10.00	10.77	11.14	12.72
	12H	10.08	10.42	11.24	11.57	13.15	9.67	10.01	10.83	11.16	12.75
8H	4H	9.58	9.95	10.72	11.09	12.67	9.23	9.60	10.37	10.74	12.32
	6H	10.18	10.48	11.34	11.67	13.24	9.82	10.13	10.99	11.31	12.89
	8H	10.38	10.65	11.55	11.81	13.41	10.02	10.29	11.19	11.45	13.05
	12H	10.49	10.72	11.66	11.88	13.51	10.12	10.35	11.29	11.51	13.14
12H	4H	9.55	9.89	10.72	11.04	12.63	9.21	9.55	10.37	10.70	12.29
	6H	10.20	10.47	11.37	11.63	13.23	9.86	10.13	11.03	11.29	12.89
	8H	10.42	10.65	11.59	11.81	13.44	10.07	10.31	11.25	11.46	13.10

END OF REPORT