

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922443

Luminaire Tested: DFN2DIP-PN4F0-090D090US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922443
REPORT IS A COMBINATION OF REPORTS P901230 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D090US940-RLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14766.7 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 155
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922443
CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P922443

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40				40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39	34				34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34	29				29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26				26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23				23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2421	2421	2421
5°	2425	2383	2398
10°	2401	2337	2321
15°	2368	2260	2201
20°	2324	2154	2053
25°	2279	2035	1910
30°	2219	1912	1729
35°	2160	1781	1570
40°	2100	1645	1388
45°	2031	1494	1222
50°	1959	1342	1061
55°	1884	1179	905
60°	1797	1009	746
65°	1696	836	672
70°	1575	675	608
75°	1423	595	554
80°	1202	500	483
85°	837	336	366

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2031 cd/sqm



TEST NUMBER: P922443

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	2.1
10°-20°	853.4	5.8
20°-30°	1198.1	8.1
30°-40°	1306.0	8.8
40°-50°	1200.4	8.1
50°-60°	942.7	6.4
60°-70°	613.6	4.2
70°-80°	315.9	2.1
80°-90°	85.4	0.6
90°-100°	89.3	0.6
100°-110°	332.9	2.3
110°-120°	883.0	6.0
120°-130°	1464.5	9.9
130°-140°	1555.6	10.5
140°-150°	1445.8	9.8
150°-160°	1162.4	7.9
160°-170°	749.0	5.1
170°-180°	257.8	1.7
0°-30°	2362.4	16.0
0°-40°	3668.4	24.8
0°-60°	5811.5	39.4
0°-90°	6826.4	46.2
90°-120°	1305.2	8.8
90°-150°	5771.2	39.1
90°-180°	7940.0	53.8
0°-180°	14766.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	2	24	39	49	53	14
95°	127	63	76	86	84	151
105°	596	655	120	141	149	637
115°	1127	1160	1209	302	161	1109
125°	1593	1619	1656	1670	1676	1421
135°	1972	2003	2020	2040	2036	1523
145°	2287	2285	2318	2332	2322	1431
155°	2518	2501	2524	2536	2520	1161
165°	2654	2642	2648	2662	2648	750
175°	2714	2700	2705	2718	2699	258
180°	2708	2708	2708	2708	2708	



TEST NUMBER: P922443

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	1.9	23.5	39.1	49.1	52.8
92.5°	49.1	41.2	47.0	51.0	52.8
95°	127.3	62.6	76.3	86.3	84.3
97.5°	229.3	68.7	99.9	105.8	107.7
100°	347.0	78.5	111.7	127.3	131.3
102.5°	476.2	472.4	115.7	137.1	143.1
105°	595.8	654.7	119.6	141.1	148.9
107.5°	734.9	783.8	123.6	145.0	152.9
110°	868.3	909.3	343.0	147.0	154.8



TEST NUMBER: P922443

CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	993.7	1028.9	995.6	150.8	156.9
115°	1126.9	1160.1	1209.2	301.8	160.8
117.5°	1242.5	1281.7	1315.1	1034.7	521.3
120°	1371.9	1401.2	1436.6	1460.1	1195.5
122.5°	1481.6	1513.0	1552.3	1563.9	1566.0
125°	1593.2	1618.8	1656.1	1669.8	1675.6
127.5°	1695.1	1722.6	1752.2	1771.7	1773.6
130°	1791.3	1822.7	1844.1	1865.7	1863.9
132.5°	1889.3	1914.9	1936.3	1954.0	1952.1
135°	1971.7	2003.0	2020.5	2040.3	2036.4
137.5°	2057.8	2081.3	2101.0	2120.6	2114.8
140°	2142.0	2157.8	2179.3	2196.9	2187.2
142.5°	2212.8	2226.5	2251.8	2267.4	2257.7
145°	2287.2	2285.1	2318.4	2332.2	2322.4
147.5°	2351.7	2345.9	2379.2	2389.0	2381.2
150°	2414.6	2400.8	2432.2	2443.8	2434.1
152.5°	2467.4	2451.8	2481.1	2493.0	2479.2
155°	2518.4	2500.9	2524.3	2536.0	2520.4
157.5°	2559.6	2544.0	2561.6	2575.3	2559.6
160°	2594.9	2583.0	2594.9	2606.6	2592.8
162.5°	2626.1	2614.4	2624.2	2637.9	2620.3
165°	2653.6	2641.9	2647.8	2661.5	2647.8
167.5°	2675.2	2663.4	2669.3	2683.1	2665.4
170°	2692.9	2681.0	2684.9	2698.7	2681.0
172.5°	2704.6	2692.9	2696.8	2710.5	2692.9
175°	2714.3	2700.5	2704.6	2718.2	2698.7
177.5°	2718.2	2704.6	2706.6	2720.3	2702.7
180°	2708.5	2708.5	2708.5	2708.5	2708.5



TEST NUMBER: P922443
 CATALOG NUMBER: DFN2DIP-PN4F0-090D090US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.86	10.66	10.86	11.67	12.99	5.83	6.63	6.82	7.63	8.96
	3H	11.54	12.26	12.55	13.27	14.62	7.02	7.73	8.02	8.74	10.09
	4H	12.15	12.83	13.17	13.84	15.20	7.46	8.14	8.48	9.16	10.51
	6H	12.57	13.20	13.60	14.21	15.58	7.79	8.41	8.81	9.43	10.79
	8H	12.70	13.29	13.73	14.33	15.69	7.88	8.47	8.91	9.50	10.87
	12H	12.76	13.32	13.80	14.35	15.74	7.92	8.48	8.96	9.51	10.90
4H	2H	9.88	10.55	10.90	11.57	12.93	6.42	7.10	7.45	8.11	9.47
	3H	11.71	12.27	12.74	13.31	14.68	7.77	8.33	8.80	9.38	10.74
	4H	12.40	12.92	13.44	13.95	15.34	8.32	8.83	9.36	9.87	11.26
	6H	12.92	13.36	13.97	14.42	15.80	8.74	9.18	9.79	10.24	11.62
	8H	13.09	13.51	14.14	14.56	15.96	8.87	9.28	9.92	10.33	11.73
	12H	13.19	13.56	14.26	14.63	16.03	8.93	9.30	10.00	10.37	11.77
8H	4H	12.37	12.78	13.42	13.83	15.23	8.60	9.01	9.65	10.06	11.46
	6H	12.93	13.27	14.01	14.37	15.77	9.12	9.46	10.19	10.55	11.95
	8H	13.15	13.45	14.23	14.53	15.95	9.31	9.61	10.39	10.68	12.10
	12H	13.29	13.56	14.38	14.63	16.09	9.43	9.69	10.51	10.76	12.22
12H	4H	12.32	12.69	13.39	13.75	15.16	8.60	8.97	9.67	10.04	11.45
	6H	12.91	13.21	13.99	14.29	15.71	9.17	9.46	10.25	10.54	11.96
	8H	13.13	13.39	14.22	14.47	15.93	9.38	9.64	10.46	10.71	12.17