

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915285

Luminaire Tested: DFN2DIP-TR3F0-030D060US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915285
REPORT IS A COMBINATION OF REPORTS P901833 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D060US927-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7058.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74		57	57	57		41
1	94	90	86	83	85	81	78	75	65	63	61		50	48	47		36
2	86	78	72	67	77	71	66	62	57	53	50		44	41	39		32
3	78	69	62	56	70	62	56	51	50	46	42		39	36	33		28
4	71	61	53	47	64	55	49	43	44	40	36		34	31	28		25
5	65	54	46	40	59	49	42	37	40	35	31		31	27	25		23
6	60	48	41	35	54	44	37	32	36	31	27		28	24	21		20
7	56	44	36	30	50	40	33	28	32	27	23		25	22	19		19
8	51	39	32	27	46	36	29	25	29	24	21		23	19	17		17
9	48	36	29	24	43	33	26	22	27	22	19		21	18	15		16
10	45	33	26	21	40	30	24	20	25	20	17		19	16	14		15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1152	1152	1152
5°	1153	1135	1143
10°	1144	1119	1127
15°	1126	1100	1102
20°	1103	1073	1076
25°	1079	1041	1047
30°	1050	1012	1010
35°	1023	977	971
40°	989	942	933
45°	956	907	895
50°	919	870	851
55°	880	828	810
60°	836	777	763
65°	788	725	708
70°	727	661	648
75°	643	584	592
80°	541	486	486
85°	382	320	314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1067 cd/sqm

TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.2
10°-20°	244.9	3.5
20°-30°	359.9	5.1
30°-40°	418.0	5.9
40°-50°	417.5	5.9
50°-60°	364.0	5.2
60°-70°	269.1	3.8
70°-80°	152.3	2.2
80°-90°	43.0	0.6
90°-100°	52.9	0.7
100°-110°	197.2	2.8
110°-120°	523.0	7.4
120°-130°	867.4	12.3
130°-140°	921.3	13.1
140°-150°	856.3	12.1
150°-160°	688.4	9.8
160°-170°	443.6	6.3
170°-180°	152.7	2.2
0°-30°	691.8	9.8
0°-40°	1109.8	15.7
0°-60°	1891.3	26.8
0°-90°	2355.6	33.4
90°-120°	773.0	11.0
90°-150°	3418.0	48.4
90°-180°	4703.0	66.6
0°-180°	7058.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	1	14	23	29	31	6
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7



TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1

TEST NUMBER: P915285

CATALOG NUMBER: DFN2DIP-TR3F0-030D060US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.94	6.67	7.03	7.76	9.25	5.51	6.24	6.60	7.33	8.82
	3H	7.58	8.23	8.68	9.33	10.84	7.11	7.77	8.21	8.86	10.37
	4H	8.16	8.78	9.26	9.87	11.39	7.69	8.31	8.80	9.41	10.92
	6H	8.54	9.11	9.66	10.21	11.74	8.07	8.64	9.19	9.74	11.27
	8H	8.64	9.18	9.76	10.30	11.82	8.17	8.71	9.29	9.83	11.35
	12H	8.68	9.19	9.80	10.30	11.85	8.21	8.72	9.33	9.83	11.37
4H	2H	6.38	7.00	7.50	8.10	9.61	6.04	6.66	7.15	7.76	9.27
	3H	8.22	8.74	9.35	9.87	11.39	7.84	8.35	8.96	9.48	11.00
	4H	8.93	9.40	10.05	10.51	12.06	8.53	9.00	9.65	10.11	11.66
	6H	9.42	9.83	10.56	10.97	12.51	9.02	9.43	10.15	10.56	12.10
	8H	9.57	9.95	10.70	11.07	12.63	9.16	9.54	10.29	10.67	12.22
	12H	9.63	9.97	10.78	11.11	12.67	9.21	9.56	10.36	10.70	12.26
8H	4H	9.11	9.49	10.24	10.62	12.17	8.75	9.13	9.88	10.26	11.81
	6H	9.72	10.04	10.88	11.21	12.76	9.36	9.68	10.52	10.85	12.40
	8H	9.94	10.21	11.09	11.36	12.93	9.57	9.85	10.73	11.00	12.57
	12H	10.05	10.30	11.22	11.44	13.05	9.68	9.92	10.84	11.06	12.67
12H	4H	9.09	9.43	10.23	10.57	12.13	8.74	9.08	9.89	10.22	11.78
	6H	9.75	10.02	10.91	11.17	12.75	9.40	9.68	10.56	10.83	12.40
	8H	9.98	10.22	11.14	11.37	12.97	9.63	9.87	10.79	11.01	12.62

END OF REPORT