

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908975

Luminaire Tested: DFN2DIP-SQ2F0-050D030US840-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P908975  
REPORT IS A COMBINATION OF REPORTS P901296 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-050D030US840-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7291.3 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 67  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908975  
CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P908975  
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51			
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43			
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37			
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26			
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19			
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4589	4589	4589
5°	4588	4506	4539
10°	4535	4408	4384
15°	4464	4252	4150
20°	4374	4042	3865
25°	4281	3809	3590
30°	4159	3570	3243
35°	4040	3314	2938
40°	3917	3051	2591
45°	3776	2760	2275
50°	3629	2468	1968
55°	3475	2156	1673
60°	3297	1832	1371
65°	3091	1504	1227
70°	2841	1198	1101
75°	2526	1036	989
80°	2074	842	838
85°	1351	523	597

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3776 cd/sqm



TEST NUMBER: P908975

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.6	2.7
10°-20°	536.9	7.4
20°-30°	753.8	10.3
30°-40°	821.7	11.3
40°-50°	755.2	10.4
50°-60°	593.1	8.1
60°-70°	386.1	5.3
70°-80°	198.7	2.7
80°-90°	52.5	0.7
90°-100°	33.7	0.5
100°-110°	125.7	1.7
110°-120°	333.3	4.6
120°-130°	552.9	7.6
130°-140°	587.3	8.1
140°-150°	545.8	7.5
150°-160°	438.8	6.0
160°-170°	282.8	3.9
170°-180°	97.3	1.3
0°-30°	1486.3	20.4
0°-40°	2308.0	31.7
0°-60°	3656.4	50.1
0°-90°	4293.8	58.9
90°-120°	492.7	6.8
90°-150°	2178.7	29.9
90°-180°	2998.0	41.1
0°-180°	7291.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	1	9	15	19	20	7
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P908975

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P908975

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P908975  
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US840-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.12	14.03	14.00	14.93	16.07	9.08	9.99	9.96	10.89	12.03
	3H	14.78	15.59	15.68	16.50	17.67	10.25	11.07	11.15	11.98	13.14
	4H	15.38	16.15	16.29	17.06	18.24	10.70	11.46	11.61	12.38	13.55
	6H	15.79	16.50	16.71	17.42	18.61	11.00	11.71	11.93	12.63	13.82
	8H	15.91	16.58	16.84	17.52	18.71	11.09	11.76	12.02	12.70	13.89
	12H	15.97	16.61	16.90	17.54	18.75	11.13	11.77	12.06	12.70	13.91
4H	2H	13.14	13.91	14.06	14.82	16.00	9.67	10.44	10.59	11.35	12.53
	3H	14.95	15.59	15.88	16.54	17.73	11.01	11.65	11.94	12.59	13.78
	4H	15.63	16.21	16.57	17.16	18.37	11.54	12.12	12.48	13.07	14.28
	6H	16.13	16.63	17.09	17.60	18.82	11.95	12.45	12.90	13.41	14.63
	8H	16.30	16.77	17.25	17.73	18.96	12.07	12.53	13.02	13.49	14.72
	12H	16.39	16.81	17.36	17.78	19.02	12.13	12.55	13.10	13.52	14.76
8H	4H	15.60	16.07	16.56	17.03	18.26	11.82	12.28	12.77	13.24	14.47
	6H	16.15	16.54	17.13	17.54	18.77	12.31	12.70	13.29	13.70	14.93
	8H	16.35	16.69	17.34	17.68	18.93	12.49	12.83	13.48	13.82	15.07
	12H	16.48	16.78	17.47	17.76	19.06	12.60	12.90	13.59	13.88	15.18
12H	4H	15.56	15.98	16.53	16.95	18.19	11.82	12.24	12.80	13.22	14.45
	6H	16.12	16.47	17.11	17.45	18.70	12.36	12.70	13.35	13.69	14.94
	8H	16.33	16.63	17.32	17.62	18.91	12.56	12.86	13.55	13.84	15.13