

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911729

Luminaire Tested: DFN2DIP-SQ2F0-060D040US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911729
REPORT IS A COMBINATION OF REPORTS P901309 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-060D040US850-FLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10979.0 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911729
CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P911729

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60		
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55	51		
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	42		
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36		
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31		
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27		
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24		
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21		
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19		
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17		
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5693	5693	5693
5°	5692	5601	5644
10°	5636	5513	5559
15°	5543	5410	5432
20°	5422	5272	5302
25°	5300	5109	5153
30°	5151	4956	4965
35°	5008	4778	4768
40°	4834	4598	4579
45°	4660	4417	4385
50°	4469	4226	4162
55°	4268	4006	3954
60°	4041	3746	3717
65°	3791	3475	3436
70°	3474	3145	3133
75°	3039	2749	2842
80°	2511	2244	2308
85°	1695	1416	1451

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4660 cd/sqm



TEST NUMBER: P911729

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	2.2
10°-20°	685.6	6.2
20°-30°	1007.6	9.2
30°-40°	1170.3	10.7
40°-50°	1168.8	10.6
50°-60°	1019.2	9.3
60°-70°	753.4	6.9
70°-80°	426.3	3.9
80°-90°	115.1	1.0
90°-100°	49.4	0.4
100°-110°	184.0	1.7
110°-120°	488.1	4.4
120°-130°	809.5	7.4
130°-140°	859.9	7.8
140°-150°	799.2	7.3
150°-160°	642.5	5.9
160°-170°	414.0	3.8
170°-180°	142.5	1.3
0°-30°	1937.0	17.6
0°-40°	3107.2	28.3
0°-60°	5295.3	48.2
0°-90°	6590.0	60.0
90°-120°	721.5	6.6
90°-150°	3190.0	29.1
90°-180°	4389.0	40.0
0°-180°	10979.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	114
90°	1	13	22	27	29	10
95°	70	35	42	48	47	83
105°	329	362	66	78	82	352
115°	623	641	668	167	89	613
125°	881	895	915	923	926	785
135°	1090	1107	1117	1128	1126	842
145°	1264	1263	1281	1289	1284	791
155°	1392	1382	1395	1402	1393	641
165°	1467	1460	1464	1471	1464	414
175°	1500	1493	1495	1502	1492	143
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P911729

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	1.0	13.0	21.6	27.2	29.2
92.5°	27.2	22.7	26.0	28.2	29.2
95°	70.3	34.6	42.1	47.7	46.6
97.5°	126.8	37.9	55.2	58.6	59.6
100°	191.7	43.4	61.8	70.3	72.5
102.5°	263.2	261.2	63.9	75.7	79.1
105°	329.3	361.9	66.1	78.0	82.3
107.5°	406.2	433.3	68.3	80.2	84.5
110°	480.0	502.6	189.6	81.3	85.5



TEST NUMBER: P911729

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	549.3	568.7	550.3	83.4	86.7
115°	622.8	641.2	668.4	166.8	88.9
117.5°	686.8	708.4	726.9	571.9	288.1
120°	758.3	774.5	794.0	807.1	660.9
122.5°	818.9	836.3	858.0	864.5	865.6
125°	880.7	894.9	915.4	923.0	926.2
127.5°	937.0	952.2	968.5	979.4	980.4
130°	990.1	1007.5	1019.3	1031.3	1030.3
132.5°	1044.2	1058.4	1070.3	1080.1	1079.1
135°	1089.8	1107.2	1116.9	1127.7	1125.6
137.5°	1137.4	1150.4	1161.3	1172.1	1168.9
140°	1184.0	1192.7	1204.6	1214.4	1208.9
142.5°	1223.1	1230.7	1244.7	1253.3	1248.0
145°	1264.3	1263.2	1281.4	1289.1	1283.7
147.5°	1299.9	1296.6	1315.1	1320.5	1316.3
150°	1334.6	1327.0	1344.4	1350.9	1345.4
152.5°	1363.8	1355.2	1371.4	1377.9	1370.4
155°	1392.0	1382.4	1395.3	1401.8	1393.1
157.5°	1414.8	1406.1	1416.0	1423.5	1414.8
160°	1434.3	1427.7	1434.3	1440.7	1433.2
162.5°	1451.6	1445.1	1450.6	1458.1	1448.4
165°	1466.8	1460.3	1463.5	1471.1	1463.5
167.5°	1478.7	1472.1	1475.5	1483.1	1473.3
170°	1488.5	1482.0	1484.1	1491.7	1482.0
172.5°	1494.9	1488.5	1490.7	1498.3	1488.5
175°	1500.3	1492.7	1494.9	1502.5	1491.7
177.5°	1502.5	1494.9	1496.0	1503.7	1493.9
180°	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P911729
 CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.08	15.04	14.94	15.92	17.04	13.63	14.59	14.50	15.48	16.60
	3H	15.72	16.59	16.60	17.48	18.63	15.23	16.10	16.11	16.99	18.14
	4H	16.30	17.12	17.20	18.02	19.18	15.81	16.62	16.70	17.53	18.68
	6H	16.69	17.44	17.60	18.35	19.52	16.19	16.94	17.10	17.85	19.02
	8H	16.79	17.51	17.71	18.44	19.60	16.29	17.01	17.21	17.93	19.10
	12H	16.84	17.52	17.76	18.44	19.63	16.33	17.01	17.25	17.93	19.13
4H	2H	14.54	15.35	15.44	16.26	17.41	14.18	15.00	15.08	15.90	17.06
	3H	16.39	17.07	17.30	18.00	19.18	15.98	16.66	16.89	17.60	18.77
	4H	17.09	17.71	18.01	18.64	19.84	16.67	17.29	17.59	18.22	19.42
	6H	17.60	18.13	18.53	19.08	20.28	17.16	17.70	18.10	18.65	19.85
	8H	17.74	18.24	18.68	19.19	20.40	17.30	17.80	18.24	18.75	19.96
	12H	17.81	18.26	18.76	19.22	20.44	17.36	17.81	18.32	18.77	19.99
8H	4H	17.29	17.79	18.22	18.73	19.95	16.91	17.41	17.85	18.36	19.57
	6H	17.90	18.31	18.86	19.30	20.51	17.51	17.93	18.48	18.92	20.13
	8H	18.11	18.47	19.08	19.45	20.68	17.71	18.08	18.69	19.06	20.29
	12H	18.23	18.55	19.21	19.52	20.80	17.82	18.14	18.80	19.11	20.39
12H	4H	17.27	17.72	18.23	18.69	19.91	16.90	17.35	17.86	18.32	19.54
	6H	17.92	18.29	18.90	19.27	20.50	17.55	17.92	18.52	18.90	20.12
	8H	18.15	18.48	19.13	19.45	20.73	17.77	18.10	18.75	19.07	20.34