

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926290

Luminaire Tested: DFN2DIP-TR3F0-070D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926290
REPORT IS A COMBINATION OF REPORTS P900280 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D030US950-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8209.1 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	66	65	64
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3439	3439	3439
5°	3443	3382	3404
10°	3407	3313	3291
15°	3358	3200	3118
20°	3294	3047	2906
25°	3229	2875	2701
30°	3141	2699	2443
35°	3056	2511	2215
40°	2968	2316	1955
45°	2867	2100	1720
50°	2762	1882	1490
55°	2653	1650	1269
60°	2526	1407	1042
65°	2379	1161	935
70°	2202	932	843
75°	1979	815	762
80°	1656	675	654
85°	1126	437	478

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2867 cd/sqm

TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	3.2
10°-20°	710.1	8.7
20°-30°	997.0	12.1
30°-40°	1086.8	13.2
40°-50°	998.8	12.2
50°-60°	784.4	9.6
60°-70°	510.6	6.2
70°-80°	262.8	3.2
80°-90°	69.7	0.8
90°-100°	56.0	0.7
100°-110°	178.0	2.2
110°-120°	304.6	3.7
120°-130°	400.5	4.9
130°-140°	449.6	5.5
140°-150°	440.9	5.4
150°-160°	369.8	4.5
160°-170°	245.3	3.0
170°-180°	85.7	1.0
0°-30°	1965.7	23.9
0°-40°	3052.5	37.2
0°-60°	4835.8	58.9
0°-90°	5678.8	69.2
90°-120°	538.5	6.6
90°-150°	1829.5	22.3
90°-180°	2530.0	30.8
0°-180°	8209.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2760	2760	2760	2760	2760	
5°	2760	2748	2715	2738	2730	262
15°	2625	2598	2513	2465	2440	740
25°	2383	2303	2138	2036	1998	1096
35°	2053	1926	1706	1549	1494	1285
45°	1679	1511	1249	1071	1012	1296
55°	1276	1082	812	662	615	1140
65°	862	659	435	350	342	854
75°	460	285	200	182	180	486
85°	107	55	47	47	47	123
90°	1	10	27	25	26	8
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2760.0	2760.0	2760.0	2760.0	2760.0
2.5°	2772.4	2760.0	2732.4	2757.6	2752.6
5°	2760.0	2747.5	2715.0	2737.5	2730.1
7.5°	2737.5	2722.6	2687.7	2697.4	2685.0
10°	2707.5	2690.1	2640.2	2632.6	2617.7
12.5°	2670.2	2647.6	2580.1	2565.2	2537.6
15°	2625.1	2597.6	2512.7	2465.3	2440.4
17.5°	2572.7	2532.7	2427.7	2372.8	2332.8
20°	2512.7	2462.7	2337.9	2275.6	2220.4
22.5°	2447.9	2390.3	2245.3	2160.5	2123.2
25°	2382.9	2302.9	2138.0	2035.7	1998.2
27.5°	2305.5	2220.4	2038.1	1920.8	1863.3
30°	2223.1	2128.0	1928.1	1801.0	1733.4
32.5°	2143.1	2028.1	1823.5	1673.5	1610.9
35°	2053.2	1925.7	1706.1	1548.7	1493.6
37.5°	1965.8	1828.2	1596.1	1423.6	1361.4
40°	1873.3	1723.6	1481.1	1303.8	1238.9
42.5°	1778.4	1618.7	1366.3	1181.3	1119.1
45°	1678.6	1511.0	1249.0	1071.4	1011.5
47.5°	1583.6	1406.4	1136.6	959.1	904.2
50°	1478.7	1301.4	1026.6	854.1	801.9
52.5°	1376.1	1188.8	921.7	756.8	709.4
55°	1276.3	1081.5	811.7	662.0	614.6
57.5°	1174.0	974.1	714.5	574.5	534.5
60°	1069.1	869.2	611.9	484.7	444.7
62.5°	966.7	766.9	524.4	404.7	384.7
65°	861.7	659.3	434.6	349.8	342.1
67.5°	761.9	559.4	349.8	307.1	299.7
70°	656.9	462.1	289.6	264.7	254.6
72.5°	557.0	372.1	242.2	222.4	217.3
75°	459.5	284.6	199.8	182.3	179.9
77.5°	362.2	202.2	157.4	147.3	142.3
80°	272.2	144.9	119.8	110.0	110.0
82.5°	189.8	97.5	82.4	77.4	77.4
85°	107.3	54.9	47.4	47.4	47.4
87.5°	40.0	19.8	19.8	17.5	17.5
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P926290

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.01	14.03	13.80	14.83	15.80	8.99	10.01	9.77	10.80	11.78
	3H	14.70	15.61	15.49	16.41	17.41	10.19	11.10	10.98	11.90	12.91
	4H	15.31	16.16	16.12	16.98	17.99	10.64	11.50	11.45	12.32	13.33
	6H	15.73	16.52	16.55	17.34	18.37	10.97	11.76	11.79	12.58	13.61
	8H	15.86	16.61	16.69	17.45	18.48	11.06	11.81	11.89	12.65	13.68
	12H	15.92	16.64	16.76	17.47	18.52	11.11	11.82	11.95	12.66	13.71
4H	2H	13.05	13.91	13.87	14.73	15.74	9.60	10.46	10.42	11.28	12.29
	3H	14.89	15.60	15.72	16.45	17.48	10.96	11.68	11.79	12.52	13.55
	4H	15.58	16.23	16.42	17.08	18.13	11.51	12.16	12.35	13.01	14.06
	6H	16.10	16.65	16.95	17.53	18.59	11.94	12.49	12.79	13.37	14.43
	8H	16.27	16.79	17.13	17.66	18.73	12.07	12.59	12.93	13.45	14.53
	12H	16.37	16.84	17.25	17.72	18.80	12.14	12.60	13.02	13.49	14.57
8H	4H	15.56	16.08	16.42	16.95	18.02	11.80	12.32	12.66	13.19	14.26
	6H	16.12	16.55	17.01	17.46	18.54	12.32	12.75	13.21	13.66	14.73
	8H	16.33	16.72	17.23	17.62	18.71	12.51	12.89	13.41	13.79	14.88
	12H	16.47	16.81	17.37	17.71	18.85	12.63	12.97	13.53	13.86	15.00
12H	4H	15.52	15.99	16.40	16.88	17.95	11.81	12.28	12.69	13.17	14.25
	6H	16.10	16.48	17.00	17.38	18.47	12.37	12.75	13.26	13.65	14.74
	8H	16.32	16.66	17.22	17.55	18.70	12.58	12.92	13.48	13.81	14.95