

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922685

Luminaire Tested: DFN2DIP-SQ2F0-080D030US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922685
REPORT IS A COMBINATION OF REPORTS P901301 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D030US940-FLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9710.8 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 101.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35
6	67	54	45	39	63	52	44	38	47	41	36	43	37	33	39	35	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6103	6103	6103
5°	6103	6005	6051
10°	6043	5911	5960
15°	5943	5801	5824
20°	5813	5652	5684
25°	5683	5478	5524
30°	5522	5314	5323
35°	5368	5123	5111
40°	5182	4930	4909
45°	4995	4735	4701
50°	4791	4530	4462
55°	4576	4295	4239
60°	4332	4016	3985
65°	4065	3725	3685
70°	3725	3371	3359
75°	3259	2947	3047
80°	2692	2406	2474
85°	1818	1519	1555

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4995 cd/sqm

TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.7
10°-20°	735.1	7.6
20°-30°	1080.3	11.1
30°-40°	1254.7	12.9
40°-50°	1253.1	12.9
50°-60°	1092.7	11.3
60°-70°	807.7	8.3
70°-80°	457.0	4.7
80°-90°	122.2	1.3
90°-100°	29.8	0.3
100°-110°	111.0	1.1
110°-120°	294.3	3.0
120°-130°	488.2	5.0
130°-140°	518.5	5.3
140°-150°	481.9	5.0
150°-160°	387.5	4.0
160°-170°	249.7	2.6
170°-180°	85.9	0.9
0°-30°	2076.6	21.4
0°-40°	3331.3	34.3
0°-60°	5677.0	58.5
0°-90°	7064.0	72.7
90°-120°	435.1	4.5
90°-150°	1923.7	19.8
90°-180°	2647.0	27.3
0°-180°	9710.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	1	8	13	16	18	9
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6

TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P922685

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.32	16.43	16.05	17.19	18.09	14.87	15.99	15.61	16.74	17.65
	3H	16.98	17.98	17.73	18.74	19.68	16.49	17.49	17.24	18.25	19.19
	4H	17.56	18.51	18.33	19.28	20.23	17.07	18.01	17.84	18.79	19.73
	6H	17.96	18.83	18.74	19.62	20.58	17.46	18.33	18.24	19.12	20.08
	8H	18.07	18.90	18.85	19.70	20.66	17.56	18.39	18.35	19.20	20.16
	12H	18.12	18.91	18.91	19.70	20.69	17.61	18.40	18.40	19.19	20.18
4H	2H	15.80	16.74	16.57	17.52	18.46	15.44	16.39	16.21	17.16	18.11
	3H	17.66	18.45	18.45	19.26	20.22	17.26	18.04	18.04	18.85	19.82
	4H	18.37	19.09	19.17	19.90	20.89	17.95	18.66	18.74	19.47	20.47
	6H	18.88	19.50	19.70	20.34	21.34	18.45	19.07	19.26	19.91	20.90
	8H	19.03	19.61	19.85	20.44	21.45	18.59	19.17	19.41	20.00	21.01
	12H	19.11	19.63	19.94	20.48	21.49	18.66	19.18	19.49	20.03	21.05
8H	4H	18.58	19.16	19.39	19.99	21.00	18.20	18.78	19.02	19.61	20.62
	6H	19.20	19.68	20.04	20.55	21.56	18.81	19.29	19.66	20.16	21.17
	8H	19.41	19.83	20.26	20.70	21.73	19.01	19.44	19.87	20.31	21.34
	12H	19.54	19.91	20.40	20.77	21.85	19.13	19.50	19.99	20.36	21.44
12H	4H	18.57	19.09	19.41	19.95	20.96	18.20	18.72	19.04	19.58	20.59
	6H	19.22	19.65	20.08	20.52	21.55	18.85	19.28	19.71	20.14	21.17
	8H	19.46	19.84	20.32	20.70	21.78	19.08	19.46	19.94	20.31	21.40