

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909319

Luminaire Tested: DFN2DIP-SQ3F0-100D120US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909319
REPORT IS A COMBINATION OF REPORTS P901538 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D120US840-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20581.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909319
CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P909319
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	49	42
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42	42	42	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	36	36	36	31
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31	31	31	31	27
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	27	27	27	23
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	24	24	24	20
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	21	21	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	19	19	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	17	17	17	15
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	15	15	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4782	4782	4782
5°	4787	4703	4735
10°	4736	4608	4579
15°	4668	4452	4340
20°	4579	4240	4046
25°	4487	4001	3763
30°	4366	3758	3404
35°	4246	3496	3089
40°	4124	3225	2728
45°	3983	2926	2400
50°	3837	2623	2081
55°	3684	2301	1774
60°	3506	1964	1459
65°	3302	1621	1311
70°	3054	1302	1184
75°	2742	1141	1074
80°	2291	948	926
85°	1554	617	687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3983 cd/sqm



TEST NUMBER: P909319

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	1.9
10°-20°	1073.8	5.2
20°-30°	1507.6	7.3
30°-40°	1643.4	8.0
40°-50°	1510.5	7.3
50°-60°	1186.3	5.8
60°-70°	772.1	3.8
70°-80°	397.5	1.9
80°-90°	108.7	0.5
90°-100°	134.9	0.7
100°-110°	502.7	2.4
110°-120°	1333.3	6.5
120°-130°	2211.4	10.7
130°-140°	2349.0	11.4
140°-150°	2183.2	10.6
150°-160°	1755.2	8.5
160°-170°	1131.0	5.5
170°-180°	389.3	1.9
0°-30°	2972.6	14.4
0°-40°	4616.1	22.4
0°-60°	7312.8	35.5
0°-90°	8591.0	41.7
90°-120°	1970.9	9.6
90°-150°	8714.5	42.3
90°-180°	11990.0	58.3
0°-180°	20581.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4106	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3604	3482	3233	3078	3022	1657
35°	3105	2912	2580	2342	2259	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1636	1228	1001	929	1725
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	3	35	59	74	80	19
95°	192	94	115	130	127	228
105°	900	989	181	213	225	961
115°	1702	1752	1826	456	243	1675
125°	2406	2444	2501	2521	2530	2146
135°	2977	3025	3051	3081	3075	2300
145°	3454	3451	3501	3522	3507	2160
155°	3803	3776	3812	3829	3806	1752
165°	4007	3989	3998	4019	3998	1132
175°	4098	4078	4084	4105	4075	390
180°	4090	4090	4090	4090	4090	



TEST NUMBER: P909319

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.8	4173.8	4173.8	4173.8	4173.8
2.5°	4192.6	4173.8	4132.1	4170.1	4162.6
5°	4173.8	4154.9	4105.6	4139.7	4128.4
7.5°	4139.7	4117.2	4064.3	4079.1	4060.4
10°	4094.4	4067.9	3992.6	3981.0	3958.6
12.5°	4037.9	4003.8	3901.6	3879.2	3837.5
15°	3969.8	3928.1	3799.8	3728.1	3690.5
17.5°	3890.4	3829.9	3671.3	3588.3	3527.8
20°	3799.8	3724.1	3535.3	3441.2	3357.8
22.5°	3701.7	3614.7	3395.5	3267.3	3210.8
25°	3603.5	3482.5	3233.2	3078.5	3021.6
27.5°	3486.5	3357.8	3082.1	2904.6	2817.6
30°	3361.8	3217.9	2915.8	2723.5	2621.3
32.5°	3240.9	3066.9	2757.5	2530.7	2436.1
35°	3104.9	2912.3	2580.0	2342.0	2258.6
37.5°	2972.7	2764.7	2413.7	2152.8	2058.6
40°	2832.9	2606.5	2239.8	1971.7	1873.5
42.5°	2689.4	2447.7	2066.3	1786.6	1692.3
45°	2538.3	2285.0	1888.8	1620.2	1529.6
47.5°	2394.9	2126.8	1718.8	1450.3	1367.4
50°	2236.1	1968.0	1552.5	1291.6	1212.6
52.5°	2081.0	1797.8	1393.8	1144.5	1072.8
55°	1930.0	1635.5	1227.5	1001.1	929.3
57.5°	1775.3	1473.1	1080.5	868.8	808.3
60°	1616.6	1314.4	925.3	733.0	672.5
62.5°	1461.9	1159.7	793.0	612.0	581.9
65°	1303.2	997.0	657.2	529.0	517.4
67.5°	1152.2	846.0	529.0	464.4	453.2
70°	993.4	698.9	438.0	400.3	385.2
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.9	430.4	302.2	275.7	272.1
77.5°	547.9	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	2.8	35.4	59.1	74.1	79.8
92.5°	74.1	62.2	71.0	77.0	79.8
95°	192.2	94.5	115.2	130.4	127.2
97.5°	346.2	103.7	150.8	159.9	162.7
100°	523.9	118.5	168.6	192.2	198.2
102.5°	719.0	713.4	174.6	207.0	216.1
105°	899.6	988.6	180.7	213.0	224.9
107.5°	1109.7	1183.6	186.6	218.9	230.9
110°	1311.1	1373.0	518.0	222.1	233.7



TEST NUMBER: P909319

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1500.6	1553.6	1503.4	227.7	236.8
115°	1701.5	1751.8	1825.9	455.8	242.9
117.5°	1876.2	1935.3	1985.9	1562.4	787.2
120°	2071.6	2115.9	2169.3	2204.8	1805.2
122.5°	2237.2	2284.6	2344.0	2361.6	2364.7
125°	2405.8	2444.5	2500.7	2521.4	2530.2
127.5°	2559.7	2601.2	2645.8	2675.3	2678.2
130°	2704.8	2752.3	2784.6	2817.3	2814.5
132.5°	2852.8	2891.4	2923.8	2950.5	2947.7
135°	2977.2	3024.6	3051.0	3080.9	3074.9
137.5°	3107.3	3142.7	3172.6	3202.1	3193.3
140°	3234.5	3258.3	3290.6	3317.4	3302.7
142.5°	3341.2	3362.0	3400.3	3423.8	3409.1
145°	3453.7	3450.6	3500.8	3521.6	3506.8
147.5°	3551.1	3542.3	3592.6	3607.3	3595.7
150°	3645.9	3625.2	3672.7	3690.3	3675.5
152.5°	3725.7	3702.2	3746.5	3764.4	3743.7
155°	3802.6	3776.3	3811.8	3829.4	3805.9
157.5°	3864.9	3841.3	3868.1	3888.8	3864.9
160°	3918.3	3900.4	3918.3	3935.8	3915.1
162.5°	3965.4	3947.9	3962.6	3983.3	3956.7
165°	4006.8	3989.3	3998.1	4018.9	3998.1
167.5°	4039.6	4021.6	4030.8	4051.5	4024.8
170°	4066.2	4048.3	4054.3	4075.0	4048.3
172.5°	4083.8	4066.2	4072.3	4093.0	4066.2
175°	4098.5	4077.8	4083.8	4104.6	4075.0
177.5°	4104.6	4083.8	4087.0	4107.7	4081.1
180°	4089.9	4089.9	4089.9	4089.9	4089.9



TEST NUMBER: P909319
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.73	12.49	12.76	13.53	14.92	7.69	8.46	8.72	9.49	10.88
	3H	13.40	14.08	14.44	15.12	16.53	8.87	9.55	9.91	10.59	12.00
	4H	14.00	14.65	15.05	15.69	17.11	9.31	9.96	10.36	11.00	12.42
	6H	14.41	15.01	15.48	16.06	17.49	9.62	10.22	10.68	11.27	12.69
	8H	14.54	15.10	15.60	16.17	17.59	9.71	10.27	10.77	11.34	12.76
	12H	14.59	15.13	15.67	16.19	17.64	9.74	10.28	10.82	11.34	12.79
4H	2H	11.74	12.39	12.80	13.43	14.84	8.27	8.92	9.33	9.97	11.38
	3H	13.55	14.09	14.62	15.17	16.59	9.61	10.15	10.68	11.22	12.65
	4H	14.24	14.73	15.31	15.80	17.25	10.15	10.64	11.22	11.71	13.16
	6H	14.75	15.17	15.83	16.26	17.70	10.56	10.98	11.64	12.07	13.51
	8H	14.92	15.31	16.00	16.39	17.85	10.68	11.08	11.76	12.16	13.62
	12H	15.01	15.37	16.11	16.46	17.92	10.74	11.10	11.84	12.19	13.66
8H	4H	14.20	14.60	15.28	15.68	17.14	10.42	10.82	11.50	11.90	13.36
	6H	14.76	15.09	15.86	16.21	17.66	10.93	11.26	12.03	12.38	13.83
	8H	14.97	15.26	16.08	16.36	17.84	11.12	11.40	12.23	12.51	13.98
	12H	15.11	15.36	16.22	16.46	17.97	11.23	11.48	12.34	12.58	14.09
12H	4H	14.15	14.51	15.25	15.60	17.06	10.42	10.78	11.52	11.87	13.34
	6H	14.73	15.02	15.85	16.13	17.60	10.98	11.26	12.09	12.37	13.84
	8H	14.95	15.20	16.06	16.30	17.81	11.18	11.43	12.29	12.53	14.05