

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918253

Luminaire Tested: DFN2DIP-TR4F0-050D120US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918253
REPORT IS A COMBINATION OF REPORTS P902036 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D120US930-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13150.7 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 133.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	29
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	20	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	20	18	17	15	13
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1338	1338	1338
5°	1341	1317	1326
10°	1327	1291	1282
15°	1309	1249	1216
20°	1285	1190	1134
25°	1260	1124	1055
30°	1227	1056	955
35°	1194	984	866
40°	1161	908	766
45°	1123	825	674
50°	1083	741	585
55°	1041	651	499
60°	993	556	410
65°	938	461	370
70°	871	371	334
75°	787	327	304
80°	665	274	263
85°	463	183	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1753 cd/sqm

TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	1.2
10°-20°	433.5	3.3
20°-30°	608.6	4.6
30°-40°	663.4	5.0
40°-50°	609.7	4.6
50°-60°	478.8	3.6
60°-70°	311.7	2.4
70°-80°	160.4	1.2
80°-90°	46.8	0.4
90°-100°	108.9	0.8
100°-110°	405.9	3.1
110°-120°	1076.4	8.2
120°-130°	1785.3	13.6
130°-140°	1896.5	14.4
140°-150°	1762.5	13.4
150°-160°	1417.0	10.8
160°-170°	913.1	6.9
170°-180°	314.3	2.4
0°-30°	1200.0	9.1
0°-40°	1863.4	14.2
0°-60°	2951.9	22.4
0°-90°	3470.8	26.4
90°-120°	1591.2	12.1
90°-150°	7035.5	53.5
90°-180°	9680.0	73.6
0°-180°	13150.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	2	29	48	60	64	12
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1374	1414	1474	368	196	1352
125°	1942	1974	2019	2036	2043	1732
135°	2404	2442	2463	2487	2482	1857
145°	2788	2786	2826	2843	2831	1744
155°	3070	3049	3077	3092	3073	1415
165°	3235	3221	3228	3245	3228	914
175°	3309	3292	3297	3314	3290	315
180°	3302	3302	3302	3302	3302	

TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.2	76.3	93.0	105.3	102.7
97.5°	279.5	83.7	121.7	129.1	131.3
100°	423.0	95.6	136.2	155.2	160.0
102.5°	580.5	575.9	141.0	167.1	174.5
105°	726.3	798.1	145.9	171.9	181.6
107.5°	895.9	955.5	150.7	176.8	186.4
110°	1058.5	1108.5	418.2	179.3	188.7

TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1211.5	1254.3	1213.7	183.8	191.2
115°	1373.7	1414.3	1474.1	367.9	196.1
117.5°	1514.7	1562.4	1603.3	1261.3	635.5
120°	1672.5	1708.2	1751.3	1780.0	1457.4
122.5°	1806.1	1844.4	1892.4	1906.6	1909.1
125°	1942.3	1973.5	2018.9	2035.6	2042.7
127.5°	2066.5	2100.0	2136.1	2159.9	2162.2
130°	2183.7	2222.0	2248.1	2274.5	2272.2
132.5°	2303.1	2334.4	2360.5	2382.1	2379.8
135°	2403.6	2441.9	2463.2	2487.3	2482.5
137.5°	2508.6	2537.2	2561.3	2585.1	2578.1
140°	2611.3	2630.6	2656.6	2678.3	2666.4
142.5°	2697.5	2714.3	2745.2	2764.2	2752.3
145°	2788.3	2785.8	2826.3	2843.1	2831.1
147.5°	2866.9	2859.8	2900.4	2912.3	2903.0
150°	2943.5	2926.8	2965.1	2979.3	2967.4
152.5°	3007.9	2988.9	3024.7	3039.1	3022.4
155°	3070.0	3048.7	3077.4	3091.6	3072.6
157.5°	3120.2	3101.2	3122.8	3139.6	3120.2
160°	3163.4	3148.9	3163.4	3177.5	3160.8
162.5°	3201.4	3187.2	3199.1	3215.9	3194.3
165°	3234.9	3220.7	3227.8	3244.6	3227.8
167.5°	3261.3	3246.8	3254.2	3270.9	3249.4
170°	3282.8	3268.4	3273.2	3289.9	3268.4
172.5°	3297.0	3282.8	3287.7	3304.4	3282.8
175°	3308.9	3292.2	3297.0	3313.8	3289.9
177.5°	3313.8	3297.0	3299.6	3316.3	3294.8
180°	3301.9	3301.9	3301.9	3301.9	3301.9

TEST NUMBER: P918253

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.40	6.07	6.54	7.20	8.77	1.37	2.04	2.52	3.17	4.75
	3H	7.07	7.66	8.21	8.80	10.39	2.55	3.15	3.70	4.29	5.88
	4H	7.67	8.23	8.82	9.37	10.97	2.99	3.56	4.15	4.70	6.29
	6H	8.08	8.60	9.24	9.74	11.35	3.31	3.83	4.47	4.97	6.57
	8H	8.20	8.70	9.37	9.85	11.45	3.39	3.89	4.56	5.04	6.64
	12H	8.26	8.73	9.43	9.88	11.50	3.43	3.90	4.60	5.05	6.67
4H	2H	5.40	5.97	6.56	7.10	8.70	1.95	2.52	3.11	3.65	5.25
	3H	7.21	7.69	8.38	8.85	10.45	3.29	3.76	4.46	4.92	6.53
	4H	7.90	8.33	9.07	9.48	11.11	3.83	4.26	5.00	5.41	7.04
	6H	8.40	8.78	9.58	9.95	11.57	4.24	4.61	5.42	5.78	7.40
	8H	8.58	8.92	9.75	10.09	11.72	4.37	4.71	5.54	5.88	7.51
	12H	8.66	8.98	9.86	10.15	11.79	4.42	4.74	5.61	5.91	7.55
8H	4H	7.85	8.20	9.03	9.37	11.00	4.10	4.44	5.27	5.61	7.24
	6H	8.41	8.70	9.61	9.91	11.54	4.61	4.89	5.80	6.10	7.73
	8H	8.63	8.88	9.83	10.06	11.71	4.80	5.05	6.00	6.23	7.88
	12H	8.76	8.98	9.97	10.16	11.84	4.91	5.13	6.12	6.31	7.99
12H	4H	7.80	8.11	8.99	9.29	10.93	4.09	4.41	5.28	5.58	7.22
	6H	8.39	8.64	9.59	9.82	11.47	4.66	4.91	5.86	6.09	7.74
	8H	8.60	8.82	9.81	10.00	11.69	4.86	5.08	6.06	6.26	7.94

END OF REPORT