

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912021

Luminaire Tested: DFN2DIP-SQ3F0-100D060US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912021
REPORT IS A COMBINATION OF REPORTS P901429 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D060US850-FLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17566.5 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 143.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912021
CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912021

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63		
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53		
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48	44		
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	37		
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32		
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28		
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25		
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24	22		
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	19		
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18		
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4944	4944	4944
5°	4949	4872	4907
10°	4906	4803	4839
15°	4831	4721	4733
20°	4730	4608	4625
25°	4630	4473	4501
30°	4505	4348	4343
35°	4386	4200	4176
40°	4241	4051	4017
45°	4096	3901	3855
50°	3937	3744	3667
55°	3770	3562	3493
60°	3582	3346	3294
65°	3375	3123	3060
70°	3113	2850	2807
75°	2750	2522	2571
80°	2311	2104	2125
85°	1627	1394	1391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4096 cd/sqm



TEST NUMBER: P912021

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	2.3
10°-20°	1142.7	6.5
20°-30°	1679.4	9.6
30°-40°	1950.5	11.1
40°-50°	1948.1	11.1
50°-60°	1698.7	9.7
60°-70°	1255.7	7.1
70°-80°	710.4	4.0
80°-90°	191.5	1.1
90°-100°	74.1	0.4
100°-110°	276.0	1.6
110°-120°	732.1	4.2
120°-130°	1214.2	6.9
130°-140°	1289.8	7.3
140°-150°	1198.7	6.8
150°-160°	963.8	5.5
160°-170°	621.0	3.5
170°-180°	213.7	1.2
0°-30°	3228.3	18.4
0°-40°	5178.7	29.5
0°-60°	8825.5	50.2
0°-90°	10983.1	62.5
90°-120°	1082.2	6.2
90°-150°	4785.0	27.2
90°-180°	6583.0	37.5
0°-180°	17566.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4315	4315	4315	4315	4315	
5°	4315	4299	4253	4286	4278	410
15°	4108	4083	4029	4046	4025	1157
25°	3718	3685	3614	3622	3614	1711
35°	3208	3166	3100	3075	3054	2003
45°	2610	2581	2518	2473	2456	2014
55°	1975	1950	1900	1851	1830	1766
65°	1332	1307	1266	1228	1208	1317
75°	697	689	668	643	652	744
85°	170	166	162	149	145	190
90°	2	20	32	41	44	16
95°	106	52	63	72	70	125
105°	494	543	99	117	124	528
115°	934	962	1003	250	133	920
125°	1321	1342	1373	1384	1389	1178
135°	1635	1661	1675	1692	1688	1263
145°	1896	1895	1922	1934	1926	1186
155°	2088	2074	2093	2103	2090	962
165°	2200	2190	2195	2207	2195	622
175°	2250	2239	2242	2254	2238	214
180°	2246	2246	2246	2246	2246	



TEST NUMBER: P912021

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4315.2	4315.2	4315.2	4315.2	4315.2
2.5°	4340.3	4319.6	4273.8	4315.2	4307.2
5°	4315.2	4298.9	4253.1	4286.2	4278.2
7.5°	4286.2	4261.4	4215.6	4249.1	4240.8
10°	4240.8	4211.8	4162.0	4195.0	4182.7
12.5°	4178.3	4153.6	4103.9	4124.6	4116.2
15°	4107.8	4083.2	4029.0	4045.7	4025.1
17.5°	4020.7	3996.1	3941.8	3962.6	3941.8
20°	3925.1	3900.5	3842.4	3854.7	3838.4
22.5°	3830.0	3792.7	3738.4	3738.4	3730.1
25°	3717.8	3684.8	3614.3	3622.2	3614.3
27.5°	3593.2	3564.1	3510.4	3498.1	3477.4
30°	3469.1	3435.6	3373.5	3361.2	3344.4
32.5°	3336.1	3311.5	3244.9	3219.9	3203.1
35°	3207.6	3166.2	3099.7	3074.6	3053.9
37.5°	3062.3	3024.8	2958.4	2929.3	2908.6
40°	2913.0	2879.5	2813.1	2776.2	2759.4
42.5°	2767.7	2734.2	2668.3	2626.4	2601.8
45°	2610.1	2581.1	2518.5	2473.2	2456.5
47.5°	2456.5	2427.5	2361.0	2315.1	2290.5
50°	2294.5	2273.8	2215.7	2157.6	2136.9
52.5°	2136.9	2107.9	2054.1	2008.4	1979.3
55°	1975.4	1950.3	1900.5	1850.7	1830.1
57.5°	1813.3	1792.6	1738.5	1688.8	1672.0
60°	1651.3	1635.0	1576.9	1531.1	1518.8
62.5°	1493.7	1464.7	1423.3	1381.9	1365.2
65°	1332.1	1307.1	1265.7	1228.2	1207.6
67.5°	1166.2	1145.0	1108.1	1079.1	1062.3
70°	1012.5	995.8	958.4	929.3	913.0
72.5°	854.9	838.2	817.6	788.5	776.1
75°	696.9	689.0	667.8	643.2	651.5
77.5°	556.1	539.3	530.9	518.6	506.3
80°	415.1	410.8	402.3	390.0	381.7
82.5°	282.2	282.2	278.2	261.5	261.5
85°	169.9	166.0	162.0	149.3	145.3
87.5°	74.9	66.4	58.1	45.8	41.4
90°	1.6	19.5	32.4	40.7	43.8
92.5°	40.7	34.2	38.9	42.3	43.8
95°	105.6	51.9	63.3	71.6	69.9
97.5°	190.1	56.9	82.7	87.8	89.4
100°	287.7	65.0	92.6	105.6	108.8
102.5°	394.8	391.7	95.9	113.7	118.7
105°	493.9	542.7	99.1	116.9	123.5
107.5°	609.4	649.9	102.5	120.2	126.8
110°	720.0	753.9	284.5	122.0	128.3



TEST NUMBER: P912021

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	823.9	853.0	825.4	125.0	130.1
115°	934.3	961.9	1002.6	250.3	133.3
117.5°	1030.2	1062.6	1090.4	857.9	432.2
120°	1137.5	1161.8	1191.2	1210.6	991.2
122.5°	1228.3	1254.4	1287.0	1296.6	1298.4
125°	1321.0	1342.2	1373.1	1384.5	1389.2
127.5°	1405.5	1428.3	1452.8	1469.0	1470.5
130°	1485.2	1511.2	1529.0	1546.9	1545.4
132.5°	1566.5	1587.6	1605.4	1620.0	1618.5
135°	1634.8	1660.8	1675.3	1691.7	1688.3
137.5°	1706.1	1725.6	1742.0	1758.2	1753.4
140°	1776.0	1789.1	1806.9	1821.5	1813.4
142.5°	1834.6	1846.0	1867.1	1880.0	1871.9
145°	1896.4	1894.6	1922.2	1933.7	1925.6
147.5°	1949.8	1945.0	1972.6	1980.7	1974.4
150°	2002.0	1990.5	2016.6	2026.3	2018.2
152.5°	2045.8	2032.8	2057.1	2067.0	2055.5
155°	2088.0	2073.5	2093.0	2102.7	2089.7
157.5°	2122.2	2109.2	2123.8	2135.3	2122.2
160°	2151.5	2141.6	2151.5	2161.1	2149.8
162.5°	2177.3	2167.7	2175.7	2187.2	2172.5
165°	2200.1	2190.5	2195.3	2206.7	2195.3
167.5°	2218.0	2208.2	2213.2	2224.7	2209.9
170°	2232.7	2222.9	2226.2	2237.5	2222.9
172.5°	2242.4	2232.7	2236.0	2247.4	2232.7
175°	2250.5	2239.1	2242.4	2253.7	2237.5
177.5°	2253.7	2242.4	2244.1	2255.5	2240.8
180°	2245.6	2245.6	2245.6	2245.6	2245.6



TEST NUMBER: P912021
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.87	14.86	14.71	15.72	16.80	13.43	14.41	14.27	15.28	16.36
	3H	15.54	16.42	16.39	17.30	18.40	15.05	15.93	15.90	16.81	17.91
	4H	16.13	16.96	17.00	17.84	18.96	15.63	16.47	16.50	17.35	18.47
	6H	16.53	17.30	17.41	18.19	19.32	16.03	16.80	16.91	17.69	18.82
	8H	16.64	17.37	17.53	18.28	19.41	16.14	16.87	17.03	17.78	18.91
	12H	16.69	17.39	17.58	18.29	19.44	16.18	16.88	17.08	17.78	18.93
4H	2H	14.34	15.18	15.22	16.06	17.18	13.99	14.83	14.86	15.71	16.82
	3H	16.22	16.91	17.10	17.83	18.96	15.81	16.51	16.69	17.42	18.55
	4H	16.93	17.57	17.83	18.48	19.64	16.51	17.14	17.41	18.05	19.21
	6H	17.45	18.00	18.36	18.93	20.09	17.02	17.57	17.93	18.50	19.66
	8H	17.60	18.11	18.52	19.04	20.21	17.16	17.68	18.08	18.60	19.78
	12H	17.68	18.14	18.61	19.09	20.27	17.23	17.69	18.16	18.64	19.82
8H	4H	17.13	17.65	18.05	18.57	19.75	16.76	17.27	17.67	18.20	19.37
	6H	17.76	18.19	18.71	19.16	20.33	17.38	17.81	18.32	18.77	19.95
	8H	17.98	18.36	18.94	19.32	20.51	17.59	17.97	18.54	18.93	20.12
	12H	18.12	18.45	19.07	19.40	20.64	17.71	18.04	18.66	18.99	20.23
12H	4H	17.12	17.59	18.06	18.53	19.71	16.76	17.22	17.69	18.16	19.34
	6H	17.79	18.17	18.75	19.13	20.32	17.42	17.80	18.37	18.76	19.95
	8H	18.04	18.37	18.99	19.32	20.56	17.66	17.99	18.61	18.94	20.18