

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920005

Luminaire Tested: DFN2DIP-SQ3F0-040D100US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920005
REPORT IS A COMBINATION OF REPORTS P901489 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D100US935-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11933.4 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 109.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1535	1535	1535
5°	1537	1513	1524
10°	1524	1492	1503
15°	1500	1466	1470
20°	1469	1431	1437
25°	1438	1389	1398
30°	1399	1350	1349
35°	1362	1304	1297
40°	1317	1258	1248
45°	1272	1211	1197
50°	1223	1163	1139
55°	1171	1106	1085
60°	1112	1039	1023
65°	1048	970	950
70°	967	885	872
75°	854	783	798
80°	718	653	660
85°	506	433	432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1991 cd/sqm

TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	1.1
10°-20°	354.9	3.0
20°-30°	521.5	4.4
30°-40°	605.7	5.1
40°-50°	605.0	5.1
50°-60°	527.5	4.4
60°-70°	389.9	3.3
70°-80°	220.6	1.8
80°-90°	63.3	0.5
90°-100°	95.8	0.8
100°-110°	357.2	3.0
110°-120°	947.3	7.9
120°-130°	1571.2	13.2
130°-140°	1669.0	14.0
140°-150°	1551.1	13.0
150°-160°	1247.1	10.5
160°-170°	803.6	6.7
170°-180°	276.6	2.3
0°-30°	1002.5	8.4
0°-40°	1608.3	13.5
0°-60°	2740.7	23.0
0°-90°	3414.6	28.6
90°-120°	1400.3	11.7
90°-150°	6191.6	51.9
90°-180°	8519.0	71.4
0°-180°	11933.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	2	25	42	53	57	11
95°	137	67	82	93	90	162
105°	639	702	128	151	160	683
115°	1209	1245	1297	324	172	1190
125°	1709	1737	1777	1792	1798	1524
135°	2115	2149	2168	2189	2185	1634
145°	2454	2452	2487	2502	2492	1535
155°	2702	2683	2708	2721	2704	1245
165°	2847	2834	2841	2855	2841	804
175°	2912	2897	2902	2916	2895	277
180°	2906	2906	2906	2906	2906	

TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	2.0	25.2	41.9	52.7	56.7
92.5°	52.7	44.2	50.5	54.7	56.7
95°	136.6	67.2	81.9	92.6	90.4
97.5°	245.9	73.6	107.1	113.6	115.6
100°	372.3	84.1	119.9	136.6	140.9
102.5°	510.8	506.9	124.1	147.1	153.5
105°	639.2	702.3	128.4	151.3	159.8
107.5°	788.5	840.9	132.6	155.6	164.0
110°	931.5	975.5	368.0	157.8	166.0

TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1066.1	1103.8	1068.2	161.8	168.3
115°	1208.9	1244.7	1297.4	323.8	172.5
117.5°	1333.0	1375.0	1410.9	1110.1	559.3
120°	1471.9	1503.3	1541.3	1566.5	1282.6
122.5°	1589.5	1623.2	1665.3	1677.8	1680.1
125°	1709.3	1736.8	1776.8	1791.5	1797.7
127.5°	1818.7	1848.1	1879.8	1900.8	1902.8
130°	1921.7	1955.5	1978.5	2001.6	1999.7
132.5°	2026.9	2054.3	2077.3	2096.3	2094.3
135°	2115.3	2149.0	2167.7	2188.9	2184.7
137.5°	2207.7	2232.9	2254.1	2275.1	2268.8
140°	2298.0	2315.1	2338.0	2357.0	2346.5
142.5°	2373.9	2388.7	2415.9	2432.6	2422.2
145°	2453.8	2451.6	2487.3	2502.1	2491.6
147.5°	2523.0	2516.8	2552.4	2562.9	2554.8
150°	2590.4	2575.7	2609.4	2621.9	2611.4
152.5°	2647.1	2630.3	2661.9	2674.5	2659.8
155°	2701.8	2683.0	2708.3	2720.8	2704.0
157.5°	2746.0	2729.3	2748.2	2762.9	2746.0
160°	2784.0	2771.2	2784.0	2796.4	2781.7
162.5°	2817.4	2804.9	2815.4	2830.1	2811.2
165°	2846.8	2834.3	2840.6	2855.3	2840.6
167.5°	2870.1	2857.3	2863.9	2878.6	2859.5
170°	2889.0	2876.3	2880.6	2895.3	2876.3
172.5°	2901.5	2889.0	2893.3	2908.0	2889.0
175°	2912.0	2897.3	2901.5	2916.3	2895.3
177.5°	2916.3	2901.5	2903.8	2918.5	2899.5
180°	2905.8	2905.8	2905.8	2905.8	2905.8

TEST NUMBER: P920005

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.32	7.02	7.44	8.13	9.68	5.88	6.57	7.00	7.69	9.24
	3H	7.96	8.59	9.09	9.71	11.27	7.47	8.10	8.60	9.22	10.78
	4H	8.54	9.13	9.68	10.26	11.83	8.05	8.64	9.19	9.76	11.33
	6H	8.93	9.47	10.08	10.60	12.18	8.43	8.97	9.58	10.10	11.68
	8H	9.03	9.55	10.18	10.69	12.26	8.53	9.04	9.68	10.19	11.76
	12H	9.07	9.56	10.22	10.70	12.29	8.56	9.05	9.71	10.19	11.78
4H	2H	6.76	7.35	7.90	8.47	10.04	6.40	7.00	7.55	8.12	9.69
	3H	8.60	9.10	9.76	10.25	11.83	8.20	8.69	9.35	9.84	11.42
	4H	9.31	9.76	10.46	10.90	12.50	8.88	9.34	10.04	10.48	12.08
	6H	9.81	10.20	10.97	11.36	12.95	9.38	9.77	10.54	10.93	12.52
	8H	9.95	10.32	11.11	11.47	13.08	9.51	9.88	10.67	11.03	12.64
	12H	10.01	10.34	11.19	11.51	13.12	9.57	9.90	10.74	11.06	12.67
8H	4H	9.49	9.85	10.65	11.00	12.61	9.11	9.47	10.27	10.63	12.23
	6H	10.10	10.40	11.28	11.60	13.20	9.72	10.02	10.90	11.22	12.82
	8H	10.32	10.58	11.51	11.75	13.38	9.93	10.19	11.11	11.36	12.99
	12H	10.44	10.67	11.63	11.84	13.50	10.03	10.26	11.22	11.43	13.09
12H	4H	9.46	9.79	10.64	10.96	12.57	9.09	9.42	10.27	10.59	12.20
	6H	10.13	10.39	11.32	11.57	13.19	9.76	10.02	10.94	11.19	12.82
	8H	10.36	10.59	11.55	11.76	13.42	9.98	10.21	11.17	11.38	13.04

END OF REPORT