

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332346-927

Luminaire Tested: **S123RDIP-S1000D805U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332346-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5190.1 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot



TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	55	54
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46
3	84	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35
5	70	59	51	45	66	55	48	43	49	43	39	42	38	34	36	33	30
6	65	53	45	39	61	50	43	37	44	38	34	38	34	30	33	30	27
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458

TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.4
10°-20°	347.3	6.7
20°-30°	500.2	9.6
30°-40°	563.4	10.9
40°-50°	539.0	10.4
50°-60°	441.4	8.5
60°-70°	297.8	5.7
70°-80°	149.8	2.9
80°-90°	42.0	0.8
90°-100°	51.4	1.0
100°-110°	153.7	3.0
110°-120°	261.5	5.0
120°-130°	343.9	6.6
130°-140°	386.6	7.4
140°-150°	380.0	7.3
150°-160°	319.9	6.2
160°-170°	212.9	4.1
170°-180°	74.6	1.4
0°-30°	972.3	18.7
0°-40°	1535.7	29.6
0°-60°	2516.0	48.5
0°-90°	3005.6	57.9
90°-120°	466.6	9.0
90°-150°	1577.1	30.4
90°-180°	2185.0	42.1
0°-180°	5190.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	7	15	17	19	5
95°	36	41	46	48	48	41
105°	139	141	146	146	147	149
115°	263	265	264	264	264	260
125°	385	387	386	383	381	343
135°	500	503	503	500	499	385
145°	606	608	609	609	606	379
155°	694	694	695	697	693	319
165°	756	754	754	758	754	213
175°	787	784	784	787	784	75
180°	788	788	788	788	788	

TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	19.0	17.2	15.3	13.5	12.8	13.2	13.5	13.9	14.2	14.1
90°	0.6	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4
92.5°	15.0	15.9	16.9	17.8	18.7	19.7	20.8	21.8	22.7	23.8	24.2
95°	36.5	37.5	38.5	39.5	40.4	41.4	42.5	43.6	44.8	45.9	46.4
97.5°	64.9	65.6	66.3	67.0	67.8	68.5	69.3	70.1	70.9	71.7	72.3
100°	84.2	85.1	85.9	86.7	87.5	88.3	89.0	89.7	90.4	91.0	91.5
102.5°	106.5	107.0	107.5	108.1	108.5	109.2	110.1	111.1	111.9	112.9	113.3
105°	139.3	139.7	139.9	140.2	140.5	141.2	142.4	143.7	145.0	146.2	146.2
107.5°	177.5	177.7	177.8	178.0	178.2	178.5	179.0	179.5	180.0	180.5	180.9
110°	201.3	201.5	201.8	202.1	202.4	202.6	203.0	203.2	203.5	203.7	204.3

TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.2	226.4	226.6	226.7	226.8	226.9	227.0	227.0	227.0	227.8
115°	263.2	263.6	264.0	264.4	264.9	265.0	264.7	264.4	264.1	263.9	264.0
117.5°	300.6	301.0	301.2	301.4	301.7	301.7	301.3	301.0	300.6	300.2	300.2
120°	323.9	324.7	325.6	326.4	327.3	327.3	326.6	325.9	325.3	324.6	324.4
122.5°	348.2	348.8	349.4	350.0	350.6	350.8	350.4	350.1	349.7	349.4	349.0
125°	385.2	385.6	386.0	386.5	386.9	387.0	386.7	386.4	386.1	385.9	385.3
127.5°	419.5	420.3	421.2	422.1	422.9	423.3	422.9	422.6	422.3	422.0	421.3
130°	442.2	443.3	444.4	445.5	446.6	446.9	446.6	446.2	445.8	445.3	444.7
132.5°	465.0	466.1	467.2	468.3	469.4	469.8	469.5	469.2	468.9	468.6	467.9
135°	499.8	500.7	501.5	502.3	503.1	503.5	503.4	503.2	503.0	503.0	502.4
137.5°	532.0	532.7	533.4	534.1	534.8	535.3	535.7	536.0	536.4	536.7	536.1
140°	554.3	555.0	555.7	556.4	557.1	557.5	557.6	557.8	557.9	558.0	557.9
142.5°	574.6	575.4	576.0	576.7	577.4	577.9	578.1	578.4	578.6	578.8	578.7
145°	606.3	606.7	606.9	607.2	607.4	607.8	608.2	608.6	609.0	609.4	609.3
147.5°	634.1	634.6	635.1	635.6	636.1	636.5	636.9	637.3	637.7	638.1	638.1
150°	653.4	653.7	653.9	654.3	654.5	654.8	655.1	655.4	655.6	655.9	655.9
152.5°	669.3	669.6	670.0	670.4	670.8	671.1	671.3	671.5	671.6	671.8	672.0
155°	694.3	694.3	694.3	694.3	694.3	694.3	694.5	694.7	694.8	694.9	695.5
157.5°	715.6	715.4	715.3	715.1	714.9	714.9	715.0	715.2	715.3	715.3	716.0
160°	729.0	728.7	728.4	728.2	727.9	727.8	727.8	727.8	727.8	727.8	728.4
162.5°	740.8	740.5	740.1	739.7	739.3	739.2	739.3	739.4	739.5	739.7	740.3
165°	756.2	755.8	755.4	755.0	754.6	754.4	754.4	754.4	754.4	754.4	755.2
167.5°	768.5	767.9	767.4	766.8	766.3	766.1	766.2	766.3	766.4	766.5	767.4
170°	775.5	774.9	774.4	773.8	773.2	772.9	772.9	772.9	772.9	772.9	774.0
172.5°	780.9	780.4	779.8	779.3	778.7	778.4	778.4	778.4	778.4	778.4	779.3
175°	786.6	786.0	785.5	785.0	784.4	784.1	784.1	784.1	784.1	784.1	785.0
177.5°	788.9	788.5	788.1	787.6	787.2	787.0	787.0	787.0	787.0	787.0	787.6
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5

TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	14.0	13.9	13.9	13.8	13.6	13.5	13.3	13.2
90°	16.0	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	24.6	25.1	25.5	25.7	25.5	25.3	25.2	25.0
95°	46.9	47.5	48.0	48.3	48.3	48.3	48.3	48.3
97.5°	73.0	73.6	74.2	74.5	74.5	74.5	74.4	74.3
100°	91.9	92.3	92.7	93.1	93.3	93.6	93.9	94.1
102.5°	113.7	114.1	114.5	114.7	114.6	114.5	114.5	114.5
105°	146.2	146.2	146.2	146.3	146.6	146.9	147.1	147.4
107.5°	181.3	181.8	182.3	182.4	182.2	182.0	181.9	181.7
110°	204.9	205.4	206.0	206.1	205.8	205.6	205.3	205.0

TEST NUMBER: P332346-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	229.0	229.7	230.0	230.0	229.9	229.8	229.8
115°	264.1	264.3	264.4	264.4	264.3	264.1	264.0	263.9
117.5°	300.2	300.2	300.2	299.9	299.6	299.2	298.8	298.4
120°	324.2	324.2	324.0	323.8	323.5	323.2	323.0	322.7
122.5°	348.6	348.2	347.9	347.5	347.1	346.7	346.3	345.9
125°	384.8	384.2	383.7	383.1	382.5	382.0	381.4	380.9
127.5°	420.5	419.7	419.0	418.3	417.6	417.0	416.4	415.7
130°	444.3	443.7	443.1	442.4	441.4	440.5	439.5	438.5
132.5°	467.3	466.6	466.0	465.2	464.5	463.7	463.0	462.3
135°	501.8	501.3	500.7	500.3	500.0	499.8	499.5	499.2
137.5°	535.6	535.0	534.4	533.9	533.4	532.8	532.3	531.8
140°	557.8	557.6	557.5	557.0	556.0	555.0	554.1	553.1
142.5°	578.6	578.5	578.3	577.9	577.1	576.4	575.6	574.9
145°	609.2	609.0	608.9	608.6	608.0	607.4	606.9	606.3
147.5°	638.1	638.1	638.1	637.6	636.8	636.0	635.2	634.4
150°	655.9	655.9	655.9	655.5	654.7	653.9	653.0	652.2
152.5°	672.2	672.4	672.6	672.4	671.7	671.0	670.3	669.6
155°	696.0	696.6	697.1	696.9	695.9	695.0	694.0	693.1
157.5°	716.5	717.1	717.6	717.6	716.8	716.1	715.3	714.5
160°	729.1	729.8	730.5	730.6	730.0	729.4	728.9	728.3
162.5°	741.0	741.7	742.4	742.3	741.4	740.5	739.7	738.8
165°	756.1	756.9	757.7	757.6	756.7	755.7	754.7	753.8
167.5°	768.3	769.1	769.9	769.9	769.1	768.3	767.4	766.5
170°	774.9	775.9	776.8	776.8	775.9	774.9	774.0	772.9
172.5°	780.1	781.0	781.8	781.8	780.8	779.8	778.9	777.9
175°	785.8	786.6	787.4	787.3	786.4	785.4	784.4	783.5
177.5°	788.3	788.9	789.6	789.6	788.8	788.0	787.3	786.5
180°	788.5	788.5	788.5	788.5	788.5	788.5	788.5	788.5

(END OF REPORT)