

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920275

Luminaire Tested: DFN2DIP-SQ3F0-120D050US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920275
REPORT IS A COMBINATION OF REPORTS P901416 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D050US935-RLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13044.1 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 162.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	93	89	86	83	80	78	73	71	70	65	63	62
2	94	86	80	75	88	82	77	72	73	69	66	65	62	59	58	55	53
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46
4	79	68	61	55	74	65	58	52	58	53	48	52	48	44	47	43	40
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	42	39	36
6	67	55	47	42	63	53	45	40	48	42	37	43	38	34	39	35	32
7	63	50	42	37	59	48	41	36	44	38	33	39	35	31	36	32	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	34	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4893	4893	4893
5°	4898	4812	4844
10°	4846	4714	4685
15°	4776	4555	4440
20°	4685	4338	4140
25°	4591	4094	3850
30°	4467	3845	3483
35°	4344	3577	3160
40°	4220	3300	2791
45°	4075	2993	2456
50°	3925	2684	2129
55°	3769	2354	1815
60°	3588	2009	1492
65°	3378	1659	1341
70°	3125	1332	1211
75°	2806	1168	1099
80°	2345	969	947
85°	1591	632	703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4075 cd/sqm

TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.2	3.1
10°-20°	1098.7	8.4
20°-30°	1542.5	11.8
30°-40°	1681.4	12.9
40°-50°	1545.4	11.8
50°-60°	1213.7	9.3
60°-70°	790.0	6.1
70°-80°	406.7	3.1
80°-90°	106.4	0.8
90°-100°	47.9	0.4
100°-110°	178.6	1.4
110°-120°	473.7	3.6
120°-130°	785.6	6.0
130°-140°	834.5	6.4
140°-150°	775.6	5.9
150°-160°	623.5	4.8
160°-170°	401.8	3.1
170°-180°	138.3	1.1
0°-30°	3041.3	23.3
0°-40°	4722.7	36.2
0°-60°	7481.7	57.4
0°-90°	8784.7	67.3
90°-120°	700.2	5.4
90°-150°	3095.8	23.7
90°-180°	4259.0	32.7
0°-180°	13044.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4270	4270	4270	4270	4270	
5°	4270	4251	4200	4235	4224	405
15°	4062	4019	3888	3814	3776	1144
25°	3687	3563	3308	3150	3091	1696
35°	3177	2980	2640	2396	2311	1988
45°	2597	2338	1932	1658	1565	2006
55°	1975	1673	1256	1024	951	1764
65°	1333	1020	672	541	529	1322
75°	711	440	309	282	278	752
85°	166	85	73	73	73	191
90°	1	13	21	26	28	12
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4270.2	4270.2	4270.2	4270.2	4270.2
2.5°	4289.5	4270.2	4227.6	4266.5	4258.7
5°	4270.2	4250.9	4200.5	4235.3	4223.9
7.5°	4235.3	4212.3	4158.3	4173.4	4154.1
10°	4189.0	4162.0	4084.8	4073.0	4050.0
12.5°	4131.2	4096.4	3991.8	3968.9	3926.2
15°	4061.5	4018.9	3887.7	3814.2	3775.7
17.5°	3980.3	3918.4	3756.0	3671.2	3609.3
20°	3887.7	3810.2	3617.1	3520.7	3435.4
22.5°	3787.2	3698.2	3474.0	3342.7	3285.0
25°	3686.8	3562.9	3307.9	3149.6	3091.4
27.5°	3567.0	3435.4	3153.3	2971.7	2882.7
30°	3439.5	3292.4	2983.2	2786.4	2681.8
32.5°	3315.7	3137.7	2821.2	2589.2	2492.4
35°	3176.7	2979.5	2639.6	2396.1	2310.7
37.5°	3041.4	2828.6	2469.4	2202.5	2106.2
40°	2898.3	2666.7	2291.5	2017.2	1916.8
42.5°	2751.5	2504.3	2114.0	1827.8	1731.5
45°	2596.9	2337.9	1932.3	1657.7	1564.9
47.5°	2450.1	2175.9	1758.5	1483.8	1398.9
50°	2287.8	2013.5	1588.4	1321.5	1240.7
52.5°	2129.2	1839.3	1426.0	1171.0	1097.6
55°	1974.6	1673.3	1255.9	1024.2	950.8
57.5°	1816.3	1507.2	1105.3	888.9	827.0
60°	1654.0	1344.8	946.7	749.9	688.0
62.5°	1495.7	1186.5	811.4	626.1	595.3
65°	1333.3	1020.1	672.4	541.2	529.3
67.5°	1178.8	865.5	541.2	475.2	463.7
70°	1016.4	715.1	448.1	409.6	394.0
72.5°	861.9	575.7	374.7	344.0	336.2
75°	710.9	440.3	309.2	282.1	278.4
77.5°	560.5	312.8	243.6	228.0	220.2
80°	421.1	224.3	185.3	170.1	170.1
82.5°	293.6	150.8	127.5	119.7	119.7
85°	166.1	84.9	73.4	73.4	73.4
87.5°	61.9	30.7	30.7	27.0	27.0
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P920275

CATALOG NUMBER: DFN2DIP-SQ3F0-120D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.11	15.11	14.91	15.93	16.93	10.07	11.07	10.87	11.89	12.89
	3H	15.80	16.69	16.61	17.52	18.55	11.27	12.16	12.08	12.99	14.02
	4H	16.41	17.25	17.24	18.09	19.13	11.72	12.56	12.55	13.40	14.44
	6H	16.84	17.61	17.68	18.45	19.51	12.05	12.82	12.89	13.66	14.72
	8H	16.97	17.70	17.82	18.56	19.62	12.14	12.87	12.99	13.73	14.79
	12H	17.03	17.73	17.89	18.59	19.67	12.18	12.88	13.04	13.74	14.82
4H	2H	14.15	14.99	14.99	15.82	16.87	10.69	11.53	11.52	12.36	13.40
	3H	15.99	16.69	16.84	17.55	18.61	12.05	12.74	12.89	13.61	14.67
	4H	16.68	17.32	17.54	18.18	19.27	12.59	13.23	13.45	14.09	15.18
	6H	17.20	17.75	18.08	18.64	19.73	13.02	13.56	13.89	14.45	15.54
	8H	17.38	17.89	18.26	18.77	19.88	13.14	13.65	14.02	14.54	15.64
	12H	17.48	17.94	18.38	18.84	19.95	13.21	13.67	14.11	14.58	15.68
8H	4H	16.66	17.17	17.54	18.06	19.16	12.88	13.39	13.76	14.28	15.38
	6H	17.23	17.65	18.13	18.58	19.68	13.40	13.82	14.30	14.75	15.85
	8H	17.44	17.82	18.36	18.74	19.86	13.59	13.96	14.50	14.88	16.00
	12H	17.59	17.91	18.50	18.83	20.00	13.71	14.04	14.62	14.95	16.12
12H	4H	16.62	17.08	17.52	17.98	19.09	12.90	13.35	13.79	14.26	15.37
	6H	17.20	17.58	18.12	18.50	19.62	13.45	13.82	14.36	14.74	15.86
	8H	17.43	17.76	18.35	18.67	19.84	13.66	13.99	14.58	14.90	16.07