

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907651

Luminaire Tested: DFN2DIP-4P3F0-030D020US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907651
REPORT IS A COMBINATION OF REPORTS P900551 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US840-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4998.9 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1343	1343	1343
5°	1345	1324	1333
10°	1333	1305	1315
15°	1313	1283	1286
20°	1285	1252	1257
25°	1258	1215	1223
30°	1224	1181	1180
35°	1192	1141	1135
40°	1152	1101	1092
45°	1113	1060	1047
50°	1070	1017	996
55°	1025	968	949
60°	973	909	895
65°	918	849	832
70°	846	775	763
75°	748	686	699
80°	628	572	578
85°	443	379	378

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1113 cd/sqm

TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	2.2
10°-20°	312.2	6.2
20°-30°	458.8	9.2
30°-40°	532.8	10.7
40°-50°	532.2	10.6
50°-60°	464.1	9.3
60°-70°	343.1	6.9
70°-80°	194.1	3.9
80°-90°	52.4	1.0
90°-100°	22.5	0.4
100°-110°	83.8	1.7
110°-120°	222.2	4.4
120°-130°	368.6	7.4
130°-140°	391.5	7.8
140°-150°	363.9	7.3
150°-160°	292.5	5.9
160°-170°	188.5	3.8
170°-180°	64.9	1.3
0°-30°	881.9	17.6
0°-40°	1414.7	28.3
0°-60°	2411.0	48.2
0°-90°	3000.5	60.0
90°-120°	328.5	6.6
90°-150°	1452.4	29.1
90°-180°	1998.0	40.0
0°-180°	4998.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	0	6	10	12	13	5
95°	32	16	19	22	21	38
105°	150	165	30	35	38	160
115°	284	292	304	76	40	279
125°	401	407	417	420	422	358
135°	496	504	508	514	512	383
145°	576	575	584	587	584	360
155°	634	629	635	638	634	292
165°	668	665	666	670	666	189
175°	683	680	681	684	679	65
180°	682	682	682	682	682	

TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	0.5	6.0	9.8	12.3	13.3
92.5°	12.3	10.4	11.8	12.8	13.3
95°	32.0	15.8	19.2	21.7	21.2
97.5°	57.7	17.3	25.1	26.7	27.2
100°	87.4	19.7	28.1	32.0	33.0
102.5°	119.9	118.9	29.1	34.5	36.1
105°	150.0	164.7	30.1	35.4	37.5
107.5°	185.0	197.2	31.1	36.5	38.5
110°	218.5	228.8	86.3	37.1	39.0



TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	250.0	258.9	250.5	38.0	39.5
115°	283.6	292.0	304.4	75.9	40.5
117.5°	312.7	322.6	330.9	260.4	131.2
120°	345.3	352.6	361.5	367.5	300.8
122.5°	372.8	380.7	390.6	393.5	394.2
125°	401.0	407.4	416.8	420.2	421.7
127.5°	426.7	433.5	441.0	445.9	446.4
130°	450.8	458.7	464.1	469.6	469.1
132.5°	475.4	481.9	487.3	491.7	491.3
135°	496.2	504.1	508.5	513.5	512.5
137.5°	517.9	523.8	528.8	533.7	532.2
140°	539.1	543.1	548.5	552.9	550.5
142.5°	556.8	560.4	566.7	570.7	568.2
145°	575.6	575.1	583.5	586.9	584.5
147.5°	591.9	590.4	598.7	601.2	599.3
150°	607.6	604.2	612.1	615.0	612.6
152.5°	621.0	617.0	624.4	627.4	623.9
155°	633.8	629.3	635.3	638.2	634.3
157.5°	644.2	640.3	644.7	648.1	644.2
160°	653.1	650.1	653.1	656.0	652.6
162.5°	660.9	657.9	660.5	663.9	659.4
165°	667.8	664.9	666.3	669.8	666.3
167.5°	673.3	670.2	671.8	675.3	670.8
170°	677.7	674.7	675.7	679.1	674.7
172.5°	680.6	677.7	678.7	682.2	677.7
175°	683.1	679.6	680.6	684.1	679.1
177.5°	684.1	680.6	681.2	684.6	680.1
180°	681.7	681.7	681.7	681.7	681.7

TEST NUMBER: P907651

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.14	10.10	10.01	10.99	12.11	8.70	9.66	9.56	10.54	11.66
	3H	10.80	11.67	11.68	12.56	13.71	10.31	11.17	11.19	12.07	13.22
	4H	11.39	12.21	12.29	13.11	14.27	10.90	11.71	11.79	12.62	13.77
	6H	11.80	12.55	12.70	13.45	14.62	11.29	12.05	12.20	12.95	14.12
	8H	11.90	12.62	12.81	13.54	14.71	11.40	12.11	12.31	13.04	14.21
	12H	11.95	12.63	12.87	13.55	14.75	11.44	12.12	12.36	13.04	14.24
4H	2H	9.61	10.42	10.51	11.33	12.48	9.25	10.07	10.15	10.97	12.13
	3H	11.48	12.16	12.39	13.09	14.26	11.07	11.75	11.98	12.69	13.86
	4H	12.19	12.81	13.12	13.74	14.94	11.77	12.39	12.69	13.32	14.52
	6H	12.71	13.25	13.65	14.20	15.40	12.28	12.81	13.21	13.77	14.96
	8H	12.86	13.36	13.80	14.31	15.52	12.42	12.92	13.36	13.87	15.08
	12H	12.94	13.39	13.89	14.35	15.57	12.49	12.94	13.44	13.90	15.12
8H	4H	12.39	12.89	13.33	13.84	15.05	12.02	12.52	12.95	13.46	14.68
	6H	13.02	13.44	13.99	14.43	15.64	12.64	13.05	13.60	14.04	15.25
	8H	13.24	13.61	14.22	14.59	15.82	12.85	13.22	13.82	14.19	15.42
	12H	13.38	13.70	14.35	14.67	15.95	12.96	13.29	13.94	14.26	15.54
12H	4H	12.38	12.83	13.34	13.80	15.02	12.02	12.47	12.97	13.43	14.65
	6H	13.05	13.42	14.03	14.40	15.63	12.68	13.05	13.65	14.03	15.25
	8H	13.30	13.62	14.27	14.59	15.87	12.91	13.24	13.89	14.21	15.49

END OF REPORT