

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924359

Luminaire Tested: DFN2DIP-HX3F0-030D070US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924359
REPORT IS A COMBINATION OF REPORTS P900777 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-030D070US950-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9444.6 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1290	1290	1290
5°	1291	1271	1280
10°	1280	1253	1262
15°	1261	1232	1234
20°	1235	1202	1206
25°	1209	1167	1173
30°	1177	1134	1131
35°	1146	1095	1088
40°	1108	1057	1046
45°	1071	1017	1003
50°	1030	976	954
55°	987	929	908
60°	938	873	856
65°	884	814	794
70°	816	743	727
75°	722	657	665
80°	609	548	548
85°	433	363	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1446 cd/sqm

TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	1.1
10°-20°	294.9	3.1
20°-30°	433.4	4.6
30°-40°	503.4	5.3
40°-50°	502.7	5.3
50°-60°	438.4	4.6
60°-70°	324.1	3.4
70°-80°	183.3	1.9
80°-90°	52.3	0.6
90°-100°	74.3	0.8
100°-110°	277.0	2.9
110°-120°	734.8	7.8
120°-130°	1218.6	12.9
130°-140°	1294.5	13.7
140°-150°	1203.1	12.7
150°-160°	967.2	10.2
160°-170°	623.3	6.6
170°-180°	214.5	2.3
0°-30°	833.1	8.8
0°-40°	1336.5	14.2
0°-60°	2277.6	24.1
0°-90°	2837.3	30.0
90°-120°	1086.1	11.5
90°-150°	4802.2	50.8
90°-180°	6607.0	70.0
0°-180°	9444.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1114	1114	1114	1114	1114	
5°	1114	1109	1098	1106	1104	106
15°	1060	1054	1040	1044	1039	299
25°	959	951	933	935	933	441
35°	828	817	800	793	788	517
45°	674	666	650	638	634	520
55°	510	503	490	478	472	456
65°	344	337	327	317	312	340
75°	180	178	172	166	168	192
85°	44	43	42	38	38	49
90°	2	20	32	41	44	9
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1113.6	1113.6	1113.6	1113.6	1113.6
2.5°	1120.1	1114.7	1102.9	1113.6	1111.6
5°	1113.6	1109.4	1097.6	1106.2	1104.1
7.5°	1106.2	1099.8	1087.9	1096.6	1094.4
10°	1094.4	1086.9	1074.1	1082.6	1079.5
12.5°	1078.3	1071.9	1059.1	1064.4	1062.3
15°	1060.1	1053.8	1039.8	1044.1	1038.7
17.5°	1037.6	1031.3	1017.3	1022.6	1017.3
20°	1013.0	1006.6	991.6	994.7	990.5
22.5°	988.4	978.8	964.8	964.8	962.6
25°	959.4	950.9	932.7	934.8	932.7
27.5°	927.3	919.8	905.9	902.8	897.4
30°	895.2	886.6	870.6	867.4	863.1
32.5°	861.0	854.6	837.4	830.9	826.6
35°	827.8	817.1	799.9	793.4	788.1
37.5°	790.3	780.7	763.5	755.9	750.6
40°	751.8	743.2	726.0	716.5	712.2
42.5°	714.3	705.7	688.6	677.8	671.4
45°	673.6	666.1	650.0	638.2	633.9
47.5°	633.9	626.5	609.3	597.5	591.1
50°	592.1	586.8	571.8	556.8	551.5
52.5°	551.5	544.0	530.1	518.3	510.8
55°	509.8	503.3	490.5	477.7	472.3
57.5°	467.9	462.6	448.7	435.8	431.5
60°	426.2	422.0	407.0	395.1	392.0
62.5°	385.5	378.0	367.3	356.6	352.3
65°	343.8	337.3	326.6	317.0	311.7
67.5°	301.0	295.5	285.9	278.5	274.2
70°	261.3	257.0	247.4	239.8	235.6
72.5°	220.7	216.3	210.9	203.5	200.3
75°	179.8	177.8	172.4	166.0	168.2
77.5°	143.5	139.2	137.0	133.8	130.7
80°	107.1	106.0	103.8	100.6	98.5
82.5°	72.8	72.8	71.8	67.4	67.4
85°	43.9	42.8	41.8	38.5	37.5
87.5°	19.3	17.2	15.0	11.8	10.7
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8

TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P924359

CATALOG NUMBER: DFN2DIP-HX3F0-030D070US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.90	6.61	7.02	7.72	9.25	5.48	6.18	6.59	7.29	8.82
	3H	7.55	8.18	8.67	9.29	10.84	7.08	7.71	8.20	8.82	10.37
	4H	8.12	8.72	9.25	9.84	11.39	7.65	8.25	8.78	9.37	10.92
	6H	8.51	9.06	9.64	10.18	11.74	8.04	8.59	9.17	9.71	11.27
	8H	8.60	9.13	9.74	10.26	11.82	8.13	8.66	9.28	9.79	11.35
	12H	8.64	9.14	9.79	10.27	11.85	8.17	8.67	9.31	9.80	11.38
4H	2H	6.34	6.95	7.48	8.06	9.61	6.00	6.60	7.14	7.72	9.27
	3H	8.19	8.69	9.33	9.83	11.40	7.80	8.30	8.94	9.44	11.01
	4H	8.89	9.35	10.04	10.48	12.07	8.49	8.95	9.63	10.08	11.66
	6H	9.39	9.78	10.54	10.94	12.51	8.98	9.38	10.14	10.53	12.11
	8H	9.53	9.90	10.68	11.04	12.64	9.12	9.49	10.27	10.64	12.23
	12H	9.59	9.93	10.76	11.08	12.68	9.18	9.51	10.34	10.67	12.26
8H	4H	9.07	9.44	10.22	10.58	12.18	8.71	9.08	9.86	10.23	11.82
	6H	9.69	9.99	10.86	11.18	12.77	9.33	9.63	10.50	10.82	12.41
	8H	9.90	10.17	11.08	11.33	12.94	9.53	9.80	10.71	10.97	12.57
	12H	10.02	10.25	11.20	11.42	13.06	9.64	9.87	10.82	11.04	12.68
12H	4H	9.05	9.38	10.22	10.54	12.14	8.70	9.03	9.87	10.19	11.79
	6H	9.71	9.98	10.89	11.14	12.75	9.36	9.63	10.54	10.80	12.41
	8H	9.94	10.17	11.12	11.34	12.98	9.59	9.82	10.77	10.98	12.63

END OF REPORT