

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925825

Luminaire Tested: DFN2DIP-SQ4F0-070D140US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925825
REPORT IS A COMBINATION OF REPORTS P901707 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US950-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19833.7 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1823	1823	1823
5°	1826	1798	1811
10°	1811	1774	1787
15°	1785	1746	1749
20°	1749	1705	1710
25°	1713	1657	1665
30°	1668	1612	1608
35°	1625	1559	1548
40°	1573	1506	1490
45°	1521	1453	1431
50°	1464	1396	1363
55°	1404	1331	1301
60°	1336	1254	1229
65°	1263	1175	1145
70°	1169	1077	1054
75°	1039	961	971
80°	882	813	811
85°	638	556	545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2418 cd/sqm

TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	1.2
10°-20°	688.1	3.5
20°-30°	1011.3	5.1
30°-40°	1174.5	5.9
40°-50°	1173.1	5.9
50°-60°	1022.9	5.2
60°-70°	756.1	3.8
70°-80°	427.8	2.2
80°-90°	120.9	0.6
90°-100°	148.7	0.7
100°-110°	554.1	2.8
110°-120°	1469.5	7.4
120°-130°	2437.3	12.3
130°-140°	2588.9	13.1
140°-150°	2406.1	12.1
150°-160°	1934.5	9.8
160°-170°	1246.5	6.3
170°-180°	429.0	2.2
0°-30°	1943.9	9.8
0°-40°	3118.5	15.7
0°-60°	5314.4	26.8
0°-90°	6619.2	33.4
90°-120°	2172.2	11.0
90°-150°	9604.5	48.4
90°-180°	13215.0	66.6
0°-180°	19833.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	3	39	65	82	88	18
95°	212	104	127	144	140	251
105°	992	1090	199	235	248	1059
115°	1875	1931	2012	502	268	1846
125°	2652	2694	2756	2779	2789	2365
135°	3281	3334	3363	3396	3389	2535
145°	3806	3803	3858	3881	3865	2381
155°	4191	4162	4201	4220	4194	1931
165°	4416	4397	4406	4429	4406	1248
175°	4517	4494	4501	4524	4491	430
180°	4508	4508	4508	4508	4508	

TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	3.1	39.1	65.1	81.8	88.0
92.5°	81.8	68.6	78.2	84.8	88.0
95°	211.9	104.2	127.1	143.7	140.2
97.5°	381.5	114.3	166.2	176.2	179.4
100°	577.5	130.5	185.9	211.9	218.5
102.5°	792.4	786.2	192.5	228.1	238.2
105°	991.5	1089.5	199.1	234.7	247.8
107.5°	1223.1	1304.4	205.7	241.3	254.4
110°	1445.0	1513.2	570.9	244.8	257.6

TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1653.8	1712.2	1656.9	251.0	261.0
115°	1875.4	1930.7	2012.5	502.4	267.6
117.5°	2067.8	2132.9	2188.7	1722.0	867.6
120°	2283.2	2332.0	2390.8	2429.9	1989.6
122.5°	2465.6	2517.9	2583.3	2602.7	2606.2
125°	2651.5	2694.1	2756.1	2778.9	2788.6
127.5°	2821.2	2866.9	2916.0	2948.5	2951.7
130°	2981.1	3033.4	3069.0	3105.1	3101.9
132.5°	3144.2	3186.7	3222.4	3251.8	3248.8
135°	3281.3	3333.6	3362.6	3395.5	3388.9
137.5°	3424.6	3463.7	3496.6	3529.1	3519.5
140°	3564.8	3591.1	3626.7	3656.2	3639.9
142.5°	3682.5	3705.3	3747.6	3773.5	3757.2
145°	3806.5	3802.9	3858.4	3881.3	3864.9
147.5°	3913.8	3904.1	3959.5	3975.7	3962.9
150°	4018.3	3995.4	4047.7	4067.1	4050.9
152.5°	4106.2	4080.3	4129.1	4148.9	4126.0
155°	4191.0	4162.0	4201.1	4220.5	4194.5
157.5°	4259.6	4233.7	4263.1	4285.9	4259.6
160°	4318.5	4298.7	4318.5	4337.8	4315.0
162.5°	4370.4	4351.0	4367.3	4390.1	4360.7
165°	4416.1	4396.7	4406.4	4429.2	4406.4
167.5°	4452.1	4432.4	4442.4	4465.3	4435.8
170°	4481.5	4461.8	4468.3	4491.2	4461.8
172.5°	4500.9	4481.5	4488.1	4511.0	4481.5
175°	4517.2	4494.3	4500.9	4523.8	4491.2
177.5°	4523.8	4500.9	4504.4	4527.2	4497.8
180°	4507.5	4507.5	4507.5	4507.5	4507.5

TEST NUMBER: P925825

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.60	8.33	8.69	9.41	10.91	7.15	7.88	8.24	8.97	10.46
	3H	9.25	9.91	10.35	11.00	12.51	8.76	9.42	9.86	10.51	12.02
	4H	9.84	10.46	10.94	11.55	13.07	9.34	9.96	10.45	11.06	12.57
	6H	10.23	10.80	11.35	11.90	13.43	9.73	10.30	10.85	11.40	12.93
	8H	10.34	10.88	11.46	12.00	13.51	9.83	10.38	10.95	11.49	13.01
	12H	10.38	10.90	11.51	12.01	13.55	9.87	10.39	11.00	11.50	13.04
4H	2H	8.04	8.66	9.16	9.76	11.27	7.69	8.31	8.80	9.41	10.92
	3H	9.90	10.42	11.02	11.54	13.07	9.49	10.01	10.62	11.14	12.66
	4H	10.61	11.09	11.74	12.20	13.75	10.19	10.67	11.32	11.78	13.33
	6H	11.13	11.53	12.26	12.67	14.21	10.69	11.10	11.83	12.24	13.78
	8H	11.28	11.66	12.41	12.78	14.34	10.84	11.22	11.97	12.35	13.90
	12H	11.34	11.69	12.49	12.83	14.39	10.89	11.24	12.04	12.38	13.94
8H	4H	10.80	11.18	11.93	12.31	13.86	10.42	10.80	11.56	11.93	13.49
	6H	11.43	11.75	12.58	12.92	14.47	11.05	11.36	12.20	12.53	14.08
	8H	11.65	11.93	12.81	13.08	14.65	11.26	11.54	12.42	12.68	14.26
	12H	11.78	12.02	12.94	13.17	14.78	11.37	11.61	12.53	12.76	14.37
12H	4H	10.78	11.13	11.93	12.26	13.82	10.41	10.76	11.56	11.90	13.46
	6H	11.46	11.74	12.62	12.88	14.46	11.09	11.36	12.25	12.51	14.08
	8H	11.70	11.94	12.86	13.09	14.69	11.32	11.56	12.48	12.71	14.31