

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929016

Luminaire Tested: DFN2DIP-HX4F0-090D090US935-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929016
REPORT IS A COMBINATION OF REPORTS P900919 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D090US935-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15343.0 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 156.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2242	2242	2242
5°	2246	2211	2226
10°	2228	2181	2196
15°	2195	2146	2149
20°	2151	2096	2101
25°	2107	2037	2045
30°	2052	1981	1974
35°	2000	1916	1899
40°	1936	1850	1828
45°	1872	1784	1755
50°	1802	1715	1671
55°	1729	1634	1594
60°	1646	1539	1505
65°	1556	1441	1400
70°	1441	1321	1287
75°	1282	1177	1183
80°	1091	994	984
85°	791	677	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1872 cd/sqm

TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	1.8
10°-20°	798.5	5.2
20°-30°	1173.4	7.6
30°-40°	1362.9	8.9
40°-50°	1361.2	8.9
50°-60°	1186.9	7.7
60°-70°	877.4	5.7
70°-80°	496.4	3.2
80°-90°	135.6	0.9
90°-100°	86.2	0.6
100°-110°	321.5	2.1
110°-120°	852.6	5.6
120°-130°	1414.1	9.2
130°-140°	1502.1	9.8
140°-150°	1396.0	9.1
150°-160°	1122.4	7.3
160°-170°	723.2	4.7
170°-180°	248.9	1.6
0°-30°	2255.7	14.7
0°-40°	3618.6	23.6
0°-60°	6166.7	40.2
0°-90°	7676.1	50.0
90°-120°	1260.3	8.2
90°-150°	5572.4	36.3
90°-180°	7667.0	50.0
0°-180°	15343.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3015	3015	3015	3015	3015	
5°	3015	3004	2972	2995	2989	286
15°	2870	2853	2815	2827	2812	808
25°	2598	2575	2526	2531	2526	1195
35°	2241	2212	2166	2148	2134	1400
45°	1824	1804	1760	1728	1716	1408
55°	1380	1363	1328	1293	1279	1234
65°	931	913	884	858	844	920
75°	487	481	467	449	455	520
85°	119	116	113	104	102	132
90°	2	23	38	47	51	14
95°	123	60	74	83	81	146
105°	575	632	116	136	144	615
115°	1088	1120	1168	291	155	1071
125°	1538	1563	1599	1612	1618	1372
135°	1904	1934	1951	1970	1966	1471
145°	2208	2206	2239	2252	2242	1381
155°	2432	2415	2437	2449	2434	1121
165°	2562	2551	2557	2570	2557	724
175°	2621	2608	2611	2625	2606	249
180°	2615	2615	2615	2615	2615	

TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3015.1	3015.1	3015.1	3015.1	3015.1
2.5°	3032.7	3018.2	2986.3	3015.1	3009.6
5°	3015.1	3003.8	2971.8	2994.9	2989.3
7.5°	2994.9	2977.7	2945.7	2969.1	2963.2
10°	2963.2	2942.9	2908.1	2931.2	2922.6
12.5°	2919.5	2902.3	2867.6	2881.9	2876.2
15°	2870.3	2853.1	2815.2	2826.9	2812.5
17.5°	2809.4	2792.1	2754.3	2768.8	2754.3
20°	2742.6	2725.4	2684.8	2693.4	2682.0
22.5°	2676.2	2650.1	2612.2	2612.2	2606.3
25°	2597.7	2574.6	2525.5	2531.0	2525.5
27.5°	2510.7	2490.4	2452.9	2444.3	2429.8
30°	2424.0	2400.6	2357.2	2348.5	2336.9
32.5°	2331.1	2313.9	2267.4	2249.9	2238.2
35°	2241.3	2212.3	2165.8	2148.4	2133.9
37.5°	2139.8	2113.6	2067.1	2046.9	2032.4
40°	2035.4	2012.1	1965.6	1939.7	1928.1
42.5°	1933.9	1910.6	1864.4	1835.2	1818.0
45°	1823.8	1803.5	1759.8	1728.1	1716.5
47.5°	1716.5	1696.2	1649.7	1617.7	1600.5
50°	1603.3	1588.8	1548.2	1507.6	1493.1
52.5°	1493.1	1472.8	1435.3	1403.3	1383.0
55°	1380.3	1362.7	1327.9	1293.2	1278.8
57.5°	1267.0	1252.6	1214.8	1180.0	1168.3
60°	1153.8	1142.5	1101.8	1069.9	1061.3
62.5°	1043.7	1023.4	994.5	965.6	953.9
65°	930.8	913.3	884.3	858.2	843.8
67.5°	814.9	800.1	774.2	754.0	742.3
70°	707.5	695.8	669.7	649.4	638.0
72.5°	597.4	585.7	571.2	551.0	542.3
75°	487.0	481.4	466.7	449.4	455.3
77.5°	388.5	376.9	371.0	362.4	353.8
80°	290.1	287.0	281.1	272.5	266.7
82.5°	197.2	197.2	194.4	182.7	182.7
85°	118.7	116.0	113.2	104.3	101.5
87.5°	52.3	46.4	40.6	32.0	28.9
90°	1.8	22.7	37.7	47.4	51.0
92.5°	47.4	39.8	45.4	49.2	51.0
95°	123.0	60.4	73.7	83.3	81.4
97.5°	221.4	66.3	96.4	102.2	104.0
100°	335.0	75.8	107.9	123.0	126.7
102.5°	459.8	456.2	111.7	132.3	138.2
105°	575.2	632.1	115.5	136.2	143.8
107.5°	709.6	756.8	119.3	140.0	147.7
110°	838.4	878.0	331.2	142.0	149.5

TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	959.5	993.4	961.3	145.6	151.4
115°	1088.0	1120.2	1167.6	291.4	155.2
117.5°	1199.7	1237.5	1269.8	999.1	503.3
120°	1324.6	1353.0	1387.2	1409.8	1154.3
122.5°	1430.6	1460.9	1498.8	1510.0	1512.1
125°	1538.3	1563.1	1599.0	1612.3	1617.9
127.5°	1636.8	1663.3	1691.9	1710.7	1712.5
130°	1729.6	1760.0	1780.6	1801.5	1799.7
132.5°	1824.2	1848.9	1869.6	1886.7	1884.9
135°	1903.8	1934.1	1950.9	1970.1	1966.3
137.5°	1986.9	2009.6	2028.7	2047.5	2041.9
140°	2068.2	2083.5	2104.2	2121.2	2111.9
142.5°	2136.6	2149.8	2174.3	2189.4	2180.0
145°	2208.5	2206.4	2238.6	2251.9	2242.4
147.5°	2270.7	2265.1	2297.2	2306.7	2299.2
150°	2331.4	2318.2	2348.5	2359.7	2350.3
152.5°	2382.4	2367.3	2395.6	2407.1	2393.8
155°	2431.6	2414.8	2437.4	2448.7	2433.6
157.5°	2471.4	2456.3	2473.4	2486.7	2471.4
160°	2505.5	2494.1	2505.5	2516.8	2503.5
162.5°	2535.6	2524.4	2533.8	2547.1	2530.0
165°	2562.2	2550.9	2556.6	2569.8	2556.6
167.5°	2583.1	2571.6	2577.4	2590.7	2573.6
170°	2600.1	2588.7	2592.5	2605.7	2588.7
172.5°	2611.4	2600.1	2603.9	2617.2	2600.1
175°	2620.8	2607.5	2611.4	2624.6	2605.7
177.5°	2624.6	2611.4	2613.4	2626.7	2609.6
180°	2615.2	2615.2	2615.2	2615.2	2615.2

TEST NUMBER: P929016

CATALOG NUMBER: DFN2DIP-HX4F0-090D090US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.08	10.94	11.04	11.91	13.19	9.65	10.51	10.61	11.48	12.75
	3H	11.74	12.51	12.71	13.50	14.79	11.27	12.04	12.24	13.02	14.32
	4H	12.33	13.06	13.31	14.05	15.35	11.86	12.59	12.84	13.57	14.88
	6H	12.73	13.41	13.72	14.40	15.71	12.26	12.93	13.25	13.92	15.23
	8H	12.84	13.48	13.84	14.49	15.80	12.36	13.00	13.36	14.01	15.32
	12H	12.89	13.50	13.89	14.50	15.83	12.40	13.01	13.41	14.02	15.35
4H	2H	10.54	11.27	11.53	12.26	13.56	10.20	10.93	11.19	11.92	13.22
	3H	12.41	13.02	13.41	14.04	15.35	12.02	12.63	13.01	13.64	14.96
	4H	13.13	13.68	14.13	14.69	16.03	12.72	13.28	13.73	14.29	15.62
	6H	13.64	14.12	14.66	15.15	16.49	13.23	13.71	14.25	14.74	16.08
	8H	13.79	14.24	14.81	15.26	16.62	13.38	13.83	14.40	14.85	16.20
	12H	13.87	14.27	14.90	15.31	16.67	13.44	13.85	14.48	14.89	16.24
8H	4H	13.32	13.77	14.34	14.80	16.15	12.96	13.41	13.98	14.44	15.79
	6H	13.96	14.33	15.00	15.39	16.74	13.59	13.96	14.63	15.03	16.38
	8H	14.18	14.50	15.23	15.56	16.92	13.81	14.13	14.86	15.19	16.55
	12H	14.31	14.60	15.36	15.64	17.05	13.92	14.21	14.98	15.26	16.67
12H	4H	13.31	13.71	14.35	14.75	16.11	12.96	13.36	13.99	14.40	15.76
	6H	13.99	14.31	15.04	15.36	16.73	13.63	13.96	14.68	15.01	16.38
	8H	14.23	14.52	15.28	15.56	16.97	13.87	14.16	14.92	15.20	16.61

END OF REPORT