

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905613

Luminaire Tested: DFN2DIP-PN2F0-030D060US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905613
REPORT IS A COMBINATION OF REPORTS P901023 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D060US835-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8910.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 80.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2528	2528	2528
5°	2528	2488	2506
10°	2504	2449	2468
15°	2463	2403	2412
20°	2409	2342	2354
25°	2355	2269	2287
30°	2289	2202	2204
35°	2226	2123	2116
40°	2149	2043	2032
45°	2072	1962	1946
50°	1988	1878	1847
55°	1899	1780	1754
60°	1799	1665	1649
65°	1689	1545	1524
70°	1548	1398	1389
75°	1356	1223	1259
80°	1122	998	1022
85°	762	631	640

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2072 cd/sqm

TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	1.2
10°-20°	309.1	3.5
20°-30°	454.3	5.1
30°-40°	527.6	5.9
40°-50°	527.0	5.9
50°-60°	459.5	5.2
60°-70°	339.7	3.8
70°-80°	192.2	2.2
80°-90°	54.3	0.6
90°-100°	66.8	0.7
100°-110°	248.9	2.8
110°-120°	660.2	7.4
120°-130°	1094.9	12.3
130°-140°	1163.0	13.1
140°-150°	1080.9	12.1
150°-160°	869.0	9.8
160°-170°	560.0	6.3
170°-180°	192.7	2.2
0°-30°	873.3	9.8
0°-40°	1400.9	15.7
0°-60°	2387.4	26.8
0°-90°	2973.6	33.4
90°-120°	975.8	11.0
90°-150°	4314.7	48.4
90°-180°	5936.0	66.6
0°-180°	8910.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	18	29	37	40	8
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	

TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7

TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9

TEST NUMBER: P905613

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.33	9.69	10.42	11.91	8.17	8.90	9.26	9.98	11.47
	3H	10.24	10.89	11.33	11.98	13.49	9.75	10.41	10.85	11.50	13.01
	4H	10.80	11.42	11.91	12.52	14.03	10.32	10.94	11.43	12.04	13.55
	6H	11.18	11.75	12.30	12.85	14.38	10.69	11.27	11.81	12.36	13.89
	8H	11.27	11.82	12.39	12.93	14.45	10.79	11.33	11.91	12.45	13.96
	12H	11.31	11.83	12.43	12.93	14.48	10.82	11.33	11.94	12.44	13.98
4H	2H	9.04	9.66	10.15	10.76	12.27	8.69	9.31	9.80	10.41	11.92
	3H	10.87	11.39	11.99	12.51	14.04	10.47	10.99	11.59	12.11	13.64
	4H	11.56	12.04	12.69	13.15	14.70	11.15	11.62	12.27	12.74	14.28
	6H	12.05	12.46	13.18	13.59	15.13	11.63	12.04	12.76	13.17	14.71
	8H	12.19	12.57	13.32	13.70	15.25	11.76	12.14	12.90	13.27	14.83
	12H	12.24	12.59	13.39	13.73	15.29	11.81	12.16	12.96	13.30	14.86
8H	4H	11.74	12.12	12.87	13.25	14.80	11.37	11.75	12.50	12.88	14.43
	6H	12.34	12.65	13.49	13.82	15.37	11.97	12.28	13.12	13.45	15.00
	8H	12.54	12.82	13.70	13.97	15.54	12.16	12.44	13.32	13.59	15.16
	12H	12.66	12.90	13.82	14.04	15.65	12.26	12.50	13.42	13.65	15.25
12H	4H	11.71	12.06	12.86	13.20	14.76	11.35	11.70	12.50	12.84	14.40
	6H	12.36	12.64	13.52	13.79	15.36	12.00	12.28	13.16	13.42	15.00
	8H	12.58	12.82	13.74	13.97	15.58	12.21	12.45	13.38	13.60	15.21