

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923395

Luminaire Tested: DFN2DIP-TR2F0-030D060US940-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923395  
REPORT IS A COMBINATION OF REPORTS P901784 AND P897145  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR2F0-030D060US940-RLLONL  
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7008.8 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 73.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923395  
CATALOG NUMBER: DFN2DIP-TR2F0-030D060US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P923395

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US940-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29	24				24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21				21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18				18
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19	16				16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	14				14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13				13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11				11
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10				10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2466	2466	2466
5°	2466	2421	2438
10°	2438	2369	2355
15°	2401	2285	2228
20°	2353	2172	2074
25°	2304	2046	1926
30°	2239	1918	1739
35°	2175	1780	1575
40°	2110	1639	1388
45°	2035	1482	1219
50°	1957	1325	1053
55°	1874	1158	895
60°	1780	983	733
65°	1670	807	655
70°	1537	643	586
75°	1369	556	525
80°	1130	451	443
85°	741	280	312

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2207 cd/sqm



TEST NUMBER: P923395

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US940-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.6	1.5
10°-20°	284.5	4.1
20°-30°	399.4	5.7
30°-40°	435.3	6.2
40°-50°	400.1	5.7
50°-60°	314.2	4.5
60°-70°	204.5	2.9
70°-80°	105.3	1.5
80°-90°	31.7	0.5
90°-100°	104.7	1.5
100°-110°	332.7	4.7
110°-120°	569.3	8.1
120°-130°	748.8	10.7
130°-140°	840.5	12.0
140°-150°	824.2	11.8
150°-160°	691.4	9.9
160°-170°	458.5	6.5
170°-180°	160.3	2.3
0°-30°	787.5	11.2
0°-40°	1222.8	17.4
0°-60°	1937.2	27.6
0°-90°	2278.7	32.5
90°-120°	1006.7	14.4
90°-150°	3420.1	48.8
90°-180°	4730.0	67.5
0°-180°	7008.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	2	18	50	47	48	7
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P923395

CATALOG NUMBER: DFN2DIP-TR2F0-030D060US940-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P923395

CATALOG NUMBER: DFN2DIP-TR2FO-030D060US940-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1



TEST NUMBER: P923395  
 CATALOG NUMBER: DFN2DIP-TR2F0-030D060US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.25	8.96	9.35	10.05	11.55	4.24	4.94	5.34	6.03	7.54
	3H	9.90	10.53	11.00	11.63	13.15	5.40	6.03	6.51	7.13	8.65
	4H	10.48	11.08	11.60	12.18	13.71	5.83	6.43	6.95	7.53	9.06
	6H	10.88	11.43	12.01	12.54	14.07	6.13	6.68	7.26	7.79	9.33
	8H	10.99	11.52	12.12	12.64	14.17	6.21	6.74	7.34	7.86	9.39
	12H	11.04	11.54	12.17	12.65	14.20	6.25	6.74	7.38	7.86	9.41
4H	2H	8.25	8.85	9.38	9.95	11.48	4.80	5.40	5.93	6.50	8.03
	3H	10.04	10.54	11.17	11.67	13.21	6.12	6.62	7.25	7.75	9.29
	4H	10.71	11.17	11.85	12.29	13.84	6.65	7.11	7.79	8.23	9.78
	6H	11.20	11.59	12.34	12.73	14.28	7.05	7.44	8.19	8.58	10.13
	8H	11.36	11.72	12.50	12.85	14.42	7.16	7.53	8.30	8.66	10.23
	12H	11.43	11.76	12.59	12.91	14.48	7.21	7.55	8.37	8.69	10.26
8H	4H	10.67	11.03	11.81	12.16	13.73	6.91	7.27	8.05	8.41	9.97
	6H	11.20	11.50	12.36	12.68	14.24	7.40	7.70	8.56	8.88	10.44
	8H	11.40	11.67	12.57	12.82	14.40	7.58	7.84	8.74	9.00	10.58
	12H	11.52	11.75	12.69	12.90	14.52	7.68	7.91	8.85	9.06	10.68
12H	4H	10.61	10.94	11.77	12.09	13.66	6.90	7.23	8.06	8.38	9.95
	6H	11.18	11.44	12.34	12.59	14.18	7.44	7.71	8.61	8.86	10.44
	8H	11.37	11.61	12.54	12.76	14.37	7.63	7.86	8.80	9.02	10.63