

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926148

Luminaire Tested: DFN2DIP-TR2F0-050D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926148
REPORT IS A COMBINATION OF REPORTS P900237 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-050D030US950-FLLFLL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7255.1 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 69.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4140	4140	4140
5°	4140	4073	4103
10°	4100	4009	4040
15°	4034	3933	3946
20°	3946	3833	3850
25°	3859	3714	3740
30°	3751	3603	3603
35°	3648	3473	3458
40°	3523	3342	3320
45°	3397	3210	3177
50°	3260	3071	3014
55°	3115	2910	2861
60°	2952	2722	2687
65°	2772	2524	2481
70°	2544	2283	2258
75°	2230	1995	2043
80°	1850	1628	1651
85°	1260	1025	1026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3397 cd/sqm

TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.4
10°-20°	491.5	6.8
20°-30°	722.3	10.0
30°-40°	838.9	11.6
40°-50°	837.9	11.5
50°-60°	730.6	10.1
60°-70°	540.1	7.4
70°-80°	305.6	4.2
80°-90°	83.2	1.1
90°-100°	56.0	0.8
100°-110°	178.0	2.5
110°-120°	304.6	4.2
120°-130°	400.5	5.5
130°-140°	449.6	6.2
140°-150°	440.9	6.1
150°-160°	369.8	5.1
160°-170°	245.3	3.4
170°-180°	85.7	1.2
0°-30°	1388.5	19.1
0°-40°	2227.5	30.7
0°-60°	3796.0	52.3
0°-90°	4724.9	65.1
90°-120°	538.5	7.4
90°-150°	1829.5	25.2
90°-180°	2530.0	34.9
0°-180°	7255.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	10	27	25	26	7
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P926148

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.37	14.38	14.18	15.22	16.26	12.95	13.96	13.76	14.80	15.84
	3H	15.02	15.93	15.84	16.78	17.84	14.56	15.47	15.38	16.32	17.38
	4H	15.60	16.46	16.44	17.31	18.39	15.14	16.00	15.98	16.85	17.93
	6H	15.98	16.78	16.84	17.64	18.73	15.52	16.32	16.38	17.18	18.27
	8H	16.08	16.84	16.95	17.72	18.81	15.63	16.38	16.49	17.26	18.35
	12H	16.13	16.85	17.00	17.73	18.84	15.67	16.39	16.54	17.26	18.38
4H	2H	13.84	14.70	14.69	15.56	16.63	13.50	14.36	14.35	15.22	16.29
	3H	15.69	16.41	16.55	17.30	18.39	15.31	16.03	16.17	16.91	18.01
	4H	16.39	17.05	17.27	17.93	19.05	16.00	16.65	16.87	17.54	18.66
	6H	16.89	17.46	17.78	18.37	19.49	16.50	17.07	17.39	17.97	19.10
	8H	17.04	17.57	17.93	18.47	19.60	16.64	17.17	17.53	18.07	19.21
	12H	17.11	17.58	18.02	18.51	19.65	16.70	17.18	17.61	18.10	19.24
8H	4H	16.59	17.12	17.48	18.02	19.16	16.24	16.77	17.13	17.67	18.81
	6H	17.20	17.64	18.12	18.59	19.72	16.85	17.29	17.77	18.23	19.37
	8H	17.41	17.80	18.34	18.73	19.89	17.05	17.44	17.98	18.38	19.53
	12H	17.53	17.87	18.46	18.80	20.01	17.16	17.51	18.10	18.44	19.64
12H	4H	16.58	17.06	17.49	17.98	19.12	16.24	16.72	17.15	17.64	18.78
	6H	17.23	17.62	18.16	18.56	19.71	16.89	17.28	17.82	18.21	19.37
	8H	17.46	17.80	18.39	18.73	19.93	17.11	17.46	18.05	18.39	19.59