

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909974

Luminaire Tested: DFN2DIP-TR3F0-090D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909974
REPORT IS A COMBINATION OF REPORTS P900284 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D030US840-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10406.7 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 117.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4681	4681	4681
5°	4686	4603	4633
10°	4637	4508	4479
15°	4570	4356	4243
20°	4483	4147	3955
25°	4394	3913	3676
30°	4275	3674	3324
35°	4159	3417	3015
40°	4040	3151	2661
45°	3902	2858	2340
50°	3760	2561	2027
55°	3610	2245	1727
60°	3437	1915	1418
65°	3238	1581	1273
70°	2997	1268	1148
75°	2693	1110	1038
80°	2253	918	890
85°	1533	594	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3902 cd/sqm

TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	3.4
10°-20°	966.5	9.3
20°-30°	1356.9	13.0
30°-40°	1479.1	14.2
40°-50°	1359.4	13.1
50°-60°	1067.6	10.3
60°-70°	694.9	6.7
70°-80°	357.7	3.4
80°-90°	94.0	0.9
90°-100°	59.3	0.6
100°-110°	188.4	1.8
110°-120°	322.4	3.1
120°-130°	424.0	4.1
130°-140°	475.9	4.6
140°-150°	466.7	4.5
150°-160°	391.5	3.8
160°-170°	259.6	2.5
170°-180°	90.7	0.9
0°-30°	2675.4	25.7
0°-40°	4154.5	39.9
0°-60°	6581.5	63.2
0°-90°	7728.2	74.3
90°-120°	570.1	5.5
90°-150°	1936.6	18.6
90°-180°	2678.0	25.7
0°-180°	10406.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3716	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2771	2720	1492
35°	2794	2621	2322	2108	2033	1749
45°	2284	2057	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	592	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	1	10	28	27	28	10
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.4	3756.4	3756.4	3756.4	3756.4
2.5°	3773.4	3756.4	3718.8	3753.2	3746.3
5°	3756.4	3739.4	3695.1	3725.7	3715.6
7.5°	3725.7	3705.5	3657.9	3671.3	3654.3
10°	3685.0	3661.2	3593.4	3582.9	3562.7
12.5°	3634.1	3603.5	3511.5	3491.3	3453.7
15°	3572.8	3535.3	3419.9	3355.3	3321.4
17.5°	3501.4	3447.0	3304.1	3229.4	3175.0
20°	3419.9	3351.7	3181.8	3097.1	3022.0
22.5°	3331.5	3253.3	3056.0	2940.5	2889.7
25°	3243.2	3134.2	2909.9	2770.7	2719.5
27.5°	3137.9	3022.0	2773.9	2614.1	2535.9
30°	3025.7	2896.2	2624.2	2451.1	2359.1
32.5°	2916.7	2760.2	2481.7	2277.7	2192.5
35°	2794.5	2621.0	2322.0	2107.8	2032.8
37.5°	2675.4	2488.3	2172.3	1937.5	1852.8
40°	2549.6	2345.8	2015.8	1774.5	1686.2
42.5°	2420.4	2203.0	1859.6	1607.9	1523.1
45°	2284.5	2056.6	1699.8	1458.1	1376.6
47.5°	2155.4	1914.1	1546.9	1305.3	1230.6
50°	2012.6	1771.2	1397.2	1162.5	1091.4
52.5°	1873.0	1618.0	1254.5	1030.1	965.5
55°	1737.0	1471.9	1104.7	901.0	836.4
57.5°	1597.8	1325.9	972.4	781.9	727.5
60°	1454.9	1183.0	832.8	659.6	605.2
62.5°	1315.8	1043.8	713.8	550.8	523.7
65°	1172.9	897.4	591.5	476.1	465.6
67.5°	1036.9	761.3	476.1	418.0	407.9
70°	894.1	629.0	394.3	360.3	346.6
72.5°	758.1	506.3	329.6	302.6	295.8
75°	625.4	387.4	272.0	248.1	244.9
77.5°	493.0	275.2	214.2	200.6	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P909974

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.48	15.56	15.20	16.29	17.17	10.45	11.53	11.18	12.27	13.15
	3H	16.16	17.13	16.90	17.88	18.79	11.66	12.62	12.39	13.37	14.28
	4H	16.78	17.69	17.53	18.44	19.37	12.11	13.02	12.87	13.78	14.70
	6H	17.20	18.04	17.97	18.81	19.75	12.44	13.28	13.21	14.05	14.98
	8H	17.33	18.13	18.11	18.92	19.86	12.54	13.33	13.32	14.12	15.06
	12H	17.40	18.16	18.18	18.94	19.90	12.59	13.34	13.37	14.12	15.09
4H	2H	14.52	15.43	15.28	16.19	17.12	11.07	11.98	11.83	12.74	13.67
	3H	16.37	17.12	17.14	17.91	18.85	12.44	13.19	13.21	13.99	14.93
	4H	17.06	17.74	17.85	18.54	19.51	12.99	13.68	13.78	14.47	15.44
	6H	17.58	18.17	18.38	18.99	19.97	13.42	14.01	14.22	14.83	15.81
	8H	17.75	18.31	18.56	19.12	20.11	13.55	14.10	14.36	14.92	15.90
	12H	17.85	18.35	18.68	19.19	20.18	13.62	14.12	14.45	14.95	15.95
8H	4H	17.04	17.60	17.85	18.41	19.40	13.29	13.84	14.09	14.65	15.64
	6H	17.61	18.06	18.45	18.92	19.91	13.80	14.26	14.64	15.12	16.11
	8H	17.82	18.22	18.67	19.08	20.09	13.99	14.40	14.84	15.25	16.26
	12H	17.96	18.32	18.81	19.16	20.23	14.12	14.47	14.97	15.32	16.38
12H	4H	17.01	17.50	17.83	18.34	19.33	13.30	13.79	14.13	14.63	15.62
	6H	17.58	17.99	18.43	18.84	19.85	13.85	14.26	14.70	15.11	16.12
	8H	17.81	18.17	18.66	19.01	20.07	14.07	14.43	14.92	15.27	16.33