

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912641

Luminaire Tested: DFN2DIP-TR3F0-060D070US850-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P912641  
REPORT IS A COMBINATION OF REPORTS P901854 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-060D070US850-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13341.3 lumens  
Efficiency: N/A  
Efficacy: 120.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 110.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P912641  
CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P912641

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49	49	42
1	96	92	89	85	88	85	81	79	70	68	66	56	55	54	44	43	42	42	42	42	42	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	36	36	36	36	31
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31	31	31	31	31	27
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	32	29	27	27	27	27	27	24
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24	24	24	24	24	21
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21	21	21	21	21	18
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	19	19	19	19	16
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17	17	17	17	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16	16	16	16	16	13
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14	14	14	14	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3427	3427	3427
5°	3431	3370	3392
10°	3395	3301	3279
15°	3346	3189	3106
20°	3282	3036	2895
25°	3217	2865	2692
30°	3130	2689	2434
35°	3045	2502	2207
40°	2958	2307	1948
45°	2857	2092	1714
50°	2752	1875	1484
55°	2643	1644	1264
60°	2517	1402	1038
65°	2371	1157	932
70°	2194	928	840
75°	1972	812	760
80°	1650	672	651
85°	1122	435	476

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2857 cd/sqm



TEST NUMBER: P912641

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	257.7	1.9
10°-20°	707.6	5.3
20°-30°	993.4	7.4
30°-40°	1082.8	8.1
40°-50°	995.2	7.5
50°-60°	781.6	5.9
60°-70°	508.8	3.8
70°-80°	261.9	2.0
80°-90°	71.5	0.5
90°-100°	86.4	0.6
100°-110°	322.1	2.4
110°-120°	854.1	6.4
120°-130°	1416.6	10.6
130°-140°	1504.8	11.3
140°-150°	1398.5	10.5
150°-160°	1124.4	8.4
160°-170°	724.5	5.4
170°-180°	249.4	1.9
0°-30°	1958.7	14.7
0°-40°	3041.5	22.8
0°-60°	4818.4	36.1
0°-90°	5660.5	42.4
90°-120°	1262.6	9.5
90°-150°	5582.5	41.8
90°-180°	7681.0	57.6
0°-180°	13341.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	2	23	38	48	51	12
95°	123	61	74	84	82	146
105°	576	633	116	136	144	616
115°	1090	1122	1170	292	156	1073
125°	1541	1566	1602	1615	1621	1375
135°	1907	1938	1954	1974	1970	1473
145°	2212	2210	2243	2256	2246	1384
155°	2436	2419	2442	2453	2438	1123
165°	2567	2556	2561	2574	2561	725
175°	2626	2612	2616	2629	2610	250
180°	2620	2620	2620	2620	2620	



TEST NUMBER: P912641

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.8	22.7	37.8	47.5	51.1
92.5°	47.5	39.8	45.5	49.4	51.1
95°	123.1	60.6	73.9	83.5	81.5
97.5°	221.7	66.4	96.6	102.5	104.2
100°	335.7	75.9	108.0	123.1	127.0
102.5°	460.6	457.0	111.9	132.6	138.4
105°	576.3	633.2	115.7	136.4	144.1
107.5°	710.9	758.2	119.6	140.3	147.9
110°	840.0	879.5	331.8	142.3	149.7



TEST NUMBER: P912641

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	961.3	995.2	963.1	145.8	151.7
115°	1090.0	1122.2	1169.7	292.0	155.6
117.5°	1201.9	1239.8	1272.1	1000.9	504.3
120°	1327.0	1355.4	1389.7	1412.4	1156.5
122.5°	1433.0	1463.4	1501.6	1512.8	1514.8
125°	1541.2	1565.9	1602.0	1615.3	1620.8
127.5°	1639.8	1666.3	1694.9	1713.8	1715.6
130°	1732.7	1763.1	1783.8	1804.8	1803.0
132.5°	1827.5	1852.3	1873.0	1890.1	1888.3
135°	1907.1	1937.5	1954.5	1973.6	1969.8
137.5°	1990.4	2013.3	2032.4	2051.3	2045.7
140°	2071.9	2087.2	2108.0	2125.1	2115.6
142.5°	2140.4	2153.7	2178.2	2193.3	2183.8
145°	2212.5	2210.5	2242.6	2255.9	2246.5
147.5°	2274.8	2269.2	2301.4	2310.8	2303.4
150°	2335.6	2322.4	2352.7	2363.9	2354.5
152.5°	2386.7	2371.6	2400.0	2411.4	2398.2
155°	2436.0	2419.1	2441.8	2453.1	2438.0
157.5°	2475.8	2460.8	2477.8	2491.1	2475.8
160°	2510.1	2498.6	2510.1	2521.3	2508.0
162.5°	2540.3	2529.0	2538.4	2551.7	2534.6
165°	2566.8	2555.6	2561.1	2574.4	2561.1
167.5°	2587.7	2576.2	2582.1	2595.4	2578.3
170°	2604.8	2593.4	2597.2	2610.5	2593.4
172.5°	2616.1	2604.8	2608.7	2621.9	2604.8
175°	2625.6	2612.2	2616.1	2629.3	2610.5
177.5°	2629.3	2616.1	2618.1	2631.4	2614.2
180°	2619.9	2619.9	2619.9	2619.9	2619.9



TEST NUMBER: P912641  
 CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.62	11.40	11.65	12.43	13.80	6.60	7.37	7.63	8.40	9.78
	3H	12.29	12.98	13.32	14.02	15.41	7.78	8.47	8.82	9.51	10.91
	4H	12.89	13.54	13.94	14.58	15.99	8.22	8.88	9.27	9.92	11.32
	6H	13.30	13.90	14.36	14.94	16.36	8.54	9.14	9.59	10.18	11.60
	8H	13.42	13.99	14.48	15.05	16.46	8.62	9.20	9.69	10.26	11.67
	12H	13.47	14.02	14.54	15.07	16.51	8.66	9.21	9.73	10.26	11.70
4H	2H	10.63	11.29	11.69	12.33	13.73	7.18	7.84	8.24	8.88	10.28
	3H	12.45	12.99	13.51	14.06	15.48	8.52	9.07	9.58	10.13	11.55
	4H	13.13	13.63	14.20	14.69	16.13	9.06	9.56	10.13	10.62	12.06
	6H	13.63	14.06	14.71	15.14	16.58	9.47	9.90	10.55	10.98	12.42
	8H	13.80	14.20	14.88	15.28	16.73	9.60	10.00	10.68	11.07	12.52
	12H	13.89	14.25	14.98	15.34	16.79	9.66	10.02	10.75	11.11	12.56
8H	4H	13.09	13.49	14.17	14.57	16.02	9.33	9.73	10.41	10.81	12.26
	6H	13.65	13.97	14.75	15.09	16.54	9.84	10.17	10.94	11.29	12.73
	8H	13.86	14.14	14.96	15.24	16.71	10.03	10.32	11.13	11.42	12.88
	12H	13.99	14.24	15.09	15.33	16.84	10.14	10.39	11.25	11.49	12.99
12H	4H	13.04	13.40	14.14	14.49	15.94	9.33	9.69	10.43	10.78	12.24
	6H	13.62	13.91	14.73	15.01	16.48	9.89	10.18	11.00	11.28	12.74
	8H	13.83	14.09	14.94	15.18	16.69	10.09	10.34	11.20	11.44	12.95