

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903919

Luminaire Tested: DFN2DIP-SQ3F0-120D080US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903919
REPORT IS A COMBINATION OF REPORTS P901470 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D080US830-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17078.9 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5356	5356	5356
5°	5361	5268	5303
10°	5305	5161	5129
15°	5228	4987	4861
20°	5128	4748	4532
25°	5026	4482	4214
30°	4890	4209	3812
35°	4756	3915	3459
40°	4619	3612	3055
45°	4461	3276	2688
50°	4297	2938	2330
55°	4126	2577	1987
60°	3927	2199	1634
65°	3698	1816	1468
70°	3421	1459	1326
75°	3072	1278	1202
80°	2567	1061	1037
85°	1741	691	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4461 cd/sqm

TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.6
10°-20°	1202.7	7.0
20°-30°	1688.5	9.9
30°-40°	1840.6	10.8
40°-50°	1691.7	9.9
50°-60°	1328.6	7.8
60°-70°	864.8	5.1
70°-80°	445.2	2.6
80°-90°	118.1	0.7
90°-100°	83.9	0.5
100°-110°	312.8	1.8
110°-120°	829.6	4.9
120°-130°	1376.0	8.1
130°-140°	1461.6	8.6
140°-150°	1358.4	8.0
150°-160°	1092.1	6.4
160°-170°	703.7	4.1
170°-180°	242.2	1.4
0°-30°	3329.4	19.5
0°-40°	5170.0	30.3
0°-60°	8190.3	48.0
0°-90°	9618.4	56.3
90°-120°	1226.4	7.2
90°-150°	5422.4	31.7
90°-180°	7460.0	43.7
0°-180°	17078.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4675	4675	4675	4675	4675	
5°	4675	4654	4598	4636	4624	443
15°	4446	4400	4256	4176	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3478	3262	2890	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1932
65°	1460	1117	736	592	580	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	2	22	37	46	50	16
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	

TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.6	4674.6	4674.6	4674.6	4674.6
2.5°	4695.7	4674.6	4628.0	4670.6	4662.0
5°	4674.6	4653.5	4598.3	4636.5	4623.9
7.5°	4636.5	4611.3	4552.1	4568.7	4547.6
10°	4585.8	4556.2	4471.7	4458.7	4433.6
12.5°	4522.4	4484.3	4369.8	4344.7	4298.1
15°	4446.2	4399.5	4255.9	4175.5	4133.3
17.5°	4357.3	4289.5	4111.7	4018.9	3951.1
20°	4255.9	4171.0	3959.6	3854.1	3760.7
22.5°	4145.9	4048.5	3803.0	3659.3	3596.1
25°	4036.0	3900.3	3621.2	3447.9	3384.2
27.5°	3904.9	3760.7	3452.0	3253.2	3155.7
30°	3765.3	3604.2	3265.7	3050.3	2935.8
32.5°	3629.7	3434.9	3088.4	2834.4	2728.5
35°	3477.6	3261.7	2889.6	2623.0	2529.6
37.5°	3329.4	3096.5	2703.3	2411.1	2305.6
40°	3172.8	2919.2	2508.6	2208.3	2098.3
42.5°	3012.1	2741.5	2314.2	2000.9	1895.5
45°	2842.9	2559.3	2115.3	1814.7	1713.2
47.5°	2682.2	2382.0	1925.0	1624.4	1531.4
50°	2504.5	2204.2	1738.8	1446.6	1358.2
52.5°	2330.8	2013.5	1561.0	1281.9	1201.6
55°	2161.6	1831.7	1374.8	1121.2	1040.8
57.5°	1988.3	1649.9	1210.0	973.1	905.3
60°	1810.6	1472.2	1036.3	821.0	753.2
62.5°	1637.4	1298.9	888.3	685.4	651.7
65°	1459.6	1116.7	736.1	592.5	579.5
67.5°	1290.4	947.4	592.5	520.2	507.7
70°	1112.7	782.8	490.6	448.4	431.3
72.5°	943.5	630.2	410.2	376.5	368.1
75°	778.3	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4

TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8

TEST NUMBER: P903919

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.51	14.40	14.42	15.32	16.50	9.48	10.36	10.38	11.28	12.46
	3H	15.19	15.98	16.11	16.91	18.12	10.66	11.45	11.58	12.38	13.59
	4H	15.80	16.55	16.73	17.48	18.70	11.11	11.86	12.05	12.79	14.01
	6H	16.22	16.91	17.17	17.85	19.08	11.43	12.12	12.37	13.06	14.29
	8H	16.35	17.00	17.30	17.96	19.19	11.52	12.17	12.47	13.13	14.36
	12H	16.41	17.03	17.37	17.98	19.23	11.56	12.18	12.52	13.13	14.38
4H	2H	13.54	14.28	14.48	15.22	16.44	10.08	10.82	11.02	11.76	12.97
	3H	15.37	15.99	16.32	16.95	18.18	11.42	12.04	12.37	13.01	14.24
	4H	16.06	16.62	17.02	17.58	18.84	11.97	12.53	12.93	13.49	14.75
	6H	16.57	17.06	17.54	18.04	19.30	12.38	12.87	13.36	13.85	15.11
	8H	16.74	17.20	17.72	18.18	19.44	12.51	12.96	13.48	13.94	15.21
	12H	16.84	17.25	17.83	18.24	19.52	12.57	12.98	13.57	13.98	15.25
8H	4H	16.03	16.48	17.00	17.46	18.73	12.25	12.70	13.22	13.68	14.95
	6H	16.59	16.97	17.59	17.99	19.25	12.76	13.14	13.76	14.16	15.42
	8H	16.80	17.13	17.81	18.14	19.43	12.95	13.28	13.95	14.29	15.57
	12H	16.94	17.23	17.95	18.23	19.56	13.06	13.35	14.07	14.36	15.69
12H	4H	15.98	16.39	16.97	17.39	18.66	12.26	12.66	13.25	13.66	14.93
	6H	16.56	16.90	17.57	17.90	19.19	12.81	13.14	13.82	14.15	15.43
	8H	16.78	17.08	17.80	18.08	19.41	13.02	13.31	14.03	14.31	15.64

END OF REPORT