

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923625

Luminaire Tested: DFN2DIP-TR3F0-090D060US940-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923625
REPORT IS A COMBINATION OF REPORTS P901845 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D060US940-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13241.9 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 140
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923625
CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P923625
 CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	65	65	65	60
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55	55	55	55	51
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	47	47	47	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	40	40	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	34	34	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	30	30	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	26	26	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	23	23	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3891	3891	3891
5°	3895	3834	3860
10°	3862	3779	3805
15°	3803	3713	3721
20°	3724	3624	3635
25°	3645	3517	3536
30°	3547	3417	3411
35°	3454	3301	3278
40°	3340	3183	3152
45°	3226	3064	3022
50°	3102	2939	2873
55°	2971	2795	2734
60°	2823	2625	2576
65°	2662	2447	2389
70°	2456	2231	2188
75°	2172	1972	1998
80°	1828	1640	1642
85°	1291	1081	1060

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3226 cd/sqm



TEST NUMBER: P923625

CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.9	2.2
10°-20°	827.0	6.2
20°-30°	1215.3	9.2
30°-40°	1411.5	10.7
40°-50°	1409.7	10.6
50°-60°	1229.3	9.3
60°-70°	908.7	6.9
70°-80°	514.1	3.9
80°-90°	138.9	1.0
90°-100°	59.5	0.4
100°-110°	222.0	1.7
110°-120°	588.7	4.4
120°-130°	976.3	7.4
130°-140°	1037.1	7.8
140°-150°	963.9	7.3
150°-160°	774.9	5.9
160°-170°	499.3	3.8
170°-180°	171.9	1.3
0°-30°	2336.2	17.6
0°-40°	3747.7	28.3
0°-60°	6386.7	48.2
0°-90°	7948.3	60.0
90°-120°	870.2	6.6
90°-150°	3847.4	29.1
90°-180°	5294.0	40.0
0°-180°	13241.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3123	3123	3123	3123	3123	
5°	3123	3111	3078	3102	3096	296
15°	2973	2955	2916	2928	2913	837
25°	2690	2666	2616	2621	2616	1238
35°	2321	2291	2243	2225	2210	1449
45°	1889	1868	1823	1790	1778	1458
55°	1430	1411	1375	1339	1324	1278
65°	964	946	916	889	874	953
75°	504	499	483	466	472	538
85°	123	120	117	108	105	137
90°	1	16	26	33	35	12
95°	85	42	51	58	56	101
105°	397	436	80	94	99	424
115°	751	774	806	201	107	740
125°	1062	1079	1104	1113	1117	947
135°	1314	1335	1347	1360	1358	1015
145°	1525	1523	1546	1555	1548	954
155°	1679	1667	1683	1691	1680	774
165°	1769	1761	1765	1774	1765	500
175°	1810	1800	1803	1812	1799	172
180°	1806	1806	1806	1806	1806	



TEST NUMBER: P923625

CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3122.7	3122.7	3122.7	3122.7	3122.7
2.5°	3140.9	3125.9	3092.8	3122.7	3117.0
5°	3122.7	3110.9	3077.8	3101.7	3095.9
7.5°	3101.7	3083.9	3050.7	3075.0	3068.9
10°	3068.9	3047.9	3011.8	3035.7	3026.8
12.5°	3023.6	3005.8	2969.8	2984.7	2978.8
15°	2972.7	2954.9	2915.6	2927.8	2912.8
17.5°	2909.6	2891.7	2852.6	2867.6	2852.6
20°	2840.5	2822.6	2780.5	2789.4	2777.7
22.5°	2771.6	2744.6	2705.4	2705.4	2699.3
25°	2690.4	2666.5	2615.6	2621.3	2615.6
27.5°	2600.2	2579.2	2540.4	2531.5	2516.5
30°	2510.4	2486.2	2441.2	2432.3	2420.3
32.5°	2414.2	2396.4	2348.2	2330.1	2318.0
35°	2321.2	2291.2	2243.1	2225.0	2210.0
37.5°	2216.1	2189.0	2140.8	2119.9	2104.9
40°	2108.0	2083.8	2035.7	2008.9	1996.9
42.5°	2002.9	1978.7	1930.9	1900.7	1882.8
45°	1888.8	1867.9	1822.6	1789.8	1777.7
47.5°	1777.7	1756.7	1708.5	1675.4	1657.6
50°	1660.5	1645.5	1603.4	1561.4	1546.4
52.5°	1546.4	1525.4	1486.5	1453.4	1432.4
55°	1429.5	1411.3	1375.3	1339.3	1324.4
57.5°	1312.2	1297.3	1258.1	1222.1	1210.0
60°	1195.0	1183.2	1141.1	1108.0	1099.1
62.5°	1080.9	1059.9	1029.9	1000.1	987.9
65°	964.0	945.8	915.9	888.9	873.9
67.5°	843.9	828.7	801.8	780.9	768.7
70°	732.7	720.6	693.6	672.5	660.8
72.5°	618.7	606.5	591.6	570.6	561.7
75°	504.4	498.6	483.3	465.5	471.5
77.5°	402.3	390.3	384.2	375.3	366.4
80°	300.4	297.2	291.1	282.2	276.3
82.5°	204.2	204.2	201.3	189.2	189.2
85°	123.0	120.1	117.3	108.0	105.1
87.5°	54.1	48.1	42.1	33.2	30.0
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.8	45.7	66.5	70.6	71.9
100°	231.3	52.3	74.5	84.9	87.5
102.5°	317.4	315.0	77.1	91.4	95.4
105°	397.2	436.4	79.7	94.0	99.3
107.5°	490.0	522.5	82.4	96.7	101.9
110°	578.9	606.2	228.7	98.1	103.2



TEST NUMBER: P923625

CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.5	685.9	663.7	100.5	104.6
115°	751.3	773.5	806.2	201.3	107.2
117.5°	828.3	854.4	876.7	689.8	347.5
120°	914.6	934.2	957.8	973.4	797.0
122.5°	987.7	1008.6	1034.8	1042.6	1044.0
125°	1062.2	1079.2	1104.0	1113.2	1117.0
127.5°	1130.2	1148.4	1168.1	1181.2	1182.4
130°	1194.2	1215.1	1229.4	1243.8	1242.6
132.5°	1259.5	1276.6	1290.8	1302.6	1301.4
135°	1314.5	1335.4	1347.0	1360.2	1357.5
137.5°	1371.8	1387.5	1400.7	1413.7	1409.9
140°	1428.0	1438.6	1452.9	1464.6	1458.1
142.5°	1475.2	1484.3	1501.3	1511.6	1505.1
145°	1524.8	1523.4	1545.6	1554.8	1548.3
147.5°	1567.8	1563.9	1586.1	1592.6	1587.5
150°	1609.7	1600.5	1621.5	1629.2	1622.7
152.5°	1644.9	1634.5	1654.0	1662.0	1652.8
155°	1678.9	1667.2	1682.9	1690.7	1680.2
157.5°	1706.4	1695.9	1707.7	1716.9	1706.4
160°	1729.9	1722.0	1729.9	1737.7	1728.6
162.5°	1750.7	1742.9	1749.4	1758.6	1746.9
165°	1769.1	1761.3	1765.1	1774.3	1765.1
167.5°	1783.4	1775.6	1779.6	1788.8	1776.9
170°	1795.3	1787.3	1790.0	1799.1	1787.3
172.5°	1803.0	1795.3	1797.9	1807.1	1795.3
175°	1809.5	1800.4	1803.0	1812.1	1799.1
177.5°	1812.1	1803.0	1804.4	1813.6	1801.8
180°	1805.6	1805.6	1805.6	1805.6	1805.6



TEST NUMBER: P923625
 CATALOG NUMBER: DFN2DIP-TR3F0-090D060US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.82	13.78	13.68	14.66	15.79	12.39	13.35	13.26	14.24	15.36
	3H	14.48	15.34	15.35	16.23	17.38	14.01	14.87	14.89	15.77	16.91
	4H	15.06	15.88	15.96	16.78	17.94	14.59	15.41	15.49	16.31	17.47
	6H	15.46	16.21	16.37	17.12	18.29	14.99	15.74	15.90	16.65	17.82
	8H	15.56	16.28	16.48	17.21	18.37	15.10	15.81	16.01	16.74	17.91
	12H	15.61	16.29	16.53	17.21	18.41	15.14	15.82	16.06	16.74	17.93
4H	2H	13.29	14.10	14.19	15.00	16.16	12.95	13.76	13.84	14.66	15.82
	3H	15.15	15.83	16.06	16.77	17.94	14.76	15.44	15.67	16.38	17.55
	4H	15.86	16.48	16.78	17.41	18.61	15.46	16.08	16.38	17.01	18.21
	6H	16.37	16.91	17.31	17.86	19.06	15.97	16.51	16.91	17.46	18.66
	8H	16.52	17.02	17.46	17.97	19.18	16.12	16.62	17.05	17.56	18.78
	12H	16.60	17.05	17.55	18.01	19.23	16.18	16.63	17.14	17.60	18.81
8H	4H	16.06	16.56	17.00	17.51	18.72	15.71	16.21	16.64	17.15	18.37
	6H	16.69	17.10	17.65	18.09	19.30	16.33	16.74	17.29	17.73	18.94
	8H	16.90	17.27	17.88	18.25	19.48	16.54	16.91	17.51	17.88	19.11
	12H	17.03	17.36	18.01	18.33	19.60	16.65	16.98	17.63	17.95	19.23
12H	4H	16.05	16.50	17.01	17.47	18.69	15.70	16.15	16.66	17.12	18.34
	6H	16.72	17.08	17.69	18.06	19.29	16.37	16.74	17.34	17.71	18.94
	8H	16.96	17.28	17.93	18.25	19.53	16.60	16.93	17.58	17.90	19.17