

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912094

Luminaire Tested: DFN2DIP-SQ3F0-120D060US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912094
REPORT IS A COMBINATION OF REPORTS P899914 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D060US850-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17200.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 170.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	57		
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52	49		
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45	42		
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	36		
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32		
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31	29		
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26		
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23		
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23	21		
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6302	6302	6302
5°	6308	6198	6240
10°	6242	6072	6035
15°	6152	5867	5719
20°	6034	5587	5332
25°	5914	5273	4959
30°	5753	4952	4486
35°	5596	4607	4070
40°	5435	4250	3594
45°	5249	3855	3163
50°	5056	3457	2742
55°	4855	3032	2338
60°	4621	2587	1922
65°	4352	2137	1728
70°	4025	1716	1560
75°	3614	1504	1415
80°	3020	1248	1220
85°	2048	813	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5249 cd/sqm

TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.5	3.0
10°-20°	1415.1	8.2
20°-30°	1986.8	11.6
30°-40°	2165.7	12.6
40°-50°	1990.5	11.6
50°-60°	1563.2	9.1
60°-70°	1017.5	5.9
70°-80°	523.8	3.0
80°-90°	139.7	0.8
90°-100°	130.2	0.8
100°-110°	413.7	2.4
110°-120°	708.0	4.1
120°-130°	931.2	5.4
130°-140°	1045.3	6.1
140°-150°	1025.0	6.0
150°-160°	859.8	5.0
160°-170°	570.2	3.3
170°-180°	199.3	1.2
0°-30°	3917.3	22.8
0°-40°	6083.0	35.4
0°-60°	9636.8	56.0
0°-90°	11317.8	65.8
90°-120°	1252.0	7.3
90°-150°	4253.5	24.7
90°-180°	5883.0	34.2
0°-180°	17200.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5500	5500	5500	5500	5500	
5°	5500	5475	5410	5455	5440	522
15°	5231	5176	5008	4913	4863	1474
25°	4749	4589	4261	4057	3982	2184
35°	4092	3838	3400	3086	2976	2561
45°	3345	3011	2489	2135	2016	2583
55°	2543	2155	1618	1319	1225	2273
65°	1717	1314	866	697	682	1703
75°	916	567	398	363	358	969
85°	214	109	94	94	94	246
90°	2	23	62	58	60	17
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5500.2	5500.2	5500.2	5500.2	5500.2
2.5°	5525.0	5500.2	5445.3	5495.4	5485.3
5°	5500.2	5475.4	5410.4	5455.3	5440.5
7.5°	5455.3	5425.7	5356.0	5375.5	5350.7
10°	5395.6	5360.8	5261.4	5246.1	5216.6
12.5°	5321.1	5276.3	5141.5	5112.0	5057.2
15°	5231.4	5176.5	5007.5	4912.9	4863.3
17.5°	5126.8	5047.1	4837.9	4728.7	4648.9
20°	5007.5	4907.7	4658.9	4534.8	4424.9
22.5°	4878.0	4763.5	4474.6	4305.6	4231.2
25°	4748.7	4589.2	4260.7	4056.8	3981.9
27.5°	4594.5	4424.9	4061.6	3827.7	3713.0
30°	4430.2	4240.7	3842.5	3588.9	3454.3
32.5°	4270.8	4041.5	3633.9	3335.0	3210.3
35°	4091.8	3837.7	3399.9	3086.2	2976.3
37.5°	3917.4	3643.4	3180.7	2836.9	2712.8
40°	3733.1	3434.8	2951.6	2598.3	2468.9
42.5°	3544.0	3225.6	2722.9	2354.3	2230.2
45°	3345.0	3011.3	2488.9	2135.2	2015.7
47.5°	3155.9	2802.7	2265.0	1911.3	1801.9
50°	2946.8	2593.5	2045.9	1702.1	1598.1
52.5°	2742.4	2369.0	1836.7	1508.2	1413.8
55°	2543.4	2155.2	1617.6	1319.2	1224.7
57.5°	2339.4	1941.3	1423.7	1144.9	1065.2
60°	2130.4	1732.1	1219.3	965.9	886.2
62.5°	1926.6	1528.3	1045.1	806.5	766.8
65°	1717.4	1313.9	866.1	697.1	681.8
67.5°	1518.3	1114.8	697.1	612.1	597.3
70°	1309.2	921.0	577.2	527.6	507.5
72.5°	1110.1	741.5	482.6	443.0	433.1
75°	915.7	567.1	398.2	363.3	358.5
77.5°	722.0	402.9	313.7	293.7	283.6
80°	542.4	288.9	238.7	219.1	219.1
82.5°	378.2	194.3	164.2	154.2	154.2
85°	213.9	109.3	94.5	94.5	94.5
87.5°	79.7	39.6	39.6	34.8	34.8
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4

TEST NUMBER: P912094

CATALOG NUMBER: DFN2DIP-SQ3F0-120D060US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.87	15.85	15.69	16.68	17.71	10.83	11.81	11.65	12.64	13.67
	3H	16.55	17.43	17.38	18.27	19.33	12.02	12.90	12.85	13.74	14.80
	4H	17.17	17.99	18.01	18.84	19.91	12.48	13.30	13.32	14.15	15.22
	6H	17.59	18.35	18.45	19.21	20.29	12.80	13.56	13.66	14.42	15.50
	8H	17.72	18.44	18.59	19.32	20.40	12.89	13.61	13.76	14.49	15.57
	12H	17.78	18.47	18.66	19.34	20.45	12.94	13.62	13.81	14.49	15.60
4H	2H	14.90	15.73	15.75	16.58	17.65	11.44	12.27	12.29	13.12	14.18
	3H	16.74	17.43	17.60	18.31	19.39	12.80	13.48	13.66	14.37	15.45
	4H	17.43	18.06	18.31	18.94	20.05	13.35	13.97	14.22	14.85	15.96
	6H	17.95	18.49	18.84	19.39	20.51	13.77	14.30	14.65	15.21	16.32
	8H	18.13	18.63	19.02	19.53	20.66	13.89	14.40	14.79	15.29	16.42
	12H	18.23	18.68	19.14	19.60	20.73	13.96	14.41	14.87	15.33	16.46
8H	4H	17.41	17.91	18.30	18.81	19.94	13.63	14.13	14.53	15.03	16.16
	6H	17.98	18.39	18.90	19.33	20.46	14.15	14.56	15.07	15.50	16.63
	8H	18.19	18.56	19.12	19.49	20.64	14.34	14.70	15.26	15.64	16.78
	12H	18.33	18.66	19.26	19.58	20.78	14.46	14.78	15.39	15.70	16.90
12H	4H	17.37	17.82	18.28	18.74	19.87	13.64	14.10	14.56	15.01	16.14
	6H	17.95	18.32	18.88	19.25	20.40	14.20	14.56	15.13	15.50	16.64
	8H	18.18	18.50	19.11	19.43	20.62	14.41	14.73	15.34	15.66	16.85

END OF REPORT