

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910093

Luminaire Tested: DFN2DIP-TR4F0-060D090US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910093
REPORT IS A COMBINATION OF REPORTS P901984 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-060D090US840-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14148.2 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 121
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1989	1989	1989
5°	1993	1958	1970
10°	1973	1919	1906
15°	1946	1856	1807
20°	1910	1769	1685
25°	1873	1671	1568
30°	1824	1570	1419
35°	1775	1462	1288
40°	1726	1350	1138
45°	1669	1226	1002
50°	1610	1101	869
55°	1548	967	741
60°	1477	827	610
65°	1394	685	549
70°	1294	552	497
75°	1170	487	452
80°	988	408	392
85°	689	272	294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1669 cd/sqm

TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	1.7
10°-20°	644.3	4.6
20°-30°	904.6	6.4
30°-40°	986.1	7.0
40°-50°	906.3	6.4
50°-60°	711.7	5.0
60°-70°	463.3	3.3
70°-80°	238.5	1.7
80°-90°	66.3	0.5
90°-100°	101.2	0.7
100°-110°	377.0	2.7
110°-120°	1000.0	7.1
120°-130°	1658.6	11.7
130°-140°	1761.8	12.5
140°-150°	1637.4	11.6
150°-160°	1316.4	9.3
160°-170°	848.2	6.0
170°-180°	292.0	2.1
0°-30°	1783.6	12.6
0°-40°	2769.6	19.6
0°-60°	4387.7	31.0
0°-90°	5155.7	36.4
90°-120°	1478.2	10.4
90°-150°	6535.9	46.2
90°-180°	8992.0	63.6
0°-180°	14148.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	2	27	44	56	60	13
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1370	342	182	1256
125°	1804	1833	1876	1891	1898	1609
135°	2233	2268	2288	2311	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2999	3014	2999	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.8	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.7
102.5°	539.3	535.0	131.0	155.2	162.1
105°	674.7	741.4	135.4	159.8	168.6
107.5°	832.3	887.7	140.0	164.2	173.2
110°	983.3	1029.8	388.5	166.5	175.3

TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.4	1165.2	1127.5	170.8	177.6
115°	1276.2	1313.8	1369.5	341.8	182.1
117.5°	1407.1	1451.5	1489.3	1171.8	590.4
120°	1553.7	1586.9	1627.0	1653.6	1353.9
122.5°	1677.9	1713.4	1758.0	1771.1	1773.5
125°	1804.3	1833.3	1875.5	1891.1	1897.6
127.5°	1919.8	1950.9	1984.4	2006.5	2008.6
130°	2028.6	2064.3	2088.5	2112.9	2110.9
132.5°	2139.6	2168.6	2192.8	2212.9	2210.8
135°	2232.9	2268.5	2288.3	2310.7	2306.2
137.5°	2330.5	2357.0	2379.4	2401.6	2395.0
140°	2425.8	2443.8	2468.0	2488.0	2477.0
142.5°	2506.0	2521.5	2550.2	2567.9	2556.9
145°	2590.3	2587.9	2625.7	2641.2	2630.1
147.5°	2663.3	2656.8	2694.4	2705.5	2696.7
150°	2734.5	2719.0	2754.5	2767.6	2756.6
152.5°	2794.3	2776.6	2809.8	2823.3	2807.7
155°	2852.1	2832.3	2858.8	2872.1	2854.4
157.5°	2898.7	2881.0	2901.0	2916.6	2898.7
160°	2938.7	2925.3	2938.7	2951.9	2936.4
162.5°	2974.1	2960.8	2971.9	2987.5	2967.5
165°	3005.2	2991.9	2998.6	3014.1	2998.6
167.5°	3029.7	3016.3	3023.0	3038.6	3018.6
170°	3049.7	3036.3	3040.7	3056.3	3036.3
172.5°	3062.9	3049.7	3054.1	3069.7	3049.7
175°	3073.9	3058.4	3062.9	3078.4	3056.3
177.5°	3078.4	3062.9	3065.2	3080.8	3060.8
180°	3067.4	3067.4	3067.4	3067.4	3067.4

TEST NUMBER: P910093

CATALOG NUMBER: DFN2DIP-TR4F0-060D090US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.12	8.85	9.19	9.92	11.37	4.09	4.82	5.16	5.89	7.34
	3H	9.79	10.44	10.87	11.52	12.99	5.27	5.93	6.35	7.00	8.48
	4H	10.39	11.01	11.48	12.09	13.57	5.72	6.34	6.81	7.42	8.90
	6H	10.81	11.38	11.91	12.46	13.95	6.04	6.61	7.14	7.69	9.18
	8H	10.93	11.47	12.03	12.57	14.05	6.12	6.67	7.23	7.76	9.25
	12H	10.99	11.50	12.10	12.59	14.10	6.16	6.68	7.27	7.77	9.28
4H	2H	8.12	8.74	9.22	9.82	11.30	4.67	5.29	5.77	6.37	7.85
	3H	9.94	10.46	11.05	11.56	13.06	6.02	6.53	7.12	7.64	9.13
	4H	10.63	11.10	11.74	12.20	13.71	6.56	7.03	7.67	8.13	9.64
	6H	11.14	11.54	12.26	12.66	14.17	6.98	7.38	8.09	8.50	10.00
	8H	11.31	11.69	12.43	12.80	14.32	7.10	7.48	8.22	8.59	10.11
	12H	11.40	11.75	12.54	12.87	14.40	7.16	7.51	8.30	8.63	10.16
8H	4H	10.59	10.97	11.71	12.08	13.60	6.83	7.21	7.95	8.32	9.84
	6H	11.15	11.47	12.29	12.62	14.14	7.35	7.66	8.49	8.81	10.33
	8H	11.37	11.64	12.51	12.78	14.31	7.54	7.81	8.68	8.95	10.48
	12H	11.50	11.74	12.65	12.87	14.45	7.66	7.89	8.80	9.02	10.60
12H	4H	10.54	10.88	11.67	12.00	13.53	6.83	7.17	7.97	8.30	9.82
	6H	11.13	11.40	12.27	12.54	14.07	7.40	7.67	8.54	8.80	10.34
	8H	11.35	11.58	12.49	12.71	14.29	7.60	7.84	8.75	8.97	10.55

END OF REPORT