

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912747

Luminaire Tested: DFN2DIP-TR4F0-040D090US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912747
REPORT IS A COMBINATION OF REPORTS P901979 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D090US850-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14272.8 lumens
Efficiency: N/A
Efficacy: 143.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	93	89	86	82	84	80	77	74	64	61	59	48	47	46	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	26	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	27	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	14	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1371	1371	1371
5°	1373	1352	1361
10°	1362	1334	1343
15°	1342	1312	1314
20°	1315	1281	1284
25°	1288	1245	1250
30°	1255	1211	1207
35°	1223	1171	1161
40°	1183	1130	1117
45°	1144	1090	1073
50°	1101	1047	1021
55°	1056	998	973
60°	1005	940	919
65°	950	879	855
70°	880	805	785
75°	782	717	721
80°	664	604	599
85°	481	410	397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1788 cd/sqm

TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.1
10°-20°	457.1	3.2
20°-30°	671.7	4.7
30°-40°	780.2	5.5
40°-50°	779.2	5.5
50°-60°	679.5	4.8
60°-70°	502.3	3.5
70°-80°	284.2	2.0
80°-90°	80.9	0.6
90°-100°	111.1	0.8
100°-110°	414.0	2.9
110°-120°	1098.2	7.7
120°-130°	1821.4	12.8
130°-140°	1934.7	13.6
140°-150°	1798.1	12.6
150°-160°	1445.6	10.1
160°-170°	931.5	6.5
170°-180°	320.6	2.2
0°-30°	1291.3	9.0
0°-40°	2071.5	14.5
0°-60°	3530.2	24.7
0°-90°	4397.6	30.8
90°-120°	1623.3	11.4
90°-150°	7177.5	50.3
90°-180°	9875.0	69.2
0°-180°	14272.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	2	29	49	61	66	13
95°	158	78	95	107	105	188
105°	741	814	149	175	185	792
115°	1401	1443	1504	375	200	1380
125°	1982	2013	2060	2077	2084	1767
135°	2452	2491	2513	2538	2533	1894
145°	2845	2842	2883	2900	2888	1779
155°	3132	3110	3140	3154	3135	1443
165°	3300	3286	3293	3310	3293	932
175°	3376	3359	3364	3381	3356	321
180°	3368	3368	3368	3368	3368	

TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	2.3	29.3	48.6	61.1	65.7
92.5°	61.1	51.2	58.4	63.4	65.7
95°	158.4	77.9	94.9	107.4	104.8
97.5°	285.1	85.4	124.2	131.6	134.0
100°	431.5	97.6	139.0	158.4	163.2
102.5°	592.2	587.5	143.8	170.5	178.0
105°	740.9	814.2	148.7	175.4	185.2
107.5°	914.0	974.8	153.7	180.3	190.2
110°	1079.8	1130.8	426.6	182.9	192.5

TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1235.9	1279.6	1238.2	187.5	195.1
115°	1401.4	1442.8	1503.9	375.4	200.0
117.5°	1545.3	1594.0	1635.6	1286.9	648.3
120°	1706.2	1742.7	1786.7	1815.9	1486.8
122.5°	1842.6	1881.6	1930.5	1945.0	1947.6
125°	1981.5	2013.3	2059.6	2076.7	2083.9
127.5°	2108.2	2142.4	2179.2	2203.5	2205.8
130°	2227.8	2266.9	2293.5	2320.4	2318.1
132.5°	2349.6	2381.5	2408.1	2430.2	2427.8
135°	2452.1	2491.1	2512.9	2537.5	2532.6
137.5°	2559.2	2588.4	2613.0	2637.3	2630.1
140°	2663.9	2683.7	2710.3	2732.2	2720.2
142.5°	2752.0	2769.1	2800.6	2820.0	2807.9
145°	2844.6	2841.9	2883.4	2900.5	2888.3
147.5°	2924.8	2917.6	2958.9	2971.1	2961.5
150°	3003.0	2985.9	3024.9	3039.3	3027.2
152.5°	3068.6	3049.2	3085.7	3100.4	3083.4
155°	3132.0	3110.3	3139.5	3154.0	3134.6
157.5°	3183.3	3163.9	3185.8	3202.9	3183.3
160°	3227.2	3212.4	3227.2	3241.7	3224.6
162.5°	3266.0	3251.5	3263.7	3280.8	3258.8
165°	3300.2	3285.6	3293.0	3310.0	3293.0
167.5°	3327.1	3312.4	3319.8	3336.9	3314.9
170°	3349.1	3334.3	3339.2	3356.3	3334.3
172.5°	3363.6	3349.1	3353.9	3371.0	3349.1
175°	3375.7	3358.6	3363.6	3380.6	3356.3
177.5°	3380.6	3363.6	3366.1	3383.2	3361.3
180°	3368.5	3368.5	3368.5	3368.5	3368.5

TEST NUMBER: P912747

CATALOG NUMBER: DFN2DIP-TR4F0-040D090US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.26	6.97	7.37	8.07	9.59	5.83	6.54	6.93	7.64	9.16
	3H	7.91	8.55	9.02	9.66	11.19	7.44	8.07	8.55	9.18	10.72
	4H	8.49	9.09	9.61	10.21	11.75	8.02	8.62	9.14	9.73	11.28
	6H	8.88	9.44	10.01	10.55	12.11	8.41	8.96	9.54	10.08	11.63
	8H	8.98	9.51	10.12	10.64	12.19	8.51	9.04	9.64	10.17	11.71
	12H	9.02	9.53	10.16	10.65	12.22	8.54	9.05	9.68	10.17	11.74
4H	2H	6.70	7.31	7.84	8.42	9.96	6.36	6.96	7.49	8.08	9.62
	3H	8.56	9.06	9.69	10.20	11.75	8.16	8.67	9.30	9.80	11.36
	4H	9.26	9.73	10.40	10.85	12.43	8.86	9.32	10.00	10.45	12.02
	6H	9.77	10.17	10.92	11.32	12.88	9.36	9.76	10.51	10.91	12.47
	8H	9.92	10.29	11.06	11.43	13.01	9.50	9.87	10.65	11.02	12.60
	12H	9.98	10.32	11.14	11.47	13.06	9.56	9.90	10.72	11.05	12.64
8H	4H	9.45	9.82	10.59	10.96	12.54	9.09	9.46	10.23	10.60	12.18
	6H	10.07	10.38	11.24	11.56	13.14	9.71	10.02	10.88	11.20	12.78
	8H	10.29	10.56	11.46	11.72	13.32	9.92	10.19	11.10	11.35	12.95
	12H	10.42	10.65	11.59	11.81	13.44	10.03	10.27	11.21	11.43	13.06
12H	4H	9.43	9.76	10.59	10.92	12.50	9.07	9.41	10.24	10.56	12.15
	6H	10.10	10.37	11.27	11.53	13.13	9.75	10.02	10.92	11.18	12.78
	8H	10.34	10.57	11.51	11.73	13.36	9.98	10.21	11.16	11.37	13.01

END OF REPORT