

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918471

Luminaire Tested: DFN2DIP-TR4F0-120D040US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918471
REPORT IS A COMBINATION OF REPORTS P901905 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D040US930-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12914.3 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 156
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918471
CATALOG NUMBER: DFN2DIP-TR4F0-120D040US930-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918471

CATALOG NUMBER: DFN2DIP-TR4F0-120D040US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.3	2.8
10°-20°	1008.1	7.8
20°-30°	1481.5	11.5
30°-40°	1720.7	13.3
40°-50°	1718.6	13.3
50°-60°	1498.5	11.6
60°-70°	1107.8	8.6
70°-80°	626.7	4.9
80°-90°	167.4	1.3
90°-100°	36.3	0.3
100°-110°	135.3	1.0
110°-120°	358.8	2.8
120°-130°	595.1	4.6
130°-140°	632.1	4.9
140°-150°	587.5	4.5
150°-160°	472.3	3.7
160°-170°	304.4	2.4
170°-180°	104.8	0.8
0°-30°	2848.0	22.1
0°-40°	4568.7	35.4
0°-60°	7785.8	60.3
0°-90°	9687.7	75.0
90°-120°	530.4	4.1
90°-150°	2345.2	18.2
90°-180°	3227.0	25.0
0°-180°	12914.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3807	3807	3807	3807	3807	
5°	3807	3792	3752	3781	3774	361
15°	3624	3602	3554	3569	3551	1021
25°	3280	3251	3188	3196	3188	1509
35°	2830	2793	2734	2712	2694	1767
45°	2303	2277	2222	2182	2167	1777
55°	1743	1720	1677	1633	1614	1558
65°	1175	1153	1117	1084	1065	1162
75°	615	608	589	567	575	656
85°	150	146	143	132	128	167
90°	1	10	16	20	21	12
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	



TEST NUMBER: P918471

CATALOG NUMBER: DFN2DIP-TR4F0-120D040US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3806.9	3806.9	3806.9	3806.9	3806.9
2.5°	3829.0	3810.7	3770.3	3806.9	3799.9
5°	3806.9	3792.4	3752.1	3781.2	3774.2
7.5°	3781.2	3759.4	3719.1	3748.6	3741.2
10°	3741.2	3715.6	3671.7	3700.8	3690.0
12.5°	3686.0	3664.3	3620.4	3638.7	3631.3
15°	3623.9	3602.2	3554.4	3569.1	3550.9
17.5°	3547.0	3525.3	3477.5	3495.8	3477.5
20°	3462.7	3441.0	3389.8	3400.6	3386.3
22.5°	3378.8	3345.8	3298.0	3298.0	3290.7
25°	3279.8	3250.7	3188.5	3195.6	3188.5
27.5°	3169.9	3144.3	3096.9	3086.0	3067.8
30°	3060.4	3030.9	2976.1	2965.2	2950.5
32.5°	2943.1	2921.4	2862.7	2840.6	2825.8
35°	2829.7	2793.2	2734.5	2712.4	2694.2
37.5°	2701.5	2668.6	2609.9	2584.3	2566.0
40°	2569.9	2540.4	2481.7	2449.1	2434.3
42.5°	2441.7	2412.2	2353.9	2317.1	2295.3
45°	2302.6	2277.0	2221.9	2181.9	2167.1
47.5°	2167.1	2141.5	2082.8	2042.5	2020.7
50°	2024.2	2006.0	1954.7	1903.4	1885.1
52.5°	1885.1	1859.5	1812.2	1771.7	1746.1
55°	1742.6	1720.5	1676.6	1632.7	1614.5
57.5°	1599.7	1581.4	1533.7	1489.8	1475.0
60°	1456.8	1442.4	1391.1	1350.8	1339.9
62.5°	1317.8	1292.1	1255.6	1219.1	1204.4
65°	1175.3	1153.1	1116.6	1083.5	1065.4
67.5°	1028.8	1010.2	977.5	951.9	937.2
70°	893.2	878.5	845.5	819.9	805.5
72.5°	754.2	739.5	721.2	695.6	684.7
75°	614.8	607.8	589.1	567.4	574.8
77.5°	490.5	475.7	468.4	457.5	446.6
80°	366.2	362.3	355.0	344.1	336.7
82.5°	248.9	248.9	245.5	230.7	230.7
85°	149.9	146.4	142.9	131.7	128.2
87.5°	66.0	58.6	51.3	40.4	36.5
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P918471

CATALOG NUMBER: DFN2DIP-TR4F0-120D040US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7



TEST NUMBER: P918471
 CATALOG NUMBER: DFN2DIP-TR4F0-120D040US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.16	14.30	13.87	15.03	15.89	12.73	13.87	13.44	14.60	15.46
	3H	14.84	15.87	15.56	16.60	17.50	14.37	15.39	15.09	16.13	17.03
	4H	15.44	16.41	16.18	17.16	18.06	14.97	15.94	15.71	16.68	17.59
	6H	15.85	16.75	16.61	17.51	18.43	15.38	16.27	16.13	17.03	17.95
	8H	15.97	16.82	16.73	17.60	18.52	15.49	16.34	16.25	17.12	18.04
	12H	16.02	16.84	16.79	17.61	18.56	15.54	16.36	16.31	17.13	18.08
4H	2H	13.65	14.62	14.40	15.37	16.28	13.31	14.28	14.05	15.03	15.93
	3H	15.54	16.35	16.30	17.14	18.06	15.15	15.96	15.91	16.74	17.67
	4H	16.27	17.01	17.04	17.79	18.74	15.86	16.60	16.64	17.38	18.34
	6H	16.80	17.44	17.59	18.25	19.21	16.39	17.03	17.18	17.84	18.80
	8H	16.96	17.55	17.75	18.36	19.33	16.54	17.14	17.34	17.95	18.92
	12H	17.04	17.58	17.86	18.41	19.38	16.62	17.16	17.44	17.99	18.96
8H	4H	16.49	17.08	17.28	17.89	18.86	16.13	16.72	16.92	17.53	18.50
	6H	17.13	17.63	17.95	18.47	19.45	16.77	17.26	17.59	18.11	19.08
	8H	17.35	17.79	18.19	18.64	19.63	16.99	17.43	17.82	18.27	19.26
	12H	17.50	17.89	18.34	18.72	19.77	17.12	17.50	17.95	18.34	19.39
12H	4H	16.49	17.02	17.30	17.85	18.83	16.14	16.67	16.95	17.50	18.48
	6H	17.16	17.60	18.00	18.45	19.44	16.81	17.25	17.65	18.10	19.09
	8H	17.42	17.81	18.26	18.64	19.69	17.06	17.45	17.90	18.29	19.33