

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910065

Luminaire Tested: DFN2DIP-TR4F0-050D110US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910065
REPORT IS A COMBINATION OF REPORTS P902018 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D110US840-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15289.3 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 126.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		71	71	71		53	53	53		36	36	36
1	93	89	85	82		83	80	77	74		63	61	59		47	46	44		32	32	31
2	85	78	72	67		76	70	65	61		55	52	49		41	39	37		29	27	26
3	78	69	62	56		69	62	56	51		49	45	41		37	34	32		26	24	23
4	71	61	53	48		63	55	49	44		43	39	35		33	30	28		23	21	20
5	65	54	47	41		58	49	42	37		39	34	31		30	26	24		21	19	17
6	60	49	41	35		54	44	37	33		35	30	27		27	24	21		19	17	15
7	55	44	36	31		50	40	33	28		32	27	24		24	21	19		17	15	14
8	51	40	32	27		46	36	30	25		29	24	21		22	19	17		16	14	12
9	48	36	29	24		43	33	27	22		26	22	19		20	17	15		15	13	11
10	45	33	26	22		40	30	24	20		24	20	17		19	16	13		14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1658	1658	1658
5°	1661	1632	1642
10°	1644	1600	1588
15°	1622	1547	1506
20°	1592	1474	1404
25°	1561	1392	1307
30°	1520	1308	1182
35°	1479	1218	1073
40°	1438	1125	948
45°	1391	1022	835
50°	1341	917	724
55°	1290	806	618
60°	1230	689	508
65°	1162	571	458
70°	1079	460	414
75°	975	406	376
80°	823	340	326
85°	574	227	245

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1989 cd/sqm

TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.3
10°-20°	536.9	3.5
20°-30°	753.8	4.9
30°-40°	821.7	5.4
40°-50°	755.2	4.9
50°-60°	593.1	3.9
60°-70°	386.1	2.5
70°-80°	198.7	1.3
80°-90°	57.3	0.4
90°-100°	123.6	0.8
100°-110°	460.8	3.0
110°-120°	1222.2	8.0
120°-130°	2027.1	13.3
130°-140°	2153.3	14.1
140°-150°	2001.2	13.1
150°-160°	1608.9	10.5
160°-170°	1036.7	6.8
170°-180°	356.8	2.3
0°-30°	1486.3	9.7
0°-40°	2308.0	15.1
0°-60°	3656.4	23.9
0°-90°	4298.5	28.1
90°-120°	1806.7	11.8
90°-150°	7988.3	52.2
90°-180°	10991.0	71.9
0°-180°	15289.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	3	32	54	68	73	14
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1536
125°	2205	2241	2292	2311	2319	1967
135°	2729	2773	2797	2824	2819	2108
145°	3166	3163	3209	3228	3215	1980
155°	3486	3462	3494	3510	3489	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3744	3763	3736	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.2
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.9	160.1	189.8	198.1
105°	824.7	906.2	165.6	195.2	206.2
107.5°	1017.3	1084.9	171.1	200.7	211.7
110°	1201.8	1258.6	474.8	203.6	214.2

TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.5	1424.1	1378.1	208.7	217.1
115°	1559.7	1605.8	1673.9	417.8	222.6
117.5°	1719.9	1774.0	1820.4	1432.2	721.5
120°	1899.0	1939.5	1988.5	2021.0	1654.8
122.5°	2050.7	2094.2	2148.6	2164.7	2167.7
125°	2205.3	2240.8	2292.3	2311.3	2319.4
127.5°	2346.4	2384.4	2425.3	2452.4	2455.0
130°	2479.4	2522.9	2552.5	2582.5	2580.0
132.5°	2615.0	2650.5	2680.2	2704.6	2702.1
135°	2729.2	2772.6	2796.7	2824.2	2818.6
137.5°	2848.3	2880.8	2908.2	2935.3	2927.2
140°	2965.0	2986.8	3016.5	3040.9	3027.4
142.5°	3062.8	3081.8	3116.9	3138.6	3125.0
145°	3165.9	3163.0	3209.0	3228.1	3214.6
147.5°	3255.2	3247.1	3293.2	3306.7	3296.1
150°	3342.2	3323.2	3366.6	3382.7	3369.2
152.5°	3415.3	3393.7	3434.2	3450.7	3431.7
155°	3485.9	3461.6	3494.1	3510.3	3488.7
157.5°	3542.8	3521.2	3545.7	3564.7	3542.8
160°	3591.8	3575.3	3591.8	3607.8	3588.9
162.5°	3634.9	3618.9	3632.4	3651.4	3626.9
165°	3673.0	3656.8	3664.9	3683.9	3664.9
167.5°	3702.9	3686.5	3694.9	3713.9	3689.4
170°	3727.4	3711.0	3716.4	3735.5	3711.0
172.5°	3743.5	3727.4	3732.9	3751.9	3727.4
175°	3757.0	3738.0	3743.5	3762.6	3735.5
177.5°	3762.6	3743.5	3746.4	3765.4	3740.9
180°	3749.0	3749.0	3749.0	3749.0	3749.0

TEST NUMBER: P910065

CATALOG NUMBER: DFN2DIP-TR4F0-050D110US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.40	7.08	7.53	8.20	9.75	2.37	3.05	3.50	4.17	5.73
	3H	8.07	8.67	9.20	9.80	11.37	3.55	4.16	4.69	5.29	6.86
	4H	8.67	9.24	9.81	10.37	11.95	4.00	4.57	5.14	5.70	7.27
	6H	9.08	9.61	10.24	10.74	12.33	4.31	4.84	5.46	5.97	7.56
	8H	9.20	9.71	10.36	10.85	12.43	4.40	4.90	5.55	6.04	7.62
	12H	9.26	9.74	10.42	10.88	12.48	4.44	4.91	5.60	6.05	7.65
4H	2H	6.40	6.98	7.55	8.10	9.68	2.95	3.53	4.10	4.65	6.23
	3H	8.22	8.69	9.37	9.85	11.44	4.29	4.77	5.45	5.92	7.51
	4H	8.90	9.34	10.06	10.48	12.09	4.83	5.27	5.99	6.41	8.02
	6H	9.41	9.78	10.57	10.95	12.55	5.24	5.62	6.41	6.78	8.38
	8H	9.58	9.93	10.75	11.09	12.70	5.37	5.72	6.53	6.88	8.49
	12H	9.67	9.99	10.85	11.15	12.77	5.43	5.75	6.61	6.91	8.53
8H	4H	8.86	9.21	10.02	10.37	11.98	5.10	5.45	6.26	6.61	8.22
	6H	9.42	9.71	10.60	10.91	12.52	5.61	5.90	6.80	7.10	8.71
	8H	9.63	9.89	10.83	11.06	12.69	5.80	6.06	6.99	7.23	8.86
	12H	9.77	9.99	10.96	11.16	12.83	5.92	6.14	7.11	7.31	8.98
12H	4H	8.80	9.12	9.98	10.29	11.91	5.10	5.42	6.28	6.58	8.20
	6H	9.39	9.65	10.58	10.82	12.45	5.66	5.91	6.85	7.09	8.72
	8H	9.61	9.83	10.80	11.00	12.67	5.87	6.09	7.06	7.26	8.93

END OF REPORT