

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921251

Luminaire Tested: DFN2DIP-4P2F0-030D030US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921251
REPORT IS A COMBINATION OF REPORTS P900539 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D030US940-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5296.8 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2606	2606	2606
5°	2605	2563	2583
10°	2579	2522	2544
15°	2536	2474	2485
20°	2479	2410	2425
25°	2423	2334	2356
30°	2354	2264	2269
35°	2288	2181	2178
40°	2208	2098	2091
45°	2127	2014	2002
50°	2039	1926	1899
55°	1946	1824	1803
60°	1841	1704	1693
65°	1726	1578	1564
70°	1579	1426	1424
75°	1378	1242	1289
80°	1133	1009	1043
85°	759	631	648

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2127 cd/sqm

TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	1.8
10°-20°	275.6	5.2
20°-30°	405.1	7.6
30°-40°	470.5	8.9
40°-50°	469.9	8.9
50°-60°	409.8	7.7
60°-70°	302.9	5.7
70°-80°	171.4	3.2
80°-90°	46.8	0.9
90°-100°	29.8	0.6
100°-110°	111.0	2.1
110°-120°	294.3	5.6
120°-130°	488.2	9.2
130°-140°	518.5	9.8
140°-150°	481.9	9.1
150°-160°	387.5	7.3
160°-170°	249.7	4.7
170°-180°	85.9	1.6
0°-30°	778.7	14.7
0°-40°	1249.2	23.6
0°-60°	2128.9	40.2
0°-90°	2650.0	50.0
90°-120°	435.1	8.2
90°-150°	1923.7	36.3
90°-180°	2647.0	50.0
0°-180°	5296.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	1	8	13	16	18	5
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6



TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P921251

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.47	11.33	11.43	12.30	13.57	10.02	10.89	10.98	11.86	13.13
	3H	12.11	12.88	13.07	13.86	15.15	11.62	12.39	12.58	13.37	14.66
	4H	12.68	13.41	13.66	14.40	15.70	12.19	12.92	13.17	13.90	15.20
	6H	13.06	13.74	14.05	14.73	16.04	12.56	13.24	13.55	14.23	15.54
	8H	13.16	13.80	14.16	14.81	16.12	12.66	13.30	13.66	14.31	15.62
	12H	13.20	13.81	14.20	14.81	16.14	12.69	13.30	13.69	14.30	15.64
4H	2H	10.92	11.65	11.91	12.63	13.94	10.56	11.29	11.55	12.28	13.58
	3H	12.76	13.37	13.75	14.38	15.70	12.35	12.96	13.35	13.97	15.29
	4H	13.45	14.01	14.46	15.02	16.36	13.03	13.59	14.03	14.59	15.93
	6H	13.95	14.43	14.96	15.46	16.79	13.51	14.00	14.53	15.03	16.36
	8H	14.08	14.53	15.10	15.56	16.91	13.65	14.10	14.67	15.12	16.47
	12H	14.15	14.55	15.18	15.59	16.95	13.70	14.11	14.74	15.14	16.50
8H	4H	13.64	14.09	14.65	15.11	16.46	13.26	13.71	14.28	14.73	16.08
	6H	14.24	14.61	15.28	15.68	17.02	13.85	14.23	14.90	15.29	16.64
	8H	14.44	14.77	15.49	15.82	17.19	14.05	14.38	15.10	15.43	16.80
	12H	14.56	14.85	15.61	15.89	17.30	14.15	14.44	15.20	15.48	16.89
12H	4H	13.62	14.02	14.66	15.06	16.42	13.25	13.65	14.29	14.69	16.05
	6H	14.26	14.59	15.31	15.64	17.01	13.89	14.22	14.94	15.27	16.64
	8H	14.49	14.78	15.54	15.82	17.23	14.11	14.39	15.16	15.44	16.85

END OF REPORT