

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921351

Luminaire Tested: DFN2DIP-4P3F0-060D020US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921351
REPORT IS A COMBINATION OF REPORTS P900557 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D020US940-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7062.3 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41
5	72	60	52	46	69	58	50	44	53	46	41	48	43	39	44	40	36
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25
9	54	41	33	28	51	39	32	27	37	30	26	34	28	24	31	26	23
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2372	2372	2372
5°	2375	2338	2354
10°	2354	2305	2322
15°	2318	2265	2271
20°	2270	2211	2219
25°	2222	2146	2160
30°	2162	2086	2084
35°	2105	2015	2004
40°	2035	1944	1928
45°	1966	1872	1850
50°	1889	1797	1759
55°	1809	1709	1676
60°	1719	1606	1581
65°	1620	1499	1469
70°	1494	1368	1347
75°	1320	1211	1234
80°	1110	1010	1020
85°	781	669	668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1966 cd/sqm

TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	2.8
10°-20°	551.3	7.8
20°-30°	810.2	11.5
30°-40°	941.0	13.3
40°-50°	939.8	13.3
50°-60°	819.5	11.6
60°-70°	605.8	8.6
70°-80°	342.7	4.9
80°-90°	91.5	1.3
90°-100°	19.8	0.3
100°-110°	74.0	1.0
110°-120°	196.2	2.8
120°-130°	325.4	4.6
130°-140°	345.7	4.9
140°-150°	321.3	4.5
150°-160°	258.3	3.7
160°-170°	166.4	2.4
170°-180°	57.3	0.8
0°-30°	1557.4	22.1
0°-40°	2498.4	35.4
0°-60°	4257.8	60.3
0°-90°	5297.8	75.0
90°-120°	290.0	4.1
90°-150°	1282.5	18.2
90°-180°	1765.0	25.0
0°-180°	7062.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2074	2052	2068	2064	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	825
35°	1548	1528	1495	1483	1473	966
45°	1259	1245	1215	1193	1185	972
55°	953	941	917	893	883	852
65°	643	631	611	592	583	635
75°	336	332	322	310	314	359
85°	82	80	78	72	70	91
90°	0	5	9	11	12	7
95°	28	14	17	19	19	33
105°	132	145	27	31	33	141
115°	250	258	269	67	36	247
125°	354	360	368	371	372	316
135°	438	445	449	453	452	338
145°	508	508	515	518	516	318
155°	560	556	561	564	560	258
165°	590	587	588	592	588	167
175°	603	600	601	604	600	57
180°	602	602	602	602	602	

TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2081.8	2081.8	2081.8	2081.8	2081.8
2.5°	2093.9	2083.9	2061.8	2081.8	2078.0
5°	2081.8	2073.9	2051.8	2067.8	2064.0
7.5°	2067.8	2055.9	2033.8	2050.0	2045.9
10°	2045.9	2031.9	2007.9	2023.8	2017.9
12.5°	2015.8	2003.9	1979.9	1989.9	1985.8
15°	1981.7	1969.9	1943.8	1951.9	1941.9
17.5°	1939.7	1927.9	1901.8	1911.6	1901.8
20°	1893.6	1881.8	1853.7	1859.7	1851.8
22.5°	1847.8	1829.7	1803.6	1803.6	1799.6
25°	1793.6	1777.7	1743.7	1747.5	1743.7
27.5°	1733.5	1719.5	1693.5	1687.7	1677.7
30°	1673.7	1657.4	1627.5	1621.6	1613.5
32.5°	1609.4	1597.6	1565.5	1553.4	1545.3
35°	1547.5	1527.5	1495.4	1483.3	1473.3
37.5°	1477.4	1459.3	1427.3	1413.2	1403.2
40°	1405.3	1389.2	1357.2	1339.3	1331.2
42.5°	1335.2	1319.1	1287.3	1267.1	1255.2
45°	1259.3	1245.2	1215.0	1193.2	1185.1
47.5°	1185.1	1171.1	1139.1	1117.0	1105.0
50°	1107.0	1097.0	1069.0	1040.9	1030.9
52.5°	1030.9	1016.9	991.0	968.9	954.9
55°	953.0	940.8	916.9	892.9	882.9
57.5°	874.9	864.9	838.7	814.8	806.6
60°	796.7	788.8	760.8	738.7	732.7
62.5°	720.6	706.6	686.6	666.6	658.6
65°	642.7	630.6	610.6	592.5	582.6
67.5°	562.6	552.4	534.6	520.6	512.5
70°	488.5	480.5	462.4	448.4	440.5
72.5°	412.4	404.4	394.4	380.4	374.4
75°	336.2	332.4	322.2	310.3	314.3
77.5°	268.2	260.2	256.1	250.2	244.2
80°	200.3	198.1	194.1	188.2	184.1
82.5°	136.2	136.2	134.2	126.2	126.2
85°	81.9	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	0.4	5.3	8.6	10.9	11.8
92.5°	10.9	9.2	10.4	11.3	11.8
95°	28.3	13.9	16.9	19.2	18.7
97.5°	50.9	15.2	22.2	23.5	24.0
100°	77.1	17.4	24.8	28.3	29.2
102.5°	105.8	105.0	25.7	30.5	31.8
105°	132.4	145.4	26.6	31.3	33.1
107.5°	163.4	174.2	27.5	32.2	34.0
110°	193.0	202.1	76.2	32.7	34.4

TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.8	228.6	221.2	33.5	34.9
115°	250.4	257.8	268.8	67.1	35.8
117.5°	276.1	284.8	292.2	230.0	115.8
120°	304.9	311.4	319.2	324.5	265.6
122.5°	329.2	336.2	344.9	347.5	348.0
125°	354.1	359.7	368.0	371.0	372.4
127.5°	376.7	382.8	389.4	393.7	394.1
130°	398.1	405.0	409.8	414.6	414.2
132.5°	419.8	425.5	430.3	434.2	433.8
135°	438.2	445.1	449.0	453.4	452.5
137.5°	457.3	462.5	466.9	471.3	469.9
140°	476.0	479.6	484.3	488.2	486.1
142.5°	491.7	494.8	500.4	503.9	501.7
145°	508.3	507.8	515.2	518.3	516.1
147.5°	522.6	521.3	528.7	530.8	529.1
150°	536.5	533.5	540.5	543.1	540.9
152.5°	548.3	544.8	551.3	554.0	550.9
155°	559.6	555.7	561.0	563.6	560.1
157.5°	568.8	565.3	569.3	572.3	568.8
160°	576.7	574.0	576.7	579.3	576.2
162.5°	583.5	580.9	583.2	586.2	582.3
165°	589.7	587.1	588.4	591.5	588.4
167.5°	594.5	591.8	593.2	596.3	592.3
170°	598.4	595.8	596.6	599.7	595.8
172.5°	601.0	598.4	599.3	602.4	598.4
175°	603.2	600.1	601.0	604.0	599.7
177.5°	604.0	601.0	601.5	604.5	600.6
180°	601.9	601.9	601.9	601.9	601.9

TEST NUMBER: P921351

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.29	13.43	13.00	14.16	15.02	11.84	12.99	12.55	13.71	14.58
	3H	13.96	14.99	14.69	15.73	16.62	13.47	14.50	14.20	15.24	16.13
	4H	14.56	15.53	15.30	16.28	17.18	14.07	15.04	14.81	15.78	16.69
	6H	14.97	15.87	15.72	16.62	17.54	14.47	15.37	15.22	16.12	17.04
	8H	15.08	15.94	15.85	16.71	17.64	14.58	15.43	15.34	16.21	17.13
	12H	15.14	15.95	15.91	16.72	17.67	14.63	15.44	15.40	16.21	17.16
4H	2H	12.78	13.75	13.52	14.49	15.40	12.42	13.39	13.17	14.14	15.05
	3H	14.66	15.47	15.42	16.26	17.18	14.26	15.06	15.01	15.85	16.77
	4H	15.39	16.12	16.16	16.91	17.86	14.96	15.70	15.73	16.48	17.43
	6H	15.91	16.55	16.70	17.36	18.32	15.48	16.12	16.27	16.93	17.89
	8H	16.07	16.66	16.86	17.47	18.44	15.63	16.22	16.42	17.03	18.00
	12H	16.15	16.69	16.96	17.51	18.49	15.70	16.24	16.51	17.06	18.04
8H	4H	15.60	16.20	16.39	17.00	17.97	15.22	15.82	16.02	16.62	17.60
	6H	16.24	16.73	17.06	17.58	18.55	15.85	16.35	16.68	17.19	18.17
	8H	16.46	16.90	17.29	17.74	18.73	16.06	16.50	16.90	17.35	18.34
	12H	16.60	16.99	17.43	17.82	18.87	16.19	16.58	17.02	17.41	18.46
12H	4H	15.60	16.13	16.41	16.96	17.94	15.23	15.77	16.04	16.59	17.57
	6H	16.27	16.71	17.10	17.55	18.54	15.89	16.34	16.73	17.18	18.17
	8H	16.52	16.91	17.36	17.74	18.79	16.14	16.53	16.97	17.36	18.41