

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331495

Luminaire Tested: **S122DIW-S485D435U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331495
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3876.3 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	76	74	72	65	64	62	55	54	53	48
2	91	84	78	73	84	78	73	69	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	77	66	58	52	71	62	55	50	54	49	44	46	42	39	39	37	34	31
5	71	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	42	35	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	2.4
10°-20°	269.0	6.9
20°-30°	390.5	10.1
30°-40°	412.0	10.6
40°-50°	364.8	9.4
50°-60°	291.1	7.5
60°-70°	197.9	5.1
70°-80°	101.5	2.6
80°-90°	25.9	0.7
90°-100°	19.7	0.5
100°-110°	72.3	1.9
110°-120°	193.1	5.0
120°-130°	318.8	8.2
130°-140°	339.1	8.7
140°-150°	315.2	8.1
150°-160°	253.4	6.5
160°-170°	163.3	4.2
170°-180°	56.2	1.4
0°-30°	752.0	19.4
0°-40°	1164.1	30.0
0°-60°	1820.1	47.0
0°-90°	2145.3	55.3
90°-120°	285.1	7.4
90°-150°	1258.2	32.5
90°-180°	1731.0	44.7
0°-180°	3876.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	22
90°	12	0	12	0	12	6
95°	18	28	18	28	18	17
105°	32	130	32	130	32	34
115°	35	246	35	246	35	88
125°	365	348	365	348	365	316
135°	444	430	444	430	444	342
145°	506	499	506	499	506	317
155°	550	549	550	549	550	254
165°	577	579	577	579	577	163
175°	589	592	589	592	589	56
180°	591	591	591	591	591	



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	10.1	10.0	10.3	10.0	9.9	10.2	10.1	9.7	9.9	10.1	10.2
90°	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5	9.0	8.5	7.8
92.5°	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4	10.2	9.9	9.5
95°	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6	17.1	16.7	16.0
97.5°	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1	22.7	22.3	20.8
100°	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9	25.1	24.4	22.7
102.5°	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0	26.0	25.0	38.6
105°	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2	27.1	26.1	52.0
107.5°	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4	35.4	36.5	67.6
110°	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8	65.3	74.8	102.2



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4	154.0	188.7	195.4
115°	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8	219.7	263.7	261.3
117.5°	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8	281.5	292.1	290.5
120°	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6	314.4	313.3	311.6
122.5°	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8	334.2	333.5	331.6
125°	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5	361.8	361.2	359.4
127.5°	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1	387.1	386.1	384.8
130°	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3	403.2	402.2	401.2
132.5°	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1	419.2	418.3	417.2
135°	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6	441.6	440.7	439.8
137.5°	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5	462.5	461.6	460.6
140°	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0	476.1	475.3	474.2
142.5°	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5	488.7	487.9	486.7
145°	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0	506.3	505.6	504.0
147.5°	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2	521.7	521.2	519.6
150°	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6	531.0	530.4	528.9
152.5°	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1	539.5	539.0	537.5
155°	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7	551.1	550.5	549.4
157.5°	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4	560.7	560.1	559.3
160°	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0	566.5	565.9	565.3
162.5°	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3	571.7	571.0	570.5
165°	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8	578.1	577.4	577.2
167.5°	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2	583.5	582.8	582.6
170°	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9	586.2	585.6	585.4
172.5°	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9	588.3	587.6	587.4
175°	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2	590.5	589.8	589.6
177.5°	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4	590.9	590.3	590.3
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	10.4	10.2	10.1	10.5	9.4	9.2	7.8	6.7	6.6	6.5	6.1
90°	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6	8.5	8.4	8.3
95°	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8	24.6	21.5	18.4
97.5°	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1	46.3	37.5	28.6
100°	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7	62.6	49.6	36.6
102.5°	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2	95.5	92.7	90.0
105°	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9	132.8	135.6	138.5
107.5°	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1	168.4	170.7	173.0
110°	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3	191.3	193.3	195.3



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2	213.0	214.8	216.5
115°	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8	247.4	249.0	250.6
117.5°	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6	278.4	280.2	282.0
120°	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2	300.6	302.0	303.5
122.5°	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3	319.8	321.3	322.8
125°	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5	348.7	350.0	351.2
127.5°	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9	375.3	376.6	378.0
130°	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7	392.2	393.7	395.2
132.5°	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8	409.0	410.3	411.6
135°	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0	431.5	433.0	434.5
137.5°	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5	453.5	454.6	455.7
140°	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2	467.9	468.7	469.4
142.5°	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5	480.2	480.8	481.5
145°	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8	498.7	498.6	498.5
147.5°	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6	515.3	514.9	514.6
150°	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6	525.9	525.2	524.6
152.5°	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8	535.1	534.3	533.6
155°	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2	548.4	547.5	546.7
157.5°	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7	559.0	558.3	557.6
160°	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	565.3	564.8	564.2
162.5°	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4	570.8	570.2	569.7
165°	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7	578.2	577.6	577.0
167.5°	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2	583.6	583.1	582.5
170°	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3	586.7	586.1	585.6
172.5°	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3	588.8	588.2	587.6
175°	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0	591.3	590.6	590.0
177.5°	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4	591.9	591.3	590.8
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	6.0	5.9	5.7	5.9	5.7	5.6	5.4	5.5	5.6	5.1	5.1
90°	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5	10.0	10.4	10.8
92.5°	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4	10.7	10.9	11.1
95°	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6	18.1	18.6	18.8
97.5°	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1	23.5	23.8	24.1
100°	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9	26.6	27.4	27.9
102.5°	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0	28.0	29.0	29.6
105°	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2	29.2	30.3	31.0
107.5°	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4	33.3	32.2	31.9
110°	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8	46.3	36.8	32.2



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4	84.7	50.1	32.9
115°	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8	131.8	87.8	62.4
117.5°	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8	260.2	249.5	233.0
120°	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6	316.7	317.9	312.0
122.5°	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8	335.5	336.2	335.3
125°	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5	363.2	363.8	364.3
127.5°	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1	389.0	390.0	390.5
130°	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3	405.3	406.4	406.9
132.5°	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1	420.9	421.8	422.2
135°	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6	443.5	444.5	444.8
137.5°	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5	464.4	465.3	465.6
140°	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0	477.9	478.7	478.9
142.5°	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5	490.3	491.1	491.2
145°	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0	507.6	508.3	508.4
147.5°	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2	522.7	523.2	523.2
150°	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6	532.1	532.7	532.8
152.5°	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1	540.7	541.3	541.2
155°	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7	552.2	552.8	552.7
157.5°	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4	562.0	562.7	562.6
160°	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0	567.6	568.2	568.1
162.5°	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3	573.0	573.6	573.5
165°	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8	579.4	580.1	580.1
167.5°	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2	584.8	585.5	585.4
170°	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9	587.6	588.2	588.1
172.5°	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9	589.6	590.3	590.2
175°	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2	591.8	592.5	592.4
177.5°	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4	591.9	592.5	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	5.2	4.9	5.0	4.7	5.0	4.9	5.2	5.1	5.1	5.6	5.5
90°	11.0	11.2	11.4	11.5	11.4	11.2	11.0	10.8	10.4	10.0	9.5
92.5°	11.2	11.3	11.4	11.5	11.4	11.3	11.2	11.1	10.9	10.7	10.4
95°	18.7	18.6	18.5	18.4	18.5	18.6	18.7	18.8	18.6	18.1	17.6
97.5°	24.2	24.3	24.4	24.5	24.4	24.3	24.2	24.1	23.8	23.5	23.1
100°	28.1	28.3	28.4	28.6	28.4	28.3	28.1	27.9	27.4	26.6	25.9
102.5°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.6	29.0	28.0	27.0
105°	31.3	31.7	32.1	32.5	32.1	31.7	31.3	31.0	30.3	29.2	28.2
107.5°	32.3	32.7	33.0	33.4	33.0	32.7	32.3	31.9	32.2	33.3	34.4
110°	32.6	33.0	33.4	33.8	33.4	33.0	32.6	32.2	36.8	46.3	55.8



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	33.2	33.5	33.8	34.1	33.8	33.5	33.2	32.9	50.1	84.7	119.4
115°	55.6	48.7	41.9	35.0	41.9	48.7	55.6	62.4	87.8	131.8	175.8
117.5°	210.5	188.0	165.6	143.1	165.6	188.0	210.5	233.0	249.5	260.2	270.8
120°	299.2	286.4	273.5	260.7	273.5	286.4	299.2	312.0	317.9	316.7	315.6
122.5°	332.8	330.3	327.8	325.3	327.8	330.3	332.8	335.3	336.2	335.5	334.8
125°	364.6	364.9	365.2	365.4	365.2	364.9	364.6	364.3	363.8	363.2	362.5
127.5°	390.6	390.6	390.7	390.7	390.7	390.6	390.6	390.5	390.0	389.0	388.1
130°	406.8	406.7	406.6	406.5	406.6	406.7	406.8	406.9	406.4	405.3	404.3
132.5°	422.1	422.0	422.0	421.9	422.0	422.0	422.1	422.2	421.8	420.9	420.1
135°	444.7	444.5	444.3	444.1	444.3	444.5	444.7	444.8	444.5	443.5	442.6
137.5°	465.3	465.0	464.7	464.3	464.7	465.0	465.3	465.6	465.3	464.4	463.5
140°	478.4	477.9	477.5	477.0	477.5	477.9	478.4	478.9	478.7	477.9	477.0
142.5°	490.7	490.3	489.8	489.3	489.8	490.3	490.7	491.2	491.1	490.3	489.5
145°	507.9	507.4	507.0	506.5	507.0	507.4	507.9	508.4	508.3	507.6	507.0
147.5°	522.8	522.4	522.0	521.6	522.0	522.4	522.8	523.2	523.2	522.7	522.2
150°	532.3	531.8	531.3	530.9	531.3	531.8	532.3	532.8	532.7	532.1	531.6
152.5°	540.6	540.0	539.3	538.7	539.3	540.0	540.6	541.2	541.3	540.7	540.1
155°	551.9	551.2	550.4	549.7	550.4	551.2	551.9	552.7	552.8	552.2	551.7
157.5°	561.9	561.1	560.4	559.7	560.4	561.1	561.9	562.6	562.7	562.0	561.4
160°	567.5	566.8	566.1	565.5	566.1	566.8	567.5	568.1	568.2	567.6	567.0
162.5°	572.7	571.9	571.1	570.3	571.1	571.9	572.7	573.5	573.6	573.0	572.3
165°	579.4	578.8	578.1	577.4	578.1	578.8	579.4	580.1	580.1	579.4	578.8
167.5°	584.5	583.7	582.8	582.0	582.8	583.7	584.5	585.4	585.5	584.8	584.2
170°	587.3	586.4	585.6	584.7	585.6	586.4	587.3	588.1	588.2	587.6	586.9
172.5°	589.3	588.5	587.6	586.8	587.6	588.5	589.3	590.2	590.3	589.6	588.9
175°	591.4	590.5	589.5	588.6	589.5	590.5	591.4	592.4	592.5	591.8	591.2
177.5°	591.7	591.0	590.3	589.7	590.3	591.0	591.7	592.4	592.5	591.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	5.4	5.6	5.7	5.9	5.7	5.9	6.0	6.1	6.5	6.6	6.7
90°	9.0	8.5	7.8	7.0	6.3	5.5	4.6	3.6	2.5	1.5	0.4
92.5°	10.2	9.9	9.5	9.2	8.8	8.4	8.3	8.3	8.4	8.5	8.6
95°	17.1	16.7	16.0	15.3	14.7	14.0	15.2	18.4	21.5	24.6	27.8
97.5°	22.7	22.3	20.8	19.2	17.7	16.2	19.8	28.6	37.5	46.3	55.1
100°	25.1	24.4	22.7	21.1	19.5	17.9	23.6	36.6	49.6	62.6	75.7
102.5°	26.0	25.0	38.6	52.1	65.6	79.1	87.2	90.0	92.7	95.5	98.2
105°	27.1	26.1	52.0	77.9	103.9	129.8	141.3	138.5	135.6	132.8	129.9
107.5°	35.4	36.5	67.6	98.7	129.8	160.9	175.3	173.0	170.7	168.4	166.1
110°	65.3	74.8	102.2	129.7	157.1	184.6	197.3	195.3	193.3	191.3	189.3



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	154.0	188.7	195.4	202.2	209.0	215.8	218.3	216.5	214.8	213.0	211.2
115°	219.7	263.7	261.3	259.0	256.6	254.2	252.2	250.6	249.0	247.4	245.8
117.5°	281.5	292.1	290.5	288.8	287.2	285.6	283.8	282.0	280.2	278.4	276.6
120°	314.4	313.3	311.6	309.9	308.2	306.5	304.9	303.5	302.0	300.6	299.2
122.5°	334.2	333.5	331.6	329.7	327.9	326.0	324.3	322.8	321.3	319.8	318.3
125°	361.8	361.2	359.4	357.6	355.8	353.9	352.4	351.2	350.0	348.7	347.5
127.5°	387.1	386.1	384.8	383.4	382.1	380.7	379.4	378.0	376.6	375.3	373.9
130°	403.2	402.2	401.2	400.1	399.1	398.0	396.7	395.2	393.7	392.2	390.7
132.5°	419.2	418.3	417.2	416.2	415.1	414.1	412.9	411.6	410.3	409.0	407.8
135°	441.6	440.7	439.8	439.0	438.1	437.2	436.1	434.5	433.0	431.5	430.0
137.5°	462.5	461.6	460.6	459.7	458.7	457.7	456.7	455.7	454.6	453.5	452.5
140°	476.1	475.3	474.2	473.2	472.2	471.1	470.2	469.4	468.7	467.9	467.2
142.5°	488.7	487.9	486.7	485.5	484.3	483.2	482.2	481.5	480.8	480.2	479.5
145°	506.3	505.6	504.0	502.4	500.8	499.2	498.4	498.5	498.6	498.7	498.8
147.5°	521.7	521.2	519.6	518.0	516.4	514.8	514.2	514.6	514.9	515.3	515.6
150°	531.0	530.4	528.9	527.4	525.9	524.3	523.9	524.6	525.2	525.9	526.6
152.5°	539.5	539.0	537.5	536.1	534.6	533.2	532.8	533.6	534.3	535.1	535.8
155°	551.1	550.5	549.4	548.2	547.1	546.0	545.8	546.7	547.5	548.4	549.2
157.5°	560.7	560.1	559.3	558.5	557.7	556.9	556.9	557.6	558.3	559.0	559.7
160°	566.5	565.9	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9
162.5°	571.7	571.0	570.5	570.0	569.5	569.1	569.1	569.7	570.2	570.8	571.4
165°	578.1	577.4	577.2	576.9	576.6	576.3	576.4	577.0	577.6	578.2	578.7
167.5°	583.5	582.8	582.6	582.3	582.0	581.8	581.9	582.5	583.1	583.6	584.2
170°	586.2	585.6	585.4	585.2	585.0	584.8	585.0	585.6	586.1	586.7	587.3
172.5°	588.3	587.6	587.4	587.2	587.0	586.9	587.0	587.6	588.2	588.8	589.3
175°	590.5	589.8	589.6	589.5	589.3	589.1	589.3	590.0	590.6	591.3	592.0
177.5°	590.9	590.3	590.3	590.2	590.1	590.0	590.3	590.8	591.3	591.9	592.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	7.8	9.2	9.4	10.5	10.1	10.2	10.4	10.2	10.1	9.9	9.7
90°	1.5	2.5	3.6	4.6	5.5	6.3	7.0	7.8	8.5	9.0	9.5
92.5°	8.5	8.4	8.3	8.3	8.4	8.8	9.2	9.5	9.9	10.2	10.4
95°	24.6	21.5	18.4	15.2	14.0	14.7	15.3	16.0	16.7	17.1	17.6
97.5°	46.3	37.5	28.6	19.8	16.2	17.7	19.2	20.8	22.3	22.7	23.1
100°	62.6	49.6	36.6	23.6	17.9	19.5	21.1	22.7	24.4	25.1	25.9
102.5°	95.5	92.7	90.0	87.2	79.1	65.6	52.1	38.6	25.0	26.0	27.0
105°	132.8	135.6	138.5	141.3	129.8	103.9	77.9	52.0	26.1	27.1	28.2
107.5°	168.4	170.7	173.0	175.3	160.9	129.8	98.7	67.6	36.5	35.4	34.4
110°	191.3	193.3	195.3	197.3	184.6	157.1	129.7	102.2	74.8	65.3	55.8



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	213.0	214.8	216.5	218.3	215.8	209.0	202.2	195.4	188.7	154.0	119.4
115°	247.4	249.0	250.6	252.2	254.2	256.6	259.0	261.3	263.7	219.7	175.8
117.5°	278.4	280.2	282.0	283.8	285.6	287.2	288.8	290.5	292.1	281.5	270.8
120°	300.6	302.0	303.5	304.9	306.5	308.2	309.9	311.6	313.3	314.4	315.6
122.5°	319.8	321.3	322.8	324.3	326.0	327.9	329.7	331.6	333.5	334.2	334.8
125°	348.7	350.0	351.2	352.4	353.9	355.8	357.6	359.4	361.2	361.8	362.5
127.5°	375.3	376.6	378.0	379.4	380.7	382.1	383.4	384.8	386.1	387.1	388.1
130°	392.2	393.7	395.2	396.7	398.0	399.1	400.1	401.2	402.2	403.2	404.3
132.5°	409.0	410.3	411.6	412.9	414.1	415.1	416.2	417.2	418.3	419.2	420.1
135°	431.5	433.0	434.5	436.1	437.2	438.1	439.0	439.8	440.7	441.6	442.6
137.5°	453.5	454.6	455.7	456.7	457.7	458.7	459.7	460.6	461.6	462.5	463.5
140°	467.9	468.7	469.4	470.2	471.1	472.2	473.2	474.2	475.3	476.1	477.0
142.5°	480.2	480.8	481.5	482.2	483.2	484.3	485.5	486.7	487.9	488.7	489.5
145°	498.7	498.6	498.5	498.4	499.2	500.8	502.4	504.0	505.6	506.3	507.0
147.5°	515.3	514.9	514.6	514.2	514.8	516.4	518.0	519.6	521.2	521.7	522.2
150°	525.9	525.2	524.6	523.9	524.3	525.9	527.4	528.9	530.4	531.0	531.6
152.5°	535.1	534.3	533.6	532.8	533.2	534.6	536.1	537.5	539.0	539.5	540.1
155°	548.4	547.5	546.7	545.8	546.0	547.1	548.2	549.4	550.5	551.1	551.7
157.5°	559.0	558.3	557.6	556.9	556.9	557.7	558.5	559.3	560.1	560.7	561.4
160°	565.3	564.8	564.2	563.6	563.6	564.2	564.8	565.3	565.9	566.5	567.0
162.5°	570.8	570.2	569.7	569.1	569.1	569.5	570.0	570.5	571.0	571.7	572.3
165°	578.2	577.6	577.0	576.4	576.3	576.6	576.9	577.2	577.4	578.1	578.8
167.5°	583.6	583.1	582.5	581.9	581.8	582.0	582.3	582.6	582.8	583.5	584.2
170°	586.7	586.1	585.6	585.0	584.8	585.0	585.2	585.4	585.6	586.2	586.9
172.5°	588.8	588.2	587.6	587.0	586.9	587.0	587.2	587.4	587.6	588.3	588.9
175°	591.3	590.6	590.0	589.3	589.1	589.3	589.5	589.6	589.8	590.5	591.2
177.5°	591.9	591.3	590.8	590.3	590.0	590.1	590.2	590.3	590.3	590.9	591.4
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	10.1	10.2	9.9	10.0	10.3	10.0	10.1
90°	10.0	10.4	10.8	11.0	11.2	11.4	11.5
92.5°	10.7	10.9	11.1	11.2	11.3	11.4	11.5
95°	18.1	18.6	18.8	18.7	18.6	18.5	18.4
97.5°	23.5	23.8	24.1	24.2	24.3	24.4	24.5
100°	26.6	27.4	27.9	28.1	28.3	28.4	28.6
102.5°	28.0	29.0	29.6	29.9	30.2	30.4	30.7
105°	29.2	30.3	31.0	31.3	31.7	32.1	32.5
107.5°	33.3	32.2	31.9	32.3	32.7	33.0	33.4
110°	46.3	36.8	32.2	32.6	33.0	33.4	33.8



TEST NUMBER: P331495

CATALOG NUMBER: S122DIW-S485D435U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	84.7	50.1	32.9	33.2	33.5	33.8	34.1
115°	131.8	87.8	62.4	55.6	48.7	41.9	35.0
117.5°	260.2	249.5	233.0	210.5	188.0	165.6	143.1
120°	316.7	317.9	312.0	299.2	286.4	273.5	260.7
122.5°	335.5	336.2	335.3	332.8	330.3	327.8	325.3
125°	363.2	363.8	364.3	364.6	364.9	365.2	365.4
127.5°	389.0	390.0	390.5	390.6	390.6	390.7	390.7
130°	405.3	406.4	406.9	406.8	406.7	406.6	406.5
132.5°	420.9	421.8	422.2	422.1	422.0	422.0	421.9
135°	443.5	444.5	444.8	444.7	444.5	444.3	444.1
137.5°	464.4	465.3	465.6	465.3	465.0	464.7	464.3
140°	477.9	478.7	478.9	478.4	477.9	477.5	477.0
142.5°	490.3	491.1	491.2	490.7	490.3	489.8	489.3
145°	507.6	508.3	508.4	507.9	507.4	507.0	506.5
147.5°	522.7	523.2	523.2	522.8	522.4	522.0	521.6
150°	532.1	532.7	532.8	532.3	531.8	531.3	530.9
152.5°	540.7	541.3	541.2	540.6	540.0	539.3	538.7
155°	552.2	552.8	552.7	551.9	551.2	550.4	549.7
157.5°	562.0	562.7	562.6	561.9	561.1	560.4	559.7
160°	567.6	568.2	568.1	567.5	566.8	566.1	565.5
162.5°	573.0	573.6	573.5	572.7	571.9	571.1	570.3
165°	579.4	580.1	580.1	579.4	578.8	578.1	577.4
167.5°	584.8	585.5	585.4	584.5	583.7	582.8	582.0
170°	587.6	588.2	588.1	587.3	586.4	585.6	584.7
172.5°	589.6	590.3	590.2	589.3	588.5	587.6	586.8
175°	591.8	592.5	592.4	591.4	590.5	589.5	588.6
177.5°	591.9	592.5	592.4	591.7	591.0	590.3	589.7
180°	590.7	590.7	590.7	590.7	590.7	590.7	590.7

(END OF REPORT)