

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908003

Luminaire Tested: DFN2DIP-HX3F0-040D040US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908003
REPORT IS A COMBINATION OF REPORTS P900737 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D040US840-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7998.1 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1821	1821	1821
5°	1823	1794	1806
10°	1807	1769	1781
15°	1780	1738	1742
20°	1743	1697	1702
25°	1706	1647	1655
30°	1661	1601	1597
35°	1618	1546	1535
40°	1564	1491	1476
45°	1511	1436	1416
50°	1453	1378	1346
55°	1392	1311	1282
60°	1324	1232	1208
65°	1248	1149	1121
70°	1152	1048	1027
75°	1020	928	939
80°	860	773	773
85°	610	512	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1511 cd/sqm

TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	1.8
10°-20°	416.2	5.2
20°-30°	611.7	7.6
30°-40°	710.5	8.9
40°-50°	709.6	8.9
50°-60°	618.7	7.7
60°-70°	457.4	5.7
70°-80°	258.8	3.2
80°-90°	70.7	0.9
90°-100°	44.9	0.6
100°-110°	167.6	2.1
110°-120°	444.4	5.6
120°-130°	737.1	9.2
130°-140°	783.0	9.8
140°-150°	727.7	9.1
150°-160°	585.1	7.3
160°-170°	377.0	4.7
170°-180°	129.8	1.6
0°-30°	1175.9	14.7
0°-40°	1886.3	23.6
0°-60°	3214.6	40.2
0°-90°	4001.4	50.0
90°-120°	656.9	8.2
90°-150°	2904.8	36.3
90°-180°	3997.0	50.0
0°-180°	7998.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	1	12	20	25	27	7
95°	64	32	38	43	42	76
105°	300	330	60	71	75	320
115°	567	584	609	152	81	558
125°	802	815	834	840	843	715
135°	992	1008	1017	1027	1025	767
145°	1151	1150	1167	1174	1169	720
155°	1268	1259	1271	1276	1269	584
165°	1336	1330	1333	1340	1333	377
175°	1366	1359	1361	1368	1358	130
180°	1363	1363	1363	1363	1363	

TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	0.9	11.8	19.7	24.7	26.6
92.5°	24.7	20.7	23.6	25.7	26.6
95°	64.0	31.5	38.4	43.4	42.4
97.5°	115.4	34.5	50.3	53.3	54.2
100°	174.6	39.5	56.2	64.0	66.0
102.5°	239.6	237.8	58.2	69.0	72.0
105°	299.8	329.5	60.2	71.0	74.9
107.5°	369.9	394.6	62.2	73.0	77.0
110°	437.1	457.7	172.7	74.0	77.9



TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	500.2	517.9	501.1	75.9	79.0
115°	567.1	583.9	608.6	151.9	81.0
117.5°	625.4	645.1	662.0	520.8	262.4
120°	690.5	705.3	723.1	735.0	601.8
122.5°	745.7	761.5	781.3	787.2	788.2
125°	801.9	814.9	833.5	840.5	843.4
127.5°	853.2	867.1	881.9	891.8	892.7
130°	901.6	917.5	928.2	939.1	938.2
132.5°	950.9	963.8	974.6	983.5	982.6
135°	992.4	1008.2	1017.0	1026.9	1025.0
137.5°	1035.7	1047.5	1057.5	1067.3	1064.4
140°	1078.1	1086.1	1096.9	1105.8	1100.9
142.5°	1113.8	1120.6	1133.5	1141.2	1136.4
145°	1151.2	1150.2	1166.9	1173.9	1168.9
147.5°	1183.7	1180.7	1197.5	1202.4	1198.6
150°	1215.3	1208.4	1224.3	1230.1	1225.2
152.5°	1241.9	1234.1	1248.8	1254.8	1247.9
155°	1267.6	1258.8	1270.6	1276.5	1268.6
157.5°	1288.3	1280.4	1289.4	1296.3	1288.3
160°	1306.1	1300.1	1306.1	1311.9	1305.0
162.5°	1321.8	1316.0	1320.9	1327.8	1318.9
165°	1335.6	1329.8	1332.7	1339.6	1332.7
167.5°	1346.6	1340.5	1343.6	1350.5	1341.6
170°	1355.4	1349.5	1351.4	1358.4	1349.5
172.5°	1361.3	1355.4	1357.5	1364.3	1355.4
175°	1366.1	1359.3	1361.3	1368.2	1358.4
177.5°	1368.2	1361.3	1362.3	1369.3	1360.4
180°	1363.3	1363.3	1363.3	1363.3	1363.3

TEST NUMBER: P908003

CATALOG NUMBER: DFN2DIP-HX3F0-040D040US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.31	10.18	10.27	11.15	12.42	8.88	9.75	9.84	10.72	11.99
	3H	10.97	11.74	11.93	12.72	14.01	10.50	11.27	11.46	12.25	13.54
	4H	11.55	12.28	12.53	13.27	14.57	11.08	11.81	12.06	12.80	14.10
	6H	11.94	12.62	12.93	13.61	14.92	11.47	12.15	12.46	13.14	14.45
	8H	12.04	12.69	13.04	13.69	15.00	11.57	12.22	12.57	13.22	14.53
	12H	12.09	12.70	13.09	13.70	15.04	11.61	12.22	12.62	13.23	14.56
4H	2H	9.77	10.50	10.76	11.49	12.79	9.43	10.16	10.42	11.15	12.45
	3H	11.63	12.24	12.63	13.25	14.57	11.24	11.85	12.24	12.86	14.18
	4H	12.34	12.90	13.34	13.90	15.24	11.94	12.49	12.94	13.50	14.84
	6H	12.85	13.33	13.86	14.36	15.69	12.44	12.92	13.46	13.95	15.29
	8H	12.99	13.44	14.01	14.46	15.82	12.58	13.03	13.60	14.06	15.41
	12H	13.06	13.47	14.10	14.51	15.86	12.64	13.05	13.68	14.09	15.45
8H	4H	12.53	12.98	13.55	14.00	15.35	12.17	12.62	13.19	13.65	15.00
	6H	13.15	13.52	14.20	14.59	15.94	12.79	13.17	13.84	14.23	15.58
	8H	13.37	13.70	14.42	14.75	16.11	13.00	13.33	14.05	14.38	15.75
	12H	13.49	13.78	14.55	14.83	16.24	13.12	13.40	14.17	14.45	15.86
12H	4H	12.52	12.92	13.55	13.96	15.32	12.17	12.57	13.20	13.61	14.97
	6H	13.18	13.51	14.23	14.56	15.93	12.83	13.16	13.88	14.21	15.58
	8H	13.42	13.71	14.47	14.75	16.16	13.06	13.35	14.12	14.40	15.81

END OF REPORT