

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912151

Luminaire Tested: DFN2DIP-SQ4F0-060D140US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912151
REPORT IS A COMBINATION OF REPORTS P901706 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D140US850-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21026.6 lumens
Efficiency: N/A
Efficacy: 135.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 155.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30
2	85	78	72	67	75	70	65	61	55	51	49	41	39	37	28	27	26
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19
5	65	54	46	41	58	49	42	37	39	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	13	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11
10	44	33	26	22	40	30	24	20	24	20	16	19	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1930	1930	1930
5°	1933	1899	1912
10°	1914	1863	1850
15°	1887	1801	1754
20°	1852	1717	1637
25°	1817	1622	1523
30°	1769	1525	1379
35°	1722	1420	1252
40°	1674	1312	1107
45°	1618	1192	975
50°	1561	1071	846
55°	1501	941	723
60°	1432	805	595
65°	1352	667	537
70°	1255	539	486
75°	1133	476	444
80°	957	400	387
85°	666	269	294

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2809 cd/sqm

TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	1.2
10°-20°	707.6	3.4
20°-30°	993.4	4.7
30°-40°	1082.8	5.1
40°-50°	995.2	4.7
50°-60°	781.6	3.7
60°-70°	508.8	2.4
70°-80°	261.9	1.2
80°-90°	76.1	0.4
90°-100°	172.8	0.8
100°-110°	644.1	3.1
110°-120°	1708.2	8.1
120°-130°	2833.3	13.5
130°-140°	3009.6	14.3
140°-150°	2797.1	13.3
150°-160°	2248.8	10.7
160°-170°	1449.0	6.9
170°-180°	498.7	2.4
0°-30°	1958.7	9.3
0°-40°	3041.5	14.5
0°-60°	4818.4	22.9
0°-90°	5665.1	26.9
90°-120°	2525.1	12.0
90°-150°	11165.0	53.1
90°-180°	15362.0	73.1
0°-180°	21026.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	4	46	76	95	102	19
95°	246	121	148	167	163	292
105°	1153	1266	231	273	288	1231
115°	2180	2244	2339	584	311	2146
125°	3082	3132	3204	3230	3242	2749
135°	3814	3875	3909	3947	3940	2947
145°	4425	4421	4485	4512	4493	2767
155°	4872	4838	4884	4906	4876	2245
165°	5134	5111	5122	5149	5122	1450
175°	5251	5224	5232	5259	5221	500
180°	5240	5240	5240	5240	5240	

TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	3.5	45.5	75.6	95.0	102.2
92.5°	95.0	79.7	90.9	98.6	102.2
95°	246.3	121.1	147.7	167.0	163.0
97.5°	443.5	132.9	193.2	204.8	208.5
100°	671.3	151.7	216.1	246.3	254.0
102.5°	921.1	913.9	223.8	265.2	276.9
105°	1152.6	1266.5	231.4	272.8	288.1
107.5°	1421.8	1516.3	239.1	280.5	295.8
110°	1679.8	1759.1	663.6	284.6	299.4

TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1922.5	1990.4	1926.1	291.8	303.4
115°	2180.1	2244.4	2339.4	584.0	311.1
117.5°	2403.8	2479.4	2544.3	2001.7	1008.5
120°	2654.2	2710.8	2779.3	2824.7	2312.8
122.5°	2866.2	2927.0	3003.1	3025.6	3029.7
125°	3082.4	3131.8	3203.9	3230.4	3241.7
127.5°	3279.5	3332.7	3389.8	3427.6	3431.2
130°	3465.4	3526.3	3567.7	3609.6	3605.9
132.5°	3655.0	3704.5	3746.0	3780.1	3776.6
135°	3814.4	3875.2	3908.9	3947.2	3939.5
137.5°	3981.0	4026.4	4064.7	4102.5	4091.3
140°	4144.0	4174.6	4216.0	4250.2	4231.3
142.5°	4280.9	4307.4	4356.5	4386.6	4367.7
145°	4424.9	4420.8	4485.2	4511.9	4492.9
147.5°	4549.7	4538.4	4602.8	4621.6	4606.8
150°	4671.2	4644.6	4705.4	4727.9	4709.0
152.5°	4773.4	4743.2	4800.0	4822.9	4796.3
155°	4871.9	4838.2	4883.7	4906.2	4876.1
157.5°	4951.7	4921.5	4955.8	4982.3	4951.7
160°	5020.1	4997.2	5020.1	5042.6	5016.1
162.5°	5080.4	5057.9	5076.9	5103.4	5069.2
165°	5133.6	5111.0	5122.4	5148.9	5122.4
167.5°	5175.5	5152.5	5164.2	5190.8	5156.5
170°	5209.6	5186.7	5194.3	5221.0	5186.7
172.5°	5232.2	5209.6	5217.3	5243.9	5209.6
175°	5251.1	5224.5	5232.2	5258.8	5221.0
177.5°	5258.8	5232.2	5236.3	5262.8	5228.6
180°	5239.8	5239.8	5239.8	5239.8	5239.8

TEST NUMBER: P912151

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.77	7.44	7.91	8.57	10.14	2.73	3.41	3.87	4.53	6.10
	3H	8.44	9.04	9.59	10.18	11.76	3.91	4.51	5.06	5.64	7.23
	4H	9.05	9.62	10.20	10.75	12.34	4.35	4.92	5.51	6.06	7.65
	6H	9.46	9.99	10.63	11.12	12.72	4.67	5.19	5.83	6.33	7.93
	8H	9.59	10.09	10.75	11.24	12.83	4.75	5.25	5.92	6.40	8.00
	12H	9.65	10.12	10.81	11.26	12.88	4.79	5.27	5.96	6.41	8.02
4H	2H	6.77	7.34	7.93	8.47	10.06	3.31	3.88	4.47	5.02	6.60
	3H	8.59	9.07	9.76	10.22	11.83	4.65	5.12	5.81	6.28	7.88
	4H	9.28	9.72	10.45	10.86	12.48	5.19	5.63	6.36	6.78	8.40
	6H	9.79	10.16	10.96	11.33	12.94	5.60	5.98	6.78	7.15	8.76
	8H	9.97	10.31	11.14	11.48	13.10	5.73	6.08	6.90	7.24	8.87
	12H	10.06	10.37	11.24	11.54	13.18	5.79	6.10	6.98	7.28	8.91
8H	4H	9.24	9.58	10.41	10.75	12.37	5.46	5.81	6.63	6.97	8.60
	6H	9.80	10.09	10.99	11.29	12.92	5.98	6.26	7.17	7.47	9.09
	8H	10.02	10.27	11.22	11.45	13.10	6.17	6.42	7.36	7.60	9.24
	12H	10.15	10.37	11.36	11.55	13.23	6.28	6.50	7.48	7.68	9.35
12H	4H	9.18	9.50	10.37	10.67	12.30	5.46	5.78	6.65	6.95	8.58
	6H	9.78	10.03	10.97	11.21	12.85	6.03	6.28	7.22	7.46	9.10
	8H	9.99	10.21	11.19	11.39	13.07	6.23	6.45	7.43	7.63	9.31