

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917923

Luminaire Tested: DFN2DIP-TR2F0-030D020US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917923
REPORT IS A COMBINATION OF REPORTS P901744 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D020US930-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3522.1 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLL0NL

Luminous Intensity Polar Plot



TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2255	2255	2255
5°	2255	2214	2229
10°	2229	2165	2153
15°	2195	2089	2037
20°	2151	1986	1897
25°	2106	1871	1761
30°	2047	1753	1590
35°	1989	1628	1440
40°	1929	1498	1269
45°	1860	1356	1114
50°	1789	1212	963
55°	1714	1059	818
60°	1627	899	670
65°	1527	738	599
70°	1405	588	536
75°	1252	508	480
80°	1033	413	405
85°	678	256	286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1860 cd/sqm

TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	2.7
10°-20°	260.1	7.4
20°-30°	365.1	10.4
30°-40°	398.0	11.3
40°-50°	365.8	10.4
50°-60°	287.3	8.2
60°-70°	187.0	5.3
70°-80°	96.3	2.7
80°-90°	26.1	0.7
90°-100°	31.9	0.9
100°-110°	101.4	2.9
110°-120°	173.5	4.9
120°-130°	228.2	6.5
130°-140°	256.1	7.3
140°-150°	251.2	7.1
150°-160°	210.7	6.0
160°-170°	139.7	4.0
170°-180°	48.8	1.4
0°-30°	720.0	20.4
0°-40°	1118.0	31.7
0°-60°	1771.2	50.3
0°-90°	2080.5	59.1
90°-120°	306.8	8.7
90°-150°	1042.3	29.6
90°-180°	1442.0	40.9
0°-180°	3522.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	0	6	15	14	15	3
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P917923

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.65	11.56	11.53	12.46	13.60	6.63	7.54	7.51	8.44	9.58
	3H	12.31	13.12	13.20	14.03	15.20	7.81	8.62	8.70	9.53	10.70
	4H	12.91	13.67	13.82	14.59	15.76	8.25	9.02	9.16	9.93	11.11
	6H	13.31	14.02	14.23	14.94	16.13	8.56	9.27	9.49	10.19	11.38
	8H	13.43	14.10	14.36	15.04	16.22	8.65	9.32	9.58	10.26	11.44
	12H	13.48	14.13	14.42	15.06	16.27	8.69	9.33	9.62	10.26	11.47
4H	2H	10.67	11.44	11.59	12.35	13.53	7.22	7.99	8.14	8.90	10.08
	3H	12.48	13.12	13.41	14.07	15.25	8.56	9.20	9.49	10.14	11.33
	4H	13.16	13.74	14.10	14.68	15.90	9.10	9.68	10.03	10.62	11.83
	6H	13.66	14.16	14.61	15.12	16.34	9.51	10.01	10.46	10.97	12.18
	8H	13.82	14.29	14.77	15.24	16.47	9.63	10.09	10.58	11.05	12.28
	12H	13.91	14.33	14.88	15.30	16.53	9.69	10.11	10.66	11.08	12.32
8H	4H	13.13	13.60	14.08	14.55	15.78	9.37	9.84	10.32	10.79	12.02
	6H	13.67	14.06	14.65	15.06	16.28	9.87	10.26	10.85	11.26	12.48
	8H	13.87	14.22	14.86	15.20	16.45	10.05	10.39	11.04	11.38	12.62
	12H	14.00	14.30	14.99	15.28	16.57	10.16	10.46	11.15	11.44	12.73
12H	4H	13.08	13.51	14.05	14.48	15.71	9.38	9.80	10.35	10.77	12.00
	6H	13.65	13.99	14.63	14.98	16.22	9.91	10.26	10.90	11.24	12.49
	8H	13.85	14.15	14.84	15.14	16.43	10.11	10.41	11.10	11.40	12.69