

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029225

Luminaire Tested: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

Issue Date: 5/6/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1029225  
REPORT IS A COMBINATION OF REPORTS P985223 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/6/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K  
Description: Define 2 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5562.9 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 74.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1029225

CATALOG NUMBER: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1029225

CATALOG NUMBER: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
| 0   | 111 | 111 | 111 | 111 | 104 | 104 | 104 | 104 | 91 | 91 | 91 | 80 | 80 | 80 | 70 | 70 | 70 |
| 1   | 99  | 94  | 89  | 85  | 93  | 88  | 84  | 80  | 77 | 74 | 71 | 68 | 65 | 63 | 58 | 57 | 55 |
| 2   | 89  | 81  | 74  | 68  | 84  | 76  | 70  | 64  | 67 | 62 | 57 | 58 | 54 | 51 | 50 | 47 | 45 |
| 3   | 81  | 70  | 62  | 56  | 76  | 66  | 59  | 53  | 58 | 52 | 47 | 51 | 46 | 42 | 44 | 40 | 37 |
| 4   | 74  | 62  | 53  | 47  | 69  | 58  | 50  | 44  | 51 | 45 | 40 | 45 | 40 | 36 | 39 | 35 | 32 |
| 5   | 68  | 55  | 46  | 40  | 63  | 52  | 44  | 38  | 46 | 39 | 34 | 40 | 35 | 31 | 35 | 31 | 27 |
| 6   | 62  | 49  | 41  | 34  | 58  | 47  | 39  | 33  | 41 | 35 | 30 | 36 | 31 | 27 | 32 | 27 | 24 |
| 7   | 58  | 44  | 36  | 30  | 54  | 42  | 34  | 29  | 37 | 31 | 26 | 33 | 27 | 23 | 29 | 24 | 21 |
| 8   | 54  | 40  | 32  | 26  | 50  | 38  | 31  | 25  | 34 | 28 | 23 | 30 | 25 | 21 | 26 | 22 | 19 |
| 9   | 50  | 37  | 29  | 23  | 47  | 35  | 28  | 23  | 31 | 25 | 21 | 28 | 22 | 19 | 24 | 20 | 17 |
| 10  | 47  | 34  | 26  | 21  | 44  | 32  | 25  | 20  | 29 | 23 | 19 | 26 | 20 | 17 | 23 | 18 | 15 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 45°   | 90°   |
|-----|-------|-------|-------|
| 0°  | 16776 | 16776 | 16776 |
| 5°  | 16852 | 16061 | 15970 |
| 10° | 16739 | 15504 | 15278 |
| 15° | 16503 | 14928 | 14568 |
| 20° | 16206 | 14325 | 13895 |
| 25° | 15911 | 13746 | 13284 |
| 30° | 15499 | 13158 | 12680 |
| 35° | 15081 | 12591 | 12236 |
| 40° | 14643 | 12101 | 11794 |
| 45° | 14224 | 11657 | 11410 |
| 50° | 13774 | 11247 | 11030 |
| 55° | 13302 | 10812 | 10643 |
| 60° | 12723 | 10358 | 10237 |
| 65° | 12122 | 9838  | 9768  |
| 70° | 11442 | 9278  | 9266  |
| 75° | 10567 | 8720  | 8791  |
| 80° | 9197  | 8135  | 8300  |
| 85° | 7811  | 7586  | 7873  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14224 cd/sqm

TEST NUMBER: P1029225

CATALOG NUMBER: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 100.5  | 1.8       |
| 10°-20°   | 288.2  | 5.2       |
| 20°-30°   | 436.6  | 7.8       |
| 30°-40°   | 531.7  | 9.6       |
| 40°-50°   | 572.0  | 10.3      |
| 50°-60°   | 555.5  | 10.0      |
| 60°-70°   | 485.2  | 8.7       |
| 70°-80°   | 373.4  | 6.7       |
| 80°-90°   | 251.6  | 4.5       |
| 90°-100°  | 206.1  | 3.7       |
| 100°-110° | 232.7  | 4.2       |
| 110°-120° | 265.8  | 4.8       |
| 120°-130° | 286.5  | 5.2       |
| 130°-140° | 289.1  | 5.2       |
| 140°-150° | 267.7  | 4.8       |
| 150°-160° | 221.8  | 4.0       |
| 160°-170° | 147.1  | 2.6       |
| 170°-180° | 51.4   | 0.9       |
| 0°-30°    | 825.2  | 14.8      |
| 0°-40°    | 1356.9 | 24.4      |
| 0°-60°    | 2484.5 | 44.7      |
| 0°-90°    | 3594.7 | 64.6      |
| 90°-120°  | 704.7  | 12.7      |
| 90°-150°  | 1547.9 | 27.8      |
| 90°-180°  | 1968.0 | 35.4      |
| 0°-180°   | 5562.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 1060 | 1060  | 1060 | 1060  | 1060 |      |
| 5°   | 1063 | 1058  | 1049 | 1058  | 1057 | 101  |
| 15°  | 1014 | 1017  | 1017 | 1031  | 1029 | 286  |
| 25°  | 922  | 932   | 946  | 965   | 969  | 424  |
| 35°  | 794  | 820   | 849  | 883   | 894  | 496  |
| 45°  | 651  | 693   | 746  | 794   | 810  | 503  |
| 55°  | 499  | 554   | 634  | 690   | 710  | 447  |
| 65°  | 341  | 416   | 507  | 570   | 590  | 339  |
| 75°  | 189  | 275   | 373  | 439   | 459  | 200  |
| 85°  | 55   | 150   | 249  | 313   | 335  | 58   |
| 90°  | 16   | 110   | 219  | 279   | 298  | 12   |
| 95°  | 36   | 113   | 206  | 264   | 282  | 36   |
| 105° | 106  | 152   | 233  | 288   | 304  | 113  |
| 115° | 189  | 209   | 277  | 323   | 338  | 187  |
| 125° | 270  | 274   | 322  | 362   | 375  | 242  |
| 135° | 346  | 351   | 368  | 400   | 410  | 268  |
| 145° | 419  | 422   | 425  | 434   | 440  | 262  |
| 155° | 479  | 480   | 481  | 484   | 482  | 220  |
| 165° | 521  | 520   | 520  | 524   | 521  | 147  |
| 175° | 542  | 540   | 540  | 543   | 540  | 51   |
| 180° | 543  | 543   | 543  | 543   | 543  |      |

TEST NUMBER: P1029225

CATALOG NUMBER: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 1059.8 | 1059.8 | 1059.8 | 1059.8 | 1059.8 |
| 2.5°   | 1067.5 | 1062.9 | 1052.2 | 1059.8 | 1056.8 |
| 5°     | 1062.9 | 1058.3 | 1049.1 | 1058.3 | 1056.8 |
| 7.5°   | 1055.2 | 1052.2 | 1044.5 | 1055.2 | 1053.7 |
| 10°    | 1046.0 | 1042.9 | 1038.3 | 1050.6 | 1049.1 |
| 12.5°  | 1030.7 | 1032.2 | 1029.1 | 1041.4 | 1039.9 |
| 15°    | 1013.8 | 1016.8 | 1016.8 | 1030.7 | 1029.1 |
| 17.5°  | 992.3  | 998.4  | 1003.0 | 1016.8 | 1016.8 |
| 20°    | 970.8  | 978.4  | 984.6  | 1001.5 | 1001.5 |
| 22.5°  | 947.7  | 956.9  | 966.1  | 983.0  | 986.1  |
| 25°    | 921.6  | 932.4  | 946.2  | 964.6  | 969.2  |
| 27.5°  | 890.9  | 907.8  | 923.1  | 946.2  | 949.3  |
| 30°    | 860.2  | 880.1  | 900.1  | 924.7  | 929.3  |
| 32.5°  | 826.4  | 849.4  | 874.0  | 903.2  | 912.4  |
| 35°    | 794.1  | 820.2  | 849.4  | 883.2  | 894.0  |
| 37.5°  | 758.8  | 788.0  | 824.8  | 861.7  | 872.5  |
| 40°    | 723.5  | 757.3  | 798.7  | 838.7  | 852.5  |
| 42.5°  | 689.7  | 723.5  | 772.6  | 817.2  | 831.0  |
| 45°    | 651.3  | 692.7  | 746.5  | 794.1  | 809.5  |
| 47.5°  | 614.4  | 658.9  | 720.4  | 769.5  | 786.4  |
| 50°    | 576.0  | 623.6  | 692.7  | 745.0  | 761.9  |
| 52.5°  | 539.1  | 589.8  | 663.6  | 717.3  | 735.7  |
| 55°    | 499.2  | 554.5  | 634.4  | 689.7  | 709.6  |
| 57.5°  | 460.8  | 522.2  | 602.1  | 662.0  | 682.0  |
| 60°    | 419.3  | 485.4  | 572.9  | 631.3  | 652.8  |
| 62.5°  | 382.5  | 451.6  | 539.1  | 602.1  | 622.1  |
| 65°    | 341.0  | 416.3  | 506.9  | 569.9  | 589.8  |
| 67.5°  | 304.1  | 382.5  | 474.6  | 537.6  | 559.1  |
| 70°    | 264.2  | 344.1  | 439.3  | 505.3  | 523.8  |
| 72.5°  | 227.3  | 310.3  | 407.0  | 471.6  | 494.6  |
| 75°    | 188.9  | 274.9  | 373.3  | 439.3  | 459.3  |
| 77.5°  | 152.1  | 241.2  | 341.0  | 407.0  | 428.5  |
| 80°    | 115.2  | 208.9  | 308.7  | 373.3  | 394.8  |
| 82.5°  | 84.5   | 176.6  | 278.0  | 342.5  | 362.5  |
| 85°    | 55.3   | 150.5  | 248.8  | 313.3  | 334.8  |
| 87.5°  | 33.8   | 126.0  | 224.3  | 287.2  | 307.2  |
| 90°    | 15.9   | 110.4  | 218.8  | 279.3  | 298.2  |
| 92.5°  | 23.9   | 108.9  | 203.1  | 263.5  | 282.0  |
| 95°    | 36.1   | 112.9  | 205.9  | 264.3  | 281.8  |
| 97.5°  | 50.6   | 120.8  | 211.7  | 268.5  | 287.0  |
| 100°   | 69.0   | 129.4  | 216.8  | 273.6  | 290.0  |
| 102.5° | 86.6   | 140.1  | 224.8  | 280.5  | 297.0  |
| 105°   | 106.2  | 152.0  | 232.9  | 287.6  | 304.5  |
| 107.5° | 127.2  | 165.9  | 242.7  | 295.4  | 310.0  |
| 110°   | 145.8  | 179.3  | 254.5  | 303.7  | 319.3  |



TEST NUMBER: P1029225

CATALOG NUMBER: S122DIW-B1005D435UB2750-4F0-XX-W2A-D1\_3000K

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 112.5° | 167.8 | 195.1 | 265.4 | 313.1 | 329.1 |
| 115°   | 189.3 | 209.0 | 277.2 | 322.8 | 338.3 |
| 117.5° | 209.3 | 225.3 | 287.5 | 332.2 | 346.2 |
| 120°   | 230.9 | 240.7 | 298.5 | 341.5 | 357.0 |
| 122.5° | 250.6 | 256.6 | 311.2 | 351.3 | 364.3 |
| 125°   | 269.7 | 273.8 | 321.5 | 361.6 | 375.0 |
| 127.5° | 289.8 | 293.3 | 332.9 | 369.5 | 381.9 |
| 130°   | 308.6 | 313.0 | 344.3 | 380.3 | 390.7 |
| 132.5° | 329.7 | 332.7 | 356.2 | 389.2 | 400.1 |
| 135°   | 346.4 | 351.4 | 367.7 | 399.6 | 410.4 |
| 137.5° | 366.5 | 370.7 | 379.3 | 408.0 | 417.0 |
| 140°   | 384.4 | 387.0 | 392.4 | 416.9 | 424.4 |
| 142.5° | 402.7 | 405.4 | 406.7 | 425.6 | 431.5 |
| 145°   | 418.6 | 421.8 | 424.6 | 434.2 | 440.1 |
| 147.5° | 434.2 | 438.3 | 440.2 | 442.6 | 445.3 |
| 150°   | 450.2 | 453.0 | 454.8 | 456.2 | 454.8 |
| 152.5° | 464.4 | 467.2 | 469.5 | 471.3 | 469.5 |
| 155°   | 478.6 | 480.0 | 481.4 | 483.7 | 482.3 |
| 157.5° | 491.0 | 491.9 | 492.8 | 496.0 | 493.8 |
| 160°   | 502.0 | 502.9 | 503.4 | 506.1 | 504.3 |
| 162.5° | 512.1 | 512.1 | 512.5 | 515.7 | 513.4 |
| 165°   | 520.8 | 520.3 | 520.3 | 523.5 | 521.2 |
| 167.5° | 528.6 | 527.2 | 527.2 | 530.4 | 528.1 |
| 170°   | 534.5 | 533.1 | 532.7 | 535.9 | 533.1 |
| 172.5° | 538.6 | 537.3 | 536.8 | 540.0 | 537.3 |
| 175°   | 541.8 | 540.5 | 539.6 | 542.8 | 540.0 |
| 177.5° | 543.7 | 542.3 | 541.4 | 544.1 | 541.4 |
| 180°   | 542.8 | 542.8 | 542.8 | 542.8 | 542.8 |

(END OF REPORT)