

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029628

Luminaire Tested: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029628
REPORT IS A COMBINATION OF REPORTS P986470 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K
Description: Define 2 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7973.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37		
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32		
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27		
3	79	71	64	58	72	64	58	53	52	48	45	42	39	36	31	30	28	23		
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	21	18		
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16		
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14		
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13		
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12		
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	1.6
10°-20°	368.0	4.6
20°-30°	534.1	6.7
30°-40°	563.1	7.1
40°-50°	498.3	6.2
50°-60°	397.9	5.0
60°-70°	270.2	3.4
70°-80°	138.3	1.7
80°-90°	37.8	0.5
90°-100°	111.5	1.4
100°-110°	354.4	4.4
110°-120°	606.5	7.6
120°-130°	797.6	10.0
130°-140°	895.3	11.2
140°-150°	878.0	11.0
150°-160°	736.5	9.2
160°-170°	488.4	6.1
170°-180°	170.7	2.1
0°-30°	1028.6	12.9
0°-40°	1591.7	20.0
0°-60°	2487.8	31.2
0°-90°	2934.1	36.8
90°-120°	1072.4	13.5
90°-150°	3643.2	45.7
90°-180°	5039.0	63.2
0°-180°	7973.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	2	52	2	52	2	7
95°	79	94	79	94	79	88
105°	327	338	327	338	327	345
115°	608	608	608	608	608	602
125°	885	888	885	888	885	791
135°	1145	1159	1145	1159	1145	885
145°	1390	1405	1390	1405	1390	869
155°	1589	1602	1589	1602	1589	732
165°	1729	1731	1729	1731	1729	488
175°	1799	1793	1799	1793	1799	171
180°	1802	1802	1802	1802	1802	

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	1.5	5.6	9.6	13.7	17.8	19.8	23.5	30.9	38.4	45.8	53.2
92.5°	33.5	36.2	38.9	41.6	44.3	45.6	45.8	46.1	46.4	46.8	47.1
95°	79.1	82.5	85.9	89.2	92.6	94.3	94.6	95.3	96.0	96.6	97.3
97.5°	132.3	135.3	138.4	141.4	144.5	146.0	146.7	148.0	149.4	150.7	152.1
100°	193.2	195.9	198.6	201.3	204.0	205.3	205.8	206.8	207.9	208.9	209.9
102.5°	257.0	259.0	261.1	263.1	265.2	266.2	266.9	268.2	269.5	270.9	272.2
105°	327.0	328.0	329.0	330.1	331.1	331.6	331.9	332.6	333.3	333.9	334.6
107.5°	397.0	398.3	399.7	401.0	402.3	403.0	403.0	403.0	403.0	403.0	403.0
110°	463.9	465.9	467.9	470.0	472.0	473.0	473.0	473.0	473.0	473.0	473.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	536.9	538.9	540.9	543.0	545.0	546.0	545.8	545.5	545.2	544.8	544.5
115°	608.4	610.4	612.4	614.5	616.5	617.5	617.2	616.5	615.8	615.2	614.5
117.5°	679.9	682.6	685.3	688.0	690.7	692.0	691.2	689.5	687.8	686.1	684.4
120°	751.3	754.0	756.7	759.4	762.1	763.5	762.1	759.4	756.7	754.0	751.3
122.5°	816.7	820.1	823.5	826.8	830.2	831.9	831.1	829.4	827.7	826.0	824.3
125°	885.2	888.2	891.3	894.3	897.4	898.9	898.4	897.4	896.3	895.3	894.3
127.5°	952.1	955.8	959.5	963.2	966.9	968.8	968.1	966.8	965.4	964.1	962.7
130°	1014.5	1018.9	1023.3	1027.6	1032.0	1034.2	1033.9	1033.2	1032.5	1031.9	1031.2
132.5°	1084.4	1087.8	1091.2	1094.5	1097.9	1099.6	1099.8	1100.1	1100.4	1100.8	1101.1
135°	1145.3	1149.0	1152.7	1156.4	1160.1	1162.0	1162.3	1163.0	1163.7	1164.3	1165.0
137.5°	1212.2	1215.2	1218.3	1221.3	1224.4	1225.9	1226.2	1226.9	1227.6	1228.2	1228.9
140°	1271.5	1274.5	1277.6	1280.6	1283.7	1285.2	1286.0	1287.7	1289.4	1291.1	1292.8
142.5°	1332.3	1335.3	1338.4	1341.4	1344.5	1346.0	1346.5	1347.5	1348.6	1349.6	1350.6
145°	1390.1	1392.5	1394.9	1397.2	1399.6	1400.8	1401.8	1403.8	1405.9	1407.9	1409.9
147.5°	1441.8	1444.8	1447.9	1450.9	1454.0	1455.5	1456.2	1457.5	1458.9	1460.2	1461.6
150°	1495.1	1497.1	1499.1	1501.2	1503.2	1504.2	1504.9	1506.2	1507.6	1508.9	1510.3
152.5°	1542.2	1544.2	1546.2	1548.3	1550.3	1551.3	1552.1	1553.8	1555.5	1557.2	1558.9
155°	1589.4	1590.4	1591.4	1592.4	1593.4	1593.9	1594.4	1595.4	1596.5	1597.5	1598.5
157.5°	1630.4	1631.1	1631.8	1632.5	1633.2	1633.5	1633.8	1634.5	1635.2	1635.8	1636.5
160°	1666.9	1667.6	1668.3	1669.0	1669.7	1670.0	1670.2	1670.5	1670.8	1671.2	1671.5
162.5°	1700.4	1700.4	1700.4	1700.4	1700.4	1700.4	1700.6	1700.9	1701.2	1701.6	1701.9
165°	1729.3	1729.0	1728.6	1728.3	1728.0	1727.8	1727.8	1727.8	1727.8	1727.8	1727.8
167.5°	1755.1	1754.1	1753.1	1752.1	1751.1	1750.6	1750.6	1750.6	1750.6	1750.6	1750.6
170°	1774.9	1773.9	1772.9	1771.9	1770.9	1770.4	1770.2	1769.9	1769.5	1769.2	1768.8
172.5°	1788.6	1787.6	1786.6	1785.5	1784.5	1784.0	1783.8	1783.5	1783.2	1782.8	1782.5
175°	1799.3	1798.3	1797.3	1796.2	1795.2	1794.7	1794.4	1793.7	1793.0	1792.3	1791.6
177.5°	1805.3	1804.3	1803.3	1802.3	1801.3	1800.8	1800.5	1799.8	1799.1	1798.4	1797.7
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	52.5	51.9	51.2	50.5	50.2	50.4	50.7	51.0	51.4	51.7	51.4
92.5°	47.5	47.8	48.2	48.5	48.7	48.7	48.7	48.7	48.7	48.7	48.7
95°	97.3	97.3	97.3	97.3	97.3	97.0	96.3	95.6	95.0	94.3	95.0
97.5°	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1
100°	209.9	209.9	209.9	209.9	209.9	209.7	209.4	209.1	208.7	208.4	208.7
102.5°	272.6	272.9	273.3	273.6	273.8	273.6	273.3	272.9	272.6	272.2	272.6
105°	335.3	335.9	336.6	337.3	337.6	337.6	337.6	337.6	337.6	337.6	337.6
107.5°	403.4	403.7	404.1	404.4	404.6	403.8	402.1	400.4	398.7	397.0	398.7
110°	473.0	473.0	473.0	473.0	473.0	472.5	471.5	470.4	469.4	468.4	469.4

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	543.5	542.5	541.4	540.4	539.9	539.6	538.9	538.2	537.6	536.9	537.6
115°	614.1	613.8	613.4	613.1	612.9	612.4	611.4	610.4	609.4	608.4	609.4
117.5°	683.4	682.4	681.4	680.4	679.9	679.4	678.4	677.3	676.3	675.3	676.3
120°	751.3	751.3	751.3	751.3	751.3	750.8	749.8	748.8	747.8	746.8	747.8
122.5°	823.3	822.3	821.3	820.3	819.8	819.5	818.8	818.1	817.4	816.7	817.4
125°	893.3	892.3	891.2	890.2	889.7	889.5	889.2	888.9	888.5	888.2	888.5
127.5°	961.4	960.0	958.7	957.4	956.7	956.2	955.2	954.1	953.1	952.1	953.1
130°	1030.5	1029.8	1029.1	1028.4	1028.1	1027.4	1026.1	1024.8	1023.4	1022.1	1023.4
132.5°	1099.4	1097.7	1096.0	1094.3	1093.5	1093.0	1092.0	1091.0	1090.0	1089.0	1090.0
135°	1164.7	1164.3	1164.0	1163.7	1163.5	1163.0	1162.0	1160.9	1159.9	1158.9	1159.9
137.5°	1228.6	1228.2	1227.9	1227.6	1227.4	1226.7	1225.4	1224.0	1222.7	1221.3	1222.7
140°	1292.8	1292.8	1292.8	1292.8	1292.8	1292.1	1290.8	1289.4	1288.1	1286.7	1288.1
142.5°	1350.9	1351.3	1351.6	1351.9	1352.1	1351.4	1350.1	1348.7	1347.4	1346.0	1347.4
145°	1410.2	1410.6	1410.9	1411.2	1411.4	1410.7	1409.4	1408.0	1406.7	1405.3	1406.7
147.5°	1462.3	1462.9	1463.6	1464.3	1464.6	1463.9	1462.6	1461.3	1459.9	1458.6	1459.9
150°	1511.3	1512.3	1513.3	1514.3	1514.8	1514.3	1513.3	1512.3	1511.3	1510.3	1511.3
152.5°	1560.3	1561.6	1563.0	1564.3	1565.0	1564.3	1563.0	1561.6	1560.3	1558.9	1560.3
155°	1600.2	1601.9	1603.6	1605.3	1606.1	1605.6	1604.6	1603.5	1602.5	1601.5	1602.5
157.5°	1638.9	1641.3	1643.6	1646.0	1647.2	1646.4	1644.7	1643.0	1641.3	1639.6	1641.3
160°	1673.5	1675.5	1677.6	1679.6	1680.6	1679.9	1678.6	1677.2	1675.9	1674.5	1675.9
162.5°	1704.3	1706.7	1709.0	1711.4	1712.6	1711.8	1710.1	1708.4	1706.7	1705.0	1706.7
165°	1730.2	1732.5	1734.9	1737.2	1738.4	1737.6	1735.9	1734.2	1732.5	1730.8	1732.5
167.5°	1753.0	1755.3	1757.7	1760.0	1761.2	1760.4	1758.7	1757.0	1755.3	1753.6	1755.3
170°	1771.2	1773.6	1775.9	1778.3	1779.5	1778.5	1776.5	1774.4	1772.4	1770.4	1772.4
172.5°	1784.9	1787.3	1789.6	1792.0	1793.2	1792.2	1790.1	1788.1	1786.0	1784.0	1786.0
175°	1794.0	1796.4	1798.7	1801.1	1802.3	1801.3	1799.3	1797.2	1795.2	1793.2	1795.2
177.5°	1799.7	1801.8	1803.8	1805.9	1806.9	1805.9	1803.8	1801.8	1799.7	1797.7	1799.7
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	51.0	50.7	50.4	50.2	50.5	51.2	51.9	52.5	53.2	45.8	38.4
92.5°	48.7	48.7	48.7	48.7	48.5	48.2	47.8	47.5	47.1	46.8	46.4
95°	95.6	96.3	97.0	97.3	97.3	97.3	97.3	97.3	97.3	96.6	96.0
97.5°	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	150.7	149.4
100°	209.1	209.4	209.7	209.9	209.9	209.9	209.9	209.9	209.9	208.9	207.9
102.5°	272.9	273.3	273.6	273.8	273.6	273.3	272.9	272.6	272.2	270.9	269.5
105°	337.6	337.6	337.6	337.6	337.3	336.6	335.9	335.3	334.6	333.9	333.3
107.5°	400.4	402.1	403.8	404.6	404.4	404.1	403.7	403.4	403.0	403.0	403.0
110°	470.4	471.5	472.5	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	538.2	538.9	539.6	539.9	540.4	541.4	542.5	543.5	544.5	544.8	545.2
115°	610.4	611.4	612.4	612.9	613.1	613.4	613.8	614.1	614.5	615.2	615.8
117.5°	677.3	678.4	679.4	679.9	680.4	681.4	682.4	683.4	684.4	686.1	687.8
120°	748.8	749.8	750.8	751.3	751.3	751.3	751.3	751.3	751.3	754.0	756.7
122.5°	818.1	818.8	819.5	819.8	820.3	821.3	822.3	823.3	824.3	826.0	827.7
125°	888.9	889.2	889.5	889.7	890.2	891.2	892.3	893.3	894.3	895.3	896.3
127.5°	954.1	955.2	956.2	956.7	957.4	958.7	960.0	961.4	962.7	964.1	965.4
130°	1024.8	1026.1	1027.4	1028.1	1028.4	1029.1	1029.8	1030.5	1031.2	1031.9	1032.5
132.5°	1091.0	1092.0	1093.0	1093.5	1094.3	1096.0	1097.7	1099.4	1101.1	1100.8	1100.4
135°	1160.9	1162.0	1163.0	1163.5	1163.7	1164.0	1164.3	1164.7	1165.0	1164.3	1163.7
137.5°	1224.0	1225.4	1226.7	1227.4	1227.6	1227.9	1228.2	1228.6	1228.9	1228.2	1227.6
140°	1289.4	1290.8	1292.1	1292.8	1292.8	1292.8	1292.8	1292.8	1292.8	1291.1	1289.4
142.5°	1348.7	1350.1	1351.4	1352.1	1351.9	1351.6	1351.3	1350.9	1350.6	1349.6	1348.6
145°	1408.0	1409.4	1410.7	1411.4	1411.2	1410.9	1410.6	1410.2	1409.9	1407.9	1405.9
147.5°	1461.3	1462.6	1463.9	1464.6	1464.3	1463.6	1462.9	1462.3	1461.6	1460.2	1458.9
150°	1512.3	1513.3	1514.3	1514.8	1514.3	1513.3	1512.3	1511.3	1510.3	1508.9	1507.6
152.5°	1561.6	1563.0	1564.3	1565.0	1564.3	1563.0	1561.6	1560.3	1558.9	1557.2	1555.5
155°	1603.5	1604.6	1605.6	1606.1	1605.3	1603.6	1601.9	1600.2	1598.5	1597.5	1596.5
157.5°	1643.0	1644.7	1646.4	1647.2	1646.0	1643.6	1641.3	1638.9	1636.5	1635.8	1635.2
160°	1677.2	1678.6	1679.9	1680.6	1679.6	1677.6	1675.5	1673.5	1671.5	1671.2	1670.8
162.5°	1708.4	1710.1	1711.8	1712.6	1711.4	1709.0	1706.7	1704.3	1701.9	1701.6	1701.2
165°	1734.2	1735.9	1737.6	1738.4	1737.2	1734.9	1732.5	1730.2	1727.8	1727.8	1727.8
167.5°	1757.0	1758.7	1760.4	1761.2	1760.0	1757.7	1755.3	1753.0	1750.6	1750.6	1750.6
170°	1774.4	1776.5	1778.5	1779.5	1778.3	1775.9	1773.6	1771.2	1768.8	1769.2	1769.5
172.5°	1788.1	1790.1	1792.2	1793.2	1792.0	1789.6	1787.3	1784.9	1782.5	1782.8	1783.2
175°	1797.2	1799.3	1801.3	1802.3	1801.1	1798.7	1796.4	1794.0	1791.6	1792.3	1793.0
177.5°	1801.8	1803.8	1805.9	1806.9	1805.9	1803.8	1801.8	1799.7	1797.7	1798.4	1799.1
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	30.9	23.5	19.8	17.8	13.7	9.6	5.6	1.5	5.6	9.6	13.7
92.5°	46.1	45.8	45.6	44.3	41.6	38.9	36.2	33.5	36.2	38.9	41.6
95°	95.3	94.6	94.3	92.6	89.2	85.9	82.5	79.1	82.5	85.9	89.2
97.5°	148.0	146.7	146.0	144.5	141.4	138.4	135.3	132.3	135.3	138.4	141.4
100°	206.8	205.8	205.3	204.0	201.3	198.6	195.9	193.2	195.9	198.6	201.3
102.5°	268.2	266.9	266.2	265.2	263.1	261.1	259.0	257.0	259.0	261.1	263.1
105°	332.6	331.9	331.6	331.1	330.1	329.0	328.0	327.0	328.0	329.0	330.1
107.5°	403.0	403.0	403.0	402.3	401.0	399.7	398.3	397.0	398.3	399.7	401.0
110°	473.0	473.0	473.0	472.0	470.0	467.9	465.9	463.9	465.9	467.9	470.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	545.5	545.8	546.0	545.0	543.0	540.9	538.9	536.9	538.9	540.9	543.0
115°	616.5	617.2	617.5	616.5	614.5	612.4	610.4	608.4	610.4	612.4	614.5
117.5°	689.5	691.2	692.0	690.7	688.0	685.3	682.6	679.9	682.6	685.3	688.0
120°	759.4	762.1	763.5	762.1	759.4	756.7	754.0	751.3	754.0	756.7	759.4
122.5°	829.4	831.1	831.9	830.2	826.8	823.5	820.1	816.7	820.1	823.5	826.8
125°	897.4	898.4	898.9	897.4	894.3	891.3	888.2	885.2	888.2	891.3	894.3
127.5°	966.8	968.1	968.8	966.9	963.2	959.5	955.8	952.1	955.8	959.5	963.2
130°	1033.2	1033.9	1034.2	1032.0	1027.6	1023.3	1018.9	1014.5	1018.9	1023.3	1027.6
132.5°	1100.1	1099.8	1099.6	1097.9	1094.5	1091.2	1087.8	1084.4	1087.8	1091.2	1094.5
135°	1163.0	1162.3	1162.0	1160.1	1156.4	1152.7	1149.0	1145.3	1149.0	1152.7	1156.4
137.5°	1226.9	1226.2	1225.9	1224.4	1221.3	1218.3	1215.2	1212.2	1215.2	1218.3	1221.3
140°	1287.7	1286.0	1285.2	1283.7	1280.6	1277.6	1274.5	1271.5	1274.5	1277.6	1280.6
142.5°	1347.5	1346.5	1346.0	1344.5	1341.4	1338.4	1335.3	1332.3	1335.3	1338.4	1341.4
145°	1403.8	1401.8	1400.8	1399.6	1397.2	1394.9	1392.5	1390.1	1392.5	1394.9	1397.2
147.5°	1457.5	1456.2	1455.5	1454.0	1450.9	1447.9	1444.8	1441.8	1444.8	1447.9	1450.9
150°	1506.2	1504.9	1504.2	1503.2	1501.2	1499.1	1497.1	1495.1	1497.1	1499.1	1501.2
152.5°	1553.8	1552.1	1551.3	1550.3	1548.3	1546.2	1544.2	1542.2	1544.2	1546.2	1548.3
155°	1595.4	1594.4	1593.9	1593.4	1592.4	1591.4	1590.4	1589.4	1590.4	1591.4	1592.4
157.5°	1634.5	1633.8	1633.5	1633.2	1632.5	1631.8	1631.1	1630.4	1631.1	1631.8	1632.5
160°	1670.5	1670.2	1670.0	1669.7	1669.0	1668.3	1667.6	1666.9	1667.6	1668.3	1669.0
162.5°	1700.9	1700.6	1700.4	1700.4	1700.4	1700.4	1700.4	1700.4	1700.4	1700.4	1700.4
165°	1727.8	1727.8	1727.8	1728.0	1728.3	1728.6	1729.0	1729.3	1729.0	1728.6	1728.3
167.5°	1750.6	1750.6	1750.6	1751.1	1752.1	1753.1	1754.1	1755.1	1754.1	1753.1	1752.1
170°	1769.9	1770.2	1770.4	1770.9	1771.9	1772.9	1773.9	1774.9	1773.9	1772.9	1771.9
172.5°	1783.5	1783.8	1784.0	1784.5	1785.5	1786.6	1787.6	1788.6	1787.6	1786.6	1785.5
175°	1793.7	1794.4	1794.7	1795.2	1796.2	1797.3	1798.3	1799.3	1798.3	1797.3	1796.2
177.5°	1799.8	1800.5	1800.8	1801.3	1802.3	1803.3	1804.3	1805.3	1804.3	1803.3	1802.3
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	17.8	19.8	23.5	30.9	38.4	45.8	53.2	52.5	51.9	51.2	50.5
92.5°	44.3	45.6	45.8	46.1	46.4	46.8	47.1	47.5	47.8	48.2	48.5
95°	92.6	94.3	94.6	95.3	96.0	96.6	97.3	97.3	97.3	97.3	97.3
97.5°	144.5	146.0	146.7	148.0	149.4	150.7	152.1	152.1	152.1	152.1	152.1
100°	204.0	205.3	205.8	206.8	207.9	208.9	209.9	209.9	209.9	209.9	209.9
102.5°	265.2	266.2	266.9	268.2	269.5	270.9	272.2	272.6	272.9	273.3	273.6
105°	331.1	331.6	331.9	332.6	333.3	333.9	334.6	335.3	335.9	336.6	337.3
107.5°	402.3	403.0	403.0	403.0	403.0	403.0	403.0	403.4	403.7	404.1	404.4
110°	472.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	545.0	546.0	545.8	545.5	545.2	544.8	544.5	543.5	542.5	541.4	540.4
115°	616.5	617.5	617.2	616.5	615.8	615.2	614.5	614.1	613.8	613.4	613.1
117.5°	690.7	692.0	691.2	689.5	687.8	686.1	684.4	683.4	682.4	681.4	680.4
120°	762.1	763.5	762.1	759.4	756.7	754.0	751.3	751.3	751.3	751.3	751.3
122.5°	830.2	831.9	831.1	829.4	827.7	826.0	824.3	823.3	822.3	821.3	820.3
125°	897.4	898.9	898.4	897.4	896.3	895.3	894.3	893.3	892.3	891.2	890.2
127.5°	966.9	968.8	968.1	966.8	965.4	964.1	962.7	961.4	960.0	958.7	957.4
130°	1032.0	1034.2	1033.9	1033.2	1032.5	1031.9	1031.2	1030.5	1029.8	1029.1	1028.4
132.5°	1097.9	1099.6	1099.8	1100.1	1100.4	1100.8	1101.1	1099.4	1097.7	1096.0	1094.3
135°	1160.1	1162.0	1162.3	1163.0	1163.7	1164.3	1165.0	1164.7	1164.3	1164.0	1163.7
137.5°	1224.4	1225.9	1226.2	1226.9	1227.6	1228.2	1228.9	1228.6	1228.2	1227.9	1227.6
140°	1283.7	1285.2	1286.0	1287.7	1289.4	1291.1	1292.8	1292.8	1292.8	1292.8	1292.8
142.5°	1344.5	1346.0	1346.5	1347.5	1348.6	1349.6	1350.6	1350.9	1351.3	1351.6	1351.9
145°	1399.6	1400.8	1401.8	1403.8	1405.9	1407.9	1409.9	1410.2	1410.6	1410.9	1411.2
147.5°	1454.0	1455.5	1456.2	1457.5	1458.9	1460.2	1461.6	1462.3	1462.9	1463.6	1464.3
150°	1503.2	1504.2	1504.9	1506.2	1507.6	1508.9	1510.3	1511.3	1512.3	1513.3	1514.3
152.5°	1550.3	1551.3	1552.1	1553.8	1555.5	1557.2	1558.9	1560.3	1561.6	1563.0	1564.3
155°	1593.4	1593.9	1594.4	1595.4	1596.5	1597.5	1598.5	1600.2	1601.9	1603.6	1605.3
157.5°	1633.2	1633.5	1633.8	1634.5	1635.2	1635.8	1636.5	1638.9	1641.3	1643.6	1646.0
160°	1669.7	1670.0	1670.2	1670.5	1670.8	1671.2	1671.5	1673.5	1675.5	1677.6	1679.6
162.5°	1700.4	1700.4	1700.6	1700.9	1701.2	1701.6	1701.9	1704.3	1706.7	1709.0	1711.4
165°	1728.0	1727.8	1727.8	1727.8	1727.8	1727.8	1727.8	1730.2	1732.5	1734.9	1737.2
167.5°	1751.1	1750.6	1750.6	1750.6	1750.6	1750.6	1750.6	1753.0	1755.3	1757.7	1760.0
170°	1770.9	1770.4	1770.2	1769.9	1769.5	1769.2	1768.8	1771.2	1773.6	1775.9	1778.3
172.5°	1784.5	1784.0	1783.8	1783.5	1783.2	1782.8	1782.5	1784.9	1787.3	1789.6	1792.0
175°	1795.2	1794.7	1794.4	1793.7	1793.0	1792.3	1791.6	1794.0	1796.4	1798.7	1801.1
177.5°	1801.3	1800.8	1800.5	1799.8	1799.1	1798.4	1797.7	1799.7	1801.8	1803.8	1805.9
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	50.2	50.4	50.7	51.0	51.4	51.7	51.4	51.0	50.7	50.4	50.2
92.5°	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7	48.7
95°	97.3	97.0	96.3	95.6	95.0	94.3	95.0	95.6	96.3	97.0	97.3
97.5°	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1	152.1
100°	209.9	209.7	209.4	209.1	208.7	208.4	208.7	209.1	209.4	209.7	209.9
102.5°	273.8	273.6	273.3	272.9	272.6	272.2	272.6	272.9	273.3	273.6	273.8
105°	337.6	337.6	337.6	337.6	337.6	337.6	337.6	337.6	337.6	337.6	337.6
107.5°	404.6	403.8	402.1	400.4	398.7	397.0	398.7	400.4	402.1	403.8	404.6
110°	473.0	472.5	471.5	470.4	469.4	468.4	469.4	470.4	471.5	472.5	473.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	539.9	539.6	538.9	538.2	537.6	536.9	537.6	538.2	538.9	539.6	539.9
115°	612.9	612.4	611.4	610.4	609.4	608.4	609.4	610.4	611.4	612.4	612.9
117.5°	679.9	679.4	678.4	677.3	676.3	675.3	676.3	677.3	678.4	679.4	679.9
120°	751.3	750.8	749.8	748.8	747.8	746.8	747.8	748.8	749.8	750.8	751.3
122.5°	819.8	819.5	818.8	818.1	817.4	816.7	817.4	818.1	818.8	819.5	819.8
125°	889.7	889.5	889.2	888.9	888.5	888.2	888.5	888.9	889.2	889.5	889.7
127.5°	956.7	956.2	955.2	954.1	953.1	952.1	953.1	954.1	955.2	956.2	956.7
130°	1028.1	1027.4	1026.1	1024.8	1023.4	1022.1	1023.4	1024.8	1026.1	1027.4	1028.1
132.5°	1093.5	1093.0	1092.0	1091.0	1090.0	1089.0	1090.0	1091.0	1092.0	1093.0	1093.5
135°	1163.5	1163.0	1162.0	1160.9	1159.9	1158.9	1159.9	1160.9	1162.0	1163.0	1163.5
137.5°	1227.4	1226.7	1225.4	1224.0	1222.7	1221.3	1222.7	1224.0	1225.4	1226.7	1227.4
140°	1292.8	1292.1	1290.8	1289.4	1288.1	1286.7	1288.1	1289.4	1290.8	1292.1	1292.8
142.5°	1352.1	1351.4	1350.1	1348.7	1347.4	1346.0	1347.4	1348.7	1350.1	1351.4	1352.1
145°	1411.4	1410.7	1409.4	1408.0	1406.7	1405.3	1406.7	1408.0	1409.4	1410.7	1411.4
147.5°	1464.6	1463.9	1462.6	1461.3	1459.9	1458.6	1459.9	1461.3	1462.6	1463.9	1464.6
150°	1514.8	1514.3	1513.3	1512.3	1511.3	1510.3	1511.3	1512.3	1513.3	1514.3	1514.8
152.5°	1565.0	1564.3	1563.0	1561.6	1560.3	1558.9	1560.3	1561.6	1563.0	1564.3	1565.0
155°	1606.1	1605.6	1604.6	1603.5	1602.5	1601.5	1602.5	1603.5	1604.6	1605.6	1606.1
157.5°	1647.2	1646.4	1644.7	1643.0	1641.3	1639.6	1641.3	1643.0	1644.7	1646.4	1647.2
160°	1680.6	1679.9	1678.6	1677.2	1675.9	1674.5	1675.9	1677.2	1678.6	1679.9	1680.6
162.5°	1712.6	1711.8	1710.1	1708.4	1706.7	1705.0	1706.7	1708.4	1710.1	1711.8	1712.6
165°	1738.4	1737.6	1735.9	1734.2	1732.5	1730.8	1732.5	1734.2	1735.9	1737.6	1738.4
167.5°	1761.2	1760.4	1758.7	1757.0	1755.3	1753.6	1755.3	1757.0	1758.7	1760.4	1761.2
170°	1779.5	1778.5	1776.5	1774.4	1772.4	1770.4	1772.4	1774.4	1776.5	1778.5	1779.5
172.5°	1793.2	1792.2	1790.1	1788.1	1786.0	1784.0	1786.0	1788.1	1790.1	1792.2	1793.2
175°	1802.3	1801.3	1799.3	1797.2	1795.2	1793.2	1795.2	1797.2	1799.3	1801.3	1802.3
177.5°	1806.9	1805.9	1803.8	1801.8	1799.7	1797.7	1799.7	1801.8	1803.8	1805.9	1806.9
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	50.5	51.2	51.9	52.5	53.2	45.8	38.4	30.9	23.5	19.8	17.8
92.5°	48.5	48.2	47.8	47.5	47.1	46.8	46.4	46.1	45.8	45.6	44.3
95°	97.3	97.3	97.3	97.3	97.3	96.6	96.0	95.3	94.6	94.3	92.6
97.5°	152.1	152.1	152.1	152.1	152.1	150.7	149.4	148.0	146.7	146.0	144.5
100°	209.9	209.9	209.9	209.9	209.9	208.9	207.9	206.8	205.8	205.3	204.0
102.5°	273.6	273.3	272.9	272.6	272.2	270.9	269.5	268.2	266.9	266.2	265.2
105°	337.3	336.6	335.9	335.3	334.6	333.9	333.3	332.6	331.9	331.6	331.1
107.5°	404.4	404.1	403.7	403.4	403.0	403.0	403.0	403.0	403.0	403.0	402.3
110°	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	473.0	472.0

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	540.4	541.4	542.5	543.5	544.5	544.8	545.2	545.5	545.8	546.0	545.0
115°	613.1	613.4	613.8	614.1	614.5	615.2	615.8	616.5	617.2	617.5	616.5
117.5°	680.4	681.4	682.4	683.4	684.4	686.1	687.8	689.5	691.2	692.0	690.7
120°	751.3	751.3	751.3	751.3	751.3	754.0	756.7	759.4	762.1	763.5	762.1
122.5°	820.3	821.3	822.3	823.3	824.3	826.0	827.7	829.4	831.1	831.9	830.2
125°	890.2	891.2	892.3	893.3	894.3	895.3	896.3	897.4	898.4	898.9	897.4
127.5°	957.4	958.7	960.0	961.4	962.7	964.1	965.4	966.8	968.1	968.8	966.9
130°	1028.4	1029.1	1029.8	1030.5	1031.2	1031.9	1032.5	1033.2	1033.9	1034.2	1032.0
132.5°	1094.3	1096.0	1097.7	1099.4	1101.1	1100.8	1100.4	1100.1	1099.8	1099.6	1097.9
135°	1163.7	1164.0	1164.3	1164.7	1165.0	1164.3	1163.7	1163.0	1162.3	1162.0	1160.1
137.5°	1227.6	1227.9	1228.2	1228.6	1228.9	1228.2	1227.6	1226.9	1226.2	1225.9	1224.4
140°	1292.8	1292.8	1292.8	1292.8	1292.8	1291.1	1289.4	1287.7	1286.0	1285.2	1283.7
142.5°	1351.9	1351.6	1351.3	1350.9	1350.6	1349.6	1348.6	1347.5	1346.5	1346.0	1344.5
145°	1411.2	1410.9	1410.6	1410.2	1409.9	1407.9	1405.9	1403.8	1401.8	1400.8	1399.6
147.5°	1464.3	1463.6	1462.9	1462.3	1461.6	1460.2	1458.9	1457.5	1456.2	1455.5	1454.0
150°	1514.3	1513.3	1512.3	1511.3	1510.3	1508.9	1507.6	1506.2	1504.9	1504.2	1503.2
152.5°	1564.3	1563.0	1561.6	1560.3	1558.9	1557.2	1555.5	1553.8	1552.1	1551.3	1550.3
155°	1605.3	1603.6	1601.9	1600.2	1598.5	1597.5	1596.5	1595.4	1594.4	1593.9	1593.4
157.5°	1646.0	1643.6	1641.3	1638.9	1636.5	1635.8	1635.2	1634.5	1633.8	1633.5	1633.2
160°	1679.6	1677.6	1675.5	1673.5	1671.5	1671.2	1670.8	1670.5	1670.2	1670.0	1669.7
162.5°	1711.4	1709.0	1706.7	1704.3	1701.9	1701.6	1701.2	1700.9	1700.6	1700.4	1700.4
165°	1737.2	1734.9	1732.5	1730.2	1727.8	1727.8	1727.8	1727.8	1727.8	1727.8	1728.0
167.5°	1760.0	1757.7	1755.3	1753.0	1750.6	1750.6	1750.6	1750.6	1750.6	1750.6	1751.1
170°	1778.3	1775.9	1773.6	1771.2	1768.8	1769.2	1769.5	1769.9	1770.2	1770.4	1770.9
172.5°	1792.0	1789.6	1787.3	1784.9	1782.5	1782.8	1783.2	1783.5	1783.8	1784.0	1784.5
175°	1801.1	1798.7	1796.4	1794.0	1791.6	1792.3	1793.0	1793.7	1794.4	1794.7	1795.2
177.5°	1805.9	1803.8	1801.8	1799.7	1797.7	1798.4	1799.1	1799.8	1800.5	1800.8	1801.3
180°	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3	1802.3

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	13.7	9.6	5.6	1.5
92.5°	41.6	38.9	36.2	33.5
95°	89.2	85.9	82.5	79.1
97.5°	141.4	138.4	135.3	132.3
100°	201.3	198.6	195.9	193.2
102.5°	263.1	261.1	259.0	257.0
105°	330.1	329.0	328.0	327.0
107.5°	401.0	399.7	398.3	397.0
110°	470.0	467.9	465.9	463.9

TEST NUMBER: P1029628

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	543.0	540.9	538.9	536.9
115°	614.5	612.4	610.4	608.4
117.5°	688.0	685.3	682.6	679.9
120°	759.4	756.7	754.0	751.3
122.5°	826.8	823.5	820.1	816.7
125°	894.3	891.3	888.2	885.2
127.5°	963.2	959.5	955.8	952.1
130°	1027.6	1023.3	1018.9	1014.5
132.5°	1094.5	1091.2	1087.8	1084.4
135°	1156.4	1152.7	1149.0	1145.3
137.5°	1221.3	1218.3	1215.2	1212.2
140°	1280.6	1277.6	1274.5	1271.5
142.5°	1341.4	1338.4	1335.3	1332.3
145°	1397.2	1394.9	1392.5	1390.1
147.5°	1450.9	1447.9	1444.8	1441.8
150°	1501.2	1499.1	1497.1	1495.1
152.5°	1548.3	1546.2	1544.2	1542.2
155°	1592.4	1591.4	1590.4	1589.4
157.5°	1632.5	1631.8	1631.1	1630.4
160°	1669.0	1668.3	1667.6	1666.9
162.5°	1700.4	1700.4	1700.4	1700.4
165°	1728.3	1728.6	1729.0	1729.3
167.5°	1752.1	1753.1	1754.1	1755.1
170°	1771.9	1772.9	1773.9	1774.9
172.5°	1785.5	1786.6	1787.6	1788.6
175°	1796.2	1797.3	1798.3	1799.3
177.5°	1802.3	1803.3	1804.3	1805.3
180°	1802.3	1802.3	1802.3	1802.3

(END OF REPORT)