

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029663

Luminaire Tested: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029663
REPORT IS A COMBINATION OF REPORTS P986570 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4671.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	58	58	54
2	93	85	80	75	87	80	75	71	71	67	64	62	59	57	54	52	50	50	50	46
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	43	43	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	38	38	35
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34	34	34	31
6	67	55	47	41	62	52	45	39	46	40	36	41	37	33	36	33	30	30	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	27	27	24
8	58	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	24	24	22
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22	22	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	2.7
10°-20°	368.0	7.9
20°-30°	534.1	11.4
30°-40°	563.1	12.1
40°-50°	498.3	10.7
50°-60°	397.9	8.5
60°-70°	270.2	5.8
70°-80°	138.3	3.0
80°-90°	33.7	0.7
90°-100°	19.6	0.4
100°-110°	73.0	1.6
110°-120°	193.6	4.1
120°-130°	321.1	6.9
130°-140°	341.1	7.3
140°-150°	317.0	6.8
150°-160°	254.9	5.5
160°-170°	164.2	3.5
170°-180°	56.5	1.2
0°-30°	1028.6	22.0
0°-40°	1591.7	34.1
0°-60°	2487.8	53.3
0°-90°	2930.1	62.7
90°-120°	286.2	6.1
90°-150°	1265.3	27.1
90°-180°	1741.0	37.3
0°-180°	4671.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	0	12	0	12	0	3
95°	28	18	28	18	28	33
105°	131	33	131	33	131	140
115°	247	35	247	35	247	243
125°	349	367	349	367	349	312
135°	432	446	432	446	432	334
145°	502	509	502	509	502	314
155°	552	553	552	553	552	254
165°	582	580	582	580	582	164
175°	595	592	595	592	595	57
180°	594	594	594	594	594	

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	0.4	1.5	2.5	3.6	4.7	5.2	5.6	6.3	7.1	7.8	8.6
92.5°	10.7	10.3	9.9	9.6	9.2	9.0	9.1	9.4	9.7	10.0	10.3
95°	27.9	24.8	21.6	18.5	15.4	13.8	14.1	14.8	15.5	16.1	16.8
97.5°	50.3	42.5	34.6	26.8	18.9	15.0	15.8	17.3	18.8	20.4	21.9
100°	76.1	63.0	49.9	36.8	23.7	17.2	18.0	19.6	21.3	22.9	24.5
102.5°	104.4	104.2	104.0	103.9	103.7	103.6	94.9	77.5	60.2	42.8	25.4
105°	130.6	133.5	136.3	139.2	142.1	143.5	130.5	104.4	78.3	52.3	26.2
107.5°	161.1	163.5	165.9	168.3	170.7	171.9	155.8	123.6	91.5	59.3	27.1
110°	190.4	192.4	194.4	196.4	198.4	199.4	185.6	158.0	130.4	102.8	75.2

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	217.9	219.6	221.3	223.0	224.7	225.6	224.8	223.2	221.5	219.9	218.3
115°	247.1	248.7	250.3	252.0	253.6	254.4	255.6	258.0	260.3	262.7	265.1
117.5°	272.4	274.3	276.2	278.1	280.0	281.0	281.8	283.4	285.1	286.7	288.3
120°	300.8	302.2	303.6	305.1	306.5	307.2	308.1	309.8	311.5	313.3	315.0
122.5°	324.9	326.4	327.9	329.4	330.9	331.7	332.7	334.6	336.5	338.4	340.3
125°	349.3	350.5	351.8	353.0	354.3	354.9	355.8	357.6	359.5	361.3	363.1
127.5°	371.7	373.0	374.4	375.7	377.0	377.7	378.4	379.9	381.3	382.8	384.2
130°	392.7	394.2	395.8	397.3	398.8	399.6	400.1	401.2	402.2	403.3	404.3
132.5°	414.2	415.4	416.7	417.9	419.2	419.8	420.3	421.4	422.4	423.5	424.5
135°	432.3	433.8	435.4	436.9	438.4	439.2	439.6	440.5	441.3	442.2	443.0
137.5°	451.2	452.3	453.5	454.6	455.7	456.3	456.8	457.7	458.7	459.6	460.6
140°	469.7	470.5	471.2	472.0	472.7	473.1	473.6	474.7	475.7	476.8	477.8
142.5°	485.1	485.8	486.4	487.1	487.8	488.1	488.7	490.0	491.2	492.5	493.7
145°	501.5	501.4	501.3	501.2	501.1	501.0	501.8	503.4	505.1	506.7	508.3
147.5°	515.6	515.3	515.1	514.8	514.5	514.4	515.2	516.8	518.5	520.1	521.7
150°	529.4	528.7	528.1	527.4	526.7	526.4	527.2	528.7	530.2	531.8	533.3
152.5°	541.0	540.2	539.5	538.7	538.0	537.6	538.3	539.7	541.2	542.6	544.0
155°	552.2	551.3	550.5	549.6	548.7	548.3	548.9	550.0	551.2	552.3	553.5
157.5°	561.2	560.4	559.7	558.9	558.2	557.8	558.2	559.1	559.9	560.8	561.6
160°	568.9	568.3	567.7	567.2	566.6	566.3	566.6	567.2	567.7	568.3	568.9
162.5°	575.8	575.2	574.6	574.1	573.5	573.2	573.4	573.9	574.4	574.9	575.4
165°	581.8	581.2	580.6	580.1	579.5	579.2	579.3	579.6	579.9	580.2	580.5
167.5°	586.5	585.9	585.4	584.8	584.3	584.0	584.1	584.4	584.7	585.0	585.3
170°	590.4	589.8	589.2	588.7	588.1	587.8	587.9	588.1	588.3	588.5	588.7
172.5°	593.0	592.4	591.8	591.3	590.7	590.4	590.5	590.7	590.9	591.1	591.3
175°	595.1	594.4	593.8	593.1	592.4	592.1	592.2	592.4	592.6	592.8	593.0
177.5°	596.0	595.3	594.7	594.0	593.3	593.0	593.0	593.1	593.2	593.3	593.4
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	9.1	9.5	10.0	10.5	10.7	10.8	11.0	11.2	11.4	11.6	11.4
92.5°	10.5	10.7	10.9	11.1	11.2	11.2	11.3	11.4	11.5	11.6	11.5
95°	17.3	17.7	18.2	18.7	18.9	18.9	18.8	18.7	18.6	18.5	18.6
97.5°	22.2	22.5	22.8	23.1	23.2	23.2	23.3	23.4	23.5	23.6	23.5
100°	25.3	26.0	26.8	27.5	27.9	28.0	28.2	28.4	28.6	28.8	28.6
102.5°	26.4	27.5	28.5	29.6	30.1	30.2	30.5	30.8	31.1	31.4	31.1
105°	27.2	28.3	29.3	30.4	30.9	31.1	31.5	31.9	32.3	32.7	32.3
107.5°	28.1	29.2	30.2	31.3	31.8	32.0	32.4	32.7	33.1	33.5	33.1
110°	65.6	56.1	46.5	37.0	32.2	32.4	32.8	33.1	33.5	33.9	33.5

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	177.1	136.0	94.8	53.7	33.1	33.2	33.5	33.8	34.1	34.4	34.1
115°	220.9	176.7	132.5	88.3	66.2	62.8	55.9	49.0	42.1	35.2	42.1
117.5°	274.7	261.0	247.4	233.7	226.9	214.4	189.4	164.3	139.3	114.3	139.3
120°	316.1	317.3	318.4	319.5	320.1	313.7	300.8	287.9	275.0	262.1	275.0
122.5°	340.9	341.5	342.0	342.6	342.9	342.9	343.0	343.1	343.2	343.3	343.2
125°	363.8	364.4	365.1	365.8	366.1	366.2	366.5	366.8	367.1	367.4	367.1
127.5°	385.2	386.1	387.1	388.0	388.5	388.5	388.6	388.7	388.8	388.9	388.8
130°	405.4	406.4	407.5	408.6	409.1	409.0	408.9	408.8	408.7	408.6	408.7
132.5°	425.4	426.2	427.1	428.0	428.4	428.4	428.3	428.2	428.1	428.0	428.1
135°	444.0	444.9	445.9	446.8	447.3	447.2	447.0	446.9	446.7	446.5	446.7
137.5°	461.6	462.5	463.5	464.4	464.9	464.8	464.5	464.2	463.9	463.6	463.9
140°	478.7	479.5	480.4	481.3	481.7	481.5	481.0	480.5	480.0	479.5	480.0
142.5°	494.5	495.3	496.0	496.8	497.2	497.0	496.5	496.0	495.5	495.0	495.5
145°	509.0	509.6	510.3	511.0	511.3	511.1	510.6	510.1	509.7	509.2	509.7
147.5°	522.2	522.6	523.1	523.6	523.8	523.6	523.2	522.9	522.5	522.1	522.5
150°	533.9	534.4	535.0	535.5	535.8	535.6	535.1	534.6	534.2	533.7	534.2
152.5°	544.6	545.2	545.7	546.3	546.6	546.3	545.6	544.9	544.3	543.6	544.3
155°	554.1	554.6	555.2	555.7	556.0	555.6	554.9	554.1	553.4	552.6	553.4
157.5°	562.3	562.9	563.6	564.3	564.6	564.2	563.5	562.7	562.0	561.2	562.0
160°	569.5	570.1	570.6	571.2	571.5	571.2	570.5	569.8	569.2	568.5	569.2
162.5°	576.1	576.7	577.4	578.1	578.4	578.0	577.1	576.2	575.4	574.5	575.4
165°	581.2	581.8	582.5	583.2	583.5	583.2	582.5	581.8	581.2	580.5	581.2
167.5°	586.0	586.6	587.3	588.0	588.3	587.9	587.0	586.1	585.3	584.4	585.3
170°	589.4	590.0	590.7	591.4	591.7	591.3	590.4	589.5	588.7	587.8	588.7
172.5°	592.0	592.6	593.3	594.0	594.3	593.9	593.0	592.1	591.3	590.4	591.3
175°	593.7	594.3	595.0	595.7	596.0	595.5	594.6	593.6	592.7	591.7	592.7
177.5°	594.1	594.7	595.4	596.1	596.4	596.0	595.1	594.3	593.4	592.6	593.4
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	11.2	11.0	10.8	10.7	10.5	10.0	9.5	9.1	8.6	7.8	7.1
92.5°	11.4	11.3	11.2	11.2	11.1	10.9	10.7	10.5	10.3	10.0	9.7
95°	18.7	18.8	18.9	18.9	18.7	18.2	17.7	17.3	16.8	16.1	15.5
97.5°	23.4	23.3	23.2	23.2	23.1	22.8	22.5	22.2	21.9	20.4	18.8
100°	28.4	28.2	28.0	27.9	27.5	26.8	26.0	25.3	24.5	22.9	21.3
102.5°	30.8	30.5	30.2	30.1	29.6	28.5	27.5	26.4	25.4	42.8	60.2
105°	31.9	31.5	31.1	30.9	30.4	29.3	28.3	27.2	26.2	52.3	78.3
107.5°	32.7	32.4	32.0	31.8	31.3	30.2	29.2	28.1	27.1	59.3	91.5
110°	33.1	32.8	32.4	32.2	37.0	46.5	56.1	65.6	75.2	102.8	130.4

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	33.8	33.5	33.2	33.1	53.7	94.8	136.0	177.1	218.3	219.9	221.5
115°	49.0	55.9	62.8	66.2	88.3	132.5	176.7	220.9	265.1	262.7	260.3
117.5°	164.3	189.4	214.4	226.9	233.7	247.4	261.0	274.7	288.3	286.7	285.1
120°	287.9	300.8	313.7	320.1	319.5	318.4	317.3	316.1	315.0	313.3	311.5
122.5°	343.1	343.0	342.9	342.9	342.6	342.0	341.5	340.9	340.3	338.4	336.5
125°	366.8	366.5	366.2	366.1	365.8	365.1	364.4	363.8	363.1	361.3	359.5
127.5°	388.7	388.6	388.5	388.5	388.0	387.1	386.1	385.2	384.2	382.8	381.3
130°	408.8	408.9	409.0	409.1	408.6	407.5	406.4	405.4	404.3	403.3	402.2
132.5°	428.2	428.3	428.4	428.4	428.0	427.1	426.2	425.4	424.5	423.5	422.4
135°	446.9	447.0	447.2	447.3	446.8	445.9	444.9	444.0	443.0	442.2	441.3
137.5°	464.2	464.5	464.8	464.9	464.4	463.5	462.5	461.6	460.6	459.6	458.7
140°	480.5	481.0	481.5	481.7	481.3	480.4	479.5	478.7	477.8	476.8	475.7
142.5°	496.0	496.5	497.0	497.2	496.8	496.0	495.3	494.5	493.7	492.5	491.2
145°	510.1	510.6	511.1	511.3	511.0	510.3	509.6	509.0	508.3	506.7	505.1
147.5°	522.9	523.2	523.6	523.8	523.6	523.1	522.6	522.2	521.7	520.1	518.5
150°	534.6	535.1	535.6	535.8	535.5	535.0	534.4	533.9	533.3	531.8	530.2
152.5°	544.9	545.6	546.3	546.6	546.3	545.7	545.2	544.6	544.0	542.6	541.2
155°	554.1	554.9	555.6	556.0	555.7	555.2	554.6	554.1	553.5	552.3	551.2
157.5°	562.7	563.5	564.2	564.6	564.3	563.6	562.9	562.3	561.6	560.8	559.9
160°	569.8	570.5	571.2	571.5	571.2	570.6	570.1	569.5	568.9	568.3	567.7
162.5°	576.2	577.1	578.0	578.4	578.1	577.4	576.7	576.1	575.4	574.9	574.4
165°	581.8	582.5	583.2	583.5	583.2	582.5	581.8	581.2	580.5	580.2	579.9
167.5°	586.1	587.0	587.9	588.3	588.0	587.3	586.6	586.0	585.3	585.0	584.7
170°	589.5	590.4	591.3	591.7	591.4	590.7	590.0	589.4	588.7	588.5	588.3
172.5°	592.1	593.0	593.9	594.3	594.0	593.3	592.6	592.0	591.3	591.1	590.9
175°	593.6	594.6	595.5	596.0	595.7	595.0	594.3	593.7	593.0	592.8	592.6
177.5°	594.3	595.1	596.0	596.4	596.1	595.4	594.7	594.1	593.4	593.3	593.2
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	6.3	5.6	5.2	4.7	3.6	2.5	1.5	0.4	1.5	2.5	3.6
92.5°	9.4	9.1	9.0	9.2	9.6	9.9	10.3	10.7	10.3	9.9	9.6
95°	14.8	14.1	13.8	15.4	18.5	21.6	24.8	27.9	24.8	21.6	18.5
97.5°	17.3	15.8	15.0	18.9	26.8	34.6	42.5	50.3	42.5	34.6	26.8
100°	19.6	18.0	17.2	23.7	36.8	49.9	63.0	76.1	63.0	49.9	36.8
102.5°	77.5	94.9	103.6	103.7	103.9	104.0	104.2	104.4	104.2	104.0	103.9
105°	104.4	130.5	143.5	142.1	139.2	136.3	133.5	130.6	133.5	136.3	139.2
107.5°	123.6	155.8	171.9	170.7	168.3	165.9	163.5	161.1	163.5	165.9	168.3
110°	158.0	185.6	199.4	198.4	196.4	194.4	192.4	190.4	192.4	194.4	196.4

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	223.2	224.8	225.6	224.7	223.0	221.3	219.6	217.9	219.6	221.3	223.0
115°	258.0	255.6	254.4	253.6	252.0	250.3	248.7	247.1	248.7	250.3	252.0
117.5°	283.4	281.8	281.0	280.0	278.1	276.2	274.3	272.4	274.3	276.2	278.1
120°	309.8	308.1	307.2	306.5	305.1	303.6	302.2	300.8	302.2	303.6	305.1
122.5°	334.6	332.7	331.7	330.9	329.4	327.9	326.4	324.9	326.4	327.9	329.4
125°	357.6	355.8	354.9	354.3	353.0	351.8	350.5	349.3	350.5	351.8	353.0
127.5°	379.9	378.4	377.7	377.0	375.7	374.4	373.0	371.7	373.0	374.4	375.7
130°	401.2	400.1	399.6	398.8	397.3	395.8	394.2	392.7	394.2	395.8	397.3
132.5°	421.4	420.3	419.8	419.2	417.9	416.7	415.4	414.2	415.4	416.7	417.9
135°	440.5	439.6	439.2	438.4	436.9	435.4	433.8	432.3	433.8	435.4	436.9
137.5°	457.7	456.8	456.3	455.7	454.6	453.5	452.3	451.2	452.3	453.5	454.6
140°	474.7	473.6	473.1	472.7	472.0	471.2	470.5	469.7	470.5	471.2	472.0
142.5°	490.0	488.7	488.1	487.8	487.1	486.4	485.8	485.1	485.8	486.4	487.1
145°	503.4	501.8	501.0	501.1	501.2	501.3	501.4	501.5	501.4	501.3	501.2
147.5°	516.8	515.2	514.4	514.5	514.8	515.1	515.3	515.6	515.3	515.1	514.8
150°	528.7	527.2	526.4	526.7	527.4	528.1	528.7	529.4	528.7	528.1	527.4
152.5°	539.7	538.3	537.6	538.0	538.7	539.5	540.2	541.0	540.2	539.5	538.7
155°	550.0	548.9	548.3	548.7	549.6	550.5	551.3	552.2	551.3	550.5	549.6
157.5°	559.1	558.2	557.8	558.2	558.9	559.7	560.4	561.2	560.4	559.7	558.9
160°	567.2	566.6	566.3	566.6	567.2	567.7	568.3	568.9	568.3	567.7	567.2
162.5°	573.9	573.4	573.2	573.5	574.1	574.6	575.2	575.8	575.2	574.6	574.1
165°	579.6	579.3	579.2	579.5	580.1	580.6	581.2	581.8	581.2	580.6	580.1
167.5°	584.4	584.1	584.0	584.3	584.8	585.4	585.9	586.5	585.9	585.4	584.8
170°	588.1	587.9	587.8	588.1	588.7	589.2	589.8	590.4	589.8	589.2	588.7
172.5°	590.7	590.5	590.4	590.7	591.3	591.8	592.4	593.0	592.4	591.8	591.3
175°	592.4	592.2	592.1	592.4	593.1	593.8	594.4	595.1	594.4	593.8	593.1
177.5°	593.1	593.0	593.0	593.3	594.0	594.7	595.3	596.0	595.3	594.7	594.0
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	4.7	5.2	5.6	6.3	7.1	7.8	8.6	9.1	9.5	10.0	10.5
92.5°	9.2	9.0	9.1	9.4	9.7	10.0	10.3	10.5	10.7	10.9	11.1
95°	15.4	13.8	14.1	14.8	15.5	16.1	16.8	17.3	17.7	18.2	18.7
97.5°	18.9	15.0	15.8	17.3	18.8	20.4	21.9	22.2	22.5	22.8	23.1
100°	23.7	17.2	18.0	19.6	21.3	22.9	24.5	25.3	26.0	26.8	27.5
102.5°	103.7	103.6	94.9	77.5	60.2	42.8	25.4	26.4	27.5	28.5	29.6
105°	142.1	143.5	130.5	104.4	78.3	52.3	26.2	27.2	28.3	29.3	30.4
107.5°	170.7	171.9	155.8	123.6	91.5	59.3	27.1	28.1	29.2	30.2	31.3
110°	198.4	199.4	185.6	158.0	130.4	102.8	75.2	65.6	56.1	46.5	37.0

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	224.7	225.6	224.8	223.2	221.5	219.9	218.3	177.1	136.0	94.8	53.7
115°	253.6	254.4	255.6	258.0	260.3	262.7	265.1	220.9	176.7	132.5	88.3
117.5°	280.0	281.0	281.8	283.4	285.1	286.7	288.3	274.7	261.0	247.4	233.7
120°	306.5	307.2	308.1	309.8	311.5	313.3	315.0	316.1	317.3	318.4	319.5
122.5°	330.9	331.7	332.7	334.6	336.5	338.4	340.3	340.9	341.5	342.0	342.6
125°	354.3	354.9	355.8	357.6	359.5	361.3	363.1	363.8	364.4	365.1	365.8
127.5°	377.0	377.7	378.4	379.9	381.3	382.8	384.2	385.2	386.1	387.1	388.0
130°	398.8	399.6	400.1	401.2	402.2	403.3	404.3	405.4	406.4	407.5	408.6
132.5°	419.2	419.8	420.3	421.4	422.4	423.5	424.5	425.4	426.2	427.1	428.0
135°	438.4	439.2	439.6	440.5	441.3	442.2	443.0	444.0	444.9	445.9	446.8
137.5°	455.7	456.3	456.8	457.7	458.7	459.6	460.6	461.6	462.5	463.5	464.4
140°	472.7	473.1	473.6	474.7	475.7	476.8	477.8	478.7	479.5	480.4	481.3
142.5°	487.8	488.1	488.7	490.0	491.2	492.5	493.7	494.5	495.3	496.0	496.8
145°	501.1	501.0	501.8	503.4	505.1	506.7	508.3	509.0	509.6	510.3	511.0
147.5°	514.5	514.4	515.2	516.8	518.5	520.1	521.7	522.2	522.6	523.1	523.6
150°	526.7	526.4	527.2	528.7	530.2	531.8	533.3	533.9	534.4	535.0	535.5
152.5°	538.0	537.6	538.3	539.7	541.2	542.6	544.0	544.6	545.2	545.7	546.3
155°	548.7	548.3	548.9	550.0	551.2	552.3	553.5	554.1	554.6	555.2	555.7
157.5°	558.2	557.8	558.2	559.1	559.9	560.8	561.6	562.3	562.9	563.6	564.3
160°	566.6	566.3	566.6	567.2	567.7	568.3	568.9	569.5	570.1	570.6	571.2
162.5°	573.5	573.2	573.4	573.9	574.4	574.9	575.4	576.1	576.7	577.4	578.1
165°	579.5	579.2	579.3	579.6	579.9	580.2	580.5	581.2	581.8	582.5	583.2
167.5°	584.3	584.0	584.1	584.4	584.7	585.0	585.3	586.0	586.6	587.3	588.0
170°	588.1	587.8	587.9	588.1	588.3	588.5	588.7	589.4	590.0	590.7	591.4
172.5°	590.7	590.4	590.5	590.7	590.9	591.1	591.3	592.0	592.6	593.3	594.0
175°	592.4	592.1	592.2	592.4	592.6	592.8	593.0	593.7	594.3	595.0	595.7
177.5°	593.3	593.0	593.0	593.1	593.2	593.3	593.4	594.1	594.7	595.4	596.1
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	10.7	10.8	11.0	11.2	11.4	11.6	11.4	11.2	11.0	10.8	10.7
92.5°	11.2	11.2	11.3	11.4	11.5	11.6	11.5	11.4	11.3	11.2	11.2
95°	18.9	18.9	18.8	18.7	18.6	18.5	18.6	18.7	18.8	18.9	18.9
97.5°	23.2	23.2	23.3	23.4	23.5	23.6	23.5	23.4	23.3	23.2	23.2
100°	27.9	28.0	28.2	28.4	28.6	28.8	28.6	28.4	28.2	28.0	27.9
102.5°	30.1	30.2	30.5	30.8	31.1	31.4	31.1	30.8	30.5	30.2	30.1
105°	30.9	31.1	31.5	31.9	32.3	32.7	32.3	31.9	31.5	31.1	30.9
107.5°	31.8	32.0	32.4	32.7	33.1	33.5	33.1	32.7	32.4	32.0	31.8
110°	32.2	32.4	32.8	33.1	33.5	33.9	33.5	33.1	32.8	32.4	32.2



TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	33.1	33.2	33.5	33.8	34.1	34.4	34.1	33.8	33.5	33.2	33.1
115°	66.2	62.8	55.9	49.0	42.1	35.2	42.1	49.0	55.9	62.8	66.2
117.5°	226.9	214.4	189.4	164.3	139.3	114.3	139.3	164.3	189.4	214.4	226.9
120°	320.1	313.7	300.8	287.9	275.0	262.1	275.0	287.9	300.8	313.7	320.1
122.5°	342.9	342.9	343.0	343.1	343.2	343.3	343.2	343.1	343.0	342.9	342.9
125°	366.1	366.2	366.5	366.8	367.1	367.4	367.1	366.8	366.5	366.2	366.1
127.5°	388.5	388.5	388.6	388.7	388.8	388.9	388.8	388.7	388.6	388.5	388.5
130°	409.1	409.0	408.9	408.8	408.7	408.6	408.7	408.8	408.9	409.0	409.1
132.5°	428.4	428.4	428.3	428.2	428.1	428.0	428.1	428.2	428.3	428.4	428.4
135°	447.3	447.2	447.0	446.9	446.7	446.5	446.7	446.9	447.0	447.2	447.3
137.5°	464.9	464.8	464.5	464.2	463.9	463.6	463.9	464.2	464.5	464.8	464.9
140°	481.7	481.5	481.0	480.5	480.0	479.5	480.0	480.5	481.0	481.5	481.7
142.5°	497.2	497.0	496.5	496.0	495.5	495.0	495.5	496.0	496.5	497.0	497.2
145°	511.3	511.1	510.6	510.1	509.7	509.2	509.7	510.1	510.6	511.1	511.3
147.5°	523.8	523.6	523.2	522.9	522.5	522.1	522.5	522.9	523.2	523.6	523.8
150°	535.8	535.6	535.1	534.6	534.2	533.7	534.2	534.6	535.1	535.6	535.8
152.5°	546.6	546.3	545.6	544.9	544.3	543.6	544.3	544.9	545.6	546.3	546.6
155°	556.0	555.6	554.9	554.1	553.4	552.6	553.4	554.1	554.9	555.6	556.0
157.5°	564.6	564.2	563.5	562.7	562.0	561.2	562.0	562.7	563.5	564.2	564.6
160°	571.5	571.2	570.5	569.8	569.2	568.5	569.2	569.8	570.5	571.2	571.5
162.5°	578.4	578.0	577.1	576.2	575.4	574.5	575.4	576.2	577.1	578.0	578.4
165°	583.5	583.2	582.5	581.8	581.2	580.5	581.2	581.8	582.5	583.2	583.5
167.5°	588.3	587.9	587.0	586.1	585.3	584.4	585.3	586.1	587.0	587.9	588.3
170°	591.7	591.3	590.4	589.5	588.7	587.8	588.7	589.5	590.4	591.3	591.7
172.5°	594.3	593.9	593.0	592.1	591.3	590.4	591.3	592.1	593.0	593.9	594.3
175°	596.0	595.5	594.6	593.6	592.7	591.7	592.7	593.6	594.6	595.5	596.0
177.5°	596.4	596.0	595.1	594.3	593.4	592.6	593.4	594.3	595.1	596.0	596.4
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	10.5	10.0	9.5	9.1	8.6	7.8	7.1	6.3	5.6	5.2	4.7
92.5°	11.1	10.9	10.7	10.5	10.3	10.0	9.7	9.4	9.1	9.0	9.2
95°	18.7	18.2	17.7	17.3	16.8	16.1	15.5	14.8	14.1	13.8	15.4
97.5°	23.1	22.8	22.5	22.2	21.9	20.4	18.8	17.3	15.8	15.0	18.9
100°	27.5	26.8	26.0	25.3	24.5	22.9	21.3	19.6	18.0	17.2	23.7
102.5°	29.6	28.5	27.5	26.4	25.4	42.8	60.2	77.5	94.9	103.6	103.7
105°	30.4	29.3	28.3	27.2	26.2	52.3	78.3	104.4	130.5	143.5	142.1
107.5°	31.3	30.2	29.2	28.1	27.1	59.3	91.5	123.6	155.8	171.9	170.7
110°	37.0	46.5	56.1	65.6	75.2	102.8	130.4	158.0	185.6	199.4	198.4

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	53.7	94.8	136.0	177.1	218.3	219.9	221.5	223.2	224.8	225.6	224.7
115°	88.3	132.5	176.7	220.9	265.1	262.7	260.3	258.0	255.6	254.4	253.6
117.5°	233.7	247.4	261.0	274.7	288.3	286.7	285.1	283.4	281.8	281.0	280.0
120°	319.5	318.4	317.3	316.1	315.0	313.3	311.5	309.8	308.1	307.2	306.5
122.5°	342.6	342.0	341.5	340.9	340.3	338.4	336.5	334.6	332.7	331.7	330.9
125°	365.8	365.1	364.4	363.8	363.1	361.3	359.5	357.6	355.8	354.9	354.3
127.5°	388.0	387.1	386.1	385.2	384.2	382.8	381.3	379.9	378.4	377.7	377.0
130°	408.6	407.5	406.4	405.4	404.3	403.3	402.2	401.2	400.1	399.6	398.8
132.5°	428.0	427.1	426.2	425.4	424.5	423.5	422.4	421.4	420.3	419.8	419.2
135°	446.8	445.9	444.9	444.0	443.0	442.2	441.3	440.5	439.6	439.2	438.4
137.5°	464.4	463.5	462.5	461.6	460.6	459.6	458.7	457.7	456.8	456.3	455.7
140°	481.3	480.4	479.5	478.7	477.8	476.8	475.7	474.7	473.6	473.1	472.7
142.5°	496.8	496.0	495.3	494.5	493.7	492.5	491.2	490.0	488.7	488.1	487.8
145°	511.0	510.3	509.6	509.0	508.3	506.7	505.1	503.4	501.8	501.0	501.1
147.5°	523.6	523.1	522.6	522.2	521.7	520.1	518.5	516.8	515.2	514.4	514.5
150°	535.5	535.0	534.4	533.9	533.3	531.8	530.2	528.7	527.2	526.4	526.7
152.5°	546.3	545.7	545.2	544.6	544.0	542.6	541.2	539.7	538.3	537.6	538.0
155°	555.7	555.2	554.6	554.1	553.5	552.3	551.2	550.0	548.9	548.3	548.7
157.5°	564.3	563.6	562.9	562.3	561.6	560.8	559.9	559.1	558.2	557.8	558.2
160°	571.2	570.6	570.1	569.5	568.9	568.3	567.7	567.2	566.6	566.3	566.6
162.5°	578.1	577.4	576.7	576.1	575.4	574.9	574.4	573.9	573.4	573.2	573.5
165°	583.2	582.5	581.8	581.2	580.5	580.2	579.9	579.6	579.3	579.2	579.5
167.5°	588.0	587.3	586.6	586.0	585.3	585.0	584.7	584.4	584.1	584.0	584.3
170°	591.4	590.7	590.0	589.4	588.7	588.5	588.3	588.1	587.9	587.8	588.1
172.5°	594.0	593.3	592.6	592.0	591.3	591.1	590.9	590.7	590.5	590.4	590.7
175°	595.7	595.0	594.3	593.7	593.0	592.8	592.6	592.4	592.2	592.1	592.4
177.5°	596.1	595.4	594.7	594.1	593.4	593.3	593.2	593.1	593.0	593.0	593.3
180°	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8	593.8

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	3.6	2.5	1.5	0.4
92.5°	9.6	9.9	10.3	10.7
95°	18.5	21.6	24.8	27.9
97.5°	26.8	34.6	42.5	50.3
100°	36.8	49.9	63.0	76.1
102.5°	103.9	104.0	104.2	104.4
105°	139.2	136.3	133.5	130.6
107.5°	168.3	165.9	163.5	161.1
110°	196.4	194.4	192.4	190.4

TEST NUMBER: P1029663

CATALOG NUMBER: S122DIW-B675D435UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	223.0	221.3	219.6	217.9
115°	252.0	250.3	248.7	247.1
117.5°	278.1	276.2	274.3	272.4
120°	305.1	303.6	302.2	300.8
122.5°	329.4	327.9	326.4	324.9
125°	353.0	351.8	350.5	349.3
127.5°	375.7	374.4	373.0	371.7
130°	397.3	395.8	394.2	392.7
132.5°	417.9	416.7	415.4	414.2
135°	436.9	435.4	433.8	432.3
137.5°	454.6	453.5	452.3	451.2
140°	472.0	471.2	470.5	469.7
142.5°	487.1	486.4	485.8	485.1
145°	501.2	501.3	501.4	501.5
147.5°	514.8	515.1	515.3	515.6
150°	527.4	528.1	528.7	529.4
152.5°	538.7	539.5	540.2	541.0
155°	549.6	550.5	551.3	552.2
157.5°	558.9	559.7	560.4	561.2
160°	567.2	567.7	568.3	568.9
162.5°	574.1	574.6	575.2	575.8
165°	580.1	580.6	581.2	581.8
167.5°	584.8	585.4	585.9	586.5
170°	588.7	589.2	589.8	590.4
172.5°	591.3	591.8	592.4	593.0
175°	593.1	593.8	594.4	595.1
177.5°	594.0	594.7	595.3	596.0
180°	593.8	593.8	593.8	593.8

(END OF REPORT)