

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982735

Luminaire Tested: S122IW-B710UB2750-4F0-XX-W2A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122IW-B710UB2750-4F0-XX-W2A_2700K
Description: Define 2 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2862.0 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.7	0.1
90°-100°	32.2	1.1
100°-110°	119.9	4.2
110°-120°	318.1	11.1
120°-130°	527.5	18.4
130°-140°	560.4	19.6
140°-150°	520.8	18.2
150°-160°	418.7	14.6
160°-170°	269.8	9.4
170°-180°	92.9	3.2
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.7	0.1
90°-120°	470.2	16.4
90°-150°	2078.9	72.6
90°-180°	2860.0	99.9
0°-180°	2862.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	14	18	19	3
95°	46	23	28	31	30	54
105°	215	236	43	51	54	229
115°	406	418	436	109	58	400
125°	574	583	596	602	604	512
135°	710	722	728	735	734	549
145°	824	823	835	840	837	515
155°	907	901	909	914	908	418
165°	956	952	954	959	954	270
175°	978	973	974	979	972	93
180°	976	976	976	976	976	

TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	8.5	14.1	17.6	19.1
92.5°	17.6	14.8	16.9	18.4	19.1
95°	45.9	22.6	27.5	31.1	30.4
97.5°	82.6	24.7	36.0	38.1	38.8
100°	125.0	28.2	40.2	45.9	47.3
102.5°	171.6	170.1	41.7	49.4	51.5
105°	214.6	235.8	43.1	50.8	53.7
107.5°	264.7	282.4	44.5	52.2	55.1
110°	312.7	327.6	123.5	52.9	55.8

TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.9	370.6	358.6	54.4	56.5
115°	405.9	417.9	435.6	108.7	57.9
117.5°	447.6	461.7	473.7	372.8	187.8
120°	494.2	504.8	517.5	526.0	430.6
122.5°	533.7	545.0	559.1	563.4	564.1
125°	574.0	583.1	596.5	601.5	603.6
127.5°	610.7	620.6	631.1	638.2	638.9
130°	645.3	656.6	664.3	672.1	671.4
132.5°	680.6	689.7	697.5	703.9	703.2
135°	710.2	721.5	727.9	734.9	733.5
137.5°	741.3	749.7	756.8	763.9	761.7
140°	771.6	777.3	785.0	791.4	787.9
142.5°	797.0	802.0	811.2	816.8	813.3
145°	823.9	823.2	835.2	840.1	836.6
147.5°	847.2	845.1	857.1	860.6	857.8
150°	869.8	864.8	876.1	880.4	876.8
152.5°	888.8	883.2	893.8	898.0	893.1
155°	907.2	900.8	909.3	913.5	907.9
157.5°	922.0	916.4	922.7	927.7	922.0
160°	934.7	930.5	934.7	938.9	934.0
162.5°	946.0	941.8	945.3	950.2	943.9
165°	955.9	951.7	953.8	958.7	953.8
167.5°	963.7	959.4	961.5	966.5	960.1
170°	970.0	965.8	967.2	972.1	965.8
172.5°	974.2	970.0	971.4	976.4	970.0
175°	977.8	972.8	974.2	979.2	972.1
177.5°	979.2	974.2	975.0	979.9	973.5
180°	975.7	975.7	975.7	975.7	975.7



TEST NUMBER: P982735

CATALOG NUMBER: S122IW-B710UB2750-4F0-XX-W2A_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT