

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030670

Luminaire Tested: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030670
REPORT IS A COMBINATION OF REPORTS P990662 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10353.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25
5	67	56	48	42	61	51	44	39	43	37	33	34	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	45	37	32	52	42	35	30	35	29	26	28	24	21	22	20	17
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14900	14900	14900	14900
5°	14910	17168	14954	12813
10°	14816	20775	14830	11189
15°	14611	24639	14729	10072
20°	14434	28367	14465	9268
25°	14172	29082	14204	8849
30°	13986	24027	13986	8574
35°	13754	16069	13667	8330
40°	13476	11600	13310	7959
45°	13128	9189	12750	7497
50°	12280	7803	11845	7043
55°	11350	6857	10888	6537
60°	10408	5971	9853	6005
65°	9372	5112	8918	5296
70°	8296	4243	7742	4465
75°	7091	3200	6634	3447
80°	5608	2137	5168	2264
85°	3861	982	3093	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 24030 cd/sqm

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	1.3
10°-20°	437.3	4.2
20°-30°	735.8	7.1
30°-40°	831.5	8.0
40°-50°	744.7	7.2
50°-60°	601.2	5.8
60°-70°	418.9	4.0
70°-80°	219.9	2.1
80°-90°	56.8	0.5
90°-100°	71.4	0.7
100°-110°	345.1	3.3
110°-120°	845.7	8.2
120°-130°	1073.6	10.4
130°-140°	1146.9	11.1
140°-150°	1072.5	10.4
150°-160°	865.1	8.4
160°-170°	558.3	5.4
170°-180°	192.4	1.9
0°-30°	1309.2	12.6
0°-40°	2140.6	20.7
0°-60°	3486.5	33.7
0°-90°	4182.0	40.4
90°-120°	1262.2	12.2
90°-150°	4555.2	44.0
90°-180°	6171.0	59.6
0°-180°	10353.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1384	1384	1384	1384	1384	
5°	1383	1644	1387	1227	1383	131
15°	1320	2448	1331	1001	1320	373
25°	1207	2905	1210	884	1207	557
35°	1065	1565	1058	812	1065	667
45°	884	845	858	690	884	676
55°	626	574	601	547	626	561
65°	388	373	369	386	388	386
75°	186	192	174	207	186	200
85°	40	44	32	40	40	46
90°	2	45	2	45	2	8
95°	92	57	92	57	92	110
105°	448	66	448	66	448	475
115°	841	884	841	884	841	830
125°	1185	1209	1185	1209	1185	1059
135°	1475	1490	1475	1490	1475	1136
145°	1702	1719	1702	1719	1702	1066
155°	1875	1872	1875	1872	1875	864
165°	1978	1973	1978	1973	1978	559
175°	2024	2017	2024	2017	2024	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1388.3	1399.0	1404.4	1412.5	1420.5	1432.6	1436.6	1443.3	1440.6	1446.0	1448.7
5°	1382.9	1401.7	1417.8	1437.9	1456.7	1470.1	1483.5	1505.0	1521.1	1523.8	1535.9
7.5°	1373.6	1400.4	1428.6	1456.7	1492.9	1514.4	1538.5	1568.1	1592.2	1631.1	1645.9
10°	1361.5	1399.0	1439.3	1478.2	1527.8	1561.3	1590.9	1640.5	1690.1	1730.4	1767.9
12.5°	1342.7	1389.7	1442.0	1499.6	1564.0	1602.9	1643.2	1708.9	1784.0	1845.7	1886.0
15°	1319.9	1378.9	1446.0	1507.7	1578.8	1651.2	1694.1	1767.9	1875.2	1932.9	2036.2
17.5°	1301.1	1361.5	1428.6	1525.1	1621.7	1694.1	1725.0	1860.5	1934.2	2030.8	2147.5
20°	1271.6	1348.1	1433.9	1530.5	1655.2	1699.5	1762.6	1899.4	1990.6	2116.7	2260.2
22.5°	1240.8	1322.6	1425.9	1526.5	1666.0	1712.9	1798.8	1907.4	2052.3	2177.0	2335.3
25°	1207.2	1295.8	1400.4	1519.8	1656.6	1725.0	1805.5	1939.6	2096.6	2253.5	2399.7
27.5°	1173.7	1270.3	1378.9	1498.3	1631.1	1711.6	1792.1	1931.6	2132.8	2303.1	2489.6
30°	1141.5	1238.1	1346.7	1468.8	1608.3	1686.1	1762.6	1936.9	2160.9	2352.8	2540.5
32.5°	1106.6	1205.9	1319.9	1421.8	1562.7	1645.9	1731.7	1936.9	2178.4	2382.3	2554.0
35°	1065.0	1167.0	1264.9	1366.8	1506.4	1598.9	1695.5	1923.5	2194.5	2391.7	2497.6
37.5°	1024.8	1114.7	1199.2	1298.4	1444.6	1543.9	1655.2	1907.4	2186.4	2351.4	2380.9
40°	979.2	1069.1	1137.5	1230.0	1384.3	1499.6	1612.3	1886.0	2151.5	2256.2	2170.3
42.5°	934.9	1006.0	1065.0	1154.9	1322.6	1435.3	1557.3	1847.1	2083.1	2104.6	1911.4
45°	884.0	934.9	987.2	1089.2	1255.5	1370.9	1506.4	1790.7	1973.1	1911.4	1667.3
47.5°	818.2	863.8	921.5	1015.4	1184.4	1303.8	1432.6	1718.3	1813.5	1684.8	1417.8
50°	755.2	794.1	847.7	939.0	1109.3	1226.0	1362.8	1604.3	1651.2	1448.7	1222.0
52.5°	692.1	721.7	774.0	865.2	1035.5	1148.2	1273.0	1487.6	1460.7	1243.4	1042.2
55°	626.4	651.9	701.5	791.4	949.7	1057.0	1176.4	1344.0	1274.3	1067.7	906.8
57.5°	562.0	588.9	639.8	714.9	863.8	968.5	1063.7	1195.2	1090.5	925.5	783.4
60°	504.4	527.2	566.1	639.8	775.3	859.8	947.0	1036.9	949.7	790.1	681.4
62.5°	444.0	465.5	501.7	568.7	685.4	760.6	830.3	904.1	807.5	690.8	594.2
65°	387.7	405.1	438.6	500.3	595.6	657.3	713.6	764.6	686.8	579.5	507.0
67.5°	336.7	351.4	379.6	434.6	515.1	559.3	605.0	647.9	582.2	496.3	434.6
70°	281.7	293.8	319.2	359.5	423.9	469.5	503.0	535.2	476.2	407.8	366.2
72.5°	233.4	245.5	261.6	303.1	347.4	375.6	411.8	429.2	395.7	339.4	297.8
75°	186.4	195.8	210.6	237.4	279.0	297.8	320.6	334.0	303.1	265.6	240.1
77.5°	146.2	150.2	161.0	179.7	207.9	229.4	246.8	254.9	233.4	209.3	187.8
80°	103.3	108.7	116.7	132.8	154.3	161.0	171.7	181.1	167.7	146.2	132.8
82.5°	68.4	75.1	79.1	85.8	99.3	107.3	110.0	118.0	106.0	97.9	92.6
85°	40.2	42.9	44.3	48.3	55.0	59.0	63.0	64.4	61.7	60.4	55.0
87.5°	20.1	20.1	20.1	22.8	24.1	26.8	28.2	28.2	28.2	26.8	25.5
90°	1.5	4.8	8.2	11.5	14.8	16.5	18.7	23.0	27.4	31.7	36.1
92.5°	34.6	32.6	30.6	28.6	26.6	25.6	27.1	30.1	33.1	36.1	39.1
95°	91.7	78.0	64.3	50.6	36.9	30.1	31.9	35.6	39.3	42.9	46.6
97.5°	166.9	157.5	148.2	138.8	129.5	124.8	116.3	99.2	82.2	65.1	48.1
100°	254.2	260.9	267.5	274.2	280.9	284.2	258.1	206.0	153.9	101.7	49.6
102.5°	353.4	357.8	362.1	366.5	370.8	373.0	343.9	285.8	227.6	169.5	111.3
105°	448.2	451.9	455.5	459.2	462.9	464.7	449.7	419.6	389.5	359.4	329.3
107.5°	548.9	551.9	554.9	557.9	560.9	562.4	564.9	569.9	575.0	580.0	585.0
110°	649.7	652.4	655.0	657.7	660.4	661.7	663.5	667.2	670.9	674.5	678.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	745.9	748.2	750.6	752.9	755.2	756.4	758.2	761.9	765.6	769.3	773.0
115°	840.7	842.7	844.7	846.7	848.7	849.7	851.2	854.2	857.2	860.2	863.2
117.5°	933.9	936.2	938.6	940.9	943.2	944.4	945.2	946.9	948.6	950.2	951.9
120°	1019.6	1022.6	1025.6	1028.7	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7
122.5°	1106.8	1109.2	1111.5	1113.9	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4
125°	1185.0	1187.7	1190.4	1193.1	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1
127.5°	1263.2	1265.9	1268.6	1271.3	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8
130°	1335.4	1338.1	1340.8	1343.5	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5
132.5°	1404.6	1407.3	1409.9	1412.6	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2
135°	1475.3	1477.3	1479.3	1481.3	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3
137.5°	1535.4	1538.1	1540.8	1543.5	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5
140°	1595.6	1597.6	1599.6	1601.6	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1
142.5°	1651.2	1653.2	1655.2	1657.3	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8
145°	1702.4	1704.7	1707.1	1709.4	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9
147.5°	1752.0	1753.7	1755.3	1757.0	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5
150°	1797.1	1798.1	1799.1	1800.1	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6
152.5°	1837.7	1838.0	1838.4	1838.7	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7
155°	1875.3	1874.6	1874.0	1873.3	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8
157.5°	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9
160°	1932.5	1932.2	1931.8	1931.5	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5
162.5°	1958.0	1957.0	1956.0	1955.0	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0
165°	1977.6	1976.6	1975.6	1974.6	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6
167.5°	1994.1	1992.8	1991.4	1990.1	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1
170°	2007.7	2006.3	2005.0	2003.6	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6
172.5°	2016.7	2015.0	2013.4	2011.7	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7
175°	2024.2	2022.5	2020.9	2019.2	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2
177.5°	2027.2	2025.5	2023.9	2022.2	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1458.1	1460.7	1470.1	1476.8	1490.3	1488.9	1488.9	1487.6	1483.5	1490.3	1494.3
5°	1560.0	1582.8	1585.5	1615.0	1616.3	1628.4	1636.5	1629.8	1645.9	1644.5	1632.4
7.5°	1686.1	1716.9	1731.7	1759.9	1792.1	1784.0	1814.9	1820.2	1817.5	1831.0	1840.4
10°	1824.3	1877.9	1915.5	1967.8	1981.2	1989.2	2009.4	2026.8	2061.7	2034.8	2052.3
12.5°	1982.5	2021.4	2071.1	2154.2	2195.8	2222.6	2232.0	2244.1	2268.2	2253.5	2254.8
15°	2115.3	2167.6	2252.1	2355.4	2367.5	2401.0	2393.0	2465.4	2500.3	2448.0	2477.5
17.5°	2253.5	2323.2	2423.8	2513.7	2564.7	2587.5	2609.0	2678.7	2676.0	2668.0	2674.7
20°	2342.0	2456.0	2580.8	2700.2	2714.9	2732.4	2790.0	2819.5	2814.2	2837.0	2851.7
22.5°	2466.8	2587.5	2720.3	2799.4	2833.0	2853.1	2898.7	2917.5	2925.5	2930.9	2921.5
25°	2571.4	2700.2	2798.1	2867.8	2888.0	2898.7	2913.4	2918.8	2914.8	2905.4	2913.4
27.5°	2642.5	2745.8	2812.8	2845.0	2834.3	2816.9	2788.7	2769.9	2728.3	2708.2	2732.4
30°	2672.0	2717.6	2737.7	2684.1	2630.4	2587.5	2533.8	2434.6	2356.8	2379.6	2348.7
32.5°	2625.0	2595.5	2499.0	2360.8	2319.2	2249.5	2097.9	1981.2	1985.2	1923.5	1949.0
35°	2486.9	2352.8	2170.3	1961.1	1906.1	1868.5	1702.2	1676.7	1623.0	1565.4	1581.5
37.5°	2242.8	2046.9	1825.6	1671.3	1589.5	1507.7	1413.8	1357.5	1325.3	1301.1	1319.9
40°	1945.0	1706.2	1523.8	1385.6	1315.9	1263.6	1199.2	1142.8	1106.6	1102.6	1109.3
42.5°	1652.6	1451.4	1283.7	1152.2	1129.4	1067.7	1026.1	981.9	971.1	953.7	963.1
45°	1399.0	1235.4	1097.2	989.9	963.1	947.0	896.0	867.9	855.8	845.1	861.2
47.5°	1215.3	1043.6	943.0	878.6	851.8	824.9	796.8	778.0	768.6	769.9	768.6
50°	1038.2	912.1	823.6	774.0	757.9	739.1	716.3	704.2	700.2	688.1	697.5
52.5°	893.3	802.1	740.4	693.5	681.4	668.0	649.2	642.5	633.1	630.4	630.4
55°	776.6	705.6	655.9	625.1	610.3	599.6	588.9	580.8	574.1	574.1	574.1
57.5°	685.4	623.7	587.5	560.7	555.3	544.6	532.5	532.5	523.1	521.8	525.8
60°	607.6	552.6	524.5	501.7	493.6	490.9	478.9	478.9	476.2	469.5	474.8
62.5°	528.5	488.3	464.1	446.7	438.6	438.6	429.2	422.5	422.5	423.9	421.2
65°	456.1	426.6	405.1	391.7	387.7	382.3	380.9	375.6	371.6	372.9	371.6
67.5°	391.7	368.9	354.1	343.4	336.7	334.0	330.0	330.0	327.3	328.6	321.9
70°	334.0	311.2	299.1	288.4	285.7	285.7	280.3	281.7	279.0	283.0	280.3
72.5°	275.0	257.5	248.2	244.1	241.4	240.1	237.4	234.7	233.4	236.1	234.7
75°	222.7	207.9	201.2	198.5	195.8	195.8	194.5	193.2	191.8	191.8	191.8
77.5°	173.0	163.6	155.6	158.3	154.3	155.6	151.6	151.6	152.9	151.6	151.6
80°	127.4	120.7	120.7	118.0	112.7	115.4	115.4	111.3	110.0	112.7	108.7
82.5°	84.5	83.2	80.5	79.1	76.5	77.8	76.5	75.1	73.8	76.5	73.8
85°	49.6	49.6	48.3	45.6	48.3	46.9	45.6	45.6	44.3	44.3	44.3
87.5°	25.5	22.8	22.8	21.5	22.8	20.1	21.5	20.1	18.8	20.1	18.8
90°	37.4	38.8	40.1	41.4	42.1	42.4	43.1	43.8	44.4	45.1	44.4
92.5°	41.4	43.8	46.1	48.4	49.6	49.8	50.1	50.4	50.8	51.1	50.8
95°	48.9	51.3	53.6	55.9	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	50.8	53.5	56.2	58.9	60.2	60.4	60.7	61.0	61.4	61.7	61.4
100°	52.3	55.0	57.7	60.4	61.7	61.9	62.2	62.5	62.9	63.2	62.9
102.5°	100.3	89.3	78.2	67.2	61.7	62.0	62.7	63.4	64.0	64.7	64.0
105°	270.2	211.0	151.9	92.8	63.2	63.5	64.2	64.9	65.5	66.2	65.5
107.5°	533.5	482.1	430.6	379.1	353.4	331.5	287.7	244.0	200.2	156.4	200.2
110°	667.2	656.2	645.1	634.1	628.6	604.7	556.9	509.2	461.4	413.6	461.4

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	776.0	779.0	782.0	785.0	786.5	786.2	785.5	784.8	784.2	783.5	784.2
115°	866.6	869.9	873.3	876.6	878.3	879.0	880.3	881.6	883.0	884.3	883.0
117.5°	954.6	957.3	960.0	962.7	964.0	964.2	964.5	964.8	965.2	965.5	965.2
120°	1040.4	1043.0	1045.7	1048.4	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1125.1	1126.7	1128.4	1130.1	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1
125°	1203.8	1204.4	1205.1	1205.8	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4
127.5°	1283.8	1284.8	1285.8	1286.8	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0
130°	1354.8	1356.2	1357.5	1358.8	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2
132.5°	1422.5	1423.9	1425.2	1426.5	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7
135°	1491.3	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3
137.5°	1552.2	1553.8	1555.5	1557.2	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7
140°	1610.5	1611.8	1613.2	1614.5	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8
142.5°	1665.8	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8
145°	1716.6	1717.2	1717.9	1718.6	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1763.2	1763.8	1764.5	1765.2	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7
150°	1805.3	1805.9	1806.6	1807.3	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1
152.5°	1842.0	1843.4	1844.7	1846.0	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9
155°	1875.5	1877.1	1878.8	1880.5	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3
157.5°	1905.9	1907.9	1909.9	1911.9	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6
160°	1931.5	1933.5	1935.5	1937.5	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3
162.5°	1954.3	1956.7	1959.0	1961.3	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5
165°	1974.3	1976.9	1979.6	1982.3	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4
167.5°	1990.8	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8
170°	2004.3	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3
172.5°	2013.4	2016.0	2018.7	2021.4	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2
175°	2020.5	2022.9	2025.2	2027.5	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4
177.5°	2023.9	2026.5	2029.2	2031.9	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1483.5	1487.6	1476.8	1474.2	1474.2	1479.5	1475.5	1439.3	1446.0	1437.9	1435.3
5°	1647.2	1639.1	1628.4	1623.0	1616.3	1597.6	1596.2	1554.6	1546.6	1519.8	1507.7
7.5°	1826.9	1820.2	1788.0	1784.0	1781.3	1763.9	1719.6	1675.4	1643.2	1612.3	1582.8
10°	2032.2	2012.0	1997.3	1967.8	1953.0	1928.9	1871.2	1829.6	1774.6	1727.7	1666.0
12.5°	2279.0	2256.2	2206.5	2185.1	2166.3	2099.2	2041.6	1994.6	1887.3	1855.1	1778.6
15°	2460.1	2411.8	2406.4	2359.5	2356.8	2283.0	2173.0	2122.0	2038.9	1920.8	1841.7
17.5°	2655.9	2613.0	2579.4	2523.1	2515.1	2445.3	2364.8	2240.1	2148.9	2036.2	1935.6
20°	2799.4	2776.6	2718.9	2696.1	2649.2	2590.2	2507.0	2352.8	2241.4	2128.7	2005.3
22.5°	2913.4	2890.6	2845.0	2814.2	2787.4	2710.9	2611.6	2480.2	2327.3	2179.7	2052.3
25°	2912.1	2905.4	2886.6	2871.9	2851.7	2795.4	2712.2	2586.1	2415.8	2253.5	2076.4
27.5°	2747.1	2765.9	2798.1	2814.2	2810.2	2802.1	2755.2	2649.2	2496.3	2303.1	2104.6
30°	2403.7	2472.1	2532.5	2613.0	2637.1	2696.1	2723.0	2662.6	2540.5	2360.8	2140.8
32.5°	1993.3	2092.5	2224.0	2268.2	2344.7	2458.7	2586.1	2609.0	2532.5	2394.3	2163.6
35°	1635.1	1716.9	1818.9	1888.6	1957.0	2142.2	2303.1	2442.6	2468.1	2376.9	2158.3
37.5°	1353.4	1411.1	1501.0	1560.0	1623.0	1781.3	2006.7	2187.8	2315.2	2317.9	2143.5
40°	1149.5	1175.0	1252.8	1295.8	1356.1	1492.9	1694.1	1930.2	2116.7	2202.5	2104.6
42.5°	973.8	1007.4	1071.7	1103.9	1142.8	1262.2	1395.0	1619.0	1849.7	2033.5	2032.2
45°	869.2	893.3	922.9	949.7	994.0	1065.0	1216.6	1384.3	1605.6	1813.5	1895.3
47.5°	776.6	799.5	829.0	837.0	866.5	933.6	1026.1	1172.4	1378.9	1585.5	1739.7
50°	698.9	717.6	737.7	752.5	765.9	820.9	890.7	1014.1	1179.1	1378.9	1570.7
52.5°	638.5	651.9	669.3	677.4	689.5	729.7	783.4	874.6	1010.0	1192.5	1378.9
55°	582.2	591.5	602.3	615.7	621.1	650.6	692.1	769.9	870.5	1034.2	1211.3
57.5°	529.8	533.9	540.6	548.6	555.3	580.8	617.0	669.3	757.9	884.0	1051.6
60°	470.8	481.5	485.6	493.6	497.6	517.8	545.9	590.2	658.6	767.3	893.3
62.5°	421.2	427.9	434.6	438.6	448.0	454.7	477.5	517.8	574.1	654.6	768.6
65°	376.9	379.6	383.6	387.7	390.3	398.4	419.8	446.7	489.6	560.7	649.2
67.5°	326.0	328.6	334.0	335.3	338.0	348.8	360.8	383.6	419.8	473.5	545.9
70°	276.3	280.3	283.0	285.7	289.7	293.8	307.2	326.0	354.1	391.7	448.0
72.5°	233.4	237.4	237.4	240.1	238.8	244.1	257.5	271.0	289.7	320.6	370.2
75°	190.5	190.5	193.2	194.5	195.8	201.2	206.6	217.3	232.1	256.2	287.1
77.5°	150.2	148.9	151.6	151.6	151.6	155.6	161.0	166.3	175.7	193.2	217.3
80°	110.0	110.0	112.7	114.0	111.3	112.7	115.4	120.7	127.4	139.5	152.9
82.5°	72.4	77.8	76.5	77.8	76.5	79.1	80.5	81.8	84.5	89.9	99.3
85°	44.3	44.3	44.3	45.6	44.3	45.6	45.6	45.6	46.9	49.6	53.7
87.5°	18.8	18.8	18.8	20.1	18.8	18.8	20.1	18.8	20.1	20.1	21.5
90°	43.8	43.1	42.4	42.1	41.4	40.1	38.8	37.4	36.1	31.7	27.4
92.5°	50.4	50.1	49.8	49.6	48.4	46.1	43.8	41.4	39.1	36.1	33.1
95°	57.1	57.1	57.1	57.1	55.9	53.6	51.3	48.9	46.6	42.9	39.3
97.5°	61.0	60.7	60.4	60.2	58.9	56.2	53.5	50.8	48.1	65.1	82.2
100°	62.5	62.2	61.9	61.7	60.4	57.7	55.0	52.3	49.6	101.7	153.9
102.5°	63.4	62.7	62.0	61.7	67.2	78.2	89.3	100.3	111.3	169.5	227.6
105°	64.9	64.2	63.5	63.2	92.8	151.9	211.0	270.2	329.3	359.4	389.5
107.5°	244.0	287.7	331.5	353.4	379.1	430.6	482.1	533.5	585.0	580.0	575.0
110°	509.2	556.9	604.7	628.6	634.1	645.1	656.2	667.2	678.2	674.5	670.9

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	784.8	785.5	786.2	786.5	785.0	782.0	779.0	776.0	773.0	769.3	765.6
115°	881.6	880.3	879.0	878.3	876.6	873.3	869.9	866.6	863.2	860.2	857.2
117.5°	964.8	964.5	964.2	964.0	962.7	960.0	957.3	954.6	951.9	950.2	948.6
120°	1049.7	1049.7	1049.7	1049.7	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7
122.5°	1131.7	1131.4	1131.1	1130.9	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7
125°	1207.8	1207.1	1206.4	1206.1	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4
127.5°	1285.6	1286.3	1287.0	1287.3	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5
130°	1357.8	1358.5	1359.2	1359.5	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8
132.5°	1424.7	1425.7	1426.7	1427.2	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2
135°	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6
137.5°	1556.3	1557.0	1557.7	1558.0	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2
140°	1613.5	1614.2	1614.9	1615.2	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1
142.5°	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8
145°	1718.9	1718.9	1718.9	1718.9	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6
147.5°	1761.3	1763.0	1764.7	1765.5	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2
150°	1805.1	1806.1	1807.1	1807.6	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3
152.5°	1842.5	1844.2	1845.9	1846.7	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0
155°	1876.3	1878.3	1880.3	1881.3	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1
157.5°	1906.2	1908.9	1911.6	1912.9	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6
160°	1932.7	1935.0	1937.3	1938.5	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2
162.5°	1957.5	1959.5	1961.5	1962.5	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7
165°	1977.8	1980.1	1982.4	1983.6	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3
167.5°	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1
170°	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6
172.5°	2015.2	2018.2	2021.2	2022.7	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0
175°	2022.0	2024.7	2027.4	2028.7	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5
177.5°	2024.9	2028.2	2031.5	2033.2	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1421.8	1417.8	1417.8	1415.1	1407.1	1392.3	1391.0	1393.7	1385.6	1377.6	1365.5
5°	1491.6	1466.1	1458.1	1450.0	1433.9	1407.1	1396.4	1387.0	1372.2	1354.8	1336.0
7.5°	1550.6	1514.4	1503.7	1488.9	1456.7	1419.2	1395.0	1374.9	1354.8	1330.6	1307.8
10°	1624.4	1572.1	1546.6	1525.1	1480.9	1428.6	1392.3	1362.8	1330.6	1301.1	1271.6
12.5°	1707.6	1623.0	1615.0	1562.7	1511.7	1433.9	1389.7	1346.7	1303.8	1267.6	1236.7
15°	1777.3	1684.8	1651.2	1616.3	1518.4	1421.8	1378.9	1330.6	1281.0	1242.1	1196.5
17.5°	1821.6	1745.1	1674.0	1627.1	1525.1	1439.3	1356.1	1301.1	1248.8	1195.2	1157.6
20°	1875.2	1763.9	1702.2	1639.1	1538.5	1425.9	1342.7	1274.3	1209.9	1161.6	1116.0
22.5°	1928.9	1778.6	1727.7	1659.3	1541.2	1412.5	1318.6	1250.2	1176.4	1128.1	1078.5
25°	1923.5	1800.1	1715.6	1657.9	1514.4	1400.4	1290.4	1209.9	1141.5	1079.8	1030.2
27.5°	1927.5	1776.0	1690.1	1623.0	1495.6	1382.9	1260.9	1176.4	1105.3	1040.9	988.6
30°	1928.9	1739.7	1664.6	1584.1	1460.7	1341.4	1227.3	1141.5	1066.4	996.6	949.7
32.5°	1924.9	1710.2	1616.3	1543.9	1405.7	1301.1	1188.4	1097.2	1020.8	956.4	912.1
35°	1915.5	1675.4	1566.7	1475.5	1349.4	1243.4	1152.2	1058.3	976.5	917.5	866.5
37.5°	1890.0	1637.8	1514.4	1424.5	1283.7	1176.4	1095.9	1018.1	939.0	869.2	826.3
40°	1871.2	1586.8	1462.1	1364.2	1212.6	1108.0	1040.9	967.1	889.3	826.3	784.7
42.5°	1828.3	1538.5	1408.4	1291.7	1142.8	1035.5	972.5	913.5	846.4	784.7	747.1
45°	1758.5	1486.2	1342.7	1224.7	1066.4	964.4	906.8	858.5	799.5	740.4	702.9
47.5°	1660.6	1411.1	1273.0	1154.9	991.3	888.0	830.3	794.1	747.1	697.5	665.3
50°	1554.6	1329.3	1201.9	1085.2	918.8	818.2	761.9	728.4	697.5	651.9	621.1
52.5°	1416.5	1242.1	1120.0	1008.7	841.0	744.5	694.8	670.7	638.5	606.3	579.5
55°	1282.3	1129.4	1028.8	922.9	764.6	674.7	626.4	600.9	582.2	555.3	533.9
57.5°	1126.7	1024.8	932.2	835.7	693.5	611.7	566.1	535.2	523.1	511.1	490.9
60°	983.2	905.4	830.3	749.8	619.7	545.9	501.7	477.5	465.5	457.4	444.0
62.5°	851.8	791.4	727.0	662.6	544.6	477.5	444.0	419.8	409.1	407.8	395.7
65°	725.7	682.8	630.4	567.4	474.8	415.8	383.6	368.9	356.8	356.8	347.4
67.5°	599.6	570.1	528.5	484.2	411.8	356.8	327.3	313.9	307.2	307.2	300.5
70°	499.0	478.9	441.3	402.4	339.4	297.8	275.0	262.9	258.9	260.2	254.9
72.5°	405.1	383.6	352.8	324.6	277.7	246.8	230.7	217.3	210.6	211.9	210.6
75°	313.9	303.1	276.3	254.9	217.3	195.8	181.1	174.4	169.0	170.4	167.7
77.5°	236.1	220.0	205.2	190.5	167.7	150.2	138.2	131.5	127.4	127.4	127.4
80°	161.0	158.3	146.2	138.2	119.4	106.0	96.6	95.2	91.2	91.2	91.2
82.5°	104.6	97.9	91.2	85.8	75.1	67.1	63.0	60.4	59.0	57.7	60.4
85°	57.7	53.7	51.0	45.6	41.6	37.6	33.5	32.2	30.9	32.2	30.9
87.5°	22.8	18.8	18.8	17.4	16.1	14.8	14.8	12.1	12.1	10.7	10.7
90°	23.0	18.7	16.5	14.8	11.5	8.2	4.8	1.5	4.8	8.2	11.5
92.5°	30.1	27.1	25.6	26.6	28.6	30.6	32.6	34.6	32.6	30.6	28.6
95°	35.6	31.9	30.1	36.9	50.6	64.3	78.0	91.7	78.0	64.3	50.6
97.5°	99.2	116.3	124.8	129.5	138.8	148.2	157.5	166.9	157.5	148.2	138.8
100°	206.0	258.1	284.2	280.9	274.2	267.5	260.9	254.2	260.9	267.5	274.2
102.5°	285.8	343.9	373.0	370.8	366.5	362.1	357.8	353.4	357.8	362.1	366.5
105°	419.6	449.7	464.7	462.9	459.2	455.5	451.9	448.2	451.9	455.5	459.2
107.5°	569.9	564.9	562.4	560.9	557.9	554.9	551.9	548.9	551.9	554.9	557.9
110°	667.2	663.5	661.7	660.4	657.7	655.0	652.4	649.7	652.4	655.0	657.7

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	761.9	758.2	756.4	755.2	752.9	750.6	748.2	745.9	748.2	750.6	752.9
115°	854.2	851.2	849.7	848.7	846.7	844.7	842.7	840.7	842.7	844.7	846.7
117.5°	946.9	945.2	944.4	943.2	940.9	938.6	936.2	933.9	936.2	938.6	940.9
120°	1034.7	1033.7	1033.2	1031.7	1028.7	1025.6	1022.6	1019.6	1022.6	1025.6	1028.7
122.5°	1119.4	1118.1	1117.4	1116.2	1113.9	1111.5	1109.2	1106.8	1109.2	1111.5	1113.9
125°	1199.1	1197.8	1197.1	1195.8	1193.1	1190.4	1187.7	1185.0	1187.7	1190.4	1193.1
127.5°	1277.8	1276.1	1275.3	1274.0	1271.3	1268.6	1265.9	1263.2	1265.9	1268.6	1271.3
130°	1349.5	1348.2	1347.5	1346.2	1343.5	1340.8	1338.1	1335.4	1338.1	1340.8	1343.5
132.5°	1418.1	1417.1	1416.6	1415.3	1412.6	1409.9	1407.3	1404.6	1407.3	1409.9	1412.6
135°	1486.3	1485.0	1484.3	1483.3	1481.3	1479.3	1477.3	1475.3	1477.3	1479.3	1481.3
137.5°	1548.5	1547.8	1547.5	1546.2	1543.5	1540.8	1538.1	1535.4	1538.1	1540.8	1543.5
140°	1606.1	1605.1	1604.6	1603.6	1601.6	1599.6	1597.6	1595.6	1597.6	1599.6	1601.6
142.5°	1661.8	1660.8	1660.3	1659.3	1657.3	1655.2	1653.2	1651.2	1653.2	1655.2	1657.3
145°	1713.9	1713.2	1712.9	1711.7	1709.4	1707.1	1704.7	1702.4	1704.7	1707.1	1709.4
147.5°	1760.5	1759.8	1759.5	1758.7	1757.0	1755.3	1753.7	1752.0	1753.7	1755.3	1757.0
150°	1802.6	1801.9	1801.6	1801.1	1800.1	1799.1	1798.1	1797.1	1798.1	1799.1	1800.1
152.5°	1839.7	1839.4	1839.2	1839.0	1838.7	1838.4	1838.0	1837.7	1838.0	1838.4	1838.7
155°	1872.8	1872.5	1872.3	1872.6	1873.3	1874.0	1874.6	1875.3	1874.6	1874.0	1873.3
157.5°	1904.9	1905.2	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4
160°	1930.5	1930.8	1931.0	1931.2	1931.5	1931.8	1932.2	1932.5	1932.2	1931.8	1931.5
162.5°	1953.0	1953.3	1953.5	1954.0	1955.0	1956.0	1957.0	1958.0	1957.0	1956.0	1955.0
165°	1972.6	1972.9	1973.1	1973.6	1974.6	1975.6	1976.6	1977.6	1976.6	1975.6	1974.6
167.5°	1988.1	1988.1	1988.1	1988.8	1990.1	1991.4	1992.8	1994.1	1992.8	1991.4	1990.1
170°	2001.6	2001.6	2001.6	2002.3	2003.6	2005.0	2006.3	2007.7	2006.3	2005.0	2003.6
172.5°	2009.7	2009.4	2009.2	2010.0	2011.7	2013.4	2015.0	2016.7	2015.0	2013.4	2011.7
175°	2017.2	2016.9	2016.7	2017.5	2019.2	2020.9	2022.5	2024.2	2022.5	2020.9	2019.2
177.5°	2020.2	2019.9	2019.7	2020.5	2022.2	2023.9	2025.5	2027.2	2025.5	2023.9	2022.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1362.8	1361.5	1364.2	1356.1	1342.7	1336.0	1317.2	1313.2	1311.9	1313.2	1314.5
5°	1325.3	1323.9	1319.9	1306.5	1290.4	1278.3	1255.5	1254.2	1246.1	1238.1	1242.1
7.5°	1289.1	1283.7	1275.6	1258.2	1236.7	1223.3	1204.5	1191.1	1180.4	1173.7	1168.3
10°	1252.8	1244.8	1236.7	1213.9	1187.1	1167.0	1144.2	1133.5	1121.4	1116.0	1110.6
12.5°	1205.9	1197.8	1183.1	1156.3	1140.2	1114.7	1091.9	1081.1	1074.4	1063.7	1057.0
15°	1168.3	1152.2	1144.2	1116.0	1082.5	1079.8	1038.2	1035.5	1022.1	1022.1	1011.4
17.5°	1125.4	1113.3	1098.6	1070.4	1046.3	1022.1	1000.7	992.6	980.5	977.9	972.5
20°	1083.8	1067.7	1062.4	1034.2	1008.7	979.2	956.4	948.3	943.0	937.6	941.6
22.5°	1040.9	1027.5	1014.1	988.6	969.8	940.3	926.9	918.8	910.8	908.1	909.4
25°	999.3	987.2	973.8	948.3	928.2	904.1	892.0	888.0	884.0	884.0	882.6
27.5°	959.1	947.0	934.9	912.1	892.0	874.6	865.2	861.2	857.1	859.8	862.5
30°	917.5	906.8	896.0	875.9	859.8	843.7	838.4	835.7	834.3	841.0	841.0
32.5°	879.9	870.5	862.5	843.7	827.6	814.2	810.2	811.5	812.9	816.9	819.6
35°	841.0	834.3	826.3	810.2	796.8	784.7	786.0	786.0	788.7	795.4	800.8
37.5°	806.2	796.8	790.1	776.6	765.9	755.2	759.2	763.2	765.9	774.0	776.6
40°	764.6	760.6	755.2	741.8	732.4	731.0	732.4	735.1	740.4	744.5	748.5
42.5°	731.0	725.7	719.0	708.2	700.2	701.5	702.9	705.6	708.2	714.9	719.0
45°	693.5	689.5	684.1	674.7	668.0	669.3	670.7	670.7	673.4	681.4	684.1
47.5°	651.9	653.2	646.5	637.1	633.1	633.1	633.1	635.8	642.5	645.2	646.5
50°	611.7	609.0	607.6	598.2	595.6	594.2	595.6	596.9	606.3	605.0	609.0
52.5°	568.7	568.7	567.4	562.0	558.0	558.0	555.3	562.0	564.7	567.4	571.4
55°	527.2	523.1	521.8	519.1	513.7	512.4	515.1	523.1	525.8	528.5	532.5
57.5°	481.5	481.5	478.9	474.8	474.8	474.8	474.8	480.2	484.2	486.9	495.0
60°	440.0	434.6	430.6	430.6	430.6	429.2	437.3	437.3	445.3	446.7	449.4
62.5°	390.3	387.7	385.0	386.3	385.0	387.7	390.3	395.7	397.0	401.1	405.1
65°	343.4	343.4	340.7	348.8	343.4	343.4	350.1	350.1	352.8	356.8	362.2
67.5°	297.8	299.1	296.4	296.4	299.1	300.5	301.8	307.2	308.5	313.9	320.6
70°	250.8	253.5	254.9	252.2	254.9	257.5	260.2	261.6	266.9	269.6	273.6
72.5°	209.3	211.9	207.9	209.3	210.6	213.3	214.6	217.3	220.0	228.0	230.7
75°	167.7	166.3	165.0	170.4	167.7	173.0	174.4	174.4	177.1	183.8	186.4
77.5°	128.8	128.8	130.1	127.4	131.5	130.1	131.5	135.5	139.5	139.5	150.2
80°	89.9	92.6	92.6	92.6	93.9	95.2	92.6	99.3	100.6	100.6	104.6
82.5°	57.7	59.0	57.7	60.4	60.4	63.0	61.7	63.0	65.7	68.4	69.8
85°	30.9	30.9	33.5	33.5	32.2	33.5	32.2	33.5	36.2	36.2	37.6
87.5°	10.7	10.7	10.7	10.7	12.1	10.7	12.1	12.1	10.7	10.7	14.8
90°	14.8	16.5	18.7	23.0	27.4	31.7	36.1	37.4	38.8	40.1	41.4
92.5°	26.6	25.6	27.1	30.1	33.1	36.1	39.1	41.4	43.8	46.1	48.4
95°	36.9	30.1	31.9	35.6	39.3	42.9	46.6	48.9	51.3	53.6	55.9
97.5°	129.5	124.8	116.3	99.2	82.2	65.1	48.1	50.8	53.5	56.2	58.9
100°	280.9	284.2	258.1	206.0	153.9	101.7	49.6	52.3	55.0	57.7	60.4
102.5°	370.8	373.0	343.9	285.8	227.6	169.5	111.3	100.3	89.3	78.2	67.2
105°	462.9	464.7	449.7	419.6	389.5	359.4	329.3	270.2	211.0	151.9	92.8
107.5°	560.9	562.4	564.9	569.9	575.0	580.0	585.0	533.5	482.1	430.6	379.1
110°	660.4	661.7	663.5	667.2	670.9	674.5	678.2	667.2	656.2	645.1	634.1

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	755.2	756.4	758.2	761.9	765.6	769.3	773.0	776.0	779.0	782.0	785.0
115°	848.7	849.7	851.2	854.2	857.2	860.2	863.2	866.6	869.9	873.3	876.6
117.5°	943.2	944.4	945.2	946.9	948.6	950.2	951.9	954.6	957.3	960.0	962.7
120°	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7	1040.4	1043.0	1045.7	1048.4
122.5°	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4	1125.1	1126.7	1128.4	1130.1
125°	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1	1203.8	1204.4	1205.1	1205.8
127.5°	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8	1283.8	1284.8	1285.8	1286.8
130°	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5	1354.8	1356.2	1357.5	1358.8
132.5°	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2	1422.5	1423.9	1425.2	1426.5
135°	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3	1491.3	1492.3	1493.3	1494.3
137.5°	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5	1552.2	1553.8	1555.5	1557.2
140°	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1	1610.5	1611.8	1613.2	1614.5
142.5°	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8	1665.8	1666.8	1667.8	1668.8
145°	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9	1716.6	1717.2	1717.9	1718.6
147.5°	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5	1763.2	1763.8	1764.5	1765.2
150°	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6	1805.3	1805.9	1806.6	1807.3
152.5°	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7	1842.0	1843.4	1844.7	1846.0
155°	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8	1875.5	1877.1	1878.8	1880.5
157.5°	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9	1905.9	1907.9	1909.9	1911.9
160°	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5	1931.5	1933.5	1935.5	1937.5
162.5°	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0	1954.3	1956.7	1959.0	1961.3
165°	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6	1974.3	1976.9	1979.6	1982.3
167.5°	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1990.8	1993.4	1996.1	1998.8
170°	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2004.3	2007.0	2009.7	2012.4
172.5°	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7	2013.4	2016.0	2018.7	2021.4
175°	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2	2020.5	2022.9	2025.2	2027.5
177.5°	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2	2023.9	2026.5	2029.2	2031.9
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1313.2	1314.5	1309.2	1305.1	1315.9	1309.2	1309.2	1310.5	1307.8	1311.9	1310.5
5°	1239.4	1240.8	1231.4	1234.1	1228.7	1227.3	1226.0	1234.1	1232.7	1231.4	1234.1
7.5°	1167.0	1167.0	1163.0	1160.3	1160.3	1156.3	1161.6	1160.3	1163.0	1163.0	1167.0
10°	1106.6	1109.3	1102.6	1095.9	1094.6	1095.9	1095.9	1097.2	1098.6	1108.0	1106.6
12.5°	1057.0	1053.0	1051.6	1047.6	1040.9	1038.2	1035.5	1050.3	1046.3	1046.3	1046.3
15°	1002.0	1011.4	1010.0	998.0	995.3	1000.7	998.0	998.0	1011.4	1010.0	1008.7
17.5°	972.5	969.8	967.1	960.4	961.8	960.4	961.8	961.8	969.8	969.8	969.8
20°	939.0	933.6	933.6	930.9	930.9	926.9	932.2	933.6	939.0	939.0	940.3
22.5°	909.4	905.4	905.4	904.1	906.8	901.4	906.8	908.1	908.1	912.1	912.1
25°	884.0	881.3	881.3	884.0	884.0	884.0	884.0	889.3	885.3	886.6	885.3
27.5°	861.2	862.5	863.8	865.2	863.8	865.2	866.5	869.2	870.5	869.2	866.5
30°	839.7	843.7	845.1	845.1	847.7	849.1	850.4	850.4	851.8	847.7	850.4
32.5°	823.6	823.6	826.3	827.6	830.3	831.6	831.6	834.3	833.0	829.0	830.3
35°	800.8	800.8	806.2	808.8	812.9	811.5	812.9	812.9	814.2	811.5	807.5
37.5°	778.0	780.7	780.7	786.0	787.4	788.7	787.4	790.1	788.7	786.0	784.7
40°	751.2	749.8	751.2	755.2	756.5	756.5	756.5	759.2	759.2	759.2	757.9
42.5°	717.6	721.7	720.3	724.3	723.0	723.0	725.7	728.4	729.7	725.7	727.0
45°	685.4	685.4	688.1	688.1	689.5	689.5	694.8	692.1	694.8	692.1	693.5
47.5°	650.6	651.9	651.9	653.2	655.9	658.6	655.9	657.3	657.3	658.6	655.9
50°	611.7	611.7	614.3	618.4	623.7	621.1	619.7	625.1	621.1	621.1	618.4
52.5°	571.4	575.4	576.8	580.8	584.8	586.2	587.5	584.8	586.2	582.2	583.5
55°	532.5	533.9	539.2	543.3	547.3	547.3	545.9	547.3	548.6	543.3	543.3
57.5°	493.6	497.6	503.0	503.0	508.4	508.4	507.0	507.0	508.4	504.4	503.0
60°	452.0	456.1	462.8	462.8	470.8	472.2	469.5	466.8	466.8	462.8	464.1
62.5°	407.8	411.8	415.8	422.5	427.9	425.2	430.6	425.2	426.6	418.5	418.5
65°	368.9	370.2	376.9	383.6	383.6	386.3	383.6	385.0	380.9	380.9	375.6
67.5°	323.3	323.3	330.0	336.7	343.4	343.4	343.4	339.4	339.4	335.3	335.3
70°	283.0	281.7	288.4	292.4	296.4	297.8	295.1	293.8	291.1	287.1	285.7
72.5°	233.4	236.1	242.8	245.5	252.2	250.8	257.5	249.5	249.5	242.8	241.4
75°	189.1	191.8	198.5	202.5	206.6	206.6	210.6	206.6	201.2	198.5	197.2
77.5°	150.2	148.9	154.3	161.0	162.3	161.0	163.6	162.3	156.9	156.9	154.3
80°	107.3	111.3	116.7	115.4	120.7	119.4	119.4	116.7	116.7	112.7	115.4
82.5°	71.1	75.1	76.5	75.1	76.5	79.1	80.5	79.1	79.1	76.5	77.8
85°	37.6	37.6	40.2	41.6	40.2	40.2	41.6	45.6	42.9	40.2	42.9
87.5°	12.1	10.7	10.7	12.1	10.7	10.7	12.1	12.1	13.4	13.4	13.4
90°	42.1	42.4	43.1	43.8	44.4	45.1	44.4	43.8	43.1	42.4	42.1
92.5°	49.6	49.8	50.1	50.4	50.8	51.1	50.8	50.4	50.1	49.8	49.6
95°	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	60.2	60.4	60.7	61.0	61.4	61.7	61.4	61.0	60.7	60.4	60.2
100°	61.7	61.9	62.2	62.5	62.9	63.2	62.9	62.5	62.2	61.9	61.7
102.5°	61.7	62.0	62.7	63.4	64.0	64.7	64.0	63.4	62.7	62.0	61.7
105°	63.2	63.5	64.2	64.9	65.5	66.2	65.5	64.9	64.2	63.5	63.2
107.5°	353.4	331.5	287.7	244.0	200.2	156.4	200.2	244.0	287.7	331.5	353.4
110°	628.6	604.7	556.9	509.2	461.4	413.6	461.4	509.2	556.9	604.7	628.6

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	786.5	786.2	785.5	784.8	784.2	783.5	784.2	784.8	785.5	786.2	786.5
115°	878.3	879.0	880.3	881.6	883.0	884.3	883.0	881.6	880.3	879.0	878.3
117.5°	964.0	964.2	964.5	964.8	965.2	965.5	965.2	964.8	964.5	964.2	964.0
120°	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1	1131.7	1131.4	1131.1	1130.9
125°	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4	1207.8	1207.1	1206.4	1206.1
127.5°	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0	1285.6	1286.3	1287.0	1287.3
130°	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2	1357.8	1358.5	1359.2	1359.5
132.5°	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7	1424.7	1425.7	1426.7	1427.2
135°	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3	1492.3	1493.3	1494.3	1494.8
137.5°	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7	1556.3	1557.0	1557.7	1558.0
140°	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8	1613.5	1614.2	1614.9	1615.2
142.5°	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8	1666.8	1667.8	1668.8	1669.3
145°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7	1761.3	1763.0	1764.7	1765.5
150°	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1	1805.1	1806.1	1807.1	1807.6
152.5°	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9	1842.5	1844.2	1845.9	1846.7
155°	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3	1876.3	1878.3	1880.3	1881.3
157.5°	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6	1906.2	1908.9	1911.6	1912.9
160°	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3	1932.7	1935.0	1937.3	1938.5
162.5°	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5	1957.5	1959.5	1961.5	1962.5
165°	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4	1977.8	1980.1	1982.4	1983.6
167.5°	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8	1993.4	1996.1	1998.8	2000.1
170°	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3	2007.0	2009.7	2012.4	2013.7
172.5°	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2	2015.2	2018.2	2021.2	2022.7
175°	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4	2022.0	2024.7	2027.4	2028.7
177.5°	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5	2024.9	2028.2	2031.5	2033.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3	1384.3
2.5°	1314.5	1317.2	1318.6	1313.2	1309.2	1315.9	1325.3	1332.0	1337.3	1344.0	1348.1
5°	1236.7	1246.1	1246.1	1248.8	1252.8	1259.5	1277.0	1289.1	1299.8	1307.8	1314.5
7.5°	1171.0	1177.7	1181.7	1188.4	1195.2	1204.5	1224.7	1242.1	1258.2	1267.6	1278.3
10°	1112.0	1117.4	1124.1	1128.1	1140.2	1153.6	1179.1	1193.8	1212.6	1227.3	1240.8
12.5°	1055.7	1074.4	1078.5	1077.1	1087.8	1102.6	1128.1	1150.9	1171.0	1185.8	1200.5
15°	1015.4	1022.1	1030.2	1028.8	1051.6	1055.7	1077.1	1103.9	1130.8	1140.2	1153.6
17.5°	971.1	981.9	989.9	994.0	1000.7	1015.4	1035.5	1055.7	1090.5	1091.9	1126.7
20°	936.3	947.0	952.4	957.7	961.8	979.2	996.6	1019.4	1047.6	1062.4	1081.1
22.5°	913.5	918.8	922.9	926.9	932.2	941.6	963.1	988.6	1007.4	1023.5	1035.5
25°	886.6	892.0	897.4	900.1	904.1	909.4	925.5	945.7	972.5	983.2	995.3
27.5°	867.9	867.9	870.5	870.5	875.9	881.3	893.3	912.1	933.6	947.0	963.1
30°	847.7	846.4	847.7	846.4	845.1	853.1	863.8	879.9	894.7	910.8	921.5
32.5°	827.6	826.3	826.3	827.6	822.3	826.3	831.6	846.4	862.5	870.5	882.6
35°	806.2	803.5	803.5	803.5	800.8	798.1	803.5	816.9	827.6	838.4	847.7
37.5°	784.7	780.7	780.7	778.0	775.3	771.3	771.3	782.0	796.8	800.8	812.9
40°	755.2	755.2	752.5	751.2	748.5	745.8	741.8	751.2	764.6	768.6	778.0
42.5°	725.7	721.7	720.3	720.3	720.3	716.3	713.6	720.3	728.4	735.1	740.4
45°	692.1	689.5	690.8	689.5	686.8	685.4	684.1	686.8	696.2	698.9	705.6
47.5°	655.9	654.6	654.6	653.2	651.9	653.2	647.9	654.6	657.3	660.0	665.3
50°	618.4	617.0	615.7	614.3	614.3	615.7	614.3	614.3	619.7	622.4	627.8
52.5°	580.8	576.8	576.8	575.4	575.4	572.8	575.4	576.8	579.5	582.2	584.8
55°	540.6	540.6	536.5	536.5	533.9	533.9	535.2	533.9	539.2	541.9	541.9
57.5°	501.7	496.3	497.6	495.0	492.3	490.9	490.9	493.6	496.3	496.3	499.0
60°	460.1	454.7	453.4	448.0	450.7	446.7	448.0	448.0	453.4	450.7	453.4
62.5°	418.5	411.8	407.8	405.1	405.1	406.4	403.8	402.4	405.1	407.8	413.1
65°	374.2	370.2	366.2	362.2	362.2	360.8	363.5	359.5	358.1	359.5	362.2
67.5°	328.6	324.6	320.6	316.6	317.9	313.9	311.2	315.2	312.5	313.9	316.6
70°	284.4	281.7	273.6	271.0	269.6	271.0	269.6	266.9	271.0	269.6	271.0
72.5°	240.1	237.4	233.4	226.7	226.7	225.3	224.0	224.0	222.7	222.7	222.7
75°	197.2	191.8	187.8	186.4	183.8	182.4	181.1	178.4	179.7	181.1	178.4
77.5°	152.9	146.2	144.9	144.9	140.8	140.8	142.2	140.8	139.5	139.5	139.5
80°	112.7	107.3	107.3	104.6	101.9	101.9	101.9	101.9	100.6	99.3	100.6
82.5°	72.4	71.1	69.8	69.8	72.4	67.1	69.8	68.4	67.1	67.1	65.7
85°	40.2	41.6	40.2	41.6	38.9	40.2	40.2	40.2	38.9	40.2	37.6
87.5°	14.8	14.8	14.8	16.1	16.1	16.1	16.1	16.1	17.4	16.1	16.1
90°	41.4	40.1	38.8	37.4	36.1	31.7	27.4	23.0	18.7	16.5	14.8
92.5°	48.4	46.1	43.8	41.4	39.1	36.1	33.1	30.1	27.1	25.6	26.6
95°	55.9	53.6	51.3	48.9	46.6	42.9	39.3	35.6	31.9	30.1	36.9
97.5°	58.9	56.2	53.5	50.8	48.1	65.1	82.2	99.2	116.3	124.8	129.5
100°	60.4	57.7	55.0	52.3	49.6	101.7	153.9	206.0	258.1	284.2	280.9
102.5°	67.2	78.2	89.3	100.3	111.3	169.5	227.6	285.8	343.9	373.0	370.8
105°	92.8	151.9	211.0	270.2	329.3	359.4	389.5	419.6	449.7	464.7	462.9
107.5°	379.1	430.6	482.1	533.5	585.0	580.0	575.0	569.9	564.9	562.4	560.9
110°	634.1	645.1	656.2	667.2	678.2	674.5	670.9	667.2	663.5	661.7	660.4

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.0	782.0	779.0	776.0	773.0	769.3	765.6	761.9	758.2	756.4	755.2
115°	876.6	873.3	869.9	866.6	863.2	860.2	857.2	854.2	851.2	849.7	848.7
117.5°	962.7	960.0	957.3	954.6	951.9	950.2	948.6	946.9	945.2	944.4	943.2
120°	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7	1034.7	1033.7	1033.2	1031.7
122.5°	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7	1119.4	1118.1	1117.4	1116.2
125°	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4	1199.1	1197.8	1197.1	1195.8
127.5°	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5	1277.8	1276.1	1275.3	1274.0
130°	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8	1349.5	1348.2	1347.5	1346.2
132.5°	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2	1418.1	1417.1	1416.6	1415.3
135°	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6	1486.3	1485.0	1484.3	1483.3
137.5°	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2	1548.5	1547.8	1547.5	1546.2
140°	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1	1606.1	1605.1	1604.6	1603.6
142.5°	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8	1661.8	1660.8	1660.3	1659.3
145°	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6	1713.9	1713.2	1712.9	1711.7
147.5°	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2	1760.5	1759.8	1759.5	1758.7
150°	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3	1802.6	1801.9	1801.6	1801.1
152.5°	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0	1839.7	1839.4	1839.2	1839.0
155°	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1	1872.8	1872.5	1872.3	1872.6
157.5°	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6	1904.9	1905.2	1905.4	1905.4
160°	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2	1930.5	1930.8	1931.0	1931.2
162.5°	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7	1953.0	1953.3	1953.5	1954.0
165°	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3	1972.6	1972.9	1973.1	1973.6
167.5°	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1988.8
170°	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2002.3
172.5°	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0	2009.7	2009.4	2009.2	2010.0
175°	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5	2017.2	2016.9	2016.7	2017.5
177.5°	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5	2020.2	2019.9	2019.7	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1384.3	1384.3	1384.3	1384.3
2.5°	1354.8	1358.8	1372.2	1388.3
5°	1327.9	1338.7	1357.5	1382.9
7.5°	1298.4	1314.5	1341.4	1373.6
10°	1264.9	1287.7	1321.2	1361.5
12.5°	1228.7	1258.2	1301.1	1342.7
15°	1205.9	1235.4	1274.3	1319.9
17.5°	1161.6	1196.5	1236.7	1301.1
20°	1116.0	1154.9	1207.2	1271.6
22.5°	1081.1	1122.7	1172.4	1240.8
25°	1039.6	1082.5	1136.1	1207.2
27.5°	995.3	1038.2	1098.6	1173.7
30°	961.8	1003.3	1061.0	1141.5
32.5°	921.5	961.8	1022.1	1106.6
35°	875.9	921.5	979.2	1065.0
37.5°	841.0	882.6	943.0	1024.8
40°	803.5	839.7	898.7	979.2
42.5°	763.2	803.5	854.4	934.9
45°	725.7	755.2	807.5	884.0
47.5°	685.4	719.0	759.2	818.2
50°	642.5	670.7	714.9	755.2
52.5°	600.9	623.7	661.3	692.1
55°	556.7	579.5	607.6	626.4
57.5°	515.1	531.2	550.0	562.0
60°	464.1	480.2	492.3	504.4
62.5°	418.5	430.6	437.3	444.0
65°	371.6	378.3	382.3	387.7
67.5°	320.6	327.3	328.6	336.7
70°	273.6	275.0	277.7	281.7
72.5°	229.4	232.1	230.7	233.4
75°	183.8	186.4	183.8	186.4
77.5°	139.5	142.2	142.2	146.2
80°	100.6	101.9	103.3	103.3
82.5°	65.7	69.8	67.1	68.4
85°	37.6	38.9	38.9	40.2
87.5°	17.4	18.8	17.4	20.1
90°	11.5	8.2	4.8	1.5
92.5°	28.6	30.6	32.6	34.6
95°	50.6	64.3	78.0	91.7
97.5°	138.8	148.2	157.5	166.9
100°	274.2	267.5	260.9	254.2
102.5°	366.5	362.1	357.8	353.4
105°	459.2	455.5	451.9	448.2
107.5°	557.9	554.9	551.9	548.9
110°	657.7	655.0	652.4	649.7



TEST NUMBER: P1030670

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	752.9	750.6	748.2	745.9
115°	846.7	844.7	842.7	840.7
117.5°	940.9	938.6	936.2	933.9
120°	1028.7	1025.6	1022.6	1019.6
122.5°	1113.9	1111.5	1109.2	1106.8
125°	1193.1	1190.4	1187.7	1185.0
127.5°	1271.3	1268.6	1265.9	1263.2
130°	1343.5	1340.8	1338.1	1335.4
132.5°	1412.6	1409.9	1407.3	1404.6
135°	1481.3	1479.3	1477.3	1475.3
137.5°	1543.5	1540.8	1538.1	1535.4
140°	1601.6	1599.6	1597.6	1595.6
142.5°	1657.3	1655.2	1653.2	1651.2
145°	1709.4	1707.1	1704.7	1702.4
147.5°	1757.0	1755.3	1753.7	1752.0
150°	1800.1	1799.1	1798.1	1797.1
152.5°	1838.7	1838.4	1838.0	1837.7
155°	1873.3	1874.0	1874.6	1875.3
157.5°	1905.4	1905.4	1905.4	1905.4
160°	1931.5	1931.8	1932.2	1932.5
162.5°	1955.0	1956.0	1957.0	1958.0
165°	1974.6	1975.6	1976.6	1977.6
167.5°	1990.1	1991.4	1992.8	1994.1
170°	2003.6	2005.0	2006.3	2007.7
172.5°	2011.7	2013.4	2015.0	2016.7
175°	2019.2	2020.9	2022.5	2024.2
177.5°	2022.2	2023.9	2025.5	2027.2
180°	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)