

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030690

Luminaire Tested: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030690
REPORT IS A COMBINATION OF REPORTS P990735 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5987.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030690

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030690

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	99	94	90	86	93	89	85	81	78	75	72	68	65	63	58	57	55
2	90	82	75	69	84	77	71	66	67	63	59	59	55	52	51	48	45
3	82	71	63	57	76	67	60	54	59	53	49	51	47	43	44	41	38
4	75	63	54	48	70	59	52	46	52	46	41	46	41	37	39	36	32
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	35	31	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	33	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	35	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13254	13254	13254
5°	13289	12864	12854
10°	13165	12516	12420
15°	12991	12131	11960
20°	12743	11702	11467
25°	12439	11219	10956
30°	12127	10782	10442
35°	11778	10323	10023
40°	11445	9903	9581
45°	11075	9499	9217
50°	10708	9096	8821
55°	10304	8682	8458
60°	9909	8260	8084
65°	9500	7811	7650
70°	8888	7306	7200
75°	8114	6732	6735
80°	7210	6147	6207
85°	6311	5678	5827

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11075 cd/sqm

TEST NUMBER: P1030690

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	2.0
10°-20°	333.0	5.6
20°-30°	497.9	8.3
30°-40°	594.5	9.9
40°-50°	622.0	10.4
50°-60°	583.7	9.7
60°-70°	487.5	8.1
70°-80°	348.6	5.8
80°-90°	208.7	3.5
90°-100°	151.8	2.5
100°-110°	199.1	3.3
110°-120°	317.2	5.3
120°-130°	358.0	6.0
130°-140°	359.8	6.0
140°-150°	324.6	5.4
150°-160°	259.0	4.3
160°-170°	167.2	2.8
170°-180°	57.6	1.0
0°-30°	947.7	15.8
0°-40°	1542.2	25.8
0°-60°	2747.9	45.9
0°-90°	3792.7	63.3
90°-120°	668.1	11.2
90°-150°	1710.4	28.6
90°-180°	2194.0	36.6
0°-180°	5987.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1233	1230	1222	1233	1231	117
15°	1174	1178	1176	1190	1188	331
25°	1060	1073	1077	1094	1094	488
35°	912	934	951	971	976	570
45°	746	778	812	837	848	575
55°	569	613	661	697	708	509
65°	393	445	504	544	558	388
75°	213	276	343	388	404	228
85°	66	133	204	250	263	68
90°	18	88	162	210	224	14
95°	42	76	147	192	205	44
105°	145	182	199	157	170	153
115°	258	277	330	366	379	256
125°	359	362	403	432	442	321
135°	444	446	462	488	493	342
145°	511	513	514	525	531	320
155°	562	561	561	563	561	259
165°	592	591	590	594	591	167
175°	606	604	604	608	604	58
180°	606	606	606	606	606	

TEST NUMBER: P1030690

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1231.3	1231.3	1231.3	1231.3	1231.3
2.5°	1238.0	1233.9	1223.2	1233.9	1232.6
5°	1232.6	1229.9	1221.9	1232.6	1231.3
7.5°	1223.2	1223.2	1215.2	1228.6	1227.2
10°	1209.8	1212.5	1205.8	1219.2	1216.5
12.5°	1193.7	1197.7	1193.7	1205.8	1203.1
15°	1173.6	1177.6	1176.3	1189.7	1188.3
17.5°	1149.4	1157.5	1156.2	1168.2	1165.5
20°	1122.6	1130.7	1133.3	1145.4	1146.8
22.5°	1094.5	1102.5	1106.5	1122.6	1121.3
25°	1059.6	1073.0	1077.0	1094.5	1094.5
27.5°	1026.1	1040.8	1048.9	1063.6	1064.9
30°	989.8	1007.3	1018.0	1034.1	1034.1
32.5°	949.6	969.7	984.5	1001.9	1005.9
35°	912.0	933.5	950.9	971.1	976.4
37.5°	871.8	895.9	916.1	938.9	942.9
40°	831.6	855.7	882.5	905.3	910.7
42.5°	787.3	818.2	846.3	871.8	879.9
45°	745.7	777.9	811.5	836.9	847.7
47.5°	701.5	737.7	775.2	803.4	811.5
50°	658.5	696.1	737.7	768.5	777.9
52.5°	612.9	653.2	700.1	732.3	744.4
55°	568.7	612.9	661.2	697.4	708.2
57.5°	525.8	571.4	623.7	659.9	672.0
60°	480.2	528.4	583.4	621.0	635.7
62.5°	437.2	486.9	545.9	583.4	596.9
65°	393.0	445.3	504.3	544.5	558.0
67.5°	348.7	403.7	462.7	507.0	517.7
70°	301.8	359.5	423.8	466.8	480.2
72.5°	258.9	316.5	383.6	427.9	441.3
75°	213.3	276.3	343.4	387.6	403.7
77.5°	174.4	237.4	304.5	351.4	363.5
80°	132.8	198.5	268.2	313.9	327.3
82.5°	96.6	163.6	234.7	280.3	293.7
85°	65.7	132.8	203.9	249.5	262.9
87.5°	40.2	107.3	175.7	221.3	234.7
90°	17.9	88.2	162.4	209.8	224.1
92.5°	26.5	81.5	152.5	200.0	212.5
95°	42.3	76.1	146.8	191.5	204.9
97.5°	63.4	99.1	139.1	183.0	196.9
100°	88.2	140.1	131.6	174.1	187.9
102.5°	116.5	160.0	141.9	164.7	179.0
105°	144.9	182.0	199.2	157.0	170.0
107.5°	173.8	206.0	267.7	234.6	187.6
110°	202.5	230.3	288.9	308.9	255.2



TEST NUMBER: P1030690

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	231.4	253.3	309.3	346.8	358.0
115°	258.4	277.2	329.6	366.3	378.8
117.5°	286.3	300.2	348.0	383.8	395.1
120°	310.7	321.5	367.0	401.5	410.9
122.5°	336.8	342.6	386.0	417.7	427.6
125°	358.8	362.4	403.1	432.2	442.5
127.5°	382.3	384.6	420.3	448.5	457.0
130°	403.9	406.2	434.8	462.1	469.2
132.5°	423.3	426.9	448.3	474.2	482.3
135°	444.5	445.8	462.4	487.8	493.2
137.5°	462.5	464.7	475.0	498.7	504.5
140°	479.1	481.8	487.2	509.1	514.9
142.5°	495.7	497.1	498.5	517.2	522.6
145°	511.0	512.9	513.8	525.4	530.8
147.5°	524.6	526.9	527.8	532.7	535.8
150°	538.1	539.5	540.4	541.3	542.6
152.5°	550.3	550.7	551.2	553.0	550.7
155°	561.5	560.6	561.1	563.3	560.6
157.5°	570.5	570.5	570.1	572.8	569.2
160°	578.6	578.2	577.7	580.4	577.3
162.5°	586.3	584.9	584.5	587.7	584.9
165°	592.2	590.8	590.4	594.0	590.8
167.5°	597.1	595.3	595.3	598.9	595.3
170°	601.2	599.4	599.4	603.0	599.4
172.5°	603.9	601.6	602.1	605.7	601.6
175°	606.1	603.9	604.3	607.5	603.9
177.5°	607.0	604.8	605.2	608.8	604.3
180°	606.1	606.1	606.1	606.1	606.1

(END OF REPORT)