

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030705

Luminaire Tested: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030705
REPORT IS A COMBINATION OF REPORTS P990801 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7185.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030705

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030705

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	97	92	88	84	90	86	82	78	73	70	67	61	59	57	50	49	47
2	88	80	73	68	81	74	68	63	63	59	55	53	50	47	43	41	39
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	33
4	73	62	53	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	43	38	44	38	33	37	32	29	30	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	25	22	25	21	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	19	17
9	49	37	29	24	45	34	27	23	30	24	20	25	21	18	21	18	15
10	46	34	26	21	42	31	25	20	27	22	18	23	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13254	13254	13254
5°	13289	12864	12854
10°	13165	12516	12420
15°	12991	12131	11960
20°	12743	11702	11467
25°	12439	11219	10956
30°	12127	10782	10442
35°	11778	10323	10023
40°	11445	9903	9581
45°	11075	9499	9217
50°	10708	9096	8821
55°	10304	8682	8458
60°	9909	8260	8084
65°	9500	7811	7650
70°	8888	7306	7200
75°	8114	6732	6735
80°	7210	6147	6207
85°	6311	5678	5827

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11075 cd/sqm

TEST NUMBER: P1030705

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.6
10°-20°	333.0	4.6
20°-30°	497.9	6.9
30°-40°	594.5	8.3
40°-50°	622.0	8.7
50°-60°	583.7	8.1
60°-70°	487.5	6.8
70°-80°	348.6	4.9
80°-90°	209.4	2.9
90°-100°	165.6	2.3
100°-110°	266.1	3.7
110°-120°	481.3	6.7
120°-130°	566.3	7.9
130°-140°	582.3	8.1
140°-150°	532.6	7.4
150°-160°	426.9	5.9
160°-170°	275.5	3.8
170°-180°	94.9	1.3
0°-30°	947.7	13.2
0°-40°	1542.2	21.5
0°-60°	2747.9	38.2
0°-90°	3793.5	52.8
90°-120°	913.0	12.7
90°-150°	2594.2	36.1
90°-180°	3391.0	47.2
0°-180°	7185.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1233	1230	1222	1233	1231	117
15°	1174	1178	1176	1190	1188	331
25°	1060	1073	1077	1094	1094	488
35°	912	934	951	971	976	570
45°	746	778	812	837	848	575
55°	569	613	661	697	708	509
65°	393	445	504	544	558	388
75°	213	276	343	388	404	228
85°	66	133	204	250	263	68
90°	18	91	169	218	233	15
95°	60	82	156	203	216	66
105°	232	272	263	169	183	245
115°	422	442	497	537	550	417
125°	589	595	637	666	677	527
135°	731	734	752	778	782	563
145°	841	845	847	859	864	526
155°	925	924	925	928	924	426
165°	976	974	973	979	974	276
175°	999	995	996	1001	995	95
180°	999	999	999	999	999	

TEST NUMBER: P1030705

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1231.3	1231.3	1231.3	1231.3	1231.3
2.5°	1238.0	1233.9	1223.2	1233.9	1232.6
5°	1232.6	1229.9	1221.9	1232.6	1231.3
7.5°	1223.2	1223.2	1215.2	1228.6	1227.2
10°	1209.8	1212.5	1205.8	1219.2	1216.5
12.5°	1193.7	1197.7	1193.7	1205.8	1203.1
15°	1173.6	1177.6	1176.3	1189.7	1188.3
17.5°	1149.4	1157.5	1156.2	1168.2	1165.5
20°	1122.6	1130.7	1133.3	1145.4	1146.8
22.5°	1094.5	1102.5	1106.5	1122.6	1121.3
25°	1059.6	1073.0	1077.0	1094.5	1094.5
27.5°	1026.1	1040.8	1048.9	1063.6	1064.9
30°	989.8	1007.3	1018.0	1034.1	1034.1
32.5°	949.6	969.7	984.5	1001.9	1005.9
35°	912.0	933.5	950.9	971.1	976.4
37.5°	871.8	895.9	916.1	938.9	942.9
40°	831.6	855.7	882.5	905.3	910.7
42.5°	787.3	818.2	846.3	871.8	879.9
45°	745.7	777.9	811.5	836.9	847.7
47.5°	701.5	737.7	775.2	803.4	811.5
50°	658.5	696.1	737.7	768.5	777.9
52.5°	612.9	653.2	700.1	732.3	744.4
55°	568.7	612.9	661.2	697.4	708.2
57.5°	525.8	571.4	623.7	659.9	672.0
60°	480.2	528.4	583.4	621.0	635.7
62.5°	437.2	486.9	545.9	583.4	596.9
65°	393.0	445.3	504.3	544.5	558.0
67.5°	348.7	403.7	462.7	507.0	517.7
70°	301.8	359.5	423.8	466.8	480.2
72.5°	258.9	316.5	383.6	427.9	441.3
75°	213.3	276.3	343.4	387.6	403.7
77.5°	174.4	237.4	304.5	351.4	363.5
80°	132.8	198.5	268.2	313.9	327.3
82.5°	96.6	163.6	234.7	280.3	293.7
85°	65.7	132.8	203.9	249.5	262.9
87.5°	40.2	107.3	175.7	221.3	234.7
90°	18.1	91.4	169.4	218.0	232.9
92.5°	33.2	86.4	160.1	209.6	222.4
95°	60.1	81.9	155.8	202.6	216.0
97.5°	95.8	123.3	148.4	194.7	208.8
100°	137.5	195.3	141.2	186.0	200.2
102.5°	185.1	232.3	163.5	176.6	191.5
105°	231.8	272.2	263.1	169.3	182.9
107.5°	280.3	315.1	381.2	303.2	218.0
110°	328.6	358.7	420.5	430.9	335.5



TEST NUMBER: P1030705

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.1	400.1	459.2	499.4	510.0
115°	421.5	442.1	497.0	536.7	550.3
117.5°	467.5	483.4	532.7	570.9	582.4
120°	508.5	521.9	568.3	605.2	614.6
122.5°	551.6	559.4	603.9	637.1	647.3
125°	588.8	594.7	636.6	666.2	677.1
127.5°	627.3	632.0	669.2	698.2	706.1
130°	663.0	667.6	697.4	725.8	732.3
132.5°	695.8	701.7	724.1	751.1	758.3
135°	730.7	733.7	751.5	777.8	782.3
137.5°	760.4	764.9	775.8	801.0	806.2
140°	788.6	793.1	799.4	822.5	827.7
142.5°	816.1	819.2	821.5	841.1	845.6
145°	841.3	845.2	846.7	858.9	864.3
147.5°	864.5	868.2	869.7	875.2	876.9
150°	886.8	889.0	890.5	892.0	892.4
152.5°	906.8	907.6	908.3	911.3	907.6
155°	925.4	923.9	924.6	928.3	923.9
157.5°	940.2	940.2	939.5	943.9	938.0
160°	953.6	952.8	952.1	956.5	951.3
162.5°	966.2	963.9	963.2	968.4	963.9
165°	975.8	973.6	972.9	978.8	973.6
167.5°	984.0	981.0	981.0	987.0	981.0
170°	990.7	987.7	987.7	993.6	987.7
172.5°	995.1	991.4	992.1	998.1	991.4
175°	998.8	995.1	995.9	1001.1	995.1
177.5°	1000.3	996.6	997.3	1003.3	995.9
180°	998.8	998.8	998.8	998.8	998.8

(END OF REPORT)