

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030711

Luminaire Tested: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030711
REPORT IS A COMBINATION OF REPORTS P990809 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7169.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030711

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030711

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57		
1	99	95	91	87	92	89	85	82	77	74	72	65	64	62	55	54	53	48		
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40		
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38	34		
4	75	64	56	50	70	60	53	48	53	47	42	45	41	37	38	35	33	29		
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28	25		
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25	22		
7	59	47	39	33	55	44	36	31	38	33	28	33	29	25	29	25	22	20		
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20	18		
9	51	39	31	26	48	36	30	25	32	26	22	28	24	20	24	21	18	16		
10	48	36	28	23	44	34	27	22	30	24	20	26	22	18	23	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16937	16937	16937
5°	16979	16352	16328
10°	16828	15798	15636
15°	16593	15222	14883
20°	16326	14585	14137
25°	15978	13910	13339
30°	15598	13212	12499
35°	15200	12498	11666
40°	14784	11751	10845
45°	14325	11021	9988
50°	13859	10209	9129
55°	13262	9362	8257
60°	12647	8428	7329
65°	12067	7417	6363
70°	11235	6297	5234
75°	10035	4987	4062
80°	8665	3505	2873
85°	6762	1882	1438

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14325 cd/sqm

TEST NUMBER: P1030711

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.1
10°-20°	418.8	5.8
20°-30°	618.6	8.6
30°-40°	722.5	10.1
40°-50°	726.3	10.1
50°-60°	638.0	8.9
60°-70°	475.2	6.6
70°-80°	270.4	3.8
80°-90°	78.9	1.1
90°-100°	35.5	0.5
100°-110°	171.8	2.4
110°-120°	421.0	5.9
120°-130°	534.5	7.5
130°-140°	571.0	8.0
140°-150°	533.9	7.4
150°-160°	430.6	6.0
160°-170°	277.9	3.9
170°-180°	95.8	1.3
0°-30°	1185.8	16.5
0°-40°	1908.2	26.6
0°-60°	3272.5	45.6
0°-90°	4097.0	57.1
90°-120°	628.3	8.8
90°-150°	2267.7	31.6
90°-180°	3072.0	42.9
0°-180°	7169.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1553	1567	1564	149
15°	1499	1494	1476	1487	1479	423
25°	1361	1353	1335	1337	1333	627
35°	1177	1169	1151	1143	1136	736
45°	965	959	942	925	919	745
55°	732	731	713	698	691	656
65°	499	492	479	468	464	493
75°	264	258	254	248	244	282
85°	70	68	68	65	65	75
90°	1	8	18	21	22	7
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1030711

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.5	1573.5	1573.5	1573.5	1573.5
2.5°	1580.2	1574.8	1559.9	1573.5	1572.1
5°	1574.8	1568.0	1553.2	1566.7	1564.0
7.5°	1562.6	1555.9	1541.0	1553.2	1551.8
10°	1546.4	1539.6	1522.0	1534.2	1531.5
12.5°	1524.7	1519.3	1503.1	1511.2	1509.9
15°	1499.0	1493.6	1476.0	1486.9	1478.7
17.5°	1470.6	1463.9	1446.3	1454.4	1451.7
20°	1438.2	1430.0	1412.5	1417.9	1413.8
22.5°	1401.6	1393.5	1375.9	1380.0	1374.6
25°	1361.0	1352.9	1335.3	1336.7	1332.6
27.5°	1319.1	1311.0	1292.0	1293.4	1289.3
30°	1273.1	1266.3	1247.4	1247.4	1237.9
32.5°	1227.1	1217.6	1204.1	1194.6	1190.6
35°	1177.0	1168.9	1151.3	1143.2	1136.5
37.5°	1127.0	1116.2	1098.6	1089.1	1085.0
40°	1074.2	1066.1	1047.2	1036.3	1030.9
42.5°	1021.5	1012.0	993.0	982.2	976.8
45°	964.6	959.2	941.6	925.4	918.6
47.5°	909.2	901.0	884.8	868.6	863.2
50°	852.3	845.6	828.0	813.1	805.0
52.5°	792.8	788.8	769.8	757.6	749.5
55°	731.9	730.6	713.0	698.1	691.3
57.5°	675.1	669.7	656.2	642.6	634.5
60°	612.9	611.5	595.3	583.1	576.3
62.5°	557.4	553.3	537.1	524.9	520.9
65°	499.2	492.5	478.9	468.1	464.1
67.5°	437.0	431.6	420.8	411.3	405.9
70°	381.5	373.4	365.3	355.8	349.1
72.5°	323.3	317.9	308.5	300.3	297.6
75°	263.8	258.4	254.4	247.6	243.5
77.5°	211.1	208.4	202.9	197.5	197.5
80°	159.6	155.6	152.9	151.5	151.5
82.5°	109.6	109.6	109.6	106.9	105.5
85°	70.4	67.6	67.6	64.9	64.9
87.5°	35.2	31.1	29.8	28.4	28.4
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9

TEST NUMBER: P1030711

CATALOG NUMBER: S123DIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)